

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920863

Luminaire Tested: DFN2DIP-TR3F0-080D040US935-FLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P920863  
REPORT IS A COMBINATION OF REPORTS P901815 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-080D040US935-FLLONL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10228.6 lumens  
Efficiency: N/A  
Efficacy: 92.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Direct

Input Watts (W): 110.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P920863  
CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P920863  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	71	71	71	67	67	67	67
1	102	97	93	90	95	92	88	85	81	79	76	72	70	68	63	62	60	56	56	56	56
2	92	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47	47	47	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40	40	40	40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34	34	34	34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	33	30	30	30	30
6	66	53	45	39	62	50	43	37	45	39	34	41	35	32	36	32	29	26	26	26	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23	23	23	23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21	21	21	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19	19	19	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17	17	17	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3340	3340	3340
5°	3343	3290	3313
10°	3314	3243	3266
15°	3264	3187	3194
20°	3196	3110	3120
25°	3129	3019	3035
30°	3045	2933	2927
35°	2965	2833	2813
40°	2867	2732	2705
45°	2769	2630	2594
50°	2662	2523	2465
55°	2550	2399	2347
60°	2423	2253	2211
65°	2285	2101	2051
70°	2108	1915	1878
75°	1864	1692	1715
80°	1569	1408	1409
85°	1109	928	910

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2769 cd/sqm



TEST NUMBER: P920863

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	252.3	2.5
10°-20°	709.8	6.9
20°-30°	1043.1	10.2
30°-40°	1211.4	11.8
40°-50°	1209.9	11.8
50°-60°	1055.0	10.3
60°-70°	779.9	7.6
70°-80°	441.2	4.3
80°-90°	118.5	1.2
90°-100°	38.3	0.4
100°-110°	142.9	1.4
110°-120°	378.9	3.7
120°-130°	628.5	6.1
130°-140°	667.6	6.5
140°-150°	620.4	6.1
150°-160°	498.8	4.9
160°-170°	321.4	3.1
170°-180°	110.6	1.1
0°-30°	2005.1	19.6
0°-40°	3216.5	31.4
0°-60°	5481.5	53.6
0°-90°	6821.1	66.7
90°-120°	560.1	5.5
90°-150°	2476.6	24.2
90°-180°	3407.0	33.3
0°-180°	10228.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2680	2680	2680	2680	2680	
5°	2680	2670	2642	2662	2657	254
15°	2551	2536	2502	2513	2500	719
25°	2309	2289	2245	2250	2245	1063
35°	1992	1966	1925	1910	1897	1244
45°	1621	1603	1564	1536	1526	1251
55°	1227	1211	1180	1150	1137	1097
65°	827	812	786	763	750	818
75°	433	428	415	400	405	462
85°	106	103	101	93	90	118
90°	1	10	17	21	23	9
95°	55	27	33	37	36	65
105°	256	281	51	60	64	273
115°	484	498	519	130	69	476
125°	684	695	711	717	719	610
135°	846	860	867	876	874	654
145°	982	981	995	1001	997	614
155°	1081	1073	1083	1088	1082	498
165°	1139	1134	1136	1142	1136	322
175°	1165	1159	1161	1166	1158	111
180°	1162	1162	1162	1162	1162	



TEST NUMBER: P920863

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2680.1	2680.1	2680.1	2680.1	2680.1
2.5°	2695.7	2682.9	2654.5	2680.1	2675.2
5°	2680.1	2670.0	2641.6	2662.1	2657.2
7.5°	2662.1	2646.8	2618.4	2639.1	2634.0
10°	2634.0	2615.9	2585.0	2605.5	2597.9
12.5°	2595.1	2579.8	2548.9	2561.7	2556.6
15°	2551.4	2536.1	2502.4	2512.8	2500.0
17.5°	2497.2	2481.9	2448.2	2461.2	2448.2
20°	2437.9	2422.6	2386.5	2394.2	2384.0
22.5°	2378.9	2355.6	2321.9	2321.9	2316.8
25°	2309.1	2288.6	2244.9	2249.8	2244.9
27.5°	2231.7	2213.7	2180.3	2172.6	2159.8
30°	2154.6	2133.8	2095.3	2087.7	2077.2
32.5°	2072.1	2056.8	2015.4	1999.8	1989.5
35°	1992.2	1966.5	1925.2	1909.6	1896.8
37.5°	1901.9	1878.7	1837.5	1819.4	1806.5
40°	1809.3	1788.5	1747.2	1724.2	1713.8
42.5°	1719.1	1698.2	1657.2	1631.2	1616.0
45°	1621.2	1603.1	1564.3	1536.1	1525.8
47.5°	1525.8	1507.7	1466.4	1438.0	1422.6
50°	1425.1	1412.3	1376.1	1340.1	1327.2
52.5°	1327.2	1309.1	1275.8	1247.4	1229.3
55°	1226.8	1211.3	1180.4	1149.5	1136.6
57.5°	1126.3	1113.4	1079.8	1048.9	1038.4
60°	1025.6	1015.5	979.4	951.0	943.3
62.5°	927.7	909.7	884.0	858.3	847.9
65°	827.4	811.8	786.1	762.8	750.0
67.5°	724.3	711.2	688.2	670.2	659.8
70°	628.9	618.5	595.3	577.2	567.1
72.5°	531.0	520.6	507.7	489.7	482.1
75°	432.8	427.9	414.8	399.5	404.7
77.5°	345.3	334.9	329.8	322.1	314.4
80°	257.9	255.1	249.9	242.3	237.0
82.5°	175.3	175.3	172.8	162.4	162.4
85°	105.6	103.1	100.7	92.7	90.2
87.5°	46.5	41.3	36.1	28.4	25.7
90°	0.8	10.1	16.8	21.1	22.6
92.5°	21.1	17.7	20.1	21.9	22.6
95°	54.6	26.9	32.7	37.0	36.2
97.5°	98.4	29.4	42.9	45.5	46.2
100°	148.9	33.7	48.0	54.6	56.3
102.5°	204.3	202.8	49.6	58.8	61.4
105°	255.6	280.9	51.3	60.5	63.9
107.5°	315.4	336.4	53.0	62.3	65.6
110°	372.6	390.2	147.2	63.1	66.4



TEST NUMBER: P920863

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	426.5	441.5	427.2	64.7	67.3
115°	483.5	497.8	518.9	129.5	69.1
117.5°	533.2	550.0	564.4	444.0	223.7
120°	588.8	601.3	616.5	626.6	513.1
122.5°	635.8	649.3	666.2	671.1	672.0
125°	683.7	694.7	710.7	716.6	719.1
127.5°	727.5	739.3	751.9	760.3	761.1
130°	768.7	782.2	791.3	800.6	799.9
132.5°	810.7	821.7	830.9	838.5	837.8
135°	846.1	859.6	867.1	875.5	873.9
137.5°	883.0	893.1	901.6	910.0	907.5
140°	919.2	926.0	935.2	942.8	938.6
142.5°	949.6	955.4	966.4	973.0	968.9
145°	981.5	980.7	994.9	1000.8	996.6
147.5°	1009.2	1006.7	1021.0	1025.2	1021.9
150°	1036.1	1030.3	1043.8	1048.8	1044.6
152.5°	1058.9	1052.1	1064.7	1069.8	1063.9
155°	1080.7	1073.2	1083.3	1088.3	1081.6
157.5°	1098.4	1091.7	1099.3	1105.2	1098.4
160°	1113.5	1108.4	1113.5	1118.5	1112.7
162.5°	1127.0	1122.0	1126.2	1132.0	1124.5
165°	1138.8	1133.8	1136.3	1142.1	1136.3
167.5°	1148.1	1142.9	1145.6	1151.4	1143.8
170°	1155.6	1150.6	1152.2	1158.1	1150.6
172.5°	1160.6	1155.6	1157.4	1163.2	1155.6
175°	1164.8	1158.9	1160.6	1166.5	1158.1
177.5°	1166.5	1160.6	1161.5	1167.4	1159.9
180°	1162.3	1162.3	1162.3	1162.3	1162.3



TEST NUMBER: P920863  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D040US935-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.82	13.86	13.62	14.68	15.69	12.39	13.43	13.19	14.25	15.26
	3H	14.49	15.42	15.30	16.25	17.29	14.02	14.95	14.83	15.78	16.82
	4H	15.08	15.95	15.91	16.79	17.84	14.61	15.49	15.44	16.32	17.38
	6H	15.48	16.29	16.32	17.13	18.20	15.01	15.82	15.85	16.66	17.73
	8H	15.58	16.35	16.43	17.22	18.28	15.11	15.89	15.97	16.75	17.82
	12H	15.63	16.37	16.49	17.23	18.32	15.16	15.90	16.02	16.75	17.85
4H	2H	13.30	14.18	14.14	15.02	16.07	12.96	13.84	13.79	14.68	15.73
	3H	15.17	15.90	16.02	16.78	17.84	14.78	15.52	15.63	16.39	17.45
	4H	15.89	16.55	16.74	17.42	18.52	15.49	16.15	16.34	17.02	18.12
	6H	16.40	16.98	17.28	17.87	18.97	16.00	16.58	16.87	17.47	18.57
	8H	16.55	17.09	17.43	17.98	19.09	16.15	16.68	17.02	17.57	18.68
	12H	16.63	17.11	17.53	18.02	19.14	16.21	16.70	17.11	17.61	18.72
8H	4H	16.09	16.63	16.97	17.52	18.63	15.74	16.28	16.61	17.16	18.27
	6H	16.72	17.17	17.63	18.10	19.21	16.36	16.81	17.27	17.74	18.85
	8H	16.94	17.33	17.85	18.26	19.38	16.57	16.97	17.49	17.89	19.02
	12H	17.07	17.42	17.99	18.33	19.51	16.69	17.04	17.61	17.96	19.14
12H	4H	16.09	16.57	16.98	17.48	18.60	15.74	16.22	16.63	17.13	18.25
	6H	16.75	17.15	17.66	18.07	19.20	16.40	16.80	17.32	17.72	18.85
	8H	16.99	17.34	17.91	18.26	19.44	16.64	16.99	17.56	17.91	19.08