

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P909980

Luminaire Tested: DFN2DIP-TR3F0-090D050US840-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P909980
REPORT IS A COMBINATION OF REPORTS P900311 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D050US840-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13466.6 lumens
Efficiency: N/A
Efficacy: 102.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 132
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	111	111	111	111	105	105	105	105	93	93	93		82	82	82		72
1	102	97	93	90	96	92	88	85	81	79	76		72	70	68		63
2	93	85	79	73	87	80	75	70	71	67	63		63	60	57		56
3	84	75	67	61	79	71	64	58	63	58	53		56	52	48		49
4	77	66	58	52	73	63	55	50	56	50	45		50	45	41		44
5	71	59	51	45	67	56	48	43	50	44	39		45	40	36		40
6	66	53	45	39	62	50	43	37	45	39	34		41	35	32		36
7	61	48	40	34	57	46	38	33	41	35	30		37	32	28		33
8	56	44	36	30	53	42	34	29	38	32	27		34	29	25		30
9	53	40	32	27	50	38	31	26	35	29	24		31	26	23		28
10	49	37	29	24	46	35	28	24	32	26	22		29	24	20		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4407	4407	4407
5°	4411	4342	4372
10°	4373	4280	4310
15°	4307	4205	4214
20°	4217	4104	4117
25°	4128	3983	4004
30°	4017	3870	3862
35°	3912	3738	3712
40°	3783	3604	3569
45°	3654	3470	3423
50°	3513	3329	3253
55°	3365	3166	3097
60°	3197	2972	2918
65°	3015	2771	2706
70°	2781	2527	2477
75°	2459	2233	2262
80°	2070	1858	1860
85°	1462	1224	1201

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3654 cd/sqm

TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.9	2.5
10°-20°	936.5	7.0
20°-30°	1376.3	10.2
30°-40°	1598.5	11.9
40°-50°	1596.5	11.9
50°-60°	1392.1	10.3
60°-70°	1029.1	7.6
70°-80°	582.2	4.3
80°-90°	158.2	1.2
90°-100°	98.8	0.7
100°-110°	314.0	2.3
110°-120°	537.3	4.0
120°-130°	706.6	5.2
130°-140°	793.2	5.9
140°-150°	777.8	5.8
150°-160°	652.5	4.8
160°-170°	432.7	3.2
170°-180°	151.2	1.1
0°-30°	2645.7	19.6
0°-40°	4244.2	31.5
0°-60°	7232.9	53.7
0°-90°	9002.5	66.9
90°-120°	950.1	7.1
90°-150°	3227.7	24.0
90°-180°	4464.0	33.1
0°-180°	13466.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3536	3536	3536	3536	3536	
5°	3536	3523	3486	3513	3506	336
15°	3367	3346	3302	3316	3299	948
25°	3047	3020	2962	2969	2962	1402
35°	2629	2595	2540	2520	2503	1642
45°	2139	2115	2064	2027	2013	1651
55°	1619	1598	1558	1517	1500	1447
65°	1092	1071	1037	1007	990	1079
75°	571	565	547	527	534	610
85°	139	136	133	122	119	155
90°	1	17	47	44	46	13
95°	70	84	86	86	84	78
105°	290	294	297	299	299	306
115°	539	547	544	543	539	533
125°	784	796	792	788	787	701
135°	1014	1029	1032	1031	1027	784
145°	1232	1241	1249	1250	1245	769
155°	1408	1412	1416	1423	1419	648
165°	1532	1530	1530	1540	1533	432
175°	1594	1590	1587	1597	1589	151
180°	1597	1597	1597	1597	1597	

TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3536.4	3536.4	3536.4	3536.4	3536.4
2.5°	3557.0	3540.1	3502.6	3536.4	3530.0
5°	3536.4	3523.1	3485.7	3512.7	3506.2
7.5°	3512.7	3492.5	3455.0	3482.4	3475.6
10°	3475.6	3451.7	3410.9	3438.0	3427.9
12.5°	3424.3	3404.1	3363.4	3380.2	3373.5
15°	3366.6	3346.4	3302.0	3315.7	3298.7
17.5°	3295.1	3274.9	3230.6	3247.5	3230.6
20°	3216.8	3196.6	3149.0	3159.1	3145.7
22.5°	3138.9	3108.3	3063.8	3063.8	3057.0
25°	3046.9	3019.8	2962.1	2968.6	2962.1
27.5°	2944.8	2920.9	2877.0	2866.9	2849.9
30°	2843.1	2815.6	2764.7	2754.6	2741.0
32.5°	2734.1	2713.9	2659.4	2638.9	2625.1
35°	2628.8	2594.8	2540.3	2519.8	2502.9
37.5°	2509.7	2479.0	2424.5	2400.8	2383.8
40°	2387.3	2360.0	2305.4	2275.1	2261.5
42.5°	2268.3	2240.9	2186.8	2152.5	2132.3
45°	2139.1	2115.4	2064.1	2026.9	2013.3
47.5°	2013.3	1989.4	1934.9	1897.4	1877.2
50°	1880.5	1863.5	1815.8	1768.3	1751.3
52.5°	1751.3	1727.5	1683.4	1646.0	1622.1
55°	1618.9	1598.3	1557.5	1516.8	1499.9
57.5°	1486.1	1469.2	1424.8	1384.0	1370.3
60°	1353.3	1340.0	1292.3	1254.9	1244.8
62.5°	1224.2	1200.3	1166.4	1132.6	1118.8
65°	1091.8	1071.2	1037.2	1006.6	989.7
67.5°	955.7	938.5	908.1	884.3	870.6
70°	829.8	816.1	785.5	761.6	748.3
72.5°	700.6	686.9	669.9	646.2	636.1
75°	571.2	564.6	547.3	527.1	534.0
77.5°	455.7	442.0	435.2	425.1	415.0
80°	340.2	336.6	329.7	319.6	312.9
82.5°	231.3	231.3	228.0	214.3	214.3
85°	139.3	136.0	132.8	122.3	119.1
87.5°	61.3	54.4	47.7	37.6	33.9
90°	1.4	17.4	47.2	44.3	45.7
92.5°	29.9	40.4	41.9	43.3	43.3
95°	70.3	83.8	86.1	86.1	83.8
97.5°	116.9	129.5	134.8	134.8	134.8
100°	170.9	182.0	185.8	185.8	184.4
102.5°	227.7	235.9	241.2	242.7	241.2
105°	289.8	293.7	296.6	298.9	298.9
107.5°	351.4	357.2	357.2	358.2	351.4
110°	411.1	418.9	418.9	418.9	415.0



TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	475.6	483.8	482.4	478.6	475.6
115°	539.2	546.9	544.5	543.1	539.2
117.5°	602.3	612.9	606.1	602.3	598.4
120°	665.8	676.4	665.8	665.8	661.5
122.5°	723.6	737.1	730.3	726.5	723.6
125°	784.3	796.3	792.4	788.1	786.7
127.5°	843.4	858.4	853.1	847.3	843.4
130°	898.9	916.2	913.7	910.9	905.5
132.5°	961.0	974.4	975.4	968.7	964.8
135°	1014.4	1029.3	1032.2	1030.8	1026.9
137.5°	1074.1	1086.1	1088.5	1087.5	1081.8
140°	1126.5	1138.6	1145.3	1145.3	1140.0
142.5°	1180.4	1192.6	1196.4	1197.8	1192.6
145°	1231.5	1241.1	1248.8	1250.3	1245.0
147.5°	1277.3	1289.3	1295.1	1297.5	1292.1
150°	1324.4	1332.6	1337.9	1342.2	1337.9
152.5°	1366.3	1374.5	1381.2	1386.5	1381.2
155°	1408.2	1412.0	1416.3	1423.1	1418.8
157.5°	1444.3	1447.1	1449.6	1459.3	1452.5
160°	1476.5	1479.5	1480.9	1489.0	1483.3
162.5°	1506.4	1506.4	1507.8	1517.0	1510.3
165°	1532.0	1530.5	1530.5	1540.1	1533.4
167.5°	1555.0	1550.6	1550.6	1560.3	1553.6
170°	1572.4	1568.5	1567.1	1576.7	1568.5
172.5°	1584.4	1580.5	1579.1	1588.7	1580.5
175°	1594.1	1590.1	1587.3	1596.9	1588.7
177.5°	1599.3	1595.5	1592.6	1600.7	1592.6
180°	1596.9	1596.9	1596.9	1596.9	1596.9

TEST NUMBER: P909980

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US840-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.80	14.83	14.60	15.66	16.66	13.37	14.41	14.17	15.23	16.23
	3H	15.46	16.39	16.27	17.22	18.26	14.99	15.92	15.80	16.75	17.79
	4H	16.05	16.93	16.88	17.77	18.82	15.58	16.46	16.41	17.30	18.35
	6H	16.45	17.26	17.29	18.11	19.17	15.98	16.79	16.82	17.64	18.70
	8H	16.56	17.33	17.41	18.20	19.26	16.09	16.86	16.94	17.73	18.79
	12H	16.61	17.35	17.46	18.20	19.29	16.14	16.87	16.99	17.73	18.82
4H	2H	14.28	15.16	15.11	15.99	17.04	13.93	14.81	14.77	15.65	16.70
	3H	16.15	16.88	16.99	17.75	18.82	15.76	16.49	16.60	17.36	18.43
	4H	16.86	17.53	17.72	18.40	19.49	16.46	17.13	17.32	18.00	19.09
	6H	17.38	17.96	18.25	18.85	19.94	16.97	17.55	17.85	18.45	19.54
	8H	17.53	18.07	18.40	18.96	20.06	17.12	17.66	18.00	18.55	19.66
	12H	17.60	18.09	18.50	19.00	20.11	17.19	17.68	18.08	18.58	19.70
8H	4H	17.07	17.61	17.94	18.50	19.60	16.71	17.25	17.59	18.14	19.25
	6H	17.70	18.14	18.60	19.07	20.18	17.34	17.79	18.24	18.71	19.82
	8H	17.91	18.31	18.83	19.23	20.36	17.55	17.95	18.46	18.87	19.99
	12H	18.05	18.40	18.96	19.31	20.49	17.67	18.02	18.58	18.93	20.11
12H	4H	17.06	17.55	17.96	18.46	19.57	16.71	17.20	17.61	18.11	19.22
	6H	17.73	18.12	18.64	19.05	20.17	17.38	17.78	18.29	18.70	19.82
	8H	17.97	18.32	18.89	19.23	20.41	17.62	17.97	18.53	18.88	20.06

END OF REPORT