

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912568

Luminaire Tested: DFN2DIP-TR3F0-030D090US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912568
REPORT IS A COMBINATION OF REPORTS P900355 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D090US850-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 12126.9 lumens
Efficiency: N/A
Efficacy: 127.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 94.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1613	1613	1613
5°	1615	1589	1600
10°	1601	1567	1578
15°	1576	1539	1543
20°	1544	1502	1507
25°	1511	1458	1466
30°	1471	1417	1414
35°	1432	1368	1359
40°	1385	1319	1307
45°	1338	1270	1253
50°	1286	1219	1191
55°	1232	1159	1134
60°	1170	1088	1068
65°	1104	1015	991
70°	1018	925	907
75°	900	818	828
80°	757	680	681
85°	535	448	440

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 3081 cd/sqm

TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	121.8	1.0
10°-20°	342.8	2.8
20°-30°	503.8	4.2
30°-40°	585.2	4.8
40°-50°	584.4	4.8
50°-60°	509.6	4.2
60°-70°	376.7	3.1
70°-80°	213.1	1.8
80°-90°	65.2	0.5
90°-100°	195.3	1.6
100°-110°	620.6	5.1
110°-120°	1062.1	8.8
120°-130°	1396.8	11.5
130°-140°	1567.9	12.9
140°-150°	1537.5	12.7
150°-160°	1289.7	10.6
160°-170°	855.3	7.1
170°-180°	299.0	2.5
0°-30°	968.5	8.0
0°-40°	1553.6	12.8
0°-60°	2647.7	21.8
0°-90°	3302.7	27.2
90°-120°	1878.1	15.5
90°-150°	6380.2	52.6
90°-180°	8824.0	72.8
0°-180°	12126.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1294	1294	1294	1294	1294	
5°	1294	1290	1276	1286	1283	123
15°	1232	1225	1209	1214	1208	347
25°	1115	1106	1084	1087	1084	513
35°	962	950	930	922	916	601
45°	783	774	756	742	737	604
55°	593	585	570	555	549	530
65°	400	392	380	368	362	395
75°	209	207	200	193	196	223
85°	51	50	49	45	44	57
90°	3	34	93	88	90	12
95°	139	166	170	170	166	155
105°	573	580	586	591	591	605
115°	1066	1081	1076	1074	1066	1054
125°	1550	1574	1566	1558	1555	1385
135°	2005	2035	2040	2038	2030	1550
145°	2434	2453	2468	2471	2461	1521
155°	2784	2791	2800	2813	2805	1281
165°	3028	3025	3025	3044	3031	854
175°	3151	3143	3138	3157	3140	299
180°	3157	3157	3157	3157	3157	

TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1294.5	1294.5	1294.5	1294.5	1294.5
2.5°	1302.1	1295.9	1282.1	1294.5	1292.2
5°	1294.5	1289.7	1275.9	1285.9	1283.4
7.5°	1285.9	1278.5	1264.7	1274.8	1272.2
10°	1272.2	1263.5	1248.6	1258.5	1254.8
12.5°	1253.5	1246.1	1231.2	1237.3	1234.9
15°	1232.3	1225.0	1208.7	1213.7	1207.5
17.5°	1206.1	1198.8	1182.5	1188.7	1182.5
20°	1177.5	1170.1	1152.7	1156.4	1151.5
22.5°	1149.0	1137.8	1121.5	1121.5	1119.0
25°	1115.3	1105.5	1084.3	1086.7	1084.3
27.5°	1077.9	1069.2	1053.1	1049.4	1043.2
30°	1040.7	1030.7	1012.1	1008.3	1003.3
32.5°	1000.9	993.4	973.5	965.9	960.9
35°	962.3	949.9	929.9	922.4	916.1
37.5°	918.7	907.5	887.5	878.8	872.6
40°	873.9	863.9	843.9	832.9	827.9
42.5°	830.3	820.3	800.5	787.9	780.5
45°	783.1	774.3	755.6	741.9	736.9
47.5°	736.9	728.3	708.3	694.6	687.1
50°	688.4	682.1	664.7	647.3	641.1
52.5°	641.1	632.4	616.3	602.5	593.8
55°	592.6	585.1	570.1	555.3	549.1
57.5°	544.0	537.8	521.6	506.6	501.6
60°	495.4	490.5	473.1	459.3	455.7
62.5°	448.1	439.4	427.0	414.5	409.6
65°	399.7	392.1	379.7	368.5	362.3
67.5°	349.9	343.6	332.4	323.7	318.7
70°	303.8	298.8	287.6	278.8	273.9
72.5°	256.5	251.4	245.2	236.5	232.9
75°	209.0	206.7	200.4	193.0	195.5
77.5°	166.8	161.8	159.3	155.6	151.9
80°	124.5	123.2	120.7	117.0	114.6
82.5°	84.6	84.6	83.5	78.4	78.4
85°	51.0	49.8	48.6	44.8	43.6
87.5°	22.4	20.0	17.4	13.8	12.4
90°	2.9	34.3	93.3	87.5	90.4
92.5°	59.0	80.0	82.8	85.6	85.6
95°	139.0	165.6	170.3	170.3	165.6
97.5°	231.2	256.0	266.5	266.5	266.5
100°	337.8	359.8	367.3	367.3	364.5
102.5°	450.1	466.3	476.8	479.6	476.8
105°	572.9	580.5	586.2	591.0	591.0
107.5°	694.7	706.1	706.1	708.0	694.7
110°	812.7	828.0	828.0	828.0	820.3

TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	940.2	956.4	953.5	946.0	940.2
115°	1065.9	1081.1	1076.3	1073.5	1065.9
117.5°	1190.5	1211.5	1198.2	1190.5	1182.9
120°	1316.2	1337.0	1316.2	1316.2	1307.5
122.5°	1430.3	1457.0	1443.7	1436.0	1430.3
125°	1550.3	1574.0	1566.5	1557.8	1555.0
127.5°	1667.3	1696.8	1686.3	1674.9	1667.3
130°	1776.7	1811.0	1806.2	1800.5	1790.0
132.5°	1899.5	1926.1	1928.0	1914.7	1907.1
135°	2005.1	2034.6	2040.3	2037.5	2029.9
137.5°	2123.1	2146.9	2151.7	2149.8	2138.4
140°	2226.9	2250.6	2263.9	2263.9	2253.5
142.5°	2333.4	2357.2	2364.8	2367.7	2357.2
145°	2434.4	2453.3	2468.5	2471.4	2461.0
147.5°	2524.7	2548.5	2559.9	2564.7	2554.2
150°	2618.0	2634.2	2644.6	2653.2	2644.6
152.5°	2700.7	2716.9	2730.2	2740.8	2730.2
155°	2783.6	2791.1	2799.8	2813.1	2804.6
157.5°	2854.9	2860.7	2865.4	2884.4	2871.1
160°	2918.7	2924.4	2927.3	2943.4	2932.0
162.5°	2977.7	2977.7	2980.5	2998.6	2985.3
165°	3028.1	3025.2	3025.2	3044.3	3031.0
167.5°	3073.8	3065.3	3065.3	3084.2	3070.9
170°	3108.1	3100.4	3097.7	3116.6	3100.4
172.5°	3131.8	3124.3	3121.4	3140.5	3124.3
175°	3150.9	3143.2	3137.6	3156.7	3140.5
177.5°	3161.3	3153.8	3148.0	3164.2	3148.0
180°	3156.7	3156.7	3156.7	3156.7	3156.7

TEST NUMBER: P912568

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US850-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.27	6.96	7.40	8.08	9.64	5.84	6.53	6.97	7.65	9.22
	3H	7.91	8.53	9.05	9.66	11.24	7.44	8.06	8.58	9.19	10.77
	4H	8.48	9.07	9.63	10.20	11.78	8.01	8.60	9.16	9.73	11.31
	6H	8.87	9.40	10.02	10.54	12.13	8.40	8.94	9.55	10.07	11.66
	8H	8.96	9.47	10.12	10.62	12.21	8.49	9.01	9.65	10.15	11.74
	12H	9.00	9.49	10.16	10.63	12.24	8.53	9.01	9.69	10.16	11.77
4H	2H	6.71	7.29	7.86	8.42	10.01	6.36	6.95	7.52	8.08	9.67
	3H	8.55	9.04	9.71	10.19	11.79	8.16	8.65	9.32	9.80	11.40
	4H	9.25	9.70	10.41	10.84	12.46	8.85	9.30	10.01	10.44	12.06
	6H	9.74	10.13	10.91	11.30	12.90	9.34	9.72	10.51	10.89	12.50
	8H	9.88	10.24	11.05	11.40	13.03	9.48	9.84	10.65	11.00	12.62
	12H	9.94	10.27	11.13	11.44	13.07	9.53	9.86	10.71	11.03	12.65
8H	4H	9.43	9.78	10.59	10.94	12.57	9.07	9.43	10.24	10.59	12.21
	6H	10.04	10.33	11.23	11.54	13.16	9.68	9.98	10.87	11.18	12.80
	8H	10.25	10.51	11.44	11.69	13.33	9.89	10.15	11.08	11.33	12.96
	12H	10.37	10.59	11.56	11.77	13.44	9.99	10.22	11.19	11.39	13.07
12H	4H	9.40	9.73	10.59	10.90	12.53	9.05	9.38	10.24	10.55	12.18
	6H	10.06	10.32	11.26	11.50	13.14	9.72	9.98	10.91	11.16	12.80
	8H	10.29	10.52	11.49	11.70	13.37	9.94	10.17	11.14	11.34	13.01

END OF REPORT