

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923485

Luminaire Tested: DFN2DIP-TR3F0-040D030US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923485
REPORT IS A COMBINATION OF REPORTS P901794 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D030US940-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5680.2 lumens
Efficiency: N/A
Efficacy: 98.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	83	78	73	84	78	73	68	67	63	60	57	54	52	47	45	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	42	40	38
4	76	66	58	52	70	61	55	49	53	48	44	45	42	38	38	35	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	28	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	26	29	26	23
8	56	44	36	31	52	41	34	29	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	26	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1839	1806	1818
10°	1820	1769	1758
15°	1794	1709	1665
20°	1759	1627	1552
25°	1724	1535	1443
30°	1678	1442	1305
35°	1632	1341	1183
40°	1586	1237	1044
45°	1531	1121	919
50°	1475	1005	796
55°	1417	881	678
60°	1349	752	557
65°	1271	620	500
70°	1176	498	450
75°	1057	435	407
80°	884	360	349
85°	602	233	255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1531 cd/sqm

TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	2.4
10°-20°	379.3	6.7
20°-30°	532.5	9.4
30°-40°	580.5	10.2
40°-50°	533.5	9.4
50°-60°	419.0	7.4
60°-70°	272.7	4.8
70°-80°	140.4	2.5
80°-90°	37.4	0.7
90°-100°	29.8	0.5
100°-110°	111.0	2.0
110°-120°	294.3	5.2
120°-130°	488.2	8.6
130°-140°	518.5	9.1
140°-150°	481.9	8.5
150°-160°	387.5	6.8
160°-170°	249.7	4.4
170°-180°	85.9	1.5
0°-30°	1049.9	18.5
0°-40°	1630.4	28.7
0°-60°	2582.9	45.5
0°-90°	3033.4	53.4
90°-120°	435.1	7.7
90°-150°	1923.7	33.9
90°-180°	2647.0	46.6
0°-180°	5680.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	8	13	16	18	5
95°	42	21	25	29	28	50
105°	199	218	40	47	50	212
115°	376	387	403	101	54	370
125°	531	540	552	557	559	474
135°	657	668	674	680	679	508
145°	762	762	773	777	774	477
155°	840	834	841	845	840	387
165°	884	881	883	887	883	250
175°	905	900	902	906	900	86
180°	903	903	903	903	903	

TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	0.6	7.8	13.0	16.4	17.6
92.5°	16.4	13.7	15.7	17.0	17.6
95°	42.4	20.9	25.4	28.8	28.1
97.5°	76.4	22.9	33.3	35.3	35.9
100°	115.7	26.1	37.3	42.4	43.8
102.5°	158.7	157.5	38.5	45.7	47.7
105°	198.6	218.2	39.9	47.0	49.7
107.5°	245.0	261.3	41.2	48.3	51.0
110°	289.4	303.1	114.3	49.0	51.6

TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	331.3	343.0	331.9	50.3	52.3
115°	375.6	386.7	403.1	100.6	53.6
117.5°	414.2	427.2	438.4	344.9	173.8
120°	457.3	467.1	478.8	486.7	398.5
122.5°	493.8	504.4	517.5	521.3	522.0
125°	531.1	539.6	552.1	556.6	558.6
127.5°	565.1	574.2	584.1	590.6	591.2
130°	597.1	607.6	614.7	621.9	621.3
132.5°	629.7	638.3	645.4	651.3	650.7
135°	657.2	667.7	673.5	680.1	678.8
137.5°	685.9	693.8	700.3	706.9	704.9
140°	714.0	719.3	726.4	732.3	729.1
142.5°	737.6	742.2	750.6	755.8	752.6
145°	762.4	761.7	772.8	777.4	774.1
147.5°	783.9	781.9	793.1	796.3	793.7
150°	804.9	800.3	810.7	814.6	811.4
152.5°	822.4	817.3	827.1	831.0	826.4
155°	839.5	833.7	841.4	845.3	840.2
157.5°	853.2	848.0	853.9	858.4	853.2
160°	865.0	861.0	865.0	868.9	864.2
162.5°	875.4	871.5	874.8	879.3	873.4
165°	884.5	880.7	882.6	887.2	882.6
167.5°	891.7	887.8	889.7	894.4	888.5
170°	897.6	893.7	895.0	899.6	893.7
172.5°	901.5	897.6	898.9	903.5	897.6
175°	904.7	900.2	901.5	906.1	899.6
177.5°	906.1	901.5	902.2	906.8	900.9
180°	902.9	902.9	902.9	902.9	902.9

TEST NUMBER: P923485

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.52	10.38	10.46	11.33	12.55	5.50	6.36	6.43	7.30	8.53
	3H	11.19	11.96	12.14	12.92	14.16	6.68	7.45	7.63	8.41	9.65
	4H	11.79	12.52	12.76	13.48	14.74	7.13	7.86	8.09	8.82	10.07
	6H	12.21	12.88	13.18	13.84	15.11	7.45	8.12	8.42	9.08	10.35
	8H	12.33	12.97	13.31	13.95	15.22	7.54	8.17	8.52	9.15	10.42
	12H	12.39	13.00	13.37	13.97	15.26	7.58	8.18	8.56	9.16	10.45
4H	2H	9.54	10.27	10.51	11.23	12.48	6.09	6.82	7.06	7.78	9.03
	3H	11.36	11.97	12.34	12.96	14.23	7.44	8.04	8.41	9.03	10.30
	4H	12.05	12.60	13.03	13.58	14.88	7.98	8.53	8.97	9.52	10.81
	6H	12.56	13.03	13.55	14.04	15.33	8.40	8.87	9.39	9.88	11.17
	8H	12.73	13.17	13.72	14.17	15.48	8.52	8.96	9.52	9.97	11.27
	12H	12.82	13.22	13.83	14.23	15.55	8.59	8.98	9.60	10.00	11.31
8H	4H	12.02	12.46	13.01	13.46	14.77	8.26	8.70	9.26	9.70	11.01
	6H	12.57	12.94	13.60	13.98	15.29	8.77	9.13	9.79	10.18	11.48
	8H	12.78	13.11	13.81	14.14	15.46	8.96	9.28	9.99	10.31	11.63
	12H	12.92	13.20	13.95	14.22	15.59	9.07	9.35	10.10	10.38	11.75
12H	4H	11.97	12.37	12.99	13.38	14.70	8.26	8.66	9.28	9.68	10.99
	6H	12.55	12.87	13.58	13.90	15.22	8.82	9.14	9.85	10.17	11.49
	8H	12.76	13.05	13.80	14.07	15.44	9.02	9.31	10.06	10.33	11.70

END OF REPORT