

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923501

Luminaire Tested: DFN2DIP-TR3F0-040D070US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923501
REPORT IS A COMBINATION OF REPORTS P901850 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D070US940-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 9211.4 lumens
Efficiency: N/A
Efficacy: 104.4 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 88.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	74	74	74	56	56	56	40	40	40
1	94	90	87	83	85	81	78	76	65	63	61	50	49	48	36	35	35
2	86	79	73	68	77	72	67	62	57	54	51	44	42	40	32	31	30
3	79	70	63	57	71	63	57	53	51	47	43	39	37	34	29	27	26
4	72	62	54	49	65	56	50	45	45	41	37	35	32	30	26	24	22
5	66	55	47	42	59	50	43	38	41	36	32	32	28	26	24	21	20
6	61	49	42	36	55	45	38	33	37	32	28	29	25	23	21	19	17
7	56	45	37	32	51	41	34	29	33	28	25	26	23	20	20	17	16
8	52	41	33	28	47	37	31	26	30	25	22	24	21	18	18	16	14
9	49	37	30	25	44	34	27	23	28	23	20	22	19	16	17	14	13
10	45	34	27	22	41	31	25	21	26	21	18	20	17	15	16	13	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1839	1806	1818
10°	1820	1769	1758
15°	1794	1709	1665
20°	1759	1627	1552
25°	1724	1535	1443
30°	1678	1442	1305
35°	1632	1341	1183
40°	1586	1237	1044
45°	1531	1121	919
50°	1475	1005	796
55°	1417	881	678
60°	1349	752	557
65°	1271	620	500
70°	1176	498	450
75°	1057	435	407
80°	884	360	349
85°	602	233	255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1531 cd/sqm

TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	1.5
10°-20°	379.3	4.1
20°-30°	532.5	5.8
30°-40°	580.5	6.3
40°-50°	533.5	5.8
50°-60°	419.0	4.5
60°-70°	272.7	3.0
70°-80°	140.4	1.5
80°-90°	39.5	0.4
90°-100°	69.5	0.8
100°-110°	259.0	2.8
110°-120°	686.8	7.5
120°-130°	1139.1	12.4
130°-140°	1209.9	13.1
140°-150°	1124.5	12.2
150°-160°	904.1	9.8
160°-170°	582.6	6.3
170°-180°	200.5	2.2
0°-30°	1049.9	11.4
0°-40°	1630.4	17.7
0°-60°	2582.9	28.0
0°-90°	3035.5	33.0
90°-120°	1015.2	11.0
90°-150°	4488.7	48.7
90°-180°	6176.0	67.0
0°-180°	9211.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	18	30	38	41	9
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	

TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4

TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6



TEST NUMBER: P923501

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.37	8.08	8.46	9.16	10.66	3.34	4.05	4.44	5.14	6.64
	3H	9.03	9.66	10.13	10.76	12.27	4.52	5.15	5.62	6.25	7.76
	4H	9.62	10.22	10.74	11.32	12.84	4.96	5.56	6.07	6.66	8.18
	6H	10.03	10.58	11.15	11.68	13.22	5.27	5.82	6.39	6.92	8.45
	8H	10.15	10.67	11.28	11.79	13.32	5.35	5.88	6.48	7.00	8.52
	12H	10.20	10.70	11.33	11.81	13.36	5.39	5.89	6.52	7.00	8.55
4H	2H	7.37	7.97	8.49	9.07	10.59	3.92	4.52	5.04	5.62	7.14
	3H	9.18	9.68	10.30	10.80	12.33	5.25	5.75	6.38	6.88	8.41
	4H	9.86	10.31	10.99	11.43	12.98	5.79	6.25	6.92	7.36	8.92
	6H	10.36	10.75	11.49	11.89	13.43	6.20	6.59	7.33	7.73	9.27
	8H	10.52	10.89	11.66	12.02	13.58	6.32	6.69	7.46	7.82	9.38
	12H	10.61	10.94	11.76	12.08	13.65	6.37	6.71	7.53	7.85	9.41
8H	4H	9.81	10.18	10.95	11.31	12.87	6.05	6.42	7.19	7.55	9.11
	6H	10.36	10.67	11.52	11.84	13.40	6.56	6.86	7.72	8.04	9.59
	8H	10.57	10.84	11.74	11.99	13.57	6.75	7.01	7.91	8.16	9.74
	12H	10.70	10.93	11.87	12.08	13.69	6.86	7.09	8.02	8.24	9.85
12H	4H	9.76	10.09	10.91	11.23	12.80	6.05	6.38	7.21	7.53	9.09
	6H	10.34	10.60	11.50	11.76	13.33	6.61	6.87	7.77	8.02	9.60
	8H	10.55	10.78	11.71	11.93	13.54	6.81	7.04	7.97	8.19	9.80

END OF REPORT