

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912632

Luminaire Tested: DFN2DIP-TR3F0-060D050US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912632
REPORT IS A COMBINATION OF REPORTS P900306 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-060D050US850-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10563.3 lumens
Efficiency: N/A
Efficacy: 111.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 94.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912632
CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P912632

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	54	54	54	54
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51	46	46	46	46
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44	39	39	39	39
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38	34	34	34	34
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33	30	30	30	30
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29	26	26	26	26
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26	23	23	23	23
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23	21	21	21	21
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21	19	19	19	19
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19	17	17	17	17
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18	16	16	16	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3427	3427	3427
5°	3431	3370	3392
10°	3395	3301	3279
15°	3346	3189	3106
20°	3282	3036	2895
25°	3217	2865	2692
30°	3130	2689	2434
35°	3045	2502	2207
40°	2958	2307	1948
45°	2857	2092	1714
50°	2752	1875	1484
55°	2643	1644	1264
60°	2517	1402	1038
65°	2371	1157	932
70°	2194	928	840
75°	1972	812	760
80°	1650	672	651
85°	1122	435	476

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2857 cd/sqm



TEST NUMBER: P912632

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	257.7	2.4
10°-20°	707.6	6.7
20°-30°	993.4	9.4
30°-40°	1082.8	10.3
40°-50°	995.2	9.4
50°-60°	781.6	7.4
60°-70°	508.8	4.8
70°-80°	261.9	2.5
80°-90°	71.8	0.7
90°-100°	108.5	1.0
100°-110°	344.8	3.3
110°-120°	590.1	5.6
120°-130°	776.0	7.3
130°-140°	871.0	8.2
140°-150°	854.2	8.1
150°-160°	716.5	6.8
160°-170°	475.2	4.5
170°-180°	166.1	1.6
0°-30°	1958.7	18.5
0°-40°	3041.5	28.8
0°-60°	4818.4	45.6
0°-90°	5660.9	53.6
90°-120°	1043.4	9.9
90°-150°	3544.6	33.6
90°-180°	4902.0	46.4
0°-180°	10563.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2750	2750	2750	2750	2750	
5°	2750	2738	2705	2728	2720	261
15°	2616	2588	2504	2456	2432	737
25°	2374	2295	2130	2028	1991	1092
35°	2046	1919	1700	1543	1488	1281
45°	1672	1506	1244	1068	1008	1292
55°	1272	1078	809	660	612	1136
65°	859	657	433	349	341	851
75°	458	284	199	182	179	484
85°	107	55	47	47	47	123
90°	2	19	52	49	50	10
95°	77	92	95	95	92	86
105°	318	322	326	328	328	336
115°	592	601	598	596	592	586
125°	861	874	870	866	864	770
135°	1114	1130	1134	1132	1128	861
145°	1352	1363	1371	1373	1367	845
155°	1546	1551	1555	1563	1558	712
165°	1682	1681	1681	1691	1684	475
175°	1751	1746	1743	1754	1745	166
180°	1754	1754	1754	1754	1754	



TEST NUMBER: P912632

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2750.1	2750.1	2750.1	2750.1	2750.1
2.5°	2762.5	2750.1	2722.6	2747.7	2742.7
5°	2750.1	2737.7	2705.2	2727.7	2720.3
7.5°	2727.7	2712.8	2678.0	2687.8	2675.4
10°	2697.8	2680.3	2630.8	2623.1	2608.3
12.5°	2660.6	2638.1	2570.8	2556.0	2528.5
15°	2615.7	2588.2	2503.7	2456.4	2431.6
17.5°	2563.5	2523.5	2419.0	2364.3	2324.5
20°	2503.7	2453.8	2329.5	2267.4	2212.5
22.5°	2439.0	2381.7	2237.3	2152.8	2115.5
25°	2374.4	2294.6	2130.4	2028.5	1991.0
27.5°	2297.3	2212.5	2030.8	1913.8	1856.6
30°	2215.1	2120.3	1921.2	1794.5	1727.2
32.5°	2135.4	2020.8	1817.0	1667.5	1605.2
35°	2045.9	1918.9	1700.0	1543.1	1488.2
37.5°	1958.7	1821.6	1590.4	1418.5	1356.4
40°	1866.6	1717.4	1475.7	1299.1	1234.4
42.5°	1772.1	1612.8	1361.4	1177.1	1115.1
45°	1672.5	1505.6	1244.5	1067.5	1007.9
47.5°	1578.0	1401.3	1132.5	955.6	901.0
50°	1473.4	1296.8	1022.9	851.0	799.0
52.5°	1371.2	1184.5	918.4	754.1	706.9
55°	1271.7	1077.6	808.8	659.6	612.3
57.5°	1169.8	970.6	711.9	572.5	532.5
60°	1065.2	866.1	609.7	483.0	443.0
62.5°	963.3	764.2	522.6	403.2	383.4
65°	858.7	657.0	433.1	348.6	340.9
67.5°	759.1	557.4	348.6	306.1	298.7
70°	654.5	460.5	288.6	263.8	253.7
72.5°	555.1	370.7	241.3	221.6	216.5
75°	457.9	283.6	199.1	181.7	179.3
77.5°	361.0	201.5	156.8	146.8	141.8
80°	271.2	144.4	119.3	109.6	109.6
82.5°	189.1	97.1	82.1	77.1	77.1
85°	106.9	54.7	47.2	47.2	47.2
87.5°	39.9	19.9	19.9	17.4	17.4
90°	1.6	19.1	51.8	48.7	50.2
92.5°	32.8	44.4	46.0	47.6	47.6
95°	77.2	92.0	94.6	94.6	92.0
97.5°	128.4	142.2	148.1	148.1	148.1
100°	187.6	199.8	204.1	204.1	202.5
102.5°	250.1	259.1	264.8	266.5	264.8
105°	318.3	322.5	325.7	328.3	328.3
107.5°	385.9	392.3	392.3	393.4	385.9
110°	451.5	460.0	460.0	460.0	455.7



TEST NUMBER: P912632

CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	522.3	531.3	529.8	525.6	522.3
115°	592.1	600.6	598.0	596.4	592.1
117.5°	661.4	673.1	665.6	661.4	657.2
120°	731.2	742.8	731.2	731.2	726.4
122.5°	794.6	809.5	802.0	797.8	794.6
125°	861.2	874.4	870.2	865.5	863.9
127.5°	926.2	942.6	936.9	930.5	926.2
130°	987.1	1006.1	1003.4	1000.3	994.4
132.5°	1055.3	1070.1	1071.2	1063.8	1059.5
135°	1114.0	1130.3	1133.5	1132.0	1127.7
137.5°	1179.5	1192.7	1195.4	1194.3	1188.0
140°	1237.1	1250.4	1257.7	1257.7	1252.0
142.5°	1296.3	1309.6	1313.8	1315.4	1309.6
145°	1352.4	1363.0	1371.4	1373.1	1367.2
147.5°	1402.7	1415.9	1422.2	1424.8	1419.0
150°	1454.5	1463.4	1469.2	1474.0	1469.2
152.5°	1500.5	1509.5	1516.8	1522.7	1516.8
155°	1546.4	1550.6	1555.4	1562.8	1558.0
157.5°	1586.1	1589.2	1591.9	1602.5	1595.1
160°	1621.5	1624.7	1626.2	1635.2	1628.9
162.5°	1654.3	1654.3	1655.8	1665.9	1658.5
165°	1682.4	1680.7	1680.7	1691.3	1683.9
167.5°	1707.6	1702.9	1702.9	1713.5	1706.1
170°	1726.7	1722.5	1720.9	1731.5	1722.5
172.5°	1739.9	1735.7	1734.1	1744.7	1735.7
175°	1750.6	1746.2	1743.1	1753.7	1744.7
177.5°	1756.3	1752.1	1748.9	1757.9	1748.9
180°	1753.7	1753.7	1753.7	1753.7	1753.7



TEST NUMBER: P912632
 CATALOG NUMBER: DFN2DIP-TR3F0-060D050US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.70	12.56	12.64	13.51	14.73	7.68	8.54	8.61	9.49	10.71
	3H	13.37	14.14	14.32	15.10	16.34	8.87	9.63	9.81	10.59	11.83
	4H	13.98	14.70	14.94	15.66	16.92	9.31	10.04	10.27	11.00	12.25
	6H	14.39	15.06	15.36	16.03	17.29	9.63	10.30	10.60	11.26	12.53
	8H	14.52	15.15	15.49	16.13	17.40	9.72	10.36	10.70	11.34	12.60
	12H	14.57	15.18	15.56	16.15	17.44	9.76	10.37	10.74	11.34	12.63
4H	2H	11.72	12.45	12.69	13.41	14.66	8.27	9.00	9.24	9.96	11.21
	3H	13.54	14.15	14.52	15.14	16.41	9.62	10.22	10.59	11.21	12.48
	4H	14.23	14.78	15.21	15.76	17.06	10.16	10.72	11.15	11.70	12.99
	6H	14.74	15.21	15.73	16.22	17.51	10.58	11.05	11.57	12.06	13.35
	8H	14.91	15.35	15.91	16.35	17.66	10.71	11.15	11.70	12.15	13.45
	12H	15.00	15.40	16.01	16.41	17.72	10.77	11.17	11.78	12.18	13.49
8H	4H	14.20	14.64	15.20	15.64	16.95	10.44	10.88	11.44	11.88	13.19
	6H	14.76	15.12	15.78	16.16	17.47	10.95	11.32	11.97	12.36	13.66
	8H	14.97	15.29	16.00	16.32	17.64	11.14	11.46	12.17	12.49	13.81
	12H	15.10	15.38	16.13	16.41	17.77	11.25	11.54	12.29	12.56	13.93
12H	4H	14.15	14.55	15.17	15.57	16.88	10.45	10.84	11.46	11.86	13.17
	6H	14.73	15.05	15.76	16.08	17.40	11.00	11.32	12.03	12.35	13.67
	8H	14.95	15.23	15.98	16.25	17.62	11.21	11.49	12.24	12.51	13.88