

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923533

Luminaire Tested: DFN2DIP-TR3F0-050D090US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923533
REPORT IS A COMBINATION OF REPORTS P900360 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D090US940-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10892.3 lumens
Efficiency: N/A
Efficacy: 93.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 116.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923533
CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P923533

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	95	91	87	84	85	82	79	76	66	64	62	51	50	49	38	37	36	30				30
2	86	79	74	69	78	72	67	63	58	55	52	45	43	41	34	32	31	26				26
3	79	70	63	58	71	64	58	53	52	47	44	40	38	35	30	28	27	22				22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19				19
5	67	55	48	42	60	51	44	39	41	36	33	33	29	26	25	22	21	17				17
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14				14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	16	15	12				12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	17	15	13	11				11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2296	2296	2296
5°	2299	2258	2273
10°	2275	2212	2197
15°	2242	2137	2082
20°	2199	2034	1940
25°	2156	1919	1803
30°	2097	1802	1631
35°	2040	1676	1479
40°	1982	1546	1306
45°	1914	1402	1148
50°	1844	1257	995
55°	1771	1101	847
60°	1686	940	696
65°	1588	775	625
70°	1470	622	563
75°	1321	544	509
80°	1105	451	436
85°	753	292	320

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2478 cd/sqm



TEST NUMBER: P923533

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	172.7	1.6
10°-20°	474.1	4.4
20°-30°	665.6	6.1
30°-40°	725.6	6.7
40°-50°	666.9	6.1
50°-60°	523.7	4.8
60°-70°	340.9	3.1
70°-80°	175.5	1.6
80°-90°	52.0	0.5
90°-100°	157.1	1.4
100°-110°	499.0	4.6
110°-120°	854.0	7.8
120°-130°	1123.1	10.3
130°-140°	1260.7	11.6
140°-150°	1236.2	11.3
150°-160°	1037.0	9.5
160°-170°	687.7	6.3
170°-180°	240.4	2.2
0°-30°	1312.4	12.0
0°-40°	2038.0	18.7
0°-60°	3228.6	29.6
0°-90°	3797.0	34.9
90°-120°	1510.1	13.9
90°-150°	5130.1	47.1
90°-180°	7095.0	65.1
0°-180°	10892.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1843	1843	1843	1843	1843	
5°	1843	1834	1813	1828	1823	175
15°	1753	1734	1678	1646	1629	494
25°	1591	1538	1427	1359	1334	732
35°	1371	1286	1139	1034	997	858
45°	1121	1009	834	715	675	865
55°	852	722	542	442	410	761
65°	575	440	290	234	228	570
75°	307	190	133	122	120	324
85°	72	37	32	32	32	82
90°	2	28	75	70	73	11
95°	112	133	137	137	133	124
105°	461	467	471	475	475	486
115°	857	869	865	863	857	848
125°	1246	1266	1260	1253	1250	1114
135°	1612	1636	1641	1638	1632	1246
145°	1957	1973	1985	1987	1979	1223
155°	2238	2244	2251	2262	2255	1030
165°	2435	2432	2432	2448	2437	687
175°	2534	2527	2523	2538	2525	241
180°	2538	2538	2538	2538	2538	



TEST NUMBER: P923533

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1842.7	1842.7	1842.7	1842.7	1842.7
2.5°	1851.0	1842.7	1824.4	1841.1	1837.7
5°	1842.7	1834.4	1812.7	1827.6	1822.7
7.5°	1827.6	1817.8	1794.4	1801.0	1792.6
10°	1807.7	1796.0	1762.7	1757.7	1747.7
12.5°	1782.7	1767.7	1722.6	1712.7	1694.2
15°	1752.7	1734.3	1677.7	1646.0	1629.3
17.5°	1717.6	1691.0	1620.9	1584.2	1557.5
20°	1677.7	1644.2	1560.8	1519.3	1482.5
22.5°	1634.3	1595.9	1499.1	1442.5	1417.6
25°	1590.9	1537.5	1427.4	1359.1	1334.0
27.5°	1539.3	1482.5	1360.8	1282.4	1244.0
30°	1484.3	1420.8	1287.4	1202.4	1157.3
32.5°	1430.8	1354.1	1217.5	1117.3	1075.6
35°	1370.8	1285.8	1139.1	1033.9	997.2
37.5°	1312.4	1220.7	1065.7	950.5	908.9
40°	1250.7	1150.8	988.8	870.5	827.2
42.5°	1187.4	1080.7	912.2	788.7	747.2
45°	1120.7	1008.9	833.8	715.3	675.3
47.5°	1057.3	939.0	758.8	640.3	603.7
50°	987.3	868.9	685.5	570.2	535.4
52.5°	918.8	793.7	615.4	505.3	473.7
55°	852.1	722.0	541.9	441.9	410.3
57.5°	783.8	650.4	477.0	383.6	356.9
60°	713.7	580.3	408.5	323.6	296.9
62.5°	645.4	512.0	350.2	270.2	256.9
65°	575.3	440.2	290.2	233.5	228.5
67.5°	508.6	373.5	233.5	205.1	200.1
70°	438.6	308.5	193.4	176.7	170.0
72.5°	371.9	248.4	161.8	148.5	145.1
75°	306.8	190.0	133.4	121.7	120.1
77.5°	241.8	135.0	105.1	98.4	95.0
80°	181.7	96.8	80.0	73.4	73.4
82.5°	126.7	65.1	55.0	51.6	51.6
85°	71.7	36.6	31.7	31.7	31.7
87.5°	26.8	13.3	13.3	11.7	11.7
90°	2.3	27.6	75.0	70.4	72.7
92.5°	47.4	64.3	66.6	68.8	68.8
95°	111.7	133.1	137.0	137.0	133.1
97.5°	185.9	205.8	214.3	214.3	214.3
100°	271.6	289.3	295.3	295.3	293.1
102.5°	361.9	375.0	383.3	385.7	383.3
105°	460.7	466.7	471.4	475.2	475.2
107.5°	558.6	567.8	567.8	569.3	558.6
110°	653.4	665.8	665.8	665.8	659.6



TEST NUMBER: P923533

CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	756.0	769.0	766.7	760.6	756.0
115°	857.0	869.2	865.4	863.2	857.0
117.5°	957.3	974.1	963.4	957.3	951.1
120°	1058.3	1075.0	1058.3	1058.3	1051.3
122.5°	1150.0	1171.5	1160.8	1154.7	1150.0
125°	1246.5	1265.6	1259.5	1252.6	1250.4
127.5°	1340.6	1364.3	1355.9	1346.8	1340.6
130°	1428.6	1456.2	1452.3	1447.7	1439.3
132.5°	1527.3	1548.7	1550.2	1539.5	1533.5
135°	1612.2	1635.9	1640.6	1638.3	1632.2
137.5°	1707.1	1726.3	1730.1	1728.6	1719.4
140°	1790.6	1809.6	1820.3	1820.3	1812.0
142.5°	1876.2	1895.3	1901.5	1903.8	1895.3
145°	1957.4	1972.6	1984.9	1987.2	1978.8
147.5°	2030.1	2049.2	2058.3	2062.2	2053.8
150°	2105.1	2118.1	2126.5	2133.3	2126.5
152.5°	2171.6	2184.6	2195.3	2203.8	2195.3
155°	2238.2	2244.3	2251.2	2261.9	2255.0
157.5°	2295.5	2300.2	2304.0	2319.2	2308.5
160°	2346.8	2351.4	2353.8	2366.7	2357.5
162.5°	2394.2	2394.2	2396.6	2411.1	2400.4
165°	2434.8	2432.5	2432.5	2447.8	2437.1
167.5°	2471.6	2464.7	2464.7	2479.9	2469.2
170°	2499.1	2493.0	2490.7	2506.0	2493.0
172.5°	2518.2	2512.1	2509.8	2525.1	2512.1
175°	2533.5	2527.4	2522.8	2538.2	2525.1
177.5°	2541.9	2535.8	2531.2	2544.2	2531.2
180°	2538.2	2538.2	2538.2	2538.2	2538.2



TEST NUMBER: P923533
 CATALOG NUMBER: DFN2DIP-TR3F0-050D090US940-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.38	9.10	9.46	10.18	11.65	4.35	5.07	5.44	6.15	7.63
	3H	10.04	10.68	11.13	11.77	13.26	5.53	6.17	6.62	7.26	8.75
	4H	10.63	11.24	11.73	12.33	13.83	5.97	6.58	7.07	7.67	9.17
	6H	11.04	11.60	12.15	12.69	14.20	6.28	6.84	7.39	7.93	9.44
	8H	11.16	11.69	12.27	12.80	14.30	6.36	6.90	7.48	8.01	9.51
	12H	11.21	11.72	12.33	12.82	14.35	6.40	6.91	7.52	8.01	9.54
4H	2H	8.38	8.99	9.49	10.08	11.58	4.93	5.54	6.04	6.63	8.13
	3H	10.19	10.70	11.30	11.81	13.32	6.26	6.77	7.38	7.89	9.40
	4H	10.87	11.33	11.99	12.44	13.97	6.80	7.27	7.92	8.37	9.90
	6H	11.37	11.77	12.50	12.90	14.42	7.21	7.61	8.34	8.74	10.26
	8H	11.54	11.91	12.66	13.03	14.57	7.33	7.70	8.46	8.82	10.36
	12H	11.62	11.96	12.76	13.09	14.63	7.39	7.73	8.53	8.86	10.40
8H	4H	10.83	11.20	11.95	12.32	13.86	7.07	7.44	8.19	8.56	10.10
	6H	11.38	11.69	12.53	12.85	14.38	7.57	7.88	8.72	9.04	10.58
	8H	11.59	11.86	12.74	13.00	14.56	7.76	8.03	8.91	9.17	10.73
	12H	11.72	11.95	12.87	13.09	14.68	7.87	8.11	9.03	9.24	10.84
12H	4H	10.77	11.11	11.92	12.24	13.79	7.07	7.40	8.21	8.54	10.08
	6H	11.35	11.62	12.51	12.76	14.32	7.62	7.89	8.77	9.03	10.59
	8H	11.56	11.80	12.72	12.94	14.53	7.82	8.06	8.98	9.20	10.79