

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912638

Luminaire Tested: DFN2DIP-TR3F0-060D070US850-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912638
REPORT IS A COMBINATION OF REPORTS P900333 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-060D070US850-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 13457.7 lumens
Efficiency: N/A
Efficacy: 121.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 110.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912638
CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P912638

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	98	98	98	98	83	83	83	68	68	68	55	55	55	49				49
1	98	93	89	86	90	86	83	80	73	70	68	60	59	57	49	48	47	41				41
2	89	81	75	70	82	75	70	65	64	60	56	53	50	48	43	41	39	35				35
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	33	29				29
4	74	63	55	49	68	59	52	46	50	45	40	42	38	34	34	31	29	25				25
5	68	56	48	42	62	52	45	40	45	39	35	37	33	30	31	28	25	22				22
6	63	51	43	37	58	47	40	35	40	35	30	34	29	26	28	25	22	19				19
7	58	46	38	32	53	42	35	30	36	31	27	31	26	23	25	22	20	17				17
8	54	41	34	28	49	39	32	27	33	28	24	28	24	21	23	20	18	15				15
9	50	38	30	25	46	35	29	24	30	25	21	26	22	19	22	18	16	14				14
10	47	35	28	23	43	32	26	22	28	23	19	24	20	17	20	17	14	12				12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3226	3226	3226
5°	3230	3179	3201
10°	3202	3133	3155
15°	3153	3079	3085
20°	3087	3004	3014
25°	3022	2916	2932
30°	2941	2834	2828
35°	2864	2737	2718
40°	2770	2639	2613
45°	2675	2540	2506
50°	2572	2437	2382
55°	2463	2318	2267
60°	2341	2176	2136
65°	2207	2029	1981
70°	2036	1850	1814
75°	1800	1635	1656
80°	1515	1360	1361
85°	1070	895	879

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2675 cd/sqm



TEST NUMBER: P912638

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	243.7	1.8
10°-20°	685.6	5.1
20°-30°	1007.6	7.5
30°-40°	1170.3	8.7
40°-50°	1168.8	8.7
50°-60°	1019.2	7.6
60°-70°	753.4	5.6
70°-80°	426.3	3.2
80°-90°	119.5	0.9
90°-100°	151.9	1.1
100°-110°	482.7	3.6
110°-120°	826.1	6.1
120°-130°	1086.4	8.1
130°-140°	1219.5	9.1
140°-150°	1195.8	8.9
150°-160°	1003.1	7.5
160°-170°	665.3	4.9
170°-180°	232.5	1.7
0°-30°	1937.0	14.4
0°-40°	3107.2	23.1
0°-60°	5295.3	39.3
0°-90°	6594.4	49.0
90°-120°	1460.7	10.9
90°-150°	4962.4	36.9
90°-180°	6863.0	51.0
0°-180°	13457.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2589	2589	2589	2589	2589	
5°	2589	2579	2552	2572	2567	246
15°	2465	2450	2417	2428	2415	694
25°	2231	2211	2168	2173	2168	1026
35°	1925	1900	1860	1845	1832	1202
45°	1566	1549	1511	1484	1474	1209
55°	1185	1170	1140	1110	1098	1060
65°	799	784	759	737	724	790
75°	418	413	401	386	391	446
85°	102	100	97	90	87	114
90°	2	27	72	68	70	13
95°	108	129	132	132	129	120
105°	446	452	456	460	460	470
115°	829	841	837	835	829	820
125°	1206	1224	1218	1212	1210	1077
135°	1560	1582	1587	1585	1579	1205
145°	1893	1908	1920	1922	1914	1183
155°	2165	2171	2178	2188	2181	997
165°	2355	2353	2353	2368	2357	664
175°	2451	2445	2440	2455	2443	233
180°	2455	2455	2455	2455	2455	



TEST NUMBER: P912638

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2589.1	2589.1	2589.1	2589.1	2589.1
2.5°	2604.2	2591.7	2564.2	2589.1	2584.3
5°	2589.1	2579.3	2551.8	2571.7	2566.9
7.5°	2571.7	2556.9	2529.4	2549.5	2544.5
10°	2544.5	2527.1	2497.1	2517.0	2509.6
12.5°	2507.0	2492.1	2462.3	2474.7	2469.7
15°	2464.6	2449.9	2417.4	2427.5	2415.1
17.5°	2412.4	2397.7	2365.2	2377.5	2365.2
20°	2355.1	2340.3	2305.4	2312.8	2303.1
22.5°	2298.1	2275.6	2243.1	2243.1	2238.1
25°	2230.6	2210.9	2168.5	2173.3	2168.5
27.5°	2155.9	2138.5	2106.2	2098.9	2086.5
30°	2081.5	2061.3	2024.1	2016.7	2006.6
32.5°	2001.6	1986.9	1947.0	1931.9	1921.9
35°	1924.6	1899.7	1859.8	1844.7	1832.3
37.5°	1837.4	1814.9	1775.1	1757.5	1745.1
40°	1747.8	1727.7	1687.9	1665.7	1655.6
42.5°	1660.6	1640.5	1601.0	1575.9	1561.0
45°	1566.1	1548.6	1511.1	1484.0	1473.9
47.5°	1473.9	1456.4	1416.6	1389.1	1374.3
50°	1376.7	1364.3	1329.5	1294.5	1282.1
52.5°	1282.1	1264.7	1232.4	1205.0	1187.6
55°	1185.2	1170.1	1140.3	1110.4	1098.0
57.5°	1088.0	1075.6	1043.1	1013.3	1003.2
60°	990.8	981.0	946.2	918.7	911.3
62.5°	896.2	878.8	853.9	829.1	819.1
65°	799.3	784.3	759.4	736.9	724.5
67.5°	699.7	687.0	664.8	647.4	637.3
70°	607.5	597.5	575.0	557.6	547.8
72.5°	512.9	502.9	490.5	473.1	465.7
75°	418.1	413.4	400.7	385.9	390.9
77.5°	333.6	323.6	318.5	311.2	303.8
80°	249.1	246.4	241.4	234.0	229.0
82.5°	169.3	169.3	166.9	156.9	156.9
85°	101.9	99.6	97.1	89.5	87.2
87.5°	44.9	39.9	34.8	27.5	24.8
90°	2.2	26.6	72.5	68.1	70.3
92.5°	45.9	62.2	64.4	66.7	66.7
95°	108.0	128.8	132.5	132.5	128.8
97.5°	179.9	199.1	207.3	207.3	207.3
100°	262.7	279.8	285.7	285.7	283.5
102.5°	350.1	362.6	370.8	373.1	370.8
105°	445.6	451.5	455.9	459.7	459.7
107.5°	540.3	549.2	549.2	550.7	540.3
110°	632.1	644.0	644.0	644.0	638.0



TEST NUMBER: P912638

CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	731.3	743.9	741.7	735.7	731.3
115°	829.0	840.8	837.2	835.0	829.0
117.5°	925.9	942.2	931.9	925.9	920.0
120°	1023.6	1039.9	1023.6	1023.6	1017.0
122.5°	1112.4	1133.2	1122.9	1116.9	1112.4
125°	1205.7	1224.2	1218.3	1211.7	1209.5
127.5°	1296.8	1319.7	1311.6	1302.7	1296.8
130°	1381.9	1408.5	1404.9	1400.4	1392.2
132.5°	1477.4	1498.1	1499.6	1489.3	1483.3
135°	1559.6	1582.4	1587.0	1584.7	1578.8
137.5°	1651.3	1669.8	1673.5	1672.0	1663.2
140°	1732.0	1750.6	1760.9	1760.9	1752.8
142.5°	1814.9	1833.4	1839.3	1841.5	1833.4
145°	1893.4	1908.1	1920.0	1922.2	1914.1
147.5°	1963.7	1982.2	1991.1	1994.8	1986.7
150°	2036.2	2048.8	2057.0	2063.6	2057.0
152.5°	2100.6	2113.2	2123.5	2131.7	2123.5
155°	2165.0	2170.9	2177.6	2187.9	2181.3
157.5°	2220.6	2225.0	2228.6	2243.5	2233.1
160°	2270.1	2274.6	2276.8	2289.3	2280.4
162.5°	2316.0	2316.0	2318.3	2332.2	2321.9
165°	2355.2	2353.0	2353.0	2367.8	2357.4
167.5°	2390.8	2384.1	2384.1	2398.9	2388.6
170°	2417.4	2411.5	2409.3	2424.1	2411.5
172.5°	2435.9	2429.9	2427.7	2442.6	2429.9
175°	2450.7	2444.8	2440.4	2455.1	2442.6
177.5°	2458.9	2452.9	2448.5	2461.1	2448.5
180°	2455.1	2455.1	2455.1	2455.1	2455.1



TEST NUMBER: P912638
 CATALOG NUMBER: DFN2DIP-TR3F0-060D070US850-FLLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.20	12.05	12.16	13.03	14.31	10.77	11.62	11.73	12.60	13.89
	3H	12.85	13.61	13.82	14.60	15.91	12.38	13.14	13.35	14.13	15.44
	4H	13.43	14.15	14.42	15.14	16.46	12.96	13.68	13.95	14.68	15.99
	6H	13.82	14.49	14.82	15.48	16.81	13.35	14.02	14.35	15.01	16.34
	8H	13.92	14.55	14.93	15.57	16.89	13.45	14.09	14.46	15.10	16.43
	12H	13.96	14.57	14.98	15.58	16.93	13.49	14.09	14.50	15.10	16.45
4H	2H	11.65	12.38	12.65	13.37	14.68	11.31	12.03	12.31	13.03	14.34
	3H	13.51	14.11	14.51	15.13	16.46	13.12	13.72	14.12	14.74	16.07
	4H	14.21	14.77	15.23	15.78	17.13	13.81	14.36	14.83	15.38	16.73
	6H	14.72	15.19	15.74	16.23	17.58	14.31	14.79	15.34	15.83	17.18
	8H	14.86	15.31	15.89	16.34	17.70	14.46	14.90	15.48	15.93	17.30
	12H	14.93	15.33	15.98	16.38	17.75	14.52	14.92	15.56	15.96	17.33
8H	4H	14.40	14.85	15.43	15.88	17.24	14.05	14.49	15.07	15.52	16.89
	6H	15.02	15.39	16.07	16.47	17.83	14.67	15.03	15.72	16.11	17.47
	8H	15.24	15.56	16.30	16.62	18.00	14.88	15.20	15.93	16.26	17.64
	12H	15.36	15.65	16.43	16.70	18.12	14.99	15.27	16.05	16.32	17.75
12H	4H	14.39	14.79	15.43	15.84	17.21	14.04	14.44	15.08	15.49	16.86
	6H	15.05	15.38	16.11	16.43	17.82	14.71	15.03	15.76	16.09	17.47
	8H	15.29	15.57	16.35	16.62	18.05	14.93	15.22	16.00	16.27	17.70