

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912661

Luminaire Tested: DFN2DIP-TR3F0-070D060US850-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912661
REPORT IS A COMBINATION OF REPORTS P901841 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D060US850-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14272.8 lumens
Efficiency: N/A
Efficacy: 123.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 115.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	60	60	60
1	99	94	90	87	91	88	84	81	75	73	70	63	62	60	53	52	50
2	90	82	76	71	83	77	71	67	66	62	58	56	53	50	46	44	42
3	82	72	65	59	76	67	61	56	58	53	49	49	46	42	41	38	36
4	75	64	56	50	69	60	53	47	52	46	42	44	40	36	37	34	31
5	69	57	49	43	64	53	46	41	46	40	36	39	35	32	33	30	27
6	63	51	43	37	59	48	41	35	42	36	31	36	31	28	30	27	24
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	28	34	29	25	30	25	22	25	22	19
9	51	38	31	26	47	36	29	25	32	26	22	27	23	20	23	20	17
10	47	35	28	23	44	33	27	22	29	24	20	25	21	18	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3764	3764	3764
5°	3768	3708	3734
10°	3735	3655	3681
15°	3678	3592	3599
20°	3602	3505	3516
25°	3526	3402	3420
30°	3431	3306	3299
35°	3342	3193	3171
40°	3231	3078	3048
45°	3121	2964	2923
50°	3001	2843	2779
55°	2874	2704	2645
60°	2731	2539	2492
65°	2575	2367	2311
70°	2376	2158	2116
75°	2100	1907	1932
80°	1768	1587	1588
85°	1249	1046	1025

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3121 cd/sqm

TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.3	2.0
10°-20°	799.9	5.6
20°-30°	1175.6	8.2
30°-40°	1365.3	9.6
40°-50°	1363.6	9.6
50°-60°	1189.1	8.3
60°-70°	879.0	6.2
70°-80°	497.3	3.5
80°-90°	135.2	0.9
90°-100°	74.1	0.5
100°-110°	276.0	1.9
110°-120°	732.1	5.1
120°-130°	1214.2	8.5
130°-140°	1289.8	9.0
140°-150°	1198.7	8.4
150°-160°	963.8	6.8
160°-170°	621.0	4.4
170°-180°	213.7	1.5
0°-30°	2259.8	15.8
0°-40°	3625.1	25.4
0°-60°	6177.8	43.3
0°-90°	7689.3	53.9
90°-120°	1082.2	7.6
90°-150°	4785.0	33.5
90°-180°	6583.0	46.1
0°-180°	14272.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3021	3021	3021	3021	3021	
5°	3021	3009	2977	3000	2995	287
15°	2876	2858	2820	2832	2818	810
25°	2602	2579	2530	2536	2530	1198
35°	2245	2216	2170	2152	2138	1402
45°	1827	1807	1763	1731	1720	1410
55°	1383	1365	1330	1296	1281	1236
65°	933	915	886	860	845	922
75°	488	482	467	450	456	521
85°	119	116	114	104	102	133
90°	2	20	32	41	44	13
95°	106	52	63	72	70	125
105°	494	543	99	117	124	528
115°	934	962	1003	250	133	920
125°	1321	1342	1373	1384	1389	1178
135°	1635	1661	1675	1692	1688	1263
145°	1896	1895	1922	1934	1926	1186
155°	2088	2074	2093	2103	2090	962
165°	2200	2190	2195	2207	2195	622
175°	2250	2239	2242	2254	2238	214
180°	2246	2246	2246	2246	2246	

TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3020.6	3020.6	3020.6	3020.6	3020.6
2.5°	3038.2	3023.7	2991.6	3020.6	3015.0
5°	3020.6	3009.3	2977.2	3000.3	2994.7
7.5°	3000.3	2983.0	2950.9	2974.4	2968.6
10°	2968.6	2948.2	2913.3	2936.5	2927.9
12.5°	2924.8	2907.6	2872.8	2887.2	2881.3
15°	2875.5	2858.2	2820.3	2832.1	2817.5
17.5°	2814.4	2797.2	2759.3	2773.8	2759.3
20°	2747.5	2730.4	2689.7	2698.3	2686.9
22.5°	2681.0	2654.8	2616.9	2616.9	2611.0
25°	2602.5	2579.3	2530.1	2535.6	2530.1
27.5°	2515.2	2494.9	2457.3	2448.7	2434.1
30°	2428.4	2404.9	2361.5	2352.9	2341.1
32.5°	2335.2	2318.0	2271.5	2253.9	2242.2
35°	2245.3	2216.3	2169.8	2152.2	2137.7
37.5°	2143.6	2117.4	2070.8	2050.5	2036.0
40°	2039.1	2015.7	1969.1	1943.3	1931.5
42.5°	1937.4	1914.0	1867.8	1838.5	1821.2
45°	1827.1	1806.8	1763.0	1731.3	1719.5
47.5°	1719.5	1699.2	1652.6	1620.6	1603.4
50°	1606.2	1591.6	1550.9	1510.3	1495.8
52.5°	1495.8	1475.5	1437.9	1405.9	1385.5
55°	1382.7	1365.2	1330.4	1295.5	1281.0
57.5°	1269.4	1254.8	1216.9	1182.1	1170.4
60°	1155.9	1144.5	1103.9	1071.8	1063.2
62.5°	1045.6	1025.3	996.3	967.4	955.6
65°	932.6	914.9	886.0	859.8	845.3
67.5°	816.3	801.6	775.6	755.3	743.6
70°	708.8	697.1	670.8	650.5	639.1
72.5°	598.4	586.8	572.2	551.9	543.3
75°	487.8	482.3	467.4	450.3	456.1
77.5°	389.3	377.5	371.6	363.0	354.4
80°	290.6	287.6	281.7	273.0	267.2
82.5°	197.5	197.5	194.7	183.1	183.1
85°	119.0	116.2	113.5	104.5	101.7
87.5°	52.3	46.6	40.7	32.1	28.9
90°	1.6	19.5	32.4	40.7	43.8
92.5°	40.7	34.2	38.9	42.3	43.8
95°	105.6	51.9	63.3	71.6	69.9
97.5°	190.1	56.9	82.7	87.8	89.4
100°	287.7	65.0	92.6	105.6	108.8
102.5°	394.8	391.7	95.9	113.7	118.7
105°	493.9	542.7	99.1	116.9	123.5
107.5°	609.4	649.9	102.5	120.2	126.8
110°	720.0	753.9	284.5	122.0	128.3

TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	823.9	853.0	825.4	125.0	130.1
115°	934.3	961.9	1002.6	250.3	133.3
117.5°	1030.2	1062.6	1090.4	857.9	432.2
120°	1137.5	1161.8	1191.2	1210.6	991.2
122.5°	1228.3	1254.4	1287.0	1296.6	1298.4
125°	1321.0	1342.2	1373.1	1384.5	1389.2
127.5°	1405.5	1428.3	1452.8	1469.0	1470.5
130°	1485.2	1511.2	1529.0	1546.9	1545.4
132.5°	1566.5	1587.6	1605.4	1620.0	1618.5
135°	1634.8	1660.8	1675.3	1691.7	1688.3
137.5°	1706.1	1725.6	1742.0	1758.2	1753.4
140°	1776.0	1789.1	1806.9	1821.5	1813.4
142.5°	1834.6	1846.0	1867.1	1880.0	1871.9
145°	1896.4	1894.6	1922.2	1933.7	1925.6
147.5°	1949.8	1945.0	1972.6	1980.7	1974.4
150°	2002.0	1990.5	2016.6	2026.3	2018.2
152.5°	2045.8	2032.8	2057.1	2067.0	2055.5
155°	2088.0	2073.5	2093.0	2102.7	2089.7
157.5°	2122.2	2109.2	2123.8	2135.3	2122.2
160°	2151.5	2141.6	2151.5	2161.1	2149.8
162.5°	2177.3	2167.7	2175.7	2187.2	2172.5
165°	2200.1	2190.5	2195.3	2206.7	2195.3
167.5°	2218.0	2208.2	2213.2	2224.7	2209.9
170°	2232.7	2222.9	2226.2	2237.5	2222.9
172.5°	2242.4	2232.7	2236.0	2247.4	2232.7
175°	2250.5	2239.1	2242.4	2253.7	2237.5
177.5°	2253.7	2242.4	2244.1	2255.5	2240.8
180°	2245.6	2245.6	2245.6	2245.6	2245.6

TEST NUMBER: P912661

CATALOG NUMBER: DFN2DIP-TR3F0-070D060US850-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.18	13.07	13.10	14.01	15.23	11.75	12.64	12.67	13.59	14.80
	3H	13.83	14.64	14.76	15.59	16.82	13.36	14.17	14.30	15.12	16.36
	4H	14.41	15.17	15.36	16.13	17.38	13.95	14.71	14.89	15.66	16.91
	6H	14.81	15.51	15.77	16.47	17.73	14.34	15.04	15.30	16.00	17.26
	8H	14.91	15.58	15.88	16.56	17.81	14.44	15.11	15.41	16.09	17.35
	12H	14.96	15.59	15.93	16.56	17.85	14.48	15.12	15.45	16.09	17.37
4H	2H	12.64	13.40	13.59	14.36	15.60	12.30	13.06	13.25	14.01	15.26
	3H	14.50	15.13	15.46	16.12	17.38	14.11	14.74	15.07	15.73	16.99
	4H	15.21	15.79	16.18	16.77	18.05	14.80	15.39	15.78	16.36	17.65
	6H	15.71	16.21	16.70	17.22	18.50	15.31	15.81	16.30	16.81	18.10
	8H	15.86	16.33	16.85	17.32	18.62	15.45	15.92	16.44	16.92	18.22
	12H	15.93	16.35	16.94	17.36	18.67	15.52	15.94	16.52	16.95	18.25
8H	4H	15.40	15.87	16.39	16.86	18.16	15.04	15.51	16.03	16.51	17.81
	6H	16.02	16.41	17.04	17.45	18.74	15.66	16.05	16.68	17.09	18.39
	8H	16.24	16.58	17.26	17.60	18.92	15.87	16.22	16.90	17.24	18.56
	12H	16.36	16.67	17.39	17.68	19.04	15.99	16.29	17.01	17.31	18.67
12H	4H	15.39	15.81	16.39	16.82	18.13	15.04	15.46	16.05	16.47	17.78
	6H	16.05	16.39	17.07	17.42	18.73	15.70	16.05	16.73	17.07	18.39
	8H	16.29	16.59	17.31	17.61	18.97	15.94	16.24	16.96	17.25	18.62