

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923596

Luminaire Tested: DFN2DIP-TR3F0-080D050US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923596
REPORT IS A COMBINATION OF REPORTS P900310 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D050US940-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10009.5 lumens
Efficiency: N/A
Efficacy: 84.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 118
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89		77	77	77		66
1	101	97	93	89	94	91	87	84	79	77	75		69	67	65		59
2	92	85	79	74	86	80	75	70	70	66	63		61	58	56		53
3	85	75	68	62	79	71	64	59	62	57	53		55	51	48		47
4	78	67	59	53	72	63	56	51	56	50	46		49	45	41		43
5	72	60	52	46	67	57	50	44	50	45	40		44	40	36		39
6	66	54	46	41	62	51	44	39	46	40	35		40	36	32		35
7	61	49	41	36	57	47	39	34	42	36	32		37	32	29		32
8	57	45	37	32	53	43	36	31	38	32	28		34	29	26		30
9	53	41	34	29	50	39	32	28	35	29	26		31	27	23		28
10	50	38	31	26	47	36	29	25	32	27	23		29	25	21		26

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3674	3674	3674
5°	3678	3613	3636
10°	3639	3539	3516
15°	3587	3419	3330
20°	3519	3255	3104
25°	3449	3071	2886
30°	3356	2883	2609
35°	3264	2682	2366
40°	3171	2474	2089
45°	3063	2243	1837
50°	2951	2010	1591
55°	2834	1762	1355
60°	2698	1503	1113
65°	2542	1240	999
70°	2352	995	901
75°	2114	871	815
80°	1769	721	698
85°	1204	466	510

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3063 cd/sqm

TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	276.3	2.8
10°-20°	758.6	7.6
20°-30°	1065.0	10.6
30°-40°	1160.9	11.6
40°-50°	1067.0	10.7
50°-60°	838.0	8.4
60°-70°	545.4	5.4
70°-80°	280.8	2.8
80°-90°	75.7	0.8
90°-100°	87.3	0.9
100°-110°	277.2	2.8
110°-120°	474.5	4.7
120°-130°	624.0	6.2
130°-140°	700.4	7.0
140°-150°	686.8	6.9
150°-160°	576.1	5.8
160°-170°	382.1	3.8
170°-180°	133.5	1.3
0°-30°	2099.9	21.0
0°-40°	3260.8	32.6
0°-60°	5165.8	51.6
0°-90°	6067.6	60.6
90°-120°	838.9	8.4
90°-150°	2850.1	28.5
90°-180°	3942.0	39.4
0°-180°	10009.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	1	15	42	39	40	10
95°	62	74	76	76	74	69
105°	256	259	262	264	264	270
115°	476	483	481	480	476	471
125°	692	703	700	696	695	619
135°	896	909	911	910	907	692
145°	1087	1096	1103	1104	1099	679
155°	1243	1247	1251	1257	1253	572
165°	1353	1351	1351	1360	1354	382
175°	1408	1404	1402	1410	1403	134
180°	1410	1410	1410	1410	1410	

TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.2	15.3	41.6	39.1	40.4
92.5°	26.4	35.7	37.0	38.3	38.3
95°	62.1	74.0	76.1	76.1	74.0
97.5°	103.3	114.3	119.0	119.0	119.0
100°	150.9	160.7	164.1	164.1	162.8
102.5°	201.1	208.3	212.9	214.3	212.9
105°	255.9	259.3	261.9	263.9	263.9
107.5°	310.3	315.4	315.4	316.3	310.3
110°	363.0	369.9	369.9	369.9	366.4

TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	420.0	427.2	426.0	422.6	420.0
115°	476.1	483.0	480.8	479.6	476.1
117.5°	531.8	541.2	535.2	531.8	528.4
120°	587.9	597.3	587.9	587.9	584.1
122.5°	638.9	650.9	644.9	641.5	638.9
125°	692.5	703.1	699.7	695.9	694.6
127.5°	744.8	758.0	753.3	748.1	744.8
130°	793.7	809.0	806.8	804.3	799.6
132.5°	848.6	860.4	861.3	855.3	851.9
135°	895.7	908.8	911.4	910.2	906.8
137.5°	948.4	959.0	961.2	960.3	955.2
140°	994.7	1005.4	1011.3	1011.3	1006.7
142.5°	1042.3	1053.0	1056.4	1057.7	1053.0
145°	1087.4	1095.9	1102.7	1104.0	1099.3
147.5°	1127.8	1138.4	1143.5	1145.7	1140.9
150°	1169.5	1176.7	1181.3	1185.2	1181.3
152.5°	1206.5	1213.7	1219.6	1224.3	1219.6
155°	1243.4	1246.8	1250.6	1256.6	1252.8
157.5°	1275.3	1277.8	1280.0	1288.5	1282.5
160°	1303.8	1306.4	1307.6	1314.8	1309.7
162.5°	1330.2	1330.2	1331.4	1339.5	1333.6
165°	1352.7	1351.4	1351.4	1359.9	1354.0
167.5°	1373.1	1369.2	1369.2	1377.8	1371.8
170°	1388.4	1385.0	1383.8	1392.2	1385.0
172.5°	1399.0	1395.6	1394.4	1402.8	1395.6
175°	1407.6	1404.1	1401.6	1410.1	1402.8
177.5°	1412.2	1408.8	1406.2	1413.5	1406.2
180°	1410.1	1410.1	1410.1	1410.1	1410.1

TEST NUMBER: P923596

CATALOG NUMBER: DFN2DIP-TR3F0-080D050US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.55	13.48	13.42	14.36	15.48	8.53	9.46	9.40	10.34	11.45
	3H	14.23	15.06	15.11	15.95	17.09	9.72	10.55	10.60	11.44	12.58
	4H	14.83	15.62	15.73	16.51	17.67	10.17	10.95	11.07	11.85	13.00
	6H	15.25	15.97	16.16	16.88	18.04	10.49	11.21	11.40	12.12	13.28
	8H	15.38	16.06	16.29	16.99	18.15	10.58	11.27	11.50	12.19	13.35
	12H	15.44	16.09	16.36	17.01	18.19	10.63	11.28	11.55	12.19	13.38
4H	2H	12.58	13.36	13.48	14.26	15.41	9.13	9.91	10.03	10.81	11.96
	3H	14.41	15.06	15.32	15.99	17.15	10.48	11.13	11.40	12.06	13.23
	4H	15.10	15.69	16.02	16.61	17.81	11.03	11.62	11.95	12.55	13.74
	6H	15.61	16.12	16.54	17.07	18.26	11.45	11.96	12.38	12.91	14.10
	8H	15.78	16.26	16.72	17.20	18.40	11.58	12.05	12.51	13.00	14.20
	12H	15.87	16.30	16.83	17.26	18.47	11.64	12.07	12.60	13.03	14.24
8H	4H	15.07	15.55	16.01	16.49	17.69	11.31	11.79	12.25	12.73	13.94
	6H	15.63	16.02	16.59	17.01	18.21	11.83	12.22	12.79	13.20	14.41
	8H	15.84	16.19	16.81	17.16	18.39	12.01	12.36	12.99	13.34	14.56
	12H	15.98	16.28	16.95	17.25	18.52	12.13	12.44	13.11	13.40	14.68
12H	4H	15.03	15.45	15.98	16.42	17.63	11.32	11.75	12.28	12.71	13.92
	6H	15.61	15.95	16.58	16.93	18.15	11.87	12.22	12.85	13.20	14.42
	8H	15.82	16.13	16.80	17.10	18.37	12.08	12.39	13.06	13.36	14.63