

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912676

Luminaire Tested: DFN2DIP-TR3F0-080D030US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912676
REPORT IS A COMBINATION OF REPORTS P900282 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D030US850-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 10485.6 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912676
CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P912676
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	112	112	112	112	106	106	106	106	96	96	96	85	85	85	76	76	76	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	75	73	69	67	66	66	66	66	62
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	57	57	57	57	53
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	49	49	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	50	46	43	43	43	43	40
5	74	62	54	48	70	59	52	47	54	48	44	49	45	41	45	41	38	38	38	38	35
6	68	56	48	42	65	54	46	41	49	43	39	45	40	36	41	37	34	34	34	34	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	30	30	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	31	27	27	27	27	25
9	55	43	35	30	52	41	34	30	38	32	28	35	30	26	32	28	25	25	25	25	23
10	52	40	32	28	49	38	31	27	35	29	25	33	28	24	30	26	23	23	23	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4569	4569	4569
5°	4574	4493	4522
10°	4526	4401	4372
15°	4461	4252	4142
20°	4376	4048	3860
25°	4289	3820	3589
30°	4173	3586	3245
35°	4060	3335	2943
40°	3944	3076	2598
45°	3809	2790	2285
50°	3670	2500	1979
55°	3524	2192	1686
60°	3355	1870	1385
65°	3161	1543	1243
70°	2925	1238	1120
75°	2629	1083	1013
80°	2199	896	868
85°	1497	581	635

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3809 cd/sqm



TEST NUMBER: P912676

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	343.7	3.3
10°-20°	943.4	9.0
20°-30°	1324.5	12.6
30°-40°	1443.8	13.8
40°-50°	1327.0	12.7
50°-60°	1042.1	9.9
60°-70°	678.3	6.5
70°-80°	349.2	3.3
80°-90°	92.1	0.9
90°-100°	65.1	0.6
100°-110°	206.9	2.0
110°-120°	354.0	3.4
120°-130°	465.6	4.4
130°-140°	522.6	5.0
140°-150°	512.5	4.9
150°-160°	429.9	4.1
160°-170°	285.1	2.7
170°-180°	99.7	1.0
0°-30°	2611.6	24.9
0°-40°	4055.4	38.7
0°-60°	6424.5	61.3
0°-90°	7544.2	71.9
90°-120°	626.0	6.0
90°-150°	2126.7	20.3
90°-180°	2941.0	28.0
0°-180°	10485.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3667	3667	3667	3667	3667	
5°	3667	3650	3607	3637	3627	348
15°	3488	3451	3338	3275	3242	983
25°	3166	3060	2840	2705	2655	1456
35°	2728	2558	2267	2058	1984	1707
45°	2230	2008	1659	1423	1344	1722
55°	1696	1437	1078	879	816	1515
65°	1145	876	577	465	454	1135
75°	610	378	266	242	239	646
85°	143	73	63	63	63	164
90°	1	11	31	29	30	10
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	



TEST NUMBER: P912676

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3666.8	3666.8	3666.8	3666.8	3666.8
2.5°	3683.3	3666.8	3630.2	3663.6	3656.9
5°	3666.8	3650.3	3606.9	3636.9	3627.0
7.5°	3636.9	3617.1	3570.6	3583.7	3567.1
10°	3597.0	3573.9	3507.7	3497.5	3477.7
12.5°	3547.5	3517.5	3427.7	3408.0	3371.4
15°	3487.6	3451.0	3338.3	3275.3	3242.2
17.5°	3417.8	3364.7	3225.3	3152.4	3099.2
20°	3338.3	3271.8	3106.0	3023.2	2949.9
22.5°	3252.0	3175.6	2983.1	2870.4	2820.7
25°	3165.8	3059.5	2840.5	2704.6	2654.6
27.5°	3062.9	2949.9	2707.7	2551.8	2475.4
30°	2953.5	2827.1	2561.7	2392.7	2302.8
32.5°	2847.1	2694.4	2422.6	2223.3	2140.3
35°	2727.8	2558.5	2266.6	2057.5	1984.2
37.5°	2611.6	2428.9	2120.5	1891.3	1808.6
40°	2488.8	2289.9	1967.7	1732.1	1645.9
42.5°	2362.7	2150.5	1815.2	1569.6	1486.7
45°	2230.0	2007.5	1659.3	1423.4	1343.9
47.5°	2104.0	1868.4	1510.0	1274.1	1201.3
50°	1964.5	1729.0	1364.0	1134.7	1065.3
52.5°	1828.3	1579.3	1224.4	1005.5	942.5
55°	1695.6	1436.8	1078.4	879.4	816.4
57.5°	1559.7	1294.2	949.2	763.3	710.1
60°	1420.2	1154.8	812.9	643.9	590.8
62.5°	1284.3	1018.8	696.8	537.6	511.2
65°	1144.9	875.9	577.3	464.8	454.5
67.5°	1012.2	743.3	464.8	408.0	398.2
70°	872.8	614.1	384.8	351.7	338.4
72.5°	740.0	494.3	321.8	295.4	288.7
75°	610.5	378.2	265.5	242.2	239.1
77.5°	481.3	268.6	209.2	195.7	189.1
80°	361.5	192.6	159.1	146.1	146.1
82.5°	252.1	129.5	109.5	102.8	102.8
85°	142.6	72.9	63.0	63.0	63.0
87.5°	53.1	26.4	26.4	23.3	23.3
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5



TEST NUMBER: P912676

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2



TEST NUMBER: P912676
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US850-RLFL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.22	15.27	14.97	16.03	16.95	10.19	11.24	10.94	12.01	12.93
	3H	15.90	16.84	16.67	17.62	18.57	11.39	12.33	12.16	13.11	14.06
	4H	16.51	17.40	17.30	18.18	19.15	11.85	12.73	12.63	13.52	14.48
	6H	16.94	17.75	17.73	18.55	19.53	12.18	12.99	12.97	13.79	14.76
	8H	17.07	17.84	17.87	18.65	19.63	12.27	13.05	13.07	13.86	14.84
	12H	17.13	17.87	17.94	18.68	19.68	12.32	13.06	13.13	13.86	14.87
4H	2H	14.26	15.14	15.05	15.93	16.89	10.81	11.69	11.60	12.48	13.44
	3H	16.10	16.83	16.90	17.65	18.63	12.17	12.91	12.97	13.73	14.71
	4H	16.79	17.46	17.60	18.28	19.29	12.72	13.39	13.54	14.21	15.22
	6H	17.31	17.88	18.14	18.73	19.74	13.15	13.72	13.98	14.57	15.58
	8H	17.48	18.02	18.32	18.86	19.89	13.28	13.82	14.11	14.66	15.68
	12H	17.58	18.07	18.43	18.93	19.96	13.35	13.83	14.20	14.69	15.73
8H	4H	16.77	17.31	17.61	18.15	19.18	13.02	13.55	13.85	14.39	15.42
	6H	17.34	17.78	18.20	18.66	19.69	13.53	13.98	14.39	14.86	15.89
	8H	17.55	17.94	18.42	18.82	19.87	13.72	14.11	14.59	14.99	16.04
	12H	17.69	18.04	18.56	18.91	20.01	13.84	14.19	14.72	15.06	16.16
12H	4H	16.74	17.22	17.59	18.08	19.11	13.03	13.51	13.88	14.37	15.40
	6H	17.31	17.71	18.18	18.59	19.63	13.58	13.98	14.45	14.85	15.90
	8H	17.54	17.88	18.41	18.75	19.85	13.80	14.14	14.67	15.01	16.11