

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P912702

Luminaire Tested: DFN2DIP-TR3F0-090D030US850-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P912702
REPORT IS A COMBINATION OF REPORTS P900284 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D030US850-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11428.2 lumens
Efficiency: N/A
Efficacy: 97.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 117.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	78	78	78
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	70	69	68
2	95	88	82	77	90	84	79	74	76	72	68	69	66	63	63	60	58
3	87	78	71	65	83	75	68	63	68	63	58	62	58	54	56	53	50
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44
5	74	63	54	48	70	60	53	47	55	49	44	51	45	42	46	42	39
6	69	57	48	43	65	54	47	41	50	44	39	46	41	37	42	38	35
7	64	51	43	38	61	49	42	37	46	39	35	42	37	33	39	34	31
8	59	47	39	34	57	45	38	33	42	36	31	39	34	30	36	31	28
9	56	43	36	31	53	42	35	30	39	33	28	36	31	27	33	29	26
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	23

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	5140	5140	5140
5°	5146	5054	5088
10°	5092	4951	4919
15°	5019	4783	4660
20°	4923	4553	4343
25°	4826	4297	4037
30°	4695	4034	3651
35°	4567	3752	3311
40°	4437	3461	2922
45°	4285	3138	2570
50°	4129	2813	2226
55°	3965	2466	1896
60°	3775	2104	1558
65°	3556	1736	1398
70°	3291	1393	1260
75°	2957	1219	1139
80°	2475	1009	977
85°	1684	653	715

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 4285 cd/sqm

TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	386.6	3.4
10°-20°	1061.3	9.3
20°-30°	1490.1	13.0
30°-40°	1624.3	14.2
40°-50°	1492.9	13.1
50°-60°	1172.4	10.3
60°-70°	763.1	6.7
70°-80°	392.8	3.4
80°-90°	103.3	0.9
90°-100°	65.1	0.6
100°-110°	206.9	1.8
110°-120°	354.0	3.1
120°-130°	465.6	4.1
130°-140°	522.6	4.6
140°-150°	512.5	4.5
150°-160°	429.9	3.8
160°-170°	285.1	2.5
170°-180°	99.7	0.9
0°-30°	2938.0	25.7
0°-40°	4562.3	39.9
0°-60°	7227.6	63.2
0°-90°	8486.9	74.3
90°-120°	626.0	5.5
90°-150°	2126.7	18.6
90°-180°	2941.0	25.7
0°-180°	11428.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4125	4125	4125	4125	4125	
5°	4125	4106	4058	4091	4080	391
15°	3924	3882	3756	3685	3648	1106
25°	3562	3442	3196	3043	2986	1638
35°	3069	2878	2550	2315	2232	1921
45°	2509	2258	1867	1601	1512	1937
55°	1908	1616	1213	989	918	1705
65°	1288	986	650	523	511	1277
75°	687	425	299	272	269	726
85°	160	82	71	71	71	184
90°	1	11	31	29	30	11
95°	46	55	57	57	55	52
105°	191	194	195	197	197	202
115°	355	360	359	358	355	351
125°	517	525	522	519	518	462
135°	668	678	680	679	677	517
145°	812	818	823	824	820	507
155°	928	930	933	938	935	427
165°	1009	1008	1008	1015	1010	285
175°	1050	1048	1046	1052	1047	100
180°	1052	1052	1052	1052	1052	

TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4125.1	4125.1	4125.1	4125.1	4125.1
2.5°	4143.8	4125.1	4083.9	4121.6	4114.1
5°	4125.1	4106.5	4057.8	4091.4	4080.3
7.5°	4091.4	4069.3	4017.0	4031.7	4013.0
10°	4046.7	4020.6	3946.2	3934.6	3912.4
12.5°	3990.8	3957.2	3856.2	3834.0	3792.8
15°	3923.5	3882.4	3755.6	3684.7	3647.5
17.5°	3845.1	3785.3	3628.4	3546.5	3486.7
20°	3755.6	3680.8	3494.1	3401.1	3318.7
22.5°	3658.6	3572.6	3355.9	3229.2	3173.4
25°	3561.6	3441.9	3195.6	3042.7	2986.4
27.5°	3445.9	3318.7	3046.2	2870.8	2784.8
30°	3322.7	3180.5	2881.8	2691.8	2590.7
32.5°	3203.0	3031.1	2725.4	2501.2	2407.7
35°	3068.8	2878.3	2549.9	2314.7	2232.3
37.5°	2938.1	2732.6	2385.6	2127.7	2034.7
40°	2799.9	2576.1	2213.7	1948.7	1851.7
42.5°	2658.1	2419.3	2042.1	1765.7	1672.6
45°	2508.8	2258.5	1866.7	1601.3	1511.8
47.5°	2366.9	2102.0	1698.8	1433.4	1351.4
50°	2210.1	1945.1	1534.4	1276.6	1198.5
52.5°	2056.9	1776.8	1377.6	1131.2	1060.3
55°	1907.5	1616.4	1213.1	989.4	918.5
57.5°	1754.7	1456.0	1067.9	858.7	798.9
60°	1597.7	1299.1	914.6	724.4	664.6
62.5°	1444.9	1146.3	783.8	604.8	575.1
65°	1288.0	985.5	649.5	522.8	511.4
67.5°	1138.7	836.1	522.8	459.0	447.9
70°	981.9	690.8	433.0	395.7	380.6
72.5°	832.5	556.1	362.0	332.3	324.8
75°	686.8	425.4	298.7	272.5	268.9
77.5°	541.4	302.2	235.2	220.2	212.7
80°	406.8	216.7	179.0	164.4	164.4
82.5°	283.6	145.7	123.2	115.7	115.7
85°	160.4	82.0	70.9	70.9	70.9
87.5°	59.8	29.7	29.7	26.2	26.2
90°	1.0	11.4	31.1	29.2	30.2
92.5°	19.6	26.6	27.6	28.5	28.5
95°	46.4	55.2	56.8	56.8	55.2
97.5°	77.1	85.3	88.8	88.8	88.8
100°	112.6	119.9	122.4	122.4	121.5
102.5°	150.0	155.5	158.9	159.9	158.9
105°	191.0	193.5	195.4	197.0	197.0
107.5°	231.6	235.3	235.3	236.0	231.6
110°	270.9	276.0	276.0	276.0	273.5

TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	313.4	318.8	317.8	315.3	313.4
115°	355.3	360.3	358.8	357.9	355.3
117.5°	396.8	403.8	399.4	396.8	394.2
120°	438.7	445.7	438.7	438.7	435.8
122.5°	476.8	485.6	481.2	478.6	476.8
125°	516.8	524.7	522.1	519.2	518.3
127.5°	555.7	565.6	562.2	558.3	555.7
130°	592.2	603.6	602.1	600.2	596.6
132.5°	633.1	642.0	642.7	638.2	635.7
135°	668.4	678.2	680.1	679.2	676.6
137.5°	707.7	715.6	717.2	716.6	712.8
140°	742.3	750.2	754.7	754.7	751.1
142.5°	777.9	785.7	788.3	789.3	785.7
145°	811.5	817.8	822.9	823.8	820.3
147.5°	841.6	849.5	853.3	854.9	851.4
150°	872.7	878.1	881.5	884.4	881.5
152.5°	900.3	905.6	910.0	913.6	910.0
155°	927.9	930.3	933.2	937.7	934.9
157.5°	951.6	953.5	955.2	961.5	957.1
160°	972.9	974.8	975.8	981.1	977.4
162.5°	992.6	992.6	993.6	999.5	995.1
165°	1009.4	1008.4	1008.4	1014.7	1010.3
167.5°	1024.6	1021.7	1021.7	1028.0	1023.6
170°	1036.0	1033.5	1032.6	1038.9	1033.5
172.5°	1043.9	1041.5	1040.5	1046.8	1041.5
175°	1050.3	1047.8	1045.9	1052.2	1046.8
177.5°	1053.8	1051.2	1049.3	1054.8	1049.3
180°	1052.2	1052.2	1052.2	1052.2	1052.2

TEST NUMBER: P912702

CATALOG NUMBER: DFN2DIP-TR3F0-090D030US850-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	14.80	15.88	15.53	16.62	17.50	10.78	11.86	11.50	12.60	13.48
	3H	16.49	17.45	17.23	18.20	19.12	11.98	12.95	12.72	13.69	14.61
	4H	17.10	18.01	17.86	18.77	19.69	12.44	13.35	13.20	14.11	15.03
	6H	17.53	18.37	18.30	19.13	20.07	12.77	13.60	13.54	14.37	15.31
	8H	17.66	18.45	18.44	19.24	20.18	12.86	13.66	13.64	14.45	15.38
	12H	17.72	18.48	18.51	19.26	20.23	12.91	13.67	13.70	14.45	15.42
4H	2H	14.85	15.76	15.61	16.52	17.44	11.40	12.31	12.16	13.07	13.99
	3H	16.69	17.44	17.46	18.24	19.18	12.77	13.52	13.54	14.31	15.25
	4H	17.39	18.07	18.17	18.86	19.83	13.32	14.00	14.10	14.80	15.77
	6H	17.90	18.49	18.71	19.31	20.29	13.74	14.33	14.55	15.15	16.13
	8H	18.08	18.63	18.89	19.45	20.43	13.87	14.43	14.68	15.24	16.23
	12H	18.18	18.67	19.01	19.51	20.50	13.95	14.44	14.78	15.28	16.27
8H	4H	17.37	17.92	18.18	18.74	19.72	13.61	14.16	14.42	14.98	15.96
	6H	17.93	18.39	18.77	19.25	20.24	14.13	14.59	14.97	15.44	16.43
	8H	18.15	18.55	18.99	19.41	20.41	14.32	14.72	15.17	15.58	16.58
	12H	18.29	18.65	19.14	19.49	20.55	14.44	14.80	15.29	15.64	16.71
12H	4H	17.33	17.83	18.16	18.66	19.66	13.63	14.12	14.45	14.96	15.95
	6H	17.91	18.32	18.76	19.17	20.18	14.18	14.58	15.03	15.44	16.44
	8H	18.13	18.49	18.98	19.34	20.40	14.39	14.75	15.24	15.60	16.66

END OF REPORT