

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926184

Luminaire Tested: DFN2DIP-TR3F0-030D030US950-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926184  
REPORT IS A COMBINATION OF REPORTS P900271 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-030D030US950-FLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5366.2 lumens  
Efficiency: N/A  
Efficacy: 114.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 46.7  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926184  
CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFL

### Luminous Intensity Polar Plot





TEST NUMBER: P926184  
 CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59	53			
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50	45			
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	37			
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36	32			
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31	27			
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27	24			
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24	21			
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21	18			
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19	16			
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17	15			
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15	13			

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1388	1388	1388
5°	1389	1367	1377
10°	1377	1348	1357
15°	1356	1324	1327
20°	1328	1292	1296
25°	1300	1254	1261
30°	1265	1219	1216
35°	1232	1177	1169
40°	1191	1135	1124
45°	1151	1093	1078
50°	1106	1048	1024
55°	1060	997	975
60°	1007	936	919
65°	949	873	852
70°	876	796	780
75°	774	703	713
80°	652	585	585
85°	461	385	378

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1151 cd/sqm



TEST NUMBER: P926184

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	104.8	2.0
10°-20°	294.9	5.5
20°-30°	433.4	8.1
30°-40°	503.4	9.4
40°-50°	502.7	9.4
50°-60°	438.4	8.2
60°-70°	324.1	6.0
70°-80°	183.3	3.4
80°-90°	50.9	0.9
90°-100°	56.0	1.0
100°-110°	178.0	3.3
110°-120°	304.6	5.7
120°-130°	400.5	7.5
130°-140°	449.6	8.4
140°-150°	440.9	8.2
150°-160°	369.8	6.9
160°-170°	245.3	4.6
170°-180°	85.7	1.6
0°-30°	833.1	15.5
0°-40°	1336.5	24.9
0°-60°	2277.6	42.4
0°-90°	2836.0	52.8
90°-120°	538.5	10.0
90°-150°	1829.5	34.1
90°-180°	2530.0	47.1
0°-180°	5366.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1114	1114	1114	1114	1114	
5°	1114	1109	1098	1106	1104	106
15°	1060	1054	1040	1044	1039	299
25°	959	951	933	935	933	441
35°	828	817	800	793	788	517
45°	674	666	650	638	634	520
55°	510	503	490	478	472	456
65°	344	337	327	317	312	340
75°	180	178	172	166	168	192
85°	44	43	42	38	38	49
90°	1	10	27	25	26	5
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	



TEST NUMBER: P926184

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1113.6	1113.6	1113.6	1113.6	1113.6
2.5°	1120.1	1114.7	1102.9	1113.6	1111.6
5°	1113.6	1109.4	1097.6	1106.2	1104.1
7.5°	1106.2	1099.8	1087.9	1096.6	1094.4
10°	1094.4	1086.9	1074.1	1082.6	1079.5
12.5°	1078.3	1071.9	1059.1	1064.4	1062.3
15°	1060.1	1053.8	1039.8	1044.1	1038.7
17.5°	1037.6	1031.3	1017.3	1022.6	1017.3
20°	1013.0	1006.6	991.6	994.7	990.5
22.5°	988.4	978.8	964.8	964.8	962.6
25°	959.4	950.9	932.7	934.8	932.7
27.5°	927.3	919.8	905.9	902.8	897.4
30°	895.2	886.6	870.6	867.4	863.1
32.5°	861.0	854.6	837.4	830.9	826.6
35°	827.8	817.1	799.9	793.4	788.1
37.5°	790.3	780.7	763.5	755.9	750.6
40°	751.8	743.2	726.0	716.5	712.2
42.5°	714.3	705.7	688.6	677.8	671.4
45°	673.6	666.1	650.0	638.2	633.9
47.5°	633.9	626.5	609.3	597.5	591.1
50°	592.1	586.8	571.8	556.8	551.5
52.5°	551.5	544.0	530.1	518.3	510.8
55°	509.8	503.3	490.5	477.7	472.3
57.5°	467.9	462.6	448.7	435.8	431.5
60°	426.2	422.0	407.0	395.1	392.0
62.5°	385.5	378.0	367.3	356.6	352.3
65°	343.8	337.3	326.6	317.0	311.7
67.5°	301.0	295.5	285.9	278.5	274.2
70°	261.3	257.0	247.4	239.8	235.6
72.5°	220.7	216.3	210.9	203.5	200.3
75°	179.8	177.8	172.4	166.0	168.2
77.5°	143.5	139.2	137.0	133.8	130.7
80°	107.1	106.0	103.8	100.6	98.5
82.5°	72.8	72.8	71.8	67.4	67.4
85°	43.9	42.8	41.8	38.5	37.5
87.5°	19.3	17.2	15.0	11.8	10.7
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3



TEST NUMBER: P926184

CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2



TEST NUMBER: P926184  
 CATALOG NUMBER: DFN2DIP-TR3F0-030D030US950-FLLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.62	9.50	9.55	10.45	11.68	8.19	9.08	9.12	10.03	11.26
	3H	10.27	11.07	11.21	12.02	13.28	9.80	10.60	10.75	11.56	12.81
	4H	10.85	11.61	11.81	12.57	13.83	10.38	11.14	11.34	12.10	13.36
	6H	11.25	11.94	12.22	12.91	14.18	10.78	11.47	11.75	12.44	13.72
	8H	11.35	12.01	12.32	13.00	14.27	10.88	11.54	11.86	12.53	13.80
	12H	11.39	12.02	12.37	13.00	14.30	10.92	11.55	11.90	12.53	13.83
4H	2H	9.08	9.83	10.04	10.79	12.06	8.74	9.49	9.70	10.45	11.71
	3H	10.94	11.56	11.91	12.56	13.83	10.55	11.18	11.52	12.17	13.44
	4H	11.64	12.22	12.63	13.21	14.51	11.24	11.82	12.23	12.80	14.10
	6H	12.15	12.65	13.15	13.66	14.96	11.75	12.24	12.74	13.25	14.55
	8H	12.30	12.76	13.29	13.76	15.08	11.89	12.35	12.89	13.36	14.67
	12H	12.37	12.78	13.38	13.80	15.12	11.95	12.37	12.97	13.39	14.71
8H	4H	11.84	12.30	12.83	13.30	14.62	11.48	11.94	12.48	12.95	14.26
	6H	12.46	12.84	13.48	13.89	15.20	12.10	12.48	13.12	13.53	14.84
	8H	12.67	13.01	13.70	14.04	15.37	12.31	12.65	13.34	13.68	15.01
	12H	12.80	13.10	13.83	14.12	15.50	12.42	12.72	13.45	13.75	15.12
12H	4H	11.82	12.24	12.84	13.26	14.58	11.48	11.89	12.49	12.91	14.23
	6H	12.49	12.83	13.52	13.86	15.19	12.14	12.48	13.17	13.51	14.84
	8H	12.72	13.02	13.76	14.05	15.42	12.37	12.67	13.40	13.69	15.07