

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915298

Luminaire Tested: DFN2DIP-TR3F0-040D030US927-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915298
REPORT IS A COMBINATION OF REPORTS P900273 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D030US927-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 5240.3 lumens
Efficiency: N/A
Efficacy: 90.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 57.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	100	96	92	88	93	89	86	83	78	75	73	67	66	64	58	56	55
2	91	84	77	72	85	78	73	68	68	64	61	59	56	53	51	48	46
3	83	73	66	60	77	69	62	57	60	55	51	52	48	45	45	42	40
4	76	65	57	51	71	61	54	48	54	48	43	47	42	39	40	37	34
5	70	58	50	44	65	55	47	42	48	42	38	42	37	34	36	33	30
6	64	52	44	38	60	49	42	36	43	37	33	38	33	29	33	29	26
7	60	47	39	33	56	44	37	32	39	33	29	35	30	26	30	26	23
8	55	43	35	30	52	40	33	28	36	30	26	32	27	23	28	24	21
9	52	39	32	26	48	37	30	25	33	27	23	29	24	21	26	22	19
10	48	36	29	24	45	34	27	23	30	25	21	27	22	19	24	20	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1536	1536	1536
5°	1538	1514	1524
10°	1525	1492	1503
15°	1501	1466	1469
20°	1470	1431	1435
25°	1439	1389	1396
30°	1401	1349	1347
35°	1364	1303	1294
40°	1319	1256	1244
45°	1274	1210	1193
50°	1225	1161	1134
55°	1173	1104	1080
60°	1115	1036	1017
65°	1051	966	944
70°	970	881	864
75°	858	778	789
80°	722	647	648
85°	510	427	418

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1274 cd/sqm

TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	116.0	2.2
10°-20°	326.5	6.2
20°-30°	479.8	9.2
30°-40°	557.3	10.6
40°-50°	556.6	10.6
50°-60°	485.3	9.3
60°-70°	358.8	6.8
70°-80°	203.0	3.9
80°-90°	55.7	1.1
90°-100°	46.5	0.9
100°-110°	147.8	2.8
110°-120°	252.9	4.8
120°-130°	332.6	6.3
130°-140°	373.3	7.1
140°-150°	366.1	7.0
150°-160°	307.1	5.9
160°-170°	203.7	3.9
170°-180°	71.2	1.4
0°-30°	922.4	17.6
0°-40°	1479.7	28.2
0°-60°	2521.7	48.1
0°-90°	3139.2	59.9
90°-120°	447.2	8.5
90°-150°	1519.2	29.0
90°-180°	2101.0	40.1
0°-180°	5240.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1233	1233	1233	1233	1233	
5°	1233	1228	1215	1225	1222	117
15°	1174	1167	1151	1156	1150	331
25°	1062	1053	1033	1035	1033	489
35°	916	905	886	878	873	572
45°	746	738	720	707	702	576
55°	564	557	543	529	523	505
65°	381	373	362	351	345	376
75°	199	197	191	184	186	213
85°	49	48	46	43	42	54
90°	1	8	22	21	22	5
95°	33	40	41	41	40	37
105°	136	138	140	141	141	144
115°	254	257	256	256	254	251
125°	369	375	373	371	370	330
135°	477	484	486	485	483	369
145°	580	584	588	588	586	362
155°	663	665	667	670	668	305
165°	721	720	720	725	722	203
175°	750	748	747	752	748	71
180°	752	752	752	752	752	

TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1233.0	1233.0	1233.0	1233.0	1233.0
2.5°	1240.2	1234.2	1221.1	1233.0	1230.7
5°	1233.0	1228.3	1215.2	1224.6	1222.4
7.5°	1224.6	1217.6	1204.5	1214.1	1211.7
10°	1211.7	1203.4	1189.2	1198.6	1195.1
12.5°	1193.8	1186.8	1172.6	1178.5	1176.1
15°	1173.7	1166.6	1151.2	1156.0	1150.1
17.5°	1148.8	1141.8	1126.3	1132.2	1126.3
20°	1121.5	1114.4	1097.9	1101.4	1096.8
22.5°	1094.3	1083.6	1068.2	1068.2	1065.8
25°	1062.2	1052.8	1032.7	1035.0	1032.7
27.5°	1026.7	1018.3	1003.1	999.5	993.6
30°	991.2	981.7	963.9	960.4	955.6
32.5°	953.2	946.2	927.2	920.0	915.2
35°	916.5	904.7	885.7	878.5	872.6
37.5°	875.0	864.3	845.3	837.0	831.1
40°	832.3	822.8	803.7	793.2	788.5
42.5°	790.8	781.2	762.4	750.4	743.4
45°	745.8	737.5	719.6	706.7	701.9
47.5°	701.9	693.6	674.6	661.6	654.5
50°	655.6	649.7	633.1	616.5	610.5
52.5°	610.5	602.3	586.9	573.9	565.5
55°	564.4	557.2	543.0	528.8	522.9
57.5°	518.1	512.2	496.7	482.5	477.8
60°	471.8	467.1	450.6	437.5	434.0
62.5°	426.8	418.5	406.7	394.8	390.1
65°	380.6	373.4	361.6	350.9	345.1
67.5°	333.2	327.2	316.6	308.3	303.6
70°	289.3	284.6	273.9	265.5	260.9
72.5°	244.3	239.5	233.6	225.3	221.7
75°	199.2	196.9	190.8	183.8	186.2
77.5°	158.8	154.1	151.7	148.1	144.7
80°	118.6	117.3	114.9	111.5	109.1
82.5°	80.6	80.6	79.5	74.7	74.7
85°	48.6	47.5	46.3	42.6	41.5
87.5°	21.4	19.0	16.6	13.1	11.8
90°	0.7	8.2	22.2	20.8	21.5
92.5°	14.0	19.0	19.7	20.4	20.4
95°	33.1	39.5	40.6	40.6	39.5
97.5°	55.1	60.9	63.5	63.5	63.5
100°	80.4	85.6	87.5	87.5	86.8
102.5°	107.2	111.1	113.5	114.2	113.5
105°	136.4	138.2	139.6	140.7	140.7
107.5°	165.4	168.1	168.1	168.6	165.4
110°	193.5	197.2	197.2	197.2	195.4

TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	223.9	227.8	227.0	225.2	223.9
115°	253.8	257.4	256.3	255.6	253.8
117.5°	283.4	288.4	285.3	283.4	281.6
120°	313.4	318.4	313.4	313.4	311.3
122.5°	340.6	346.9	343.7	341.9	340.6
125°	369.2	374.8	373.0	370.9	370.3
127.5°	397.0	404.0	401.6	398.8	397.0
130°	423.0	431.2	430.1	428.7	426.2
132.5°	452.3	458.6	459.1	455.9	454.1
135°	477.4	484.4	485.8	485.1	483.3
137.5°	505.5	511.2	512.3	511.9	509.1
140°	530.2	535.9	539.1	539.1	536.5
142.5°	555.6	561.3	563.1	563.8	561.3
145°	579.6	584.2	587.8	588.4	586.0
147.5°	601.2	606.8	609.5	610.7	608.2
150°	623.4	627.2	629.7	631.8	629.7
152.5°	643.1	646.9	650.1	652.6	650.1
155°	662.8	664.6	666.6	669.8	667.8
157.5°	679.8	681.1	682.3	686.8	683.7
160°	695.0	696.3	697.0	700.8	698.1
162.5°	709.0	709.0	709.7	714.0	710.8
165°	721.0	720.3	720.3	724.8	721.7
167.5°	731.9	729.8	729.8	734.4	731.2
170°	740.1	738.2	737.6	742.1	738.2
172.5°	745.7	743.9	743.2	747.7	743.9
175°	750.3	748.5	747.1	751.6	747.7
177.5°	752.7	750.9	749.6	753.4	749.6
180°	751.6	751.6	751.6	751.6	751.6

TEST NUMBER: P915298

CATALOG NUMBER: DFN2DIP-TR3F0-040D030US927-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.58	10.54	10.44	11.42	12.55	9.15	10.11	10.02	11.00	12.12
	3H	11.24	12.10	12.12	12.99	14.14	10.77	11.63	11.65	12.53	13.67
	4H	11.82	12.64	12.72	13.54	14.70	11.35	12.17	12.25	13.07	14.23
	6H	12.22	12.97	13.13	13.88	15.05	11.75	12.50	12.66	13.41	14.58
	8H	12.32	13.04	13.24	13.97	15.14	11.86	12.57	12.77	13.50	14.67
	12H	12.37	13.05	13.29	13.97	15.17	11.90	12.58	12.82	13.50	14.70
4H	2H	10.05	10.86	10.95	11.76	12.92	9.71	10.52	10.61	11.42	12.58
	3H	11.91	12.59	12.82	13.53	14.70	11.52	12.20	12.43	13.14	14.31
	4H	12.62	13.24	13.55	14.17	15.37	12.22	12.84	13.14	13.77	14.97
	6H	13.13	13.67	14.07	14.62	15.82	12.73	13.27	13.67	14.22	15.42
	8H	13.28	13.78	14.22	14.73	15.94	12.88	13.38	13.81	14.32	15.54
	12H	13.36	13.81	14.31	14.77	15.99	12.94	13.39	13.90	14.36	15.58
8H	4H	12.82	13.32	13.76	14.27	15.48	12.47	12.97	13.40	13.91	15.13
	6H	13.45	13.86	14.41	14.85	16.06	13.09	13.50	14.05	14.49	15.70
	8H	13.66	14.03	14.64	15.01	16.24	13.30	13.66	14.27	14.64	15.87
	12H	13.79	14.11	14.77	15.09	16.37	13.41	13.74	14.39	14.71	15.99
12H	4H	12.81	13.26	13.77	14.23	15.45	12.46	12.91	13.42	13.88	15.10
	6H	13.48	13.84	14.45	14.82	16.05	13.13	13.49	14.10	14.47	15.70
	8H	13.72	14.04	14.69	15.01	16.29	13.36	13.69	14.34	14.66	15.94