

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P915309

Luminaire Tested: DFN2DIP-TR3F0-040D050US927-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P915309
REPORT IS A COMBINATION OF REPORTS P901822 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D050US927-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6614.7 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P915309
CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P915309

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48	41	41	41	41
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41	35	35	35	35
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35	30	30	30	30
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30	26	26	26	26
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26	23	23	23	23
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23	20	20	20	20
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21	18	18	18	18
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19	16	16	16	16
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17	14	14	14	14
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15	13	13	13	13
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14	12	12	12	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1632	1632	1632
5°	1634	1605	1615
10°	1617	1572	1562
15°	1593	1519	1479
20°	1563	1446	1379
25°	1532	1364	1282
30°	1491	1281	1159
35°	1450	1191	1051
40°	1409	1099	928
45°	1361	996	816
50°	1311	893	707
55°	1259	783	602
60°	1198	668	495
65°	1129	551	444
70°	1045	442	400
75°	939	387	362
80°	785	320	310
85°	534	207	227

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1361 cd/sqm



TEST NUMBER: P915309

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.7	1.9
10°-20°	336.9	5.1
20°-30°	473.1	7.2
30°-40°	515.7	7.8
40°-50°	473.9	7.2
50°-60°	372.2	5.6
60°-70°	242.3	3.7
70°-80°	124.7	1.9
80°-90°	34.2	0.5
90°-100°	44.1	0.7
100°-110°	164.3	2.5
110°-120°	435.8	6.6
120°-130°	722.8	10.9
130°-140°	767.8	11.6
140°-150°	713.6	10.8
150°-160°	573.7	8.7
160°-170°	369.7	5.6
170°-180°	127.2	1.9
0°-30°	932.7	14.1
0°-40°	1448.4	21.9
0°-60°	2294.6	34.7
0°-90°	2695.7	40.8
90°-120°	644.2	9.7
90°-150°	2848.4	43.1
90°-180°	3919.0	59.2
0°-180°	6614.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1310	1310	1310	1310	1310	
5°	1310	1304	1288	1299	1296	124
15°	1246	1233	1192	1170	1158	351
25°	1131	1093	1014	966	948	520
35°	974	914	810	735	709	610
45°	796	717	593	508	480	615
55°	606	513	385	314	292	541
65°	409	313	206	166	162	405
75°	218	135	95	86	85	231
85°	51	26	22	22	22	58
90°	1	12	19	24	26	6
95°	63	31	38	43	42	74
105°	294	323	59	70	74	314
115°	556	573	597	149	79	548
125°	786	799	817	824	827	701
135°	973	989	997	1007	1005	752
145°	1129	1128	1144	1151	1146	706
155°	1243	1234	1246	1252	1244	573
165°	1310	1304	1307	1314	1307	370
175°	1340	1333	1335	1342	1332	127
180°	1337	1337	1337	1337	1337	



TEST NUMBER: P915309

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1309.6	1309.6	1309.6	1309.6	1309.6
2.5°	1315.6	1309.6	1296.6	1308.5	1306.1
5°	1309.6	1303.7	1288.2	1298.9	1295.5
7.5°	1298.9	1291.9	1275.3	1279.9	1274.1
10°	1284.8	1276.4	1252.8	1249.1	1242.1
12.5°	1267.0	1256.3	1224.2	1217.2	1204.1
15°	1245.6	1232.6	1192.3	1169.8	1158.0
17.5°	1220.8	1201.7	1151.9	1125.9	1106.9
20°	1192.3	1168.5	1109.3	1079.7	1053.6
22.5°	1161.5	1134.2	1065.4	1025.2	1007.5
25°	1130.7	1092.7	1014.5	966.0	948.1
27.5°	1094.0	1053.6	967.1	911.4	884.1
30°	1054.9	1009.7	914.9	854.5	822.5
32.5°	1016.9	962.3	865.2	794.1	764.4
35°	974.3	913.8	809.5	734.8	708.7
37.5°	932.8	867.5	757.3	675.5	645.9
40°	888.9	817.8	702.8	618.7	587.9
42.5°	843.8	768.0	648.3	560.5	531.0
45°	796.5	717.0	592.6	508.4	480.0
47.5°	751.5	667.3	539.3	455.1	429.0
50°	701.6	617.5	487.1	405.3	380.5
52.5°	653.0	564.1	437.4	359.1	336.6
55°	605.6	513.2	385.2	314.1	291.6
57.5°	557.1	462.2	339.0	272.6	253.7
60°	507.2	412.4	290.3	230.0	211.0
62.5°	458.8	363.9	248.8	192.0	182.6
65°	408.9	312.8	206.2	166.0	162.3
67.5°	361.6	265.5	166.0	145.8	142.2
70°	311.7	219.3	137.4	125.6	120.8
72.5°	264.4	176.6	114.9	105.5	103.1
75°	218.0	135.1	94.8	86.5	85.4
77.5°	171.9	95.9	74.7	69.9	67.5
80°	129.1	68.8	56.8	52.2	52.2
82.5°	90.1	46.3	39.1	36.7	36.7
85°	50.9	26.1	22.5	22.5	22.5
87.5°	19.0	9.4	9.4	8.3	8.3
90°	1.0	11.6	19.3	24.2	26.1
92.5°	24.2	20.4	23.2	25.2	26.1
95°	62.8	30.9	37.7	42.6	41.6
97.5°	113.1	33.9	49.3	52.3	53.2
100°	171.3	38.7	55.1	62.8	64.8
102.5°	235.0	233.1	57.1	67.7	70.7
105°	294.1	323.1	59.0	69.6	73.5
107.5°	362.7	386.8	61.0	71.5	75.5
110°	428.6	448.8	169.3	72.6	76.4



TEST NUMBER: P915309

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	490.4	507.8	491.4	74.5	77.4
115°	556.2	572.6	596.8	149.0	79.4
117.5°	613.2	632.6	649.1	510.6	257.3
120°	677.1	691.6	709.0	720.6	590.0
122.5°	731.2	746.7	766.1	771.9	772.9
125°	786.3	799.0	817.4	824.1	827.0
127.5°	836.6	850.2	864.8	874.4	875.4
130°	884.1	899.6	910.1	920.8	920.0
132.5°	932.5	945.1	955.6	964.4	963.5
135°	973.1	988.6	997.2	1007.0	1005.0
137.5°	1015.6	1027.2	1037.0	1046.6	1043.8
140°	1057.2	1065.0	1075.5	1084.3	1079.5
142.5°	1092.1	1098.9	1111.4	1119.1	1114.3
145°	1128.9	1127.8	1144.2	1151.0	1146.2
147.5°	1160.7	1157.8	1174.3	1179.1	1175.3
150°	1191.7	1184.9	1200.4	1206.2	1201.3
152.5°	1217.7	1210.1	1224.6	1230.4	1223.6
155°	1242.9	1234.3	1245.9	1251.6	1244.0
157.5°	1263.2	1255.5	1264.2	1271.1	1263.2
160°	1280.7	1274.9	1280.7	1286.4	1279.7
162.5°	1296.1	1290.4	1295.1	1301.9	1293.2
165°	1309.6	1303.9	1306.8	1313.5	1306.8
167.5°	1320.3	1314.5	1317.5	1324.2	1315.5
170°	1329.0	1323.2	1325.2	1331.9	1323.2
172.5°	1334.8	1329.0	1331.0	1337.8	1329.0
175°	1339.7	1332.8	1334.8	1341.6	1331.9
177.5°	1341.6	1334.8	1335.9	1342.6	1333.9
180°	1336.7	1336.7	1336.7	1336.7	1336.7



TEST NUMBER: P915309
 CATALOG NUMBER: DFN2DIP-TR3F0-040D050US927-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.87	8.63	8.91	9.67	11.07	3.84	4.61	4.88	5.65	7.05
	3H	9.53	10.21	10.58	11.26	12.68	5.02	5.70	6.07	6.75	8.17
	4H	10.13	10.77	11.19	11.83	13.25	5.47	6.11	6.53	7.16	8.59
	6H	10.54	11.13	11.61	12.19	13.63	5.78	6.37	6.85	7.43	8.86
	8H	10.66	11.22	11.74	12.30	13.73	5.86	6.43	6.94	7.50	8.93
	12H	10.72	11.25	11.80	12.32	13.77	5.90	6.44	6.98	7.50	8.96
4H	2H	7.88	8.52	8.94	9.57	11.00	4.43	5.07	5.49	6.12	7.55
	3H	9.69	10.22	10.76	11.30	12.74	5.76	6.30	6.84	7.38	8.82
	4H	10.37	10.86	11.45	11.93	13.39	6.30	6.79	7.38	7.86	9.33
	6H	10.87	11.29	11.96	12.39	13.84	6.71	7.13	7.80	8.23	9.68
	8H	11.04	11.43	12.13	12.52	13.99	6.84	7.23	7.93	8.32	9.79
	12H	11.13	11.48	12.23	12.58	14.06	6.90	7.25	8.00	8.35	9.82
8H	4H	10.33	10.72	11.42	11.81	13.28	6.57	6.97	7.66	8.05	9.52
	6H	10.89	11.21	12.00	12.34	13.80	7.08	7.40	8.19	8.53	10.00
	8H	11.10	11.38	12.21	12.49	13.98	7.27	7.55	8.38	8.66	10.15
	12H	11.22	11.47	12.35	12.58	14.11	7.38	7.63	8.50	8.73	10.26
12H	4H	10.28	10.64	11.39	11.73	13.21	6.57	6.93	7.68	8.03	9.50
	6H	10.86	11.14	11.98	12.25	13.74	7.13	7.41	8.24	8.52	10.01
	8H	11.07	11.32	12.19	12.43	13.95	7.33	7.58	8.45	8.68	10.21