

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926227

Luminaire Tested: DFN2DIP-TR3F0-040D070US950-FLLONL

Issue Date: 11/21/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P926227  
REPORT IS A COMBINATION OF REPORTS P901849 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-040D070US950-FLLONL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -


**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10389.0 lumens  
Efficiency: N/A  
Efficacy: 117.8 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Indirect

Input Watts (W): 88.2  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926227  
CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P926227  
 CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	104	104	104	104	94	94	94	94	76	76	76	59	59	59	44	44	44	36			36
1	95	90	87	83	86	82	79	76	66	64	62	52	50	49	39	38	37	31			31
2	86	79	73	68	78	72	67	62	58	54	51	46	43	41	34	32	31	26			26
3	79	69	62	57	71	63	57	52	51	47	43	40	37	35	30	28	26	22			22
4	72	61	54	48	65	56	49	44	45	41	37	36	32	30	27	25	23	19			19
5	66	55	47	41	59	50	43	38	41	35	32	32	28	26	24	22	20	16			16
6	61	49	41	35	55	45	38	33	37	31	27	29	25	22	22	19	17	14			14
7	56	44	36	31	51	40	33	29	33	28	24	26	23	20	20	17	15	13			13
8	52	40	32	27	47	37	30	25	30	25	21	24	20	18	18	16	14	11			11
9	48	36	29	24	44	33	27	22	28	23	19	22	18	16	17	14	12	10			10
10	45	33	26	21	41	31	24	20	25	20	17	20	17	14	16	13	11	9			9

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	1850	1850	1850
5°	1852	1823	1836
10°	1836	1797	1809
15°	1808	1766	1769
20°	1771	1723	1728
25°	1733	1672	1681
30°	1687	1625	1622
35°	1643	1570	1559
40°	1588	1513	1499
45°	1534	1457	1437
50°	1475	1398	1366
55°	1413	1329	1300
60°	1342	1248	1225
65°	1266	1164	1136
70°	1168	1061	1040
75°	1033	938	950
80°	869	780	781
85°	614	513	504

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1534 cd/sqm



TEST NUMBER: P926227

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	139.8	1.3
10°-20°	393.2	3.8
20°-30°	577.9	5.6
30°-40°	671.2	6.5
40°-50°	670.3	6.5
50°-60°	584.5	5.6
60°-70°	432.1	4.2
70°-80°	244.5	2.4
80°-90°	68.5	0.7
90°-100°	74.3	0.7
100°-110°	277.0	2.7
110°-120°	734.8	7.1
120°-130°	1218.6	11.7
130°-140°	1294.5	12.5
140°-150°	1203.1	11.6
150°-160°	967.2	9.3
160°-170°	623.3	6.0
170°-180°	214.5	2.1
0°-30°	1110.8	10.7
0°-40°	1782.0	17.2
0°-60°	3036.8	29.2
0°-90°	3781.8	36.4
90°-120°	1086.1	10.5
90°-150°	4802.2	46.2
90°-180°	6607.0	63.6
0°-180°	10389.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1485	1485	1485	1485	1485	
5°	1485	1479	1463	1475	1472	141
15°	1413	1405	1386	1392	1385	398
25°	1279	1268	1244	1246	1244	589
35°	1104	1090	1067	1058	1051	689
45°	898	888	867	851	845	693
55°	680	671	654	637	630	608
65°	458	450	436	423	416	453
75°	240	237	230	221	224	256
85°	58	57	56	51	50	65
90°	2	20	32	41	44	10
95°	106	52	64	72	70	125
105°	496	545	100	117	124	530
115°	938	965	1006	251	134	923
125°	1326	1347	1378	1390	1394	1182
135°	1641	1667	1681	1698	1694	1267
145°	1903	1902	1929	1941	1932	1190
155°	2096	2081	2100	2110	2097	966
165°	2208	2198	2203	2215	2203	624
175°	2259	2247	2250	2262	2246	215
180°	2254	2254	2254	2254	2254	



TEST NUMBER: P926227

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1484.8	1484.8	1484.8	1484.8	1484.8
2.5°	1493.5	1486.3	1470.6	1484.8	1482.1
5°	1484.8	1479.2	1463.4	1474.8	1472.1
7.5°	1474.8	1466.3	1450.6	1462.1	1459.2
10°	1459.2	1449.2	1432.1	1443.5	1439.2
12.5°	1437.7	1429.2	1412.1	1419.3	1416.3
15°	1413.4	1405.0	1386.4	1392.1	1385.0
17.5°	1383.5	1375.0	1356.4	1363.5	1356.4
20°	1350.6	1342.1	1322.1	1326.3	1320.8
22.5°	1317.9	1305.0	1286.4	1286.4	1283.5
25°	1279.2	1267.9	1243.6	1246.4	1243.6
27.5°	1236.4	1226.4	1208.0	1203.7	1196.6
30°	1193.6	1182.2	1160.8	1156.5	1150.8
32.5°	1147.9	1139.5	1116.6	1108.0	1102.2
35°	1103.7	1089.5	1066.6	1058.0	1050.8
37.5°	1053.7	1040.8	1017.9	1008.0	1000.8
40°	1002.4	990.8	967.9	955.2	949.5
42.5°	952.4	940.8	918.1	903.7	895.2
45°	898.1	888.2	866.6	851.1	845.2
47.5°	845.2	835.2	812.4	796.7	788.2
50°	789.5	782.4	762.4	742.4	735.2
52.5°	735.2	725.3	706.8	691.1	681.1
55°	679.7	671.0	654.0	636.8	629.7
57.5°	623.9	616.9	598.2	581.1	575.4
60°	568.2	562.6	542.6	526.9	522.6
62.5°	514.0	504.0	489.8	475.5	469.7
65°	458.4	449.7	435.5	422.6	415.6
67.5°	401.3	394.0	381.3	371.3	365.6
70°	348.4	342.7	329.8	319.8	314.2
72.5°	294.2	288.4	281.3	271.3	267.0
75°	239.8	237.1	229.8	221.3	224.2
77.5°	191.3	185.6	182.7	178.4	174.2
80°	142.8	141.3	138.4	134.2	131.4
82.5°	97.1	97.1	95.8	90.0	90.0
85°	58.5	57.1	55.7	51.3	50.0
87.5°	25.8	22.9	20.0	15.7	14.2
90°	1.5	19.6	32.5	40.8	44.0
92.5°	40.8	34.2	39.1	42.5	44.0
95°	105.9	52.1	63.5	71.8	70.1
97.5°	190.7	57.1	83.1	88.1	89.7
100°	288.8	65.3	92.9	105.9	109.2
102.5°	396.2	393.1	96.3	114.1	119.1
105°	495.8	544.7	99.5	117.3	123.9
107.5°	611.5	652.2	102.8	120.7	127.3
110°	722.6	756.6	285.4	122.4	128.8



TEST NUMBER: P926227

CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	826.9	856.1	828.5	125.5	130.5
115°	937.7	965.4	1006.2	251.2	133.8
117.5°	1033.9	1066.5	1094.3	861.0	433.8
120°	1141.6	1166.0	1195.5	1215.0	994.8
122.5°	1232.8	1258.9	1291.7	1301.4	1303.1
125°	1325.8	1347.0	1378.1	1389.5	1394.3
127.5°	1410.6	1433.4	1458.0	1474.3	1475.8
130°	1490.5	1516.7	1534.5	1552.5	1551.0
132.5°	1572.1	1593.4	1611.2	1625.9	1624.4
135°	1640.6	1666.7	1681.3	1697.7	1694.5
137.5°	1712.2	1731.9	1748.3	1764.6	1759.7
140°	1782.4	1795.5	1813.4	1828.1	1819.9
142.5°	1841.2	1852.7	1873.8	1886.7	1878.6
145°	1903.2	1901.5	1929.2	1940.6	1932.5
147.5°	1956.8	1952.1	1979.7	1987.8	1981.5
150°	2009.1	1997.8	2023.9	2033.5	2025.4
152.5°	2053.1	2040.1	2064.6	2074.4	2063.0
155°	2095.6	2081.0	2100.5	2110.2	2097.3
157.5°	2129.8	2116.8	2131.5	2143.0	2129.8
160°	2159.3	2149.4	2159.3	2168.9	2157.5
162.5°	2185.2	2175.5	2183.6	2195.1	2180.4
165°	2208.0	2198.4	2203.2	2214.6	2203.2
167.5°	2226.1	2216.1	2221.2	2232.6	2218.0
170°	2240.8	2230.9	2234.2	2245.6	2230.9
172.5°	2250.5	2240.8	2244.1	2255.4	2240.8
175°	2258.6	2247.1	2250.5	2261.8	2245.6
177.5°	2261.8	2250.5	2252.2	2263.7	2248.9
180°	2253.7	2253.7	2253.7	2253.7	2253.7



TEST NUMBER: P926227  
 CATALOG NUMBER: DFN2DIP-TR3F0-040D070US950-FLLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.95	8.70	9.02	9.77	11.22	7.52	8.27	8.59	9.34	10.80
	3H	9.59	10.27	10.67	11.34	12.82	9.13	9.80	10.20	10.88	12.35
	4H	10.17	10.81	11.26	11.89	13.36	9.70	10.34	10.79	11.42	12.90
	6H	10.56	11.15	11.65	12.23	13.72	10.09	10.68	11.18	11.76	13.25
	8H	10.66	11.21	11.75	12.31	13.80	10.19	10.75	11.29	11.84	13.33
	12H	10.70	11.23	11.80	12.32	13.83	10.22	10.75	11.33	11.85	13.35
4H	2H	8.40	9.03	9.49	10.11	11.59	8.05	8.69	9.15	9.77	11.25
	3H	10.24	10.77	11.34	11.88	13.37	9.85	10.38	10.95	11.49	12.98
	4H	10.94	11.43	12.05	12.53	14.04	10.54	11.03	11.65	12.13	13.64
	6H	11.44	11.86	12.56	12.98	14.49	11.04	11.46	12.15	12.58	14.08
	8H	11.59	11.98	12.70	13.09	14.61	11.18	11.57	12.29	12.68	14.20
	12H	11.65	12.00	12.78	13.13	14.65	11.23	11.59	12.36	12.71	14.24
8H	4H	11.13	11.52	12.24	12.63	14.15	10.77	11.16	11.88	12.27	13.79
	6H	11.74	12.07	12.88	13.22	14.74	11.38	11.71	12.52	12.86	14.38
	8H	11.96	12.24	13.10	13.37	14.91	11.59	11.88	12.73	13.01	14.55
	12H	12.08	12.33	13.22	13.45	15.03	11.70	11.95	12.84	13.08	14.65
12H	4H	11.11	11.46	12.24	12.58	14.11	10.76	11.11	11.89	12.24	13.76
	6H	11.77	12.05	12.91	13.19	14.72	11.42	11.71	12.56	12.84	14.38
	8H	12.00	12.25	13.14	13.38	14.95	11.65	11.90	12.79	13.03	14.60