

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918025

Luminaire Tested: DFN2DIP-TR3F0-030D090US930-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918025
REPORT IS A COMBINATION OF REPORTS P900356 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-030D090US930-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 8572.8 lumens
Efficiency: N/A
Efficacy: 90.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 94.9
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918025
CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P918025
 CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	101	101	101	101	90	90	90	90	69	69	69	50	50	50	33	33	33	24				24
1	92	88	85	81	82	79	76	73	61	59	57	44	43	42	29	28	28	21				21
2	84	77	71	67	75	69	64	60	53	50	47	39	37	35	26	25	24	18				18
3	77	68	61	56	68	61	55	50	47	43	40	35	32	30	23	22	20	15				15
4	70	60	53	47	62	54	48	43	42	38	34	31	28	26	21	19	18	13				13
5	64	54	46	40	57	48	42	37	38	33	29	28	25	22	19	17	16	12				12
6	59	48	40	35	53	43	37	32	34	29	26	25	22	20	17	15	14	11				11
7	55	43	36	30	49	39	32	28	31	26	23	23	20	17	16	14	12	9				9
8	51	39	32	27	45	35	29	24	28	23	20	21	18	16	14	12	11	8				8
9	47	36	29	24	42	32	26	22	25	21	18	19	16	14	13	11	10	8				8
10	44	33	26	21	39	29	23	19	23	19	16	18	15	13	12	10	9	7				7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1260	1260	1260
5°	1261	1239	1247
10°	1248	1213	1205
15°	1230	1172	1142
20°	1206	1116	1064
25°	1183	1053	989
30°	1151	989	895
35°	1119	919	811
40°	1087	848	716
45°	1050	769	630
50°	1012	689	546
55°	972	604	465
60°	925	515	382
65°	871	425	343
70°	806	341	309
75°	725	299	279
80°	607	247	240
85°	413	160	175

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 2263 cd/sqm



TEST NUMBER: P918025

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	94.7	1.1
10°-20°	260.1	3.0
20°-30°	365.1	4.3
30°-40°	398.0	4.6
40°-50°	365.8	4.3
50°-60°	287.3	3.4
60°-70°	187.0	2.2
70°-80°	96.3	1.1
80°-90°	31.2	0.4
90°-100°	143.6	1.7
100°-110°	456.3	5.3
110°-120°	780.8	9.1
120°-130°	1026.9	12.0
130°-140°	1152.6	13.4
140°-150°	1130.3	13.2
150°-160°	948.2	11.1
160°-170°	628.8	7.3
170°-180°	219.8	2.6
0°-30°	720.0	8.4
0°-40°	1118.0	13.0
0°-60°	1771.2	20.7
0°-90°	2085.6	24.3
90°-120°	1380.7	16.1
90°-150°	4690.5	54.7
90°-180°	6487.0	75.7
0°-180°	8572.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1011	1011	1011	1011	1011	
5°	1011	1006	994	1003	1000	96
15°	962	951	920	903	894	271
25°	873	843	783	746	732	401
35°	752	705	625	567	547	471
45°	615	553	458	392	370	475
55°	467	396	297	242	225	418
65°	316	242	159	128	125	313
75°	168	104	73	67	66	178
85°	39	20	17	17	17	45
90°	2	25	69	64	66	9
95°	102	122	125	125	122	114
105°	421	427	431	434	434	444
115°	784	795	791	789	784	775
125°	1140	1157	1152	1145	1143	1018
135°	1474	1496	1500	1498	1492	1139
145°	1790	1804	1815	1817	1809	1118
155°	2046	2052	2058	2068	2062	942
165°	2226	2224	2224	2238	2228	628
175°	2316	2311	2307	2321	2309	220
180°	2321	2321	2321	2321	2321	



TEST NUMBER: P918025

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1010.9	1010.9	1010.9	1010.9	1010.9
2.5°	1015.5	1010.9	1000.8	1010.0	1008.2
5°	1010.9	1006.3	994.4	1002.7	999.9
7.5°	1002.7	997.2	984.4	988.0	983.4
10°	991.6	985.3	967.0	964.2	958.8
12.5°	978.0	969.7	945.0	939.5	929.4
15°	961.5	951.4	920.3	902.9	893.8
17.5°	942.2	927.6	889.2	869.1	854.4
20°	920.3	902.0	856.2	833.5	813.3
22.5°	896.6	875.5	822.4	791.3	777.6
25°	872.8	843.4	783.1	745.6	731.8
27.5°	844.4	813.3	746.5	703.5	682.4
30°	814.2	779.4	706.2	659.7	634.9
32.5°	784.9	742.8	667.9	612.9	590.0
35°	752.0	705.3	624.8	567.2	547.1
37.5°	720.0	669.6	584.6	521.4	498.6
40°	686.2	631.3	542.5	477.5	453.8
42.5°	651.3	592.9	500.4	432.7	409.9
45°	614.8	553.4	457.5	392.4	370.5
47.5°	580.0	515.1	416.3	351.2	331.2
50°	541.6	476.6	376.0	312.8	293.7
52.5°	504.0	435.5	337.6	277.2	259.8
55°	467.4	396.1	297.3	242.5	225.1
57.5°	430.0	356.8	261.7	210.4	195.8
60°	391.5	318.4	224.1	177.5	162.9
62.5°	354.1	280.9	192.1	148.2	141.0
65°	315.6	241.5	159.1	128.1	125.3
67.5°	279.1	204.9	128.1	112.5	109.7
70°	240.6	169.3	106.1	96.9	93.3
72.5°	204.0	136.2	88.7	81.4	79.6
75°	168.3	104.3	73.2	66.8	65.9
77.5°	132.6	74.0	57.6	54.0	52.1
80°	99.7	53.1	43.9	40.3	40.3
82.5°	69.5	35.7	30.2	28.4	28.4
85°	39.3	20.1	17.4	17.4	17.4
87.5°	14.7	7.3	7.3	6.4	6.4
90°	2.1	25.2	68.6	64.3	66.4
92.5°	43.4	58.8	60.9	62.9	62.9
95°	102.2	121.7	125.2	125.2	121.7
97.5°	170.0	188.2	195.9	195.9	195.9
100°	248.3	264.5	270.0	270.0	268.0
102.5°	330.9	342.8	350.5	352.6	350.5
105°	421.2	426.7	431.0	434.5	434.5
107.5°	510.7	519.1	519.1	520.5	510.7
110°	597.5	608.7	608.7	608.7	603.1



TEST NUMBER: P918025

CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	691.2	703.1	701.0	695.4	691.2
115°	783.6	794.8	791.2	789.2	783.6
117.5°	875.2	890.6	880.8	875.2	869.6
120°	967.6	982.9	967.6	967.6	961.2
122.5°	1051.5	1071.1	1061.4	1055.7	1051.5
125°	1139.7	1157.2	1151.6	1145.2	1143.2
127.5°	1225.7	1247.4	1239.7	1231.3	1225.7
130°	1306.2	1331.4	1327.9	1323.6	1316.0
132.5°	1396.4	1416.0	1417.4	1407.6	1402.1
135°	1474.1	1495.7	1500.0	1497.9	1492.3
137.5°	1560.8	1578.3	1581.8	1580.5	1572.1
140°	1637.1	1654.6	1664.3	1664.3	1656.7
142.5°	1715.5	1732.9	1738.5	1740.7	1732.9
145°	1789.7	1803.6	1814.8	1816.9	1809.2
147.5°	1856.1	1873.6	1882.0	1885.5	1877.8
150°	1924.7	1936.6	1944.2	1950.5	1944.2
152.5°	1985.5	1997.4	2007.2	2014.9	2007.2
155°	2046.4	2051.9	2058.3	2068.1	2061.8
157.5°	2098.8	2103.1	2106.6	2120.5	2110.7
160°	2145.7	2149.9	2152.1	2163.9	2155.5
162.5°	2189.1	2189.1	2191.2	2204.5	2194.7
165°	2226.2	2224.1	2224.1	2238.1	2228.3
167.5°	2259.8	2253.5	2253.5	2267.4	2257.6
170°	2285.0	2279.3	2277.3	2291.2	2279.3
172.5°	2302.4	2296.9	2294.7	2308.8	2296.9
175°	2316.4	2310.8	2306.6	2320.7	2308.8
177.5°	2324.1	2318.5	2314.3	2326.2	2314.3
180°	2320.7	2320.7	2320.7	2320.7	2320.7



TEST NUMBER: P918025
 CATALOG NUMBER: DFN2DIP-TR3F0-030D090US930-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	4.81	5.47	5.97	6.61	8.21	0.79	1.45	1.94	2.58	4.18
	3H	6.47	7.05	7.63	8.20	9.81	1.96	2.55	3.12	3.69	5.31
	4H	7.06	7.62	8.23	8.77	10.38	2.40	2.95	3.57	4.10	5.72
	6H	7.47	7.98	8.64	9.13	10.76	2.70	3.22	3.88	4.37	5.99
	8H	7.58	8.07	8.76	9.24	10.86	2.79	3.28	3.97	4.44	6.06
	12H	7.64	8.10	8.82	9.26	10.90	2.82	3.29	4.01	4.44	6.09
4H	2H	4.81	5.37	5.99	6.51	8.13	1.36	1.91	2.53	3.06	4.68
	3H	6.61	7.08	7.79	8.25	9.88	2.68	3.15	3.87	4.32	5.95
	4H	7.29	7.72	8.47	8.88	10.53	3.22	3.65	4.40	4.81	6.46
	6H	7.78	8.15	8.97	9.33	10.97	3.62	3.99	4.81	5.17	6.81
	8H	7.95	8.29	9.14	9.47	11.12	3.75	4.09	4.93	5.26	6.92
	12H	8.03	8.34	9.24	9.53	11.19	3.80	4.11	5.00	5.30	6.96
8H	4H	7.24	7.58	8.43	8.76	10.41	3.48	3.82	4.67	5.00	6.65
	6H	7.79	8.07	9.00	9.29	10.94	3.99	4.27	5.19	5.49	7.14
	8H	8.00	8.25	9.21	9.44	11.11	4.17	4.42	5.38	5.61	7.28
	12H	8.13	8.34	9.34	9.53	11.23	4.28	4.50	5.49	5.69	7.39
12H	4H	7.19	7.50	8.39	8.68	10.34	3.48	3.79	4.68	4.97	6.63
	6H	7.77	8.01	8.98	9.20	10.88	4.03	4.28	5.24	5.47	7.14
	8H	7.97	8.19	9.19	9.38	11.08	4.23	4.45	5.45	5.64	7.34