

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926315

Luminaire Tested: DFN2DIP-TR3F0-080D030US950-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926315
REPORT IS A COMBINATION OF REPORTS P901801 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D030US950-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10389.1 lumens
Efficiency: N/A
Efficacy: 100.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77
1	103	98	94	91	97	94	90	87	84	82	79	76	74	72	68	67	65
2	94	86	80	74	89	82	76	71	74	69	66	67	63	60	60	57	55
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35
6	67	54	45	39	63	52	44	38	47	41	36	43	37	33	39	35	31
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28
8	57	44	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3700	3700	3700
5°	3704	3646	3671
10°	3672	3594	3619
15°	3616	3531	3539
20°	3541	3446	3457
25°	3467	3345	3363
30°	3374	3250	3243
35°	3285	3139	3117
40°	3177	3027	2997
45°	3068	2914	2874
50°	2950	2795	2732
55°	2826	2658	2600
60°	2685	2496	2450
65°	2531	2327	2272
70°	2336	2122	2080
75°	2065	1875	1900
80°	1738	1560	1561
85°	1228	1028	1008

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3068 cd/sqm

TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	279.5	2.7
10°-20°	786.4	7.6
20°-30°	1155.7	11.1
30°-40°	1342.3	12.9
40°-50°	1340.6	12.9
50°-60°	1169.0	11.3
60°-70°	864.1	8.3
70°-80°	488.9	4.7
80°-90°	130.7	1.3
90°-100°	31.9	0.3
100°-110°	118.7	1.1
110°-120°	314.9	3.0
120°-130°	522.3	5.0
130°-140°	554.8	5.3
140°-150°	515.6	5.0
150°-160°	414.5	4.0
160°-170°	267.1	2.6
170°-180°	91.9	0.9
0°-30°	2221.6	21.4
0°-40°	3563.9	34.3
0°-60°	6073.6	58.5
0°-90°	7557.4	72.7
90°-120°	465.5	4.5
90°-150°	2058.1	19.8
90°-180°	2832.0	27.3
0°-180°	10389.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2970	2970	2970	2970	2970	
5°	2970	2958	2927	2950	2944	282
15°	2827	2810	2773	2784	2770	796
25°	2558	2536	2487	2493	2487	1177
35°	2207	2179	2133	2116	2102	1378
45°	1796	1776	1733	1702	1691	1386
55°	1359	1342	1308	1274	1259	1215
65°	917	900	871	845	831	906
75°	480	474	460	443	448	512
85°	117	114	112	103	100	130
90°	1	8	14	18	19	10
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	

TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2969.6	2969.6	2969.6	2969.6	2969.6
2.5°	2986.9	2972.7	2941.2	2969.6	2964.2
5°	2969.6	2958.4	2927.0	2949.7	2944.2
7.5°	2949.7	2932.7	2901.2	2924.2	2918.5
10°	2918.5	2898.4	2864.2	2886.9	2878.5
12.5°	2875.5	2858.5	2824.2	2838.4	2832.7
15°	2827.0	2810.0	2772.7	2784.2	2770.0
17.5°	2767.0	2750.0	2712.7	2727.0	2712.7
20°	2701.3	2684.3	2644.3	2652.8	2641.5
22.5°	2635.8	2610.0	2572.7	2572.7	2567.0
25°	2558.5	2535.8	2487.4	2492.8	2487.4
27.5°	2472.8	2452.8	2415.8	2407.3	2393.1
30°	2387.4	2364.3	2321.7	2313.2	2301.6
32.5°	2295.9	2278.9	2233.1	2215.9	2204.4
35°	2207.4	2178.9	2133.1	2115.9	2101.7
37.5°	2107.4	2081.6	2035.9	2015.9	2001.7
40°	2004.7	1981.6	1936.0	1910.5	1898.9
42.5°	1904.8	1881.7	1836.3	1807.4	1790.6
45°	1796.3	1776.3	1733.2	1702.0	1690.6
47.5°	1690.6	1670.5	1624.8	1593.3	1576.3
50°	1579.1	1564.8	1524.8	1484.8	1470.6
52.5°	1470.6	1450.6	1413.6	1382.2	1362.1
55°	1359.4	1342.1	1307.9	1273.7	1259.4
57.5°	1247.9	1233.7	1196.4	1162.2	1150.6
60°	1136.4	1125.2	1085.2	1053.7	1045.2
62.5°	1027.9	1008.0	979.5	951.0	939.5
65°	916.8	899.5	871.0	845.2	831.0
67.5°	802.5	788.0	762.5	742.6	731.1
70°	696.8	685.3	659.6	639.6	628.3
72.5°	588.3	576.9	562.6	542.6	534.1
75°	479.6	474.1	459.6	442.7	448.4
77.5°	382.6	371.1	365.4	356.9	348.4
80°	285.7	282.7	276.9	268.5	262.6
82.5°	194.2	194.2	191.5	179.9	179.9
85°	117.0	114.2	111.5	102.7	100.0
87.5°	51.5	45.8	40.0	31.5	28.5
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2

TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9

TEST NUMBER: P926315

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.64	14.75	14.38	15.51	16.41	13.22	14.33	13.95	15.08	15.99
	3H	15.31	16.31	16.06	17.08	18.01	14.84	15.84	15.59	16.61	17.54
	4H	15.91	16.85	16.67	17.62	18.57	15.44	16.38	16.20	17.15	18.10
	6H	16.31	17.18	17.09	17.96	18.93	15.84	16.71	16.62	17.49	18.46
	8H	16.42	17.25	17.21	18.05	19.01	15.95	16.78	16.74	17.58	18.55
	12H	16.47	17.26	17.27	18.06	19.05	16.00	16.79	16.79	17.59	18.58
4H	2H	14.13	15.07	14.90	15.85	16.80	13.79	14.73	14.56	15.51	16.45
	3H	16.01	16.80	16.79	17.61	18.57	15.62	16.41	16.40	17.22	18.18
	4H	16.73	17.44	17.52	18.25	19.24	16.32	17.04	17.12	17.85	18.84
	6H	17.25	17.87	18.06	18.70	19.70	16.84	17.46	17.66	18.30	19.29
	8H	17.40	17.98	18.21	18.81	19.82	16.99	17.57	17.81	18.40	19.41
	12H	17.48	18.00	18.32	18.85	19.87	17.06	17.58	17.90	18.43	19.45
8H	4H	16.94	17.52	17.76	18.35	19.36	16.58	17.16	17.40	17.99	19.00
	6H	17.57	18.05	18.41	18.92	19.93	17.21	17.69	18.06	18.56	19.57
	8H	17.79	18.21	18.64	19.08	20.11	17.42	17.85	18.28	18.72	19.75
	12H	17.92	18.30	18.78	19.16	20.24	17.54	17.92	18.40	18.78	19.86
12H	4H	16.93	17.46	17.77	18.31	19.32	16.59	17.11	17.42	17.96	18.98
	6H	17.60	18.03	18.46	18.89	19.92	17.25	17.68	18.11	18.55	19.58
	8H	17.85	18.22	18.71	19.08	20.17	17.49	17.87	18.35	18.73	19.81