

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918030

Luminaire Tested: DFN2DIP-TR3F0-040D040US930-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918030
REPORT IS A COMBINATION OF REPORTS P900287 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D040US930-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 6114.7 lumens
Efficiency: N/A
Efficacy: 94.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 64.5
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	71	71	71	59	59	59
1	98	94	90	87	91	87	84	81	74	72	70	63	61	59	52	51	50
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42
3	82	72	65	59	75	67	61	55	58	53	49	49	45	42	41	38	36
4	75	64	56	50	69	60	52	47	51	46	41	43	39	36	36	33	31
5	69	57	49	43	63	53	46	40	46	40	36	39	35	31	33	29	27
6	63	51	43	37	58	48	40	35	41	36	31	35	31	27	30	26	24
7	59	46	38	33	54	43	36	31	37	32	28	32	28	24	27	24	21
8	54	42	34	29	50	39	32	27	34	29	24	29	25	22	25	21	19
9	51	38	31	26	47	36	29	24	31	26	22	27	23	19	23	20	17
10	47	35	28	23	44	33	26	22	29	23	20	25	21	18	21	18	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1581	1581	1581
5°	1583	1558	1569
10°	1569	1536	1546
15°	1545	1509	1512
20°	1513	1472	1477
25°	1481	1429	1437
30°	1441	1389	1386
35°	1404	1341	1332
40°	1357	1293	1281
45°	1311	1245	1228
50°	1260	1195	1167
55°	1207	1136	1111
60°	1147	1067	1047
65°	1082	995	971
70°	998	907	889
75°	883	801	812
80°	743	667	667
85°	525	439	431

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 1311 cd/sqm

TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	119.4	2.0
10°-20°	336.0	5.5
20°-30°	493.8	8.1
30°-40°	573.6	9.4
40°-50°	572.9	9.4
50°-60°	499.5	8.2
60°-70°	369.3	6.0
70°-80°	208.9	3.4
80°-90°	58.1	0.9
90°-100°	63.8	1.0
100°-110°	202.8	3.3
110°-120°	347.0	5.7
120°-130°	456.4	7.5
130°-140°	512.3	8.4
140°-150°	502.4	8.2
150°-160°	421.4	6.9
160°-170°	279.5	4.6
170°-180°	97.7	1.6
0°-30°	949.3	15.5
0°-40°	1522.9	24.9
0°-60°	2595.3	42.4
0°-90°	3231.5	52.8
90°-120°	613.6	10.0
90°-150°	2084.7	34.1
90°-180°	2883.0	47.1
0°-180°	6114.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1269	1269	1269	1269	1269	
5°	1269	1264	1251	1260	1258	120
15°	1208	1201	1185	1190	1184	340
25°	1093	1084	1063	1065	1063	503
35°	943	931	912	904	898	589
45°	768	759	741	727	722	592
55°	581	574	559	544	538	519
65°	392	384	372	361	355	387
75°	205	203	196	189	192	219
85°	50	49	48	44	43	56
90°	1	11	30	29	30	6
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	

TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1268.9	1268.9	1268.9	1268.9	1268.9
2.5°	1276.3	1270.2	1256.8	1268.9	1266.6
5°	1268.9	1264.1	1250.7	1260.4	1258.1
7.5°	1260.4	1253.1	1239.7	1249.5	1247.1
10°	1247.1	1238.5	1223.9	1233.6	1230.0
12.5°	1228.7	1221.4	1206.8	1212.9	1210.4
15°	1207.9	1200.7	1184.8	1189.7	1183.6
17.5°	1182.3	1175.1	1159.2	1165.2	1159.2
20°	1154.2	1147.0	1129.9	1133.5	1128.8
22.5°	1126.3	1115.2	1099.3	1099.3	1096.9
25°	1093.2	1083.5	1062.8	1065.2	1062.8
27.5°	1056.6	1048.1	1032.3	1028.7	1022.6
30°	1020.1	1010.3	992.1	988.4	983.5
32.5°	981.0	973.8	954.2	946.9	941.9
35°	943.2	931.1	911.5	904.2	898.1
37.5°	900.5	889.5	869.9	861.4	855.3
40°	856.6	846.8	827.2	816.4	811.5
42.5°	813.9	804.0	784.6	772.3	765.1
45°	767.5	759.0	740.6	727.3	722.4
47.5°	722.4	713.8	694.3	680.9	673.6
50°	674.7	668.6	651.6	634.5	628.4
52.5°	628.4	619.9	604.1	590.6	582.0
55°	580.9	573.5	558.9	544.2	538.2
57.5°	533.2	527.2	511.2	496.6	491.7
60°	485.6	480.8	463.7	450.3	446.6
62.5°	439.3	430.7	418.6	406.3	401.5
65°	391.8	384.3	372.2	361.2	355.1
67.5°	342.9	336.7	325.9	317.3	312.4
70°	297.7	292.9	281.8	273.3	268.5
72.5°	251.4	246.5	240.4	231.9	228.2
75°	205.0	202.6	196.4	189.1	191.6
77.5°	163.5	158.6	156.1	152.5	148.9
80°	122.1	120.7	118.3	114.7	112.3
82.5°	83.0	83.0	81.9	76.9	76.9
85°	50.0	48.8	47.6	43.9	42.7
87.5°	22.0	19.6	17.1	13.5	12.1
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1



TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4

TEST NUMBER: P918030

CATALOG NUMBER: DFN2DIP-TR3F0-040D040US930-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.07	9.96	10.00	10.91	12.14	8.64	9.53	9.57	10.48	11.71
	3H	10.72	11.52	11.67	12.48	13.73	10.26	11.05	11.20	12.01	13.26
	4H	11.31	12.06	12.26	13.02	14.29	10.84	11.59	11.80	12.56	13.82
	6H	11.70	12.39	12.67	13.36	14.64	11.23	11.93	12.20	12.89	14.17
	8H	11.80	12.46	12.78	13.45	14.72	11.33	11.99	12.31	12.98	14.25
	12H	11.85	12.48	12.83	13.46	14.75	11.37	12.00	12.36	12.98	14.28
4H	2H	9.53	10.29	10.50	11.25	12.51	9.19	9.94	10.15	10.91	12.17
	3H	11.39	12.02	12.36	13.01	14.29	11.00	11.63	11.97	12.62	13.90
	4H	12.10	12.67	13.08	13.66	14.96	11.70	12.27	12.68	13.26	14.56
	6H	12.61	13.10	13.60	14.11	15.41	12.20	12.70	13.20	13.71	15.01
	8H	12.75	13.21	13.75	14.22	15.53	12.34	12.81	13.34	13.81	15.12
	12H	12.82	13.24	13.84	14.26	15.58	12.41	12.82	13.42	13.84	15.16
8H	4H	12.29	12.76	13.29	13.76	15.07	11.94	12.40	12.93	13.40	14.71
	6H	12.91	13.30	13.93	14.34	15.65	12.56	12.94	13.58	13.98	15.29
	8H	13.13	13.47	14.16	14.50	15.83	12.76	13.10	13.79	14.13	15.46
	12H	13.25	13.55	14.29	14.58	15.95	12.88	13.17	13.91	14.20	15.57
12H	4H	12.28	12.70	13.29	13.72	15.03	11.93	12.35	12.94	13.37	14.68
	6H	12.94	13.28	13.97	14.31	15.64	12.59	12.93	13.62	13.96	15.29
	8H	13.18	13.48	14.21	14.50	15.88	12.83	13.12	13.86	14.15	15.52