

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926347

Luminaire Tested: DFN2DIP-TR3F0-090D040US950-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926347
REPORT IS A COMBINATION OF REPORTS P901818 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D040US950-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 11076.0 lumens
Efficiency: N/A
Efficacy: 89.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 124.4
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71
1	102	98	94	91	96	92	89	86	82	79	77	72	71	69	64	62	61
2	93	86	80	75	88	81	76	72	73	68	65	64	61	59	57	54	52
3	86	76	69	63	80	72	66	61	65	60	55	57	54	50	51	48	45
4	79	68	60	54	74	65	58	52	58	52	48	52	47	44	46	42	40
5	73	61	53	47	68	58	51	45	52	46	42	47	42	38	42	38	35
6	67	55	47	41	63	52	45	40	47	41	37	43	38	34	38	34	31
7	62	50	42	37	59	48	40	35	43	37	33	39	34	30	35	31	28
8	58	46	38	33	55	44	37	32	40	34	29	36	31	27	32	28	25
9	54	42	35	29	51	40	33	29	37	31	27	33	28	25	30	26	23
10	51	39	32	27	48	37	30	26	34	28	24	31	26	23	28	24	21

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4422	4422	4422
5°	4427	4348	4377
10°	4380	4259	4231
15°	4318	4115	4009
20°	4235	3917	3736
25°	4151	3697	3473
30°	4039	3470	3140
35°	3929	3228	2848
40°	3817	2977	2514
45°	3686	2700	2211
50°	3552	2420	1915
55°	3411	2121	1631
60°	3247	1810	1340
65°	3059	1493	1203
70°	2831	1198	1084
75°	2544	1048	980
80°	2129	868	840
85°	1448	562	615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3686 cd/sqm

TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.6	3.0
10°-20°	913.0	8.2
20°-30°	1281.8	11.6
30°-40°	1397.3	12.6
40°-50°	1284.2	11.6
50°-60°	1008.6	9.1
60°-70°	656.5	5.9
70°-80°	337.9	3.1
80°-90°	88.5	0.8
90°-100°	42.5	0.4
100°-110°	158.3	1.4
110°-120°	419.9	3.8
120°-130°	696.4	6.3
130°-140°	739.7	6.7
140°-150°	687.5	6.2
150°-160°	552.7	5.0
160°-170°	356.1	3.2
170°-180°	122.6	1.1
0°-30°	2527.4	22.8
0°-40°	3924.6	35.4
0°-60°	6217.4	56.1
0°-90°	7300.4	65.9
90°-120°	620.6	5.6
90°-150°	2744.1	24.8
90°-180°	3776.0	34.1
0°-180°	11076.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	1	11	19	23	25	10
95°	60	30	36	41	40	72
105°	283	311	57	67	71	303
115°	536	552	575	144	76	527
125°	758	770	787	794	797	676
135°	938	952	961	970	968	724
145°	1088	1087	1102	1109	1104	680
155°	1198	1189	1200	1206	1198	552
165°	1262	1256	1259	1266	1259	356
175°	1291	1284	1286	1292	1283	123
180°	1288	1288	1288	1288	1288	

TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	0.9	11.2	18.6	23.4	25.1
92.5°	23.4	19.6	22.3	24.2	25.1
95°	60.5	29.8	36.3	41.0	40.1
97.5°	109.0	32.6	47.5	50.4	51.2
100°	164.9	37.3	53.1	60.5	62.4
102.5°	226.4	224.7	55.0	65.2	68.0
105°	283.2	311.3	56.9	67.1	70.8
107.5°	349.5	372.7	58.8	69.0	72.7
110°	412.9	432.4	163.1	69.9	73.6

TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	472.5	489.2	473.4	71.7	74.6
115°	535.8	551.6	575.0	143.5	76.5
117.5°	590.8	609.4	625.3	492.0	247.8
120°	652.3	666.3	683.1	694.3	568.5
122.5°	704.4	719.4	738.1	743.6	744.6
125°	757.6	769.8	787.4	794.0	796.8
127.5°	806.0	819.1	833.1	842.5	843.3
130°	851.7	866.7	876.8	887.1	886.3
132.5°	898.3	910.5	920.7	929.1	928.2
135°	937.5	952.5	960.8	970.1	968.3
137.5°	978.4	989.6	999.0	1008.3	1005.5
140°	1018.5	1026.0	1036.2	1044.6	1040.0
142.5°	1052.2	1058.7	1070.8	1078.1	1073.5
145°	1087.6	1086.6	1102.3	1108.9	1104.3
147.5°	1118.2	1115.4	1131.3	1135.9	1132.3
150°	1148.0	1141.6	1156.5	1162.1	1157.4
152.5°	1173.2	1165.8	1179.7	1185.3	1178.9
155°	1197.5	1189.2	1200.3	1205.9	1198.4
157.5°	1217.0	1209.6	1218.1	1224.6	1217.0
160°	1233.8	1228.2	1233.8	1239.3	1232.9
162.5°	1248.7	1243.2	1247.8	1254.3	1245.9
165°	1261.8	1256.2	1259.0	1265.5	1259.0
167.5°	1272.1	1266.3	1269.3	1275.8	1267.4
170°	1280.5	1274.8	1276.6	1283.2	1274.8
172.5°	1286.0	1280.5	1282.4	1288.9	1280.5
175°	1290.6	1284.1	1286.0	1292.5	1283.2
177.5°	1292.5	1286.0	1286.9	1293.5	1285.1
180°	1287.9	1287.9	1287.9	1287.9	1287.9

TEST NUMBER: P926347

CATALOG NUMBER: DFN2DIP-TR3F0-090D040US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.63	14.61	14.45	15.44	16.47	9.61	10.59	10.42	11.42	12.45
	3H	15.31	16.19	16.14	17.03	18.08	10.80	11.68	11.63	12.52	13.58
	4H	15.92	16.75	16.76	17.59	18.66	11.25	12.08	12.10	12.93	14.00
	6H	16.34	17.10	17.20	17.96	19.04	11.58	12.34	12.44	13.20	14.28
	8H	16.47	17.19	17.33	18.06	19.14	11.67	12.39	12.54	13.27	14.35
	12H	16.53	17.22	17.40	18.09	19.19	11.72	12.41	12.59	13.27	14.38
4H	2H	13.67	14.49	14.51	15.34	16.41	10.22	11.04	11.07	11.89	12.96
	3H	15.50	16.18	16.36	17.07	18.15	11.57	12.26	12.43	13.14	14.22
	4H	16.19	16.81	17.06	17.69	18.80	12.12	12.75	12.99	13.62	14.73
	6H	16.70	17.24	17.59	18.14	19.26	12.54	13.08	13.43	13.98	15.10
	8H	16.88	17.38	17.77	18.28	19.40	12.67	13.17	13.56	14.07	15.20
	12H	16.97	17.42	17.88	18.34	19.47	12.74	13.19	13.65	14.11	15.24
8H	4H	16.17	16.67	17.06	17.57	18.69	12.41	12.91	13.30	13.81	14.93
	6H	16.73	17.14	17.64	18.08	19.21	12.92	13.34	13.84	14.28	15.40
	8H	16.94	17.31	17.87	18.24	19.38	13.11	13.48	14.04	14.41	15.55
	12H	17.08	17.40	18.01	18.32	19.52	13.23	13.55	14.16	14.48	15.67
12H	4H	16.12	16.58	17.03	17.49	18.62	12.42	12.87	13.33	13.79	14.92
	6H	16.70	17.07	17.63	18.00	19.14	12.97	13.34	13.90	14.27	15.41
	8H	16.92	17.25	17.85	18.17	19.36	13.18	13.51	14.11	14.43	15.62

END OF REPORT