

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926350

Luminaire Tested: DFN2DIP-TR3F0-090D050US950-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P926350  
REPORT IS A COMBINATION OF REPORTS P900312 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-090D050US950-RLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 11519.6 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 132  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9951  
Total Harmonic Distortion (THDi): 0.07  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P926350  
CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P926350  
 CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	110	110	110	110	104	104	104	104	91	91	91	79	79	79	68	68	68	63		
1	101	97	93	90	95	91	88	85	81	78	76	71	69	67	61	60	59	55		
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	53	51	47		
3	85	76	69	63	80	72	65	60	64	59	54	56	52	49	49	46	44	40		
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	35		
5	72	61	53	47	68	57	50	45	51	45	41	46	41	37	40	37	34	31		
6	67	55	47	41	62	52	45	39	47	41	36	41	37	33	37	33	30	27		
7	62	50	42	36	58	47	40	35	42	37	32	38	33	30	34	30	27	25		
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	22		
9	54	42	34	29	51	40	33	28	36	30	26	32	28	24	29	25	22	20		
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	18		

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	4422	4422	4422
5°	4427	4348	4377
10°	4380	4259	4231
15°	4318	4115	4009
20°	4235	3917	3736
25°	4151	3697	3473
30°	4039	3470	3140
35°	3929	3228	2848
40°	3817	2977	2514
45°	3686	2700	2211
50°	3552	2420	1915
55°	3411	2121	1631
60°	3247	1810	1340
65°	3059	1493	1203
70°	2831	1198	1084
75°	2544	1048	980
80°	2129	868	840
85°	1448	562	615

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3686 cd/sqm



TEST NUMBER: P926350

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	332.6	2.9
10°-20°	913.0	7.9
20°-30°	1281.8	11.1
30°-40°	1397.3	12.1
40°-50°	1284.2	11.1
50°-60°	1008.6	8.8
60°-70°	656.5	5.7
70°-80°	337.9	2.9
80°-90°	90.6	0.8
90°-100°	93.4	0.8
100°-110°	296.6	2.6
110°-120°	507.6	4.4
120°-130°	667.5	5.8
130°-140°	749.3	6.5
140°-150°	734.8	6.4
150°-160°	616.4	5.4
160°-170°	408.8	3.5
170°-180°	142.9	1.2
0°-30°	2527.4	21.9
0°-40°	3924.6	34.1
0°-60°	6217.4	54.0
0°-90°	7302.4	63.4
90°-120°	897.5	7.8
90°-150°	3049.2	26.5
90°-180°	4217.0	36.6
0°-180°	11519.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	1	16	45	42	43	11
95°	66	79	81	81	79	74
105°	274	277	280	282	282	289
115°	509	517	514	513	509	504
125°	741	752	749	744	743	662
135°	958	972	975	974	970	741
145°	1163	1172	1180	1181	1176	727
155°	1330	1334	1338	1344	1340	612
165°	1447	1446	1446	1455	1449	408
175°	1506	1502	1500	1509	1501	143
180°	1509	1509	1509	1509	1509	



TEST NUMBER: P926350

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.3	16.4	44.6	41.9	43.2
92.5°	28.2	38.2	39.6	40.9	40.9
95°	66.4	79.2	81.4	81.4	79.2
97.5°	110.5	122.3	127.4	127.4	127.4
100°	161.4	171.9	175.5	175.5	174.2
102.5°	215.1	222.9	227.8	229.2	227.8
105°	273.8	277.4	280.2	282.4	282.4
107.5°	332.0	337.4	337.4	338.4	332.0
110°	388.4	395.7	395.7	395.7	392.0



TEST NUMBER: P926350

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	449.3	457.1	455.7	452.1	449.3
115°	509.3	516.7	514.4	513.1	509.3
117.5°	569.0	579.0	572.6	569.0	565.3
120°	629.0	639.0	629.0	629.0	624.9
122.5°	683.5	696.3	689.9	686.3	683.5
125°	740.9	752.2	748.6	744.5	743.2
127.5°	796.8	810.9	805.9	800.4	796.8
130°	849.2	865.5	863.2	860.5	855.5
132.5°	907.8	920.5	921.5	915.1	911.5
135°	958.3	972.3	975.1	973.7	970.1
137.5°	1014.7	1026.0	1028.3	1027.4	1021.9
140°	1064.2	1075.6	1081.9	1081.9	1077.0
142.5°	1115.1	1126.6	1130.2	1131.5	1126.6
145°	1163.4	1172.5	1179.7	1181.1	1176.1
147.5°	1206.6	1218.0	1223.4	1225.7	1220.6
150°	1251.2	1258.9	1263.9	1268.0	1263.9
152.5°	1290.8	1298.5	1304.8	1309.8	1304.8
155°	1330.3	1333.9	1338.0	1344.4	1340.3
157.5°	1364.4	1367.1	1369.4	1378.5	1372.1
160°	1394.8	1397.6	1398.9	1406.7	1401.2
162.5°	1423.1	1423.1	1424.4	1433.1	1426.7
165°	1447.2	1445.8	1445.8	1454.9	1448.6
167.5°	1469.0	1464.9	1464.9	1474.0	1467.6
170°	1485.4	1481.8	1480.4	1489.5	1481.8
172.5°	1496.7	1493.1	1491.8	1500.8	1493.1
175°	1505.9	1502.2	1499.5	1508.6	1500.8
177.5°	1510.8	1507.2	1504.5	1512.2	1504.5
180°	1508.6	1508.6	1508.6	1508.6	1508.6



TEST NUMBER: P926350  
 CATALOG NUMBER: DFN2DIP-TR3F0-090D050US950-RLFL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.43	14.38	14.27	15.24	16.31	9.40	10.36	10.24	11.21	12.28
	3H	15.10	15.96	15.96	16.82	17.92	10.59	11.45	11.45	12.31	13.41
	4H	15.71	16.52	16.58	17.39	18.50	11.05	11.85	11.92	12.72	13.83
	6H	16.13	16.87	17.01	17.75	18.87	11.37	12.11	12.25	12.99	14.11
	8H	16.26	16.96	17.15	17.86	18.98	11.46	12.17	12.35	13.06	14.18
	12H	16.32	16.99	17.21	17.88	19.03	11.51	12.18	12.40	13.07	14.21
4H	2H	13.46	14.26	14.33	15.14	16.24	10.01	10.81	10.88	11.69	12.79
	3H	15.29	15.96	16.17	16.86	17.98	11.36	12.03	12.25	12.94	14.06
	4H	15.98	16.58	16.87	17.49	18.64	11.91	12.52	12.81	13.42	14.57
	6H	16.49	17.01	17.40	17.94	19.09	12.33	12.85	13.24	13.78	14.93
	8H	16.66	17.15	17.58	18.07	19.23	12.46	12.95	13.37	13.87	15.03
	12H	16.76	17.20	17.69	18.14	19.30	12.53	12.97	13.46	13.90	15.07
8H	4H	15.95	16.44	16.87	17.36	18.53	12.19	12.68	13.11	13.60	14.77
	6H	16.51	16.92	17.45	17.88	19.04	12.71	13.11	13.65	14.07	15.24
	8H	16.72	17.08	17.67	18.03	19.22	12.90	13.25	13.85	14.21	15.39
	12H	16.86	17.18	17.81	18.12	19.35	13.02	13.33	13.97	14.28	15.51
12H	4H	15.91	16.35	16.84	17.29	18.46	12.20	12.64	13.14	13.58	14.75
	6H	16.49	16.85	17.44	17.80	18.98	12.76	13.11	13.71	14.07	15.25
	8H	16.71	17.02	17.66	17.97	19.20	12.97	13.28	13.92	14.23	15.46