

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904574

Luminaire Tested: DFN2DIP-TR4F0-040D120US830-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904574
REPORT IS A COMBINATION OF REPORTS P900513 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D120US830-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13742.3 lumens
Efficiency: N/A
Efficacy: 111.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 123.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	52	52	52	35	35	35
1	93	88	85	81	83	79	76	73	62	60	58	46	44	43	31	30	30
2	84	77	71	66	75	69	64	60	54	51	48	40	38	36	27	26	25
3	77	68	61	55	68	61	55	50	48	44	40	35	33	30	24	23	21
4	70	60	52	47	62	54	47	42	42	38	34	32	29	26	22	20	18
5	64	53	45	40	57	48	41	36	38	33	29	28	25	22	19	17	16
6	59	48	40	34	53	43	36	31	34	29	25	25	22	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	22	23	20	17	16	14	12
8	51	39	31	26	45	35	28	24	28	23	20	21	18	15	15	13	11
9	47	35	28	23	42	32	26	21	25	21	17	19	16	14	14	11	10
10	44	32	25	21	39	29	23	19	23	19	16	18	15	12	13	10	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1165	1165	1165
5°	1167	1149	1157
10°	1158	1134	1141
15°	1141	1115	1117
20°	1118	1089	1092
25°	1095	1058	1063
30°	1066	1029	1026
35°	1039	995	987
40°	1006	961	950
45°	972	926	912
50°	936	890	868
55°	898	848	827
60°	855	799	781
65°	808	747	726
70°	748	684	667
75°	665	609	613
80°	565	514	509
85°	409	348	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2790 cd/sqm

TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.0
10°-20°	388.5	2.8
20°-30°	570.9	4.2
30°-40°	663.1	4.8
40°-50°	662.3	4.8
50°-60°	577.5	4.2
60°-70°	426.9	3.1
70°-80°	241.5	1.8
80°-90°	73.9	0.5
90°-100°	221.3	1.6
100°-110°	703.3	5.1
110°-120°	1203.6	8.8
120°-130°	1582.9	11.5
130°-140°	1776.7	12.9
140°-150°	1742.3	12.7
150°-160°	1461.5	10.6
160°-170°	969.3	7.1
170°-180°	338.8	2.5
0°-30°	1097.5	8.0
0°-40°	1760.6	12.8
0°-60°	3000.3	21.8
0°-90°	3742.6	27.2
90°-120°	2128.2	15.5
90°-150°	7230.1	52.6
90°-180°	10000.0	72.8
0°-180°	13742.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	3	39	106	99	102	14
95°	157	188	193	193	188	175
105°	649	658	664	670	670	685
115°	1208	1225	1220	1216	1208	1195
125°	1757	1784	1775	1765	1762	1570
135°	2272	2306	2312	2309	2300	1756
145°	2758	2780	2797	2801	2789	1724
155°	3154	3163	3173	3188	3178	1452
165°	3432	3428	3428	3450	3435	968
175°	3571	3562	3556	3577	3559	339
180°	3577	3577	3577	3577	3577	

TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	3.2	38.8	105.7	99.2	102.5
92.5°	66.8	90.6	93.8	97.1	97.1
95°	157.4	187.7	193.0	193.0	187.7
97.5°	262.0	290.1	302.0	302.0	302.0
100°	382.9	407.6	416.2	416.2	413.0
102.5°	510.1	528.4	540.3	543.6	540.3
105°	649.2	657.8	664.3	669.7	669.7
107.5°	787.2	800.2	800.2	802.3	787.2
110°	921.0	938.2	938.2	938.2	929.6

TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1065.4	1083.8	1080.5	1072.0	1065.4
115°	1207.8	1225.1	1219.6	1216.4	1207.8
117.5°	1349.1	1372.8	1357.7	1349.1	1340.5
120°	1491.5	1515.1	1491.5	1491.5	1481.8
122.5°	1620.9	1651.1	1636.0	1627.3	1620.9
125°	1756.7	1783.7	1775.1	1765.4	1762.1
127.5°	1889.4	1922.8	1910.9	1898.0	1889.4
130°	2013.4	2052.2	2046.8	2040.3	2028.4
132.5°	2152.5	2182.7	2184.8	2169.7	2161.2
135°	2272.2	2305.6	2312.2	2308.9	2300.3
137.5°	2405.9	2432.9	2438.3	2436.1	2423.2
140°	2523.5	2550.4	2565.5	2565.5	2553.6
142.5°	2644.3	2671.3	2679.8	2683.0	2671.3
145°	2758.5	2780.1	2797.4	2800.7	2788.8
147.5°	2861.0	2887.9	2901.0	2906.3	2894.5
150°	2966.7	2985.0	2996.9	3006.6	2996.9
152.5°	3060.5	3078.8	3094.0	3105.9	3094.0
155°	3154.3	3163.0	3172.7	3187.8	3178.1
157.5°	3235.3	3241.7	3247.1	3268.6	3253.6
160°	3307.5	3314.0	3317.2	3335.6	3322.6
162.5°	3374.3	3374.3	3377.6	3398.1	3383.0
165°	3431.5	3428.3	3428.3	3449.8	3434.7
167.5°	3483.3	3473.6	3473.6	3495.1	3480.1
170°	3522.1	3513.4	3510.2	3531.8	3513.4
172.5°	3549.0	3540.4	3537.2	3558.8	3540.4
175°	3570.6	3562.0	3555.6	3577.0	3558.8
177.5°	3582.5	3573.8	3567.3	3585.7	3567.3
180°	3577.0	3577.0	3577.0	3577.0	3577.0

TEST NUMBER: P904574

CATALOG NUMBER: DFN2DIP-TR4F0-040D120US830-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.19	5.88	6.32	7.00	8.56	4.76	5.44	5.89	6.57	8.13
	3H	6.83	7.45	7.97	8.58	10.16	6.36	6.98	7.50	8.11	9.69
	4H	7.41	8.00	8.56	9.13	10.71	6.94	7.53	8.09	8.66	10.24
	6H	7.80	8.34	8.96	9.48	11.07	7.33	7.87	8.49	9.00	10.60
	8H	7.90	8.42	9.06	9.57	11.15	7.43	7.94	8.59	9.09	10.68
	12H	7.95	8.43	9.11	9.58	11.19	7.47	7.95	8.63	9.10	10.71
4H	2H	5.63	6.21	6.78	7.34	8.93	5.28	5.87	6.44	7.00	8.58
	3H	7.48	7.97	8.64	9.12	10.72	7.09	7.57	8.25	8.73	10.33
	4H	8.19	8.63	9.35	9.78	11.40	7.78	8.23	8.94	9.38	10.99
	6H	8.69	9.07	9.86	10.24	11.85	8.28	8.67	9.45	9.83	11.44
	8H	8.84	9.19	10.00	10.35	11.98	8.42	8.78	9.59	9.94	11.57
	12H	8.90	9.23	10.08	10.40	12.02	8.48	8.80	9.66	9.98	11.60
8H	4H	8.37	8.73	9.54	9.89	11.51	8.01	8.37	9.18	9.53	11.15
	6H	8.99	9.29	10.18	10.49	12.11	8.63	8.93	9.82	10.13	11.75
	8H	9.21	9.47	10.40	10.65	12.29	8.84	9.10	10.03	10.28	11.92
	12H	9.33	9.56	10.53	10.74	12.41	8.95	9.18	10.15	10.35	12.03
12H	4H	8.34	8.67	9.53	9.84	11.47	7.99	8.32	9.18	9.49	11.12
	6H	9.02	9.28	10.21	10.46	12.10	8.67	8.93	9.86	10.11	11.75
	8H	9.25	9.48	10.45	10.66	12.33	8.90	9.12	10.09	10.30	11.97

END OF REPORT