

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918108

Luminaire Tested: DFN2DIP-TR3F0-070D040US930-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P918108  
REPORT IS A COMBINATION OF REPORTS P900293 AND P897195  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-070D040US930-FLLFLL  
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8536.2 lumens  
Efficiency: N/A  
Efficacy: 85.6 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 99.7  
Input Voltage (V):  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: 0.9971  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P918108  
CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P918108  
 CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	111	111	111	111	104	104	104	104	92	92	92	81	81	81	71	71	71	66				66
1	101	97	93	89	95	91	88	85	81	78	76	72	70	68	63	61	60	56				56
2	92	85	78	73	87	80	74	70	71	67	63	63	60	57	55	53	51	47				47
3	84	75	67	61	79	70	64	58	63	57	53	56	51	48	49	46	43	40				40
4	77	66	58	52	72	63	55	50	56	50	45	50	45	41	44	40	37	34				34
5	71	59	51	44	67	56	48	43	50	44	39	45	40	36	40	36	32	30				30
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	36	32	29	26				26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	25	23				23
8	56	44	36	30	53	42	34	29	38	31	27	34	29	25	30	26	23	21				21
9	53	40	32	27	49	38	31	26	34	28	24	31	26	22	28	24	21	19				19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	20	26	22	19	17				17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2767	2767	2767
5°	2770	2726	2745
10°	2746	2687	2706
15°	2704	2641	2646
20°	2648	2577	2585
25°	2592	2501	2514
30°	2523	2430	2425
35°	2457	2347	2331
40°	2375	2263	2241
45°	2294	2179	2149
50°	2206	2090	2043
55°	2113	1988	1945
60°	2008	1866	1832
65°	1893	1740	1699
70°	1747	1587	1556
75°	1544	1402	1420
80°	1299	1167	1167
85°	919	769	754

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2294 cd/sqm



TEST NUMBER: P918108

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	209.0	2.4
10°-20°	588.1	6.9
20°-30°	864.2	10.1
30°-40°	1003.7	11.8
40°-50°	1002.5	11.7
50°-60°	874.2	10.2
60°-70°	646.2	7.6
70°-80°	365.6	4.3
80°-90°	99.4	1.2
90°-100°	63.8	0.7
100°-110°	202.8	2.4
110°-120°	347.0	4.1
120°-130°	456.4	5.3
130°-140°	512.3	6.0
140°-150°	502.4	5.9
150°-160°	421.4	4.9
160°-170°	279.5	3.3
170°-180°	97.7	1.1
0°-30°	1661.3	19.5
0°-40°	2665.1	31.2
0°-60°	4541.7	53.2
0°-90°	5653.0	66.2
90°-120°	613.6	7.2
90°-150°	2084.7	24.4
90°-180°	2883.0	33.8
0°-180°	8536.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2221	2221	2221	2221	2221	
5°	2221	2212	2189	2206	2202	211
15°	2114	2101	2073	2082	2071	595
25°	1913	1896	1860	1864	1860	880
35°	1651	1629	1595	1582	1572	1031
45°	1343	1328	1296	1273	1264	1037
55°	1016	1004	978	952	942	909
65°	686	673	651	632	621	678
75°	359	355	344	331	335	383
85°	88	85	83	77	75	98
90°	1	11	30	29	30	8
95°	45	54	56	56	54	51
105°	187	190	192	193	193	198
115°	348	353	352	351	348	344
125°	506	514	512	509	508	453
135°	655	665	667	666	663	506
145°	795	802	807	808	804	497
155°	910	912	915	919	916	419
165°	989	988	988	995	990	279
175°	1030	1027	1025	1031	1026	98
180°	1031	1031	1031	1031	1031	



TEST NUMBER: P918108

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2220.6	2220.6	2220.6	2220.6	2220.6
2.5°	2233.6	2222.9	2199.3	2220.6	2216.6
5°	2220.6	2212.3	2188.7	2205.7	2201.6
7.5°	2205.7	2193.0	2169.4	2186.7	2182.4
10°	2182.4	2167.4	2141.8	2158.8	2152.5
12.5°	2150.2	2137.5	2111.9	2122.5	2118.2
15°	2114.0	2101.3	2073.4	2082.0	2071.3
17.5°	2069.1	2056.4	2028.5	2039.2	2028.5
20°	2019.9	2007.3	1977.3	1983.7	1975.3
22.5°	1971.0	1951.7	1923.9	1923.9	1919.5
25°	1913.3	1896.2	1860.0	1864.1	1860.0
27.5°	1849.1	1834.2	1806.5	1800.2	1789.5
30°	1785.3	1768.0	1736.1	1729.7	1721.1
32.5°	1716.8	1704.1	1669.9	1657.0	1648.4
35°	1650.7	1629.4	1595.1	1582.2	1571.6
37.5°	1575.9	1556.6	1522.4	1507.5	1496.8
40°	1499.1	1481.9	1447.6	1428.6	1420.0
42.5°	1424.3	1407.1	1373.1	1351.6	1338.9
45°	1343.2	1328.3	1296.1	1272.8	1264.1
47.5°	1264.1	1249.2	1215.0	1191.4	1178.8
50°	1180.8	1170.1	1140.2	1110.4	1099.7
52.5°	1099.7	1084.8	1057.1	1033.6	1018.6
55°	1016.5	1003.6	978.0	952.4	941.8
57.5°	933.2	922.5	894.6	869.0	860.5
60°	849.8	841.4	811.5	788.0	781.6
62.5°	768.7	753.7	732.5	711.2	702.5
65°	685.6	672.6	651.3	632.1	621.4
67.5°	600.1	589.3	570.2	555.3	546.7
70°	521.1	512.5	493.2	478.3	469.9
72.5°	439.9	431.4	420.7	405.8	399.4
75°	358.6	354.6	343.6	331.0	335.3
77.5°	286.2	277.5	273.2	266.8	260.6
80°	213.6	211.4	207.1	200.7	196.4
82.5°	145.2	145.2	143.2	134.6	134.6
85°	87.5	85.4	83.4	76.8	74.8
87.5°	38.5	34.2	29.9	23.6	21.3
90°	0.9	11.2	30.5	28.6	29.5
92.5°	19.2	26.1	27.1	28.0	28.0
95°	45.4	54.1	55.7	55.7	54.1
97.5°	75.6	83.6	87.1	87.1	87.1
100°	110.4	117.6	120.0	120.0	119.1
102.5°	147.1	152.4	155.8	156.7	155.8
105°	187.2	189.6	191.5	193.1	193.1
107.5°	227.0	230.7	230.7	231.3	227.0
110°	265.5	270.5	270.5	270.5	268.1



TEST NUMBER: P918108

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	307.2	312.5	311.5	309.1	307.2
115°	348.2	353.3	351.6	350.7	348.2
117.5°	389.0	395.8	391.5	389.0	386.5
120°	430.1	436.8	430.1	430.1	427.2
122.5°	467.3	476.1	471.7	469.2	467.3
125°	506.5	514.3	511.8	509.0	508.1
127.5°	544.8	554.4	551.0	547.2	544.8
130°	580.5	591.7	590.2	588.3	584.9
132.5°	620.6	629.3	630.0	625.6	623.1
135°	655.2	664.8	666.7	665.7	663.2
137.5°	693.7	701.5	703.0	702.4	698.7
140°	727.6	735.4	739.7	739.7	736.3
142.5°	762.5	770.2	772.7	773.6	770.2
145°	795.4	801.6	806.6	807.6	804.1
147.5°	824.9	832.7	836.4	838.0	834.5
150°	855.4	860.7	864.1	866.9	864.1
152.5°	882.5	887.7	892.1	895.5	892.1
155°	909.5	912.0	914.8	919.2	916.3
157.5°	932.9	934.7	936.2	942.5	938.1
160°	953.7	955.5	956.4	961.7	958.0
162.5°	972.9	972.9	973.9	979.7	975.4
165°	989.4	988.5	988.5	994.7	990.3
167.5°	1004.4	1001.5	1001.5	1007.8	1003.4
170°	1015.5	1013.0	1012.1	1018.3	1013.0
172.5°	1023.3	1020.8	1019.9	1026.1	1020.8
175°	1029.6	1027.0	1025.2	1031.4	1026.1
177.5°	1033.0	1030.5	1028.6	1033.9	1028.6
180°	1031.4	1031.4	1031.4	1031.4	1031.4



TEST NUMBER: P918108  
 CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.13	13.16	12.94	13.99	15.01	11.70	12.73	12.51	13.56	14.58
	3H	13.80	14.72	14.61	15.56	16.60	13.33	14.25	14.14	15.09	16.14
	4H	14.38	15.26	15.22	16.10	17.16	13.92	14.79	14.75	15.63	16.69
	6H	14.79	15.59	15.63	16.44	17.51	14.32	15.12	15.16	15.97	17.05
	8H	14.89	15.66	15.75	16.53	17.60	14.42	15.19	15.28	16.06	17.13
	12H	14.94	15.67	15.80	16.54	17.64	14.47	15.20	15.33	16.06	17.16
4H	2H	12.61	13.48	13.45	14.33	15.39	12.27	13.14	13.11	13.98	15.04
	3H	14.48	15.21	15.33	16.09	17.16	14.09	14.82	14.94	15.70	16.77
	4H	15.19	15.86	16.06	16.73	17.83	14.79	15.46	15.66	16.33	17.43
	6H	15.71	16.28	16.59	17.18	18.29	15.31	15.88	16.18	16.78	17.88
	8H	15.86	16.40	16.74	17.29	18.41	15.45	15.99	16.33	16.88	18.00
	12H	15.94	16.42	16.84	17.33	18.45	15.52	16.00	16.42	16.92	18.04
8H	4H	15.40	15.94	16.28	16.83	17.95	15.04	15.58	15.93	16.47	17.59
	6H	16.03	16.47	16.94	17.41	18.52	15.67	16.11	16.58	17.05	18.17
	8H	16.24	16.64	17.16	17.57	18.70	15.88	16.27	16.80	17.20	18.34
	12H	16.38	16.72	17.30	17.64	18.83	16.00	16.35	16.92	17.27	18.45
12H	4H	15.39	15.88	16.29	16.79	17.91	15.04	15.53	15.95	16.44	17.56
	6H	16.06	16.45	16.98	17.38	18.51	15.71	16.10	16.63	17.03	18.17
	8H	16.30	16.65	17.22	17.57	18.75	15.95	16.29	16.87	17.21	18.40