

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918111

Luminaire Tested: DFN2DIP-TR3F0-070D040US930-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918111
REPORT IS A COMBINATION OF REPORTS P901814 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D040US930-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8079.5 lumens
Efficiency: N/A
Efficacy: 81.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 99.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	102	102	102	102	89	89	89	77	77	77	65	65	65
1	101	96	93	89	94	90	87	84	79	77	74	68	67	65	59	57	56
2	92	85	79	74	86	80	74	70	70	66	62	61	58	55	52	50	48
3	84	75	68	62	79	71	64	59	62	57	53	54	51	47	47	44	42
4	78	67	59	53	72	63	56	51	56	50	46	49	45	41	42	39	37
5	71	60	52	46	67	57	49	44	50	44	40	44	40	36	38	35	32
6	66	54	46	40	62	51	44	39	45	40	35	40	35	32	35	32	29
7	61	49	41	36	57	46	39	34	41	36	31	37	32	29	32	29	26
8	57	45	37	32	53	42	35	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	29	25	31	27	23	28	24	21
10	50	38	31	26	47	36	29	25	32	27	23	29	24	21	26	22	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2939	2939	2939
5°	2942	2890	2909
10°	2912	2831	2813
15°	2870	2735	2664
20°	2815	2604	2483
25°	2759	2457	2308
30°	2685	2307	2087
35°	2611	2146	1893
40°	2537	1979	1671
45°	2450	1794	1470
50°	2361	1608	1273
55°	2267	1410	1084
60°	2159	1203	891
65°	2034	992	799
70°	1882	796	720
75°	1691	696	652
80°	1415	577	559
85°	963	373	408

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2450 cd/sqm

TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	221.1	2.7
10°-20°	606.9	7.5
20°-30°	852.0	10.5
30°-40°	928.8	11.5
40°-50°	853.6	10.6
50°-60°	670.4	8.3
60°-70°	436.4	5.4
70°-80°	224.6	2.8
80°-90°	59.3	0.7
90°-100°	36.3	0.4
100°-110°	135.3	1.7
110°-120°	358.8	4.4
120°-130°	595.1	7.4
130°-140°	632.1	7.8
140°-150°	587.5	7.3
150°-160°	472.3	5.8
160°-170°	304.4	3.8
170°-180°	104.8	1.3
0°-30°	1679.9	20.8
0°-40°	2608.7	32.3
0°-60°	4132.7	51.2
0°-90°	4852.9	60.1
90°-120°	530.4	6.6
90°-150°	2345.2	29.0
90°-180°	3227.0	39.9
0°-180°	8079.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2359	2359	2359	2359	2359	
5°	2359	2348	2320	2340	2333	224
15°	2244	2220	2147	2107	2086	632
25°	2036	1968	1827	1740	1708	937
35°	1755	1646	1458	1324	1276	1098
45°	1434	1291	1067	916	864	1108
55°	1091	924	694	566	525	975
65°	736	564	371	299	292	730
75°	393	243	171	156	154	415
85°	92	47	40	40	40	105
90°	1	10	16	20	21	8
95°	52	25	31	35	34	61
105°	242	266	49	57	60	259
115°	458	471	491	123	65	451
125°	647	658	673	679	681	577
135°	801	814	821	829	828	619
145°	929	929	942	948	944	581
155°	1023	1016	1026	1030	1024	472
165°	1078	1074	1076	1082	1076	305
175°	1103	1097	1099	1105	1097	105
180°	1101	1101	1101	1101	1101	



TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2358.7	2358.7	2358.7	2358.7	2358.7
2.5°	2369.3	2358.7	2335.2	2356.7	2352.4
5°	2358.7	2348.1	2320.3	2339.5	2333.1
7.5°	2339.5	2326.8	2296.9	2305.3	2294.7
10°	2313.9	2299.0	2256.3	2249.8	2237.1
12.5°	2281.9	2262.7	2205.0	2192.3	2168.7
15°	2243.5	2219.9	2147.4	2106.9	2085.6
17.5°	2198.6	2164.5	2074.8	2027.8	1993.6
20°	2147.4	2104.6	1998.0	1944.7	1897.6
22.5°	2092.0	2042.8	1918.9	1846.4	1814.5
25°	2036.5	1968.0	1827.2	1739.8	1707.6
27.5°	1970.3	1897.6	1741.8	1641.5	1592.4
30°	1899.9	1818.6	1647.8	1539.1	1481.4
32.5°	1831.5	1733.2	1558.4	1430.2	1376.7
35°	1754.7	1645.8	1458.1	1323.6	1276.4
37.5°	1680.0	1562.4	1364.1	1216.6	1163.4
40°	1600.9	1473.0	1265.8	1114.3	1058.7
42.5°	1519.9	1383.3	1167.7	1009.6	956.4
45°	1434.5	1291.4	1067.4	915.7	864.5
47.5°	1353.4	1201.9	971.3	819.6	772.7
50°	1263.7	1112.2	877.3	729.9	685.3
52.5°	1176.1	1015.9	787.7	646.8	606.3
55°	1090.7	924.2	693.7	565.7	525.2
57.5°	1003.3	832.5	610.6	491.0	456.8
60°	913.6	742.8	522.9	414.3	380.0
62.5°	826.1	655.4	448.2	345.8	328.8
65°	736.5	563.5	371.4	299.0	292.4
67.5°	651.1	478.1	299.0	262.4	256.2
70°	561.4	394.9	247.5	226.2	217.6
72.5°	476.1	318.0	207.0	190.0	185.7
75°	392.7	243.2	170.7	155.8	153.8
77.5°	309.6	172.8	134.5	125.9	121.6
80°	232.6	123.8	102.4	94.0	94.0
82.5°	162.2	83.3	70.4	66.1	66.1
85°	91.7	46.9	40.5	40.5	40.5
87.5°	34.2	17.0	17.0	14.9	14.9
90°	0.7	9.5	15.9	20.0	21.4
92.5°	20.0	16.7	19.1	20.7	21.4
95°	51.7	25.4	31.0	35.1	34.2
97.5°	93.2	27.9	40.6	43.0	43.8
100°	141.0	31.9	45.4	51.7	53.3
102.5°	193.5	192.0	47.0	55.7	58.1
105°	242.1	266.0	48.6	57.3	60.5
107.5°	298.6	318.5	50.2	58.9	62.1
110°	352.9	369.5	139.4	59.8	62.9



TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	403.8	418.1	404.6	61.3	63.8
115°	457.9	471.4	491.4	122.6	65.4
117.5°	504.9	520.8	534.4	420.4	211.8
120°	557.5	569.4	583.8	593.4	485.8
122.5°	602.0	614.8	630.8	635.5	636.3
125°	647.4	657.9	672.9	678.6	680.9
127.5°	688.8	700.0	712.0	720.0	720.7
130°	727.9	740.7	749.3	758.1	757.4
132.5°	767.7	778.1	786.8	794.0	793.3
135°	801.2	814.0	821.1	829.1	827.5
137.5°	836.2	845.7	853.8	861.7	859.3
140°	870.4	876.9	885.6	892.8	888.8
142.5°	899.2	904.7	915.1	921.4	917.5
145°	929.4	928.6	942.1	947.7	943.7
147.5°	955.6	953.2	966.8	970.8	967.7
150°	981.1	975.6	988.4	993.1	989.1
152.5°	1002.7	996.3	1008.2	1013.0	1007.5
155°	1023.4	1016.3	1025.8	1030.5	1024.2
157.5°	1040.1	1033.7	1041.0	1046.5	1040.1
160°	1054.4	1049.6	1054.4	1059.2	1053.6
162.5°	1067.1	1062.4	1066.4	1072.0	1064.8
165°	1078.3	1073.6	1075.9	1081.5	1075.9
167.5°	1087.1	1082.2	1084.8	1090.3	1083.1
170°	1094.3	1089.5	1091.0	1096.7	1089.5
172.5°	1099.0	1094.3	1095.9	1101.5	1094.3
175°	1102.9	1097.4	1099.0	1104.6	1096.7
177.5°	1104.6	1099.0	1099.8	1105.5	1098.3
180°	1100.7	1100.7	1100.7	1100.7	1100.7

TEST NUMBER: P918111

CATALOG NUMBER: DFN2DIP-TR3F0-070D040US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.73	12.65	12.61	13.54	14.66	7.71	8.63	8.58	9.52	10.64
	3H	13.41	14.23	14.29	15.13	16.28	8.90	9.72	9.78	10.62	11.77
	4H	14.01	14.79	14.91	15.69	16.85	9.35	10.13	10.25	11.03	12.19
	6H	14.43	15.15	15.34	16.06	17.23	9.67	10.38	10.58	11.30	12.47
	8H	14.56	15.24	15.48	16.16	17.34	9.76	10.44	10.68	11.37	12.54
	12H	14.62	15.26	15.54	16.19	17.38	9.80	10.45	10.73	11.37	12.57
4H	2H	11.76	12.54	12.67	13.44	14.60	8.31	9.09	9.22	9.99	11.15
	3H	13.59	14.23	14.50	15.17	16.34	9.66	10.31	10.58	11.24	12.42
	4H	14.28	14.86	15.20	15.79	16.99	10.21	10.80	11.14	11.73	12.93
	6H	14.79	15.29	15.73	16.25	17.45	10.63	11.13	11.57	12.09	13.29
	8H	14.96	15.43	15.90	16.38	17.59	10.75	11.23	11.70	12.17	13.39
	12H	15.05	15.48	16.01	16.44	17.66	10.82	11.24	11.78	12.21	13.43
8H	4H	14.25	14.72	15.19	15.67	16.88	10.49	10.96	11.43	11.91	13.12
	6H	14.81	15.20	15.78	16.19	17.40	11.00	11.39	11.97	12.38	13.60
	8H	15.02	15.36	16.00	16.34	17.57	11.19	11.53	12.17	12.51	13.74
	12H	15.15	15.46	16.13	16.43	17.71	11.31	11.61	12.29	12.58	13.86
12H	4H	14.20	14.63	15.17	15.60	16.81	10.50	10.92	11.46	11.89	13.11
	6H	14.78	15.13	15.76	16.11	17.34	11.05	11.39	12.03	12.38	13.61
	8H	15.00	15.30	15.98	16.28	17.56	11.26	11.56	12.24	12.54	13.81

END OF REPORT