

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904645

Luminaire Tested: DFN2DIP-TR4F0-060D110US830-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904645
REPORT IS A COMBINATION OF REPORTS P902020 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-060D110US830-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15071.2 lumens
Efficiency: N/A
Efficacy: 109.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 138.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	103	103	103	103	93	93	93	93	73	73	73	56	56	56	40	40	40
1	94	90	86	83	85	81	78	75	65	63	61	49	48	47	35	35	34
2	86	79	73	68	77	71	66	62	57	54	51	44	42	40	31	30	29
3	78	70	63	57	70	63	57	52	50	46	43	39	36	34	28	26	25
4	72	62	54	48	64	56	49	44	45	40	37	35	32	29	25	23	22
5	66	55	47	42	59	50	43	38	40	35	32	31	28	25	23	21	19
6	61	49	42	36	55	45	38	33	36	31	28	28	25	22	21	19	17
7	56	44	37	32	51	41	34	29	33	28	24	26	22	20	19	17	15
8	52	40	33	28	47	37	30	26	30	25	22	24	20	18	18	15	14
9	48	37	30	25	44	34	27	23	27	23	19	22	18	16	16	14	12
10	45	34	27	22	41	31	25	21	25	21	17	20	17	14	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1857	1857	1857
5°	1860	1827	1839
10°	1841	1792	1779
15°	1816	1732	1687
20°	1783	1651	1573
25°	1748	1559	1463
30°	1702	1465	1324
35°	1657	1364	1202
40°	1611	1260	1062
45°	1558	1144	935
50°	1502	1027	811
55°	1445	902	692
60°	1378	772	569
65°	1301	639	512
70°	1208	515	464
75°	1092	454	422
80°	922	381	365
85°	643	254	275

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1856 cd/sqm

TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.1	1.5
10°-20°	601.3	4.0
20°-30°	844.3	5.6
30°-40°	920.3	6.1
40°-50°	845.9	5.6
50°-60°	664.3	4.4
60°-70°	432.4	2.9
70°-80°	222.6	1.5
80°-90°	63.0	0.4
90°-100°	115.4	0.8
100°-110°	430.1	2.9
110°-120°	1140.7	7.6
120°-130°	1892.0	12.6
130°-140°	2009.7	13.3
140°-150°	1867.8	12.4
150°-160°	1501.7	10.0
160°-170°	967.6	6.4
170°-180°	333.0	2.2
0°-30°	1664.7	11.0
0°-40°	2585.0	17.2
0°-60°	4095.1	27.2
0°-90°	4813.1	31.9
90°-120°	1686.2	11.2
90°-150°	7455.8	49.5
90°-180°	10258.0	68.1
0°-180°	15071.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2337	2337	2337	2337	2337	
5°	2337	2327	2299	2318	2312	222
15°	2223	2200	2128	2088	2067	626
25°	2018	1950	1811	1724	1692	928
35°	1739	1631	1445	1312	1265	1088
45°	1421	1280	1058	907	857	1098
55°	1081	916	687	561	520	966
65°	730	558	368	296	290	724
75°	389	241	169	154	152	412
85°	91	46	40	40	40	104
90°	2	30	50	63	68	14
95°	164	81	99	112	109	195
105°	770	846	155	182	192	822
115°	1456	1499	1562	390	208	1433
125°	2058	2091	2140	2157	2165	1836
135°	2547	2588	2610	2636	2631	1968
145°	2955	2952	2995	3013	3000	1848
155°	3254	3231	3261	3276	3256	1499
165°	3428	3413	3421	3438	3421	969
175°	3506	3489	3494	3512	3486	334
180°	3499	3499	3499	3499	3499	

TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2337.3	2337.3	2337.3	2337.3	2337.3
2.5°	2347.9	2337.3	2313.9	2335.2	2331.0
5°	2337.3	2326.8	2299.1	2318.3	2312.0
7.5°	2318.3	2305.6	2276.1	2284.3	2273.8
10°	2292.8	2278.0	2235.9	2229.4	2216.8
12.5°	2261.3	2242.1	2184.9	2172.4	2149.0
15°	2223.1	2199.7	2127.9	2087.7	2066.6
17.5°	2178.7	2144.8	2055.9	2009.4	1975.6
20°	2127.9	2085.5	1979.8	1927.0	1880.4
22.5°	2072.9	2024.2	1901.5	1829.7	1798.0
25°	2018.0	1950.2	1810.6	1724.0	1692.1
27.5°	1952.5	1880.4	1726.0	1626.5	1577.9
30°	1882.6	1802.0	1632.9	1525.1	1467.9
32.5°	1814.9	1717.5	1544.3	1417.2	1364.2
35°	1738.8	1630.9	1444.8	1311.5	1264.8
37.5°	1664.7	1548.2	1351.7	1205.6	1152.8
40°	1586.4	1459.6	1254.2	1104.1	1049.1
42.5°	1506.1	1370.7	1157.1	1000.4	947.7
45°	1421.4	1279.6	1057.7	907.3	856.6
47.5°	1341.1	1191.0	962.5	812.2	765.7
50°	1252.3	1102.1	869.4	723.3	679.1
52.5°	1165.4	1006.7	780.5	640.9	600.8
55°	1080.8	915.9	687.4	560.6	520.4
57.5°	994.2	824.9	605.0	486.5	452.6
60°	905.3	736.1	518.2	410.5	376.5
62.5°	818.7	649.5	444.1	342.7	325.8
65°	729.8	558.4	368.1	296.2	289.7
67.5°	645.2	473.7	296.2	260.1	253.8
70°	556.3	391.3	245.2	224.2	215.7
72.5°	471.7	315.1	205.1	188.3	184.0
75°	389.2	241.0	169.2	154.4	152.4
77.5°	306.8	171.3	133.3	124.8	120.6
80°	230.5	122.7	101.4	93.1	93.1
82.5°	160.7	82.6	69.7	65.5	65.5
85°	90.9	46.5	40.2	40.2	40.2
87.5°	33.9	16.9	16.9	14.8	14.8
90°	2.5	30.3	50.5	63.4	68.2
92.5°	63.4	53.3	60.7	65.9	68.2
95°	164.5	80.9	98.6	111.5	108.9
97.5°	296.1	88.7	128.9	136.8	139.2
100°	448.3	101.3	144.3	164.5	169.6
102.5°	615.1	610.3	149.4	177.1	184.9
105°	769.7	845.7	154.6	182.2	192.5
107.5°	949.5	1012.6	159.7	187.3	197.6
110°	1121.7	1174.7	443.2	190.0	199.9

TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1283.8	1329.2	1286.2	194.8	202.6
115°	1455.8	1498.7	1562.3	389.9	207.7
117.5°	1605.2	1655.8	1699.0	1336.7	673.4
120°	1772.4	1810.2	1856.0	1886.3	1544.4
122.5°	1914.0	1954.5	2005.4	2020.4	2023.2
125°	2058.3	2091.4	2139.5	2157.2	2164.7
127.5°	2190.0	2225.4	2263.6	2288.9	2291.3
130°	2314.1	2354.8	2382.4	2410.4	2408.0
132.5°	2440.7	2473.8	2501.5	2524.3	2522.0
135°	2547.2	2587.7	2610.3	2635.9	2630.7
137.5°	2658.4	2688.8	2714.3	2739.6	2732.1
140°	2767.3	2787.7	2815.4	2838.2	2825.6
142.5°	2858.6	2876.4	2909.2	2929.3	2916.7
145°	2954.9	2952.1	2995.1	3012.9	3000.3
147.5°	3038.2	3030.7	3073.6	3086.3	3076.4
150°	3119.3	3101.6	3142.2	3157.2	3144.6
152.5°	3187.6	3167.4	3205.3	3220.7	3202.9
155°	3253.5	3230.8	3261.2	3276.3	3256.1
157.5°	3306.6	3286.5	3309.4	3327.1	3306.6
160°	3352.3	3337.0	3352.3	3367.3	3349.6
162.5°	3392.6	3377.6	3390.2	3408.0	3385.1
165°	3428.1	3413.0	3420.6	3438.3	3420.6
167.5°	3456.0	3440.8	3448.6	3466.3	3443.5
170°	3478.9	3463.6	3468.6	3486.5	3463.6
172.5°	3493.9	3478.9	3484.0	3501.7	3478.9
175°	3506.5	3488.8	3493.9	3511.7	3486.5
177.5°	3511.7	3493.9	3496.6	3514.4	3491.6
180°	3499.1	3499.1	3499.1	3499.1	3499.1

TEST NUMBER: P904645

CATALOG NUMBER: DFN2DIP-TR4F0-060D110US830-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	7.32	8.02	8.42	9.12	10.63	3.29	3.99	4.40	5.09	6.60
	3H	8.99	9.61	10.10	10.72	12.25	4.47	5.10	5.58	6.20	7.73
	4H	9.59	10.18	10.71	11.29	12.82	4.92	5.51	6.04	6.62	8.15
	6H	10.00	10.55	11.13	11.66	13.20	5.23	5.78	6.36	6.89	8.43
	8H	10.13	10.65	11.26	11.77	13.31	5.32	5.84	6.45	6.96	8.50
	12H	10.18	10.68	11.32	11.80	13.35	5.36	5.85	6.50	6.97	8.53
4H	2H	7.32	7.92	8.45	9.02	10.55	3.87	4.47	5.00	5.57	7.11
	3H	9.14	9.63	10.27	10.77	12.31	5.21	5.71	6.35	6.84	8.38
	4H	9.83	10.28	10.96	11.40	12.97	5.76	6.21	6.89	7.33	8.90
	6H	10.33	10.72	11.48	11.87	13.42	6.17	6.56	7.31	7.70	9.26
	8H	10.51	10.87	11.65	12.01	13.58	6.30	6.66	7.44	7.79	9.37
	12H	10.60	10.92	11.76	12.07	13.65	6.36	6.68	7.52	7.83	9.41
8H	4H	9.78	10.15	10.93	11.28	12.86	6.03	6.39	7.17	7.52	9.10
	6H	10.35	10.65	11.51	11.82	13.39	6.54	6.84	7.70	8.02	9.59
	8H	10.56	10.82	11.73	11.98	13.57	6.73	6.99	7.90	8.15	9.74
	12H	10.69	10.92	11.87	12.08	13.70	6.85	7.08	8.02	8.23	9.85
12H	4H	9.73	10.06	10.89	11.21	12.78	6.02	6.35	7.18	7.50	9.08
	6H	10.32	10.58	11.49	11.74	13.33	6.59	6.85	7.76	8.01	9.60
	8H	10.54	10.77	11.71	11.92	13.54	6.79	7.02	7.97	8.18	9.80

END OF REPORT