

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P918167

Luminaire Tested: DFN2DIP-TR3F0-090D050US930-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P918167
REPORT IS A COMBINATION OF REPORTS P901832 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D050US930-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10272.8 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 132
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66
1	101	97	93	90	94	91	87	84	79	77	75	69	67	65	59	58	57
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49
3	85	75	68	62	79	71	65	59	62	58	53	55	51	48	47	45	42
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33
6	66	54	46	41	62	51	44	39	46	40	35	40	36	32	35	32	29
7	61	49	41	36	57	47	39	34	42	36	32	37	32	29	33	29	26
8	57	45	37	32	53	43	36	31	38	32	28	34	29	26	30	26	23
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3779	3779	3779
5°	3783	3716	3740
10°	3743	3640	3616
15°	3690	3516	3426
20°	3620	3348	3193
25°	3548	3159	2968
30°	3452	2966	2684
35°	3358	2758	2434
40°	3262	2544	2148
45°	3151	2307	1889
50°	3035	2068	1637
55°	2915	1813	1394
60°	2775	1547	1145
65°	2614	1276	1028
70°	2420	1024	926
75°	2174	896	838
80°	1820	741	718
85°	1238	480	525

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 3151 cd/sqm

TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	284.2	2.8
10°-20°	780.3	7.6
20°-30°	1095.5	10.7
30°-40°	1194.1	11.6
40°-50°	1097.5	10.7
50°-60°	861.9	8.4
60°-70°	561.0	5.5
70°-80°	288.8	2.8
80°-90°	76.1	0.7
90°-100°	45.4	0.4
100°-110°	169.1	1.6
110°-120°	448.5	4.4
120°-130°	743.9	7.2
130°-140°	790.2	7.7
140°-150°	734.4	7.1
150°-160°	590.4	5.7
160°-170°	380.5	3.7
170°-180°	130.9	1.3
0°-30°	2159.9	21.0
0°-40°	3354.0	32.6
0°-60°	5313.5	51.7
0°-90°	6239.5	60.7
90°-120°	663.0	6.5
90°-150°	2931.5	28.5
90°-180°	4033.0	39.3
0°-180°	10272.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3033	3033	3033	3033	3033	
5°	3033	3019	2983	3008	3000	288
15°	2884	2854	2761	2709	2682	813
25°	2618	2530	2349	2237	2196	1204
35°	2256	2116	1875	1702	1641	1412
45°	1844	1660	1372	1177	1111	1424
55°	1402	1188	892	727	675	1253
65°	947	724	478	384	376	939
75°	505	313	220	200	198	534
85°	118	60	52	52	52	135
90°	1	12	20	25	27	10
95°	65	32	39	44	43	77
105°	303	333	61	72	76	323
115°	572	589	614	153	82	564
125°	809	822	841	848	851	722
135°	1002	1018	1026	1036	1034	774
145°	1162	1161	1178	1185	1180	727
155°	1279	1270	1282	1288	1280	589
165°	1348	1342	1345	1352	1345	381
175°	1379	1372	1374	1381	1371	131
180°	1376	1376	1376	1376	1376	

TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3032.7	3032.7	3032.7	3032.7	3032.7
2.5°	3046.4	3032.7	3002.3	3030.1	3024.5
5°	3032.7	3019.0	2983.2	3007.9	2999.7
7.5°	3007.9	2991.6	2953.2	2963.9	2950.2
10°	2975.0	2955.8	2901.1	2892.6	2876.3
12.5°	2933.9	2909.2	2835.0	2818.6	2788.3
15°	2884.4	2854.2	2761.0	2708.8	2681.5
17.5°	2826.8	2782.9	2667.5	2607.2	2563.3
20°	2761.0	2706.0	2568.8	2500.4	2439.8
22.5°	2689.7	2626.5	2467.2	2374.0	2333.0
25°	2618.3	2530.4	2349.3	2236.9	2195.5
27.5°	2533.3	2439.8	2239.5	2110.5	2047.3
30°	2442.7	2338.2	2118.6	1978.9	1904.6
32.5°	2354.7	2228.4	2003.6	1838.8	1770.1
35°	2256.1	2116.0	1874.6	1701.7	1641.1
37.5°	2160.0	2008.9	1753.8	1564.2	1495.8
40°	2058.4	1893.9	1627.4	1432.6	1361.3
42.5°	1954.1	1778.6	1501.3	1298.1	1229.6
45°	1844.4	1660.4	1372.3	1177.2	1111.4
47.5°	1740.1	1545.3	1248.9	1053.8	993.5
50°	1624.8	1430.0	1128.0	938.5	881.1
52.5°	1512.1	1306.3	1012.8	831.6	779.5
55°	1402.3	1188.3	891.9	727.4	675.2
57.5°	1290.0	1070.4	785.1	631.3	587.3
60°	1174.6	955.0	672.4	532.6	488.6
62.5°	1062.3	842.7	576.3	444.7	422.8
65°	946.9	724.5	477.5	384.3	375.9
67.5°	837.1	614.7	384.3	337.5	329.3
70°	721.9	507.8	318.3	290.9	279.8
72.5°	612.0	408.8	266.1	244.3	238.8
75°	504.9	312.7	219.6	200.3	197.7
77.5°	398.0	222.2	172.9	161.9	156.4
80°	299.1	159.3	131.6	120.8	120.8
82.5°	208.5	107.1	90.6	85.0	85.0
85°	117.9	60.3	52.1	52.1	52.1
87.5°	43.9	21.8	21.8	19.2	19.2
90°	1.0	11.9	19.9	24.9	26.8
92.5°	24.9	21.0	23.9	25.9	26.8
95°	64.7	31.8	38.8	43.9	42.8
97.5°	116.4	34.9	50.7	53.8	54.7
100°	176.3	39.9	56.7	64.7	66.7
102.5°	241.9	239.9	58.8	69.6	72.7
105°	302.6	332.6	60.7	71.7	75.7
107.5°	373.3	398.1	62.8	73.6	77.7
110°	441.1	461.9	174.2	74.7	78.6

TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	504.8	522.6	505.7	76.6	79.7
115°	572.4	589.3	614.2	153.4	81.7
117.5°	631.1	651.0	668.1	525.5	264.8
120°	696.8	711.8	729.7	741.7	607.2
122.5°	752.5	768.5	788.5	794.4	795.5
125°	809.3	822.3	841.2	848.2	851.2
127.5°	861.0	875.0	890.1	899.9	900.9
130°	909.9	925.9	936.7	947.7	946.8
132.5°	959.7	972.7	983.5	992.5	991.6
135°	1001.5	1017.5	1026.3	1036.4	1034.4
137.5°	1045.2	1057.2	1067.2	1077.2	1074.2
140°	1088.0	1096.1	1106.9	1115.9	1111.0
142.5°	1124.0	1131.0	1143.9	1151.8	1146.8
145°	1161.8	1160.7	1177.6	1184.6	1179.7
147.5°	1194.6	1191.6	1208.5	1213.5	1209.6
150°	1226.5	1219.5	1235.4	1241.4	1236.4
152.5°	1253.3	1245.4	1260.3	1266.3	1259.3
155°	1279.2	1270.3	1282.2	1288.2	1280.3
157.5°	1300.1	1292.2	1301.1	1308.1	1300.1
160°	1318.1	1312.1	1318.1	1324.0	1317.0
162.5°	1333.9	1328.0	1332.9	1339.9	1331.0
165°	1347.9	1342.0	1344.9	1351.8	1344.9
167.5°	1358.9	1352.8	1355.9	1362.9	1353.9
170°	1367.8	1361.8	1363.8	1370.8	1361.8
172.5°	1373.8	1367.8	1369.9	1376.8	1367.8
175°	1378.8	1371.7	1373.8	1380.7	1370.8
177.5°	1380.7	1373.8	1374.8	1381.8	1372.8
180°	1375.7	1375.7	1375.7	1375.7	1375.7

TEST NUMBER: P918167

CATALOG NUMBER: DFN2DIP-TR3F0-090D050US930-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.66	13.59	13.53	14.47	15.58	8.64	9.56	9.51	10.45	11.56
	3H	14.34	15.17	15.22	16.06	17.20	9.83	10.66	10.71	11.55	12.69
	4H	14.94	15.73	15.84	16.62	17.77	10.28	11.06	11.18	11.96	13.11
	6H	15.36	16.08	16.27	16.99	18.15	10.60	11.32	11.51	12.23	13.39
	8H	15.49	16.17	16.40	17.09	18.25	10.69	11.38	11.61	12.30	13.46
	12H	15.55	16.20	16.47	17.12	18.30	10.74	11.39	11.66	12.30	13.49
4H	2H	12.69	13.47	13.59	14.37	15.52	9.24	10.02	10.14	10.92	12.07
	3H	14.52	15.17	15.43	16.10	17.26	10.59	11.24	11.50	12.17	13.34
	4H	15.21	15.80	16.13	16.72	17.91	11.14	11.73	12.06	12.66	13.85
	6H	15.72	16.23	16.65	17.18	18.37	11.56	12.07	12.49	13.02	14.21
	8H	15.89	16.37	16.83	17.31	18.51	11.69	12.16	12.62	13.10	14.31
	12H	15.98	16.41	16.94	17.37	18.58	11.75	12.18	12.71	13.14	14.35
8H	4H	15.18	15.66	16.12	16.60	17.80	11.42	11.90	12.36	12.84	14.04
	6H	15.74	16.13	16.70	17.12	18.32	11.94	12.33	12.90	13.31	14.51
	8H	15.95	16.30	16.92	17.27	18.49	12.12	12.47	13.09	13.44	14.66
	12H	16.09	16.39	17.06	17.36	18.63	12.24	12.55	13.22	13.51	14.78
12H	4H	15.14	15.56	16.09	16.52	17.73	11.43	11.86	12.39	12.82	14.03
	6H	15.71	16.06	16.69	17.04	18.26	11.98	12.33	12.95	13.30	14.52
	8H	15.93	16.24	16.91	17.21	18.48	12.19	12.50	13.17	13.46	14.73

END OF REPORT