

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904788

Luminaire Tested: DFN2DIP-TR4F0-100D110US830-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904788
REPORT IS A COMBINATION OF REPORTS P900508 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D110US830-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17187.2 lumens
Efficiency: N/A
Efficacy: 92.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 185.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLFL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34
4	75	64	57	51	69	60	53	48	51	46	42	42	38	35	34	32	30
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3095	3095	3095
5°	3100	3046	3065
10°	3069	2986	2965
15°	3027	2887	2811
20°	2971	2751	2622
25°	2914	2598	2439
30°	2837	2442	2207
35°	2762	2274	2003
40°	2685	2100	1770
45°	2596	1907	1559
50°	2504	1712	1352
55°	2408	1504	1153
60°	2297	1286	949
65°	2169	1065	854
70°	2014	859	773
75°	1819	757	703
80°	1537	635	609
85°	1071	423	457

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2596 cd/sqm

TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	365.1	2.1
10°-20°	1002.2	5.8
20°-30°	1407.1	8.2
30°-40°	1533.9	8.9
40°-50°	1409.8	8.2
50°-60°	1107.2	6.4
60°-70°	720.7	4.2
70°-80°	371.0	2.2
80°-90°	104.0	0.6
90°-100°	202.9	1.2
100°-110°	644.7	3.8
110°-120°	1103.3	6.4
120°-130°	1451.0	8.4
130°-140°	1628.6	9.5
140°-150°	1597.1	9.3
150°-160°	1339.7	7.8
160°-170°	888.5	5.2
170°-180°	310.5	1.8
0°-30°	2774.5	16.1
0°-40°	4308.3	25.1
0°-60°	6825.3	39.7
0°-90°	8020.9	46.7
90°-120°	1950.9	11.4
90°-150°	6627.6	38.6
90°-180°	9166.0	53.3
0°-180°	17187.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3896	3896	3896	3896	3896	
5°	3896	3878	3832	3864	3853	369
15°	3705	3666	3546	3480	3444	1044
25°	3363	3250	3018	2873	2820	1547
35°	2898	2718	2408	2186	2108	1814
45°	2369	2133	1763	1512	1428	1830
55°	1801	1526	1146	934	867	1610
65°	1216	931	613	494	483	1206
75°	649	402	282	257	254	686
85°	152	77	67	67	67	174
90°	3	36	97	91	94	17
95°	144	172	177	177	172	161
105°	595	603	609	614	614	628
115°	1107	1123	1118	1115	1107	1095
125°	1610	1635	1627	1618	1615	1439
135°	2083	2114	2119	2116	2109	1610
145°	2529	2548	2564	2567	2556	1580
155°	2892	2899	2908	2922	2913	1331
165°	3146	3142	3142	3162	3148	887
175°	3273	3265	3259	3279	3262	311
180°	3279	3279	3279	3279	3279	

TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3895.5	3895.5	3895.5	3895.5	3895.5
2.5°	3913.1	3895.5	3856.6	3892.1	3885.1
5°	3895.5	3877.9	3831.9	3863.8	3853.2
7.5°	3863.8	3842.7	3793.4	3807.2	3789.7
10°	3821.4	3796.7	3726.4	3715.6	3694.7
12.5°	3768.8	3736.9	3641.5	3620.6	3581.7
15°	3705.1	3666.2	3546.5	3479.6	3444.4
17.5°	3631.0	3574.6	3426.5	3349.0	3292.6
20°	3546.5	3475.8	3299.7	3211.8	3134.0
22.5°	3454.9	3373.7	3169.1	3049.5	2996.7
25°	3363.3	3250.4	3017.6	2873.2	2820.2
27.5°	3254.0	3134.0	2876.6	2710.9	2629.8
30°	3137.7	3003.4	2721.4	2541.9	2446.6
32.5°	3024.8	2862.4	2573.7	2362.0	2273.7
35°	2897.9	2718.1	2408.0	2185.8	2108.0
37.5°	2774.6	2580.4	2252.8	2009.3	1921.4
40°	2644.0	2432.7	2090.5	1840.2	1748.6
42.5°	2510.1	2284.5	1928.5	1667.5	1579.5
45°	2369.1	2132.7	1762.8	1512.2	1427.7
47.5°	2235.2	1985.0	1604.2	1353.6	1276.2
50°	2087.1	1836.8	1449.0	1205.5	1131.8
52.5°	1942.3	1677.9	1300.9	1068.2	1001.3
55°	1801.3	1526.4	1145.7	934.3	867.3
57.5°	1657.0	1374.9	1008.4	810.9	754.4
60°	1508.8	1226.8	863.7	684.1	627.6
62.5°	1364.4	1082.4	740.2	571.2	543.1
65°	1216.4	930.6	613.4	493.7	482.9
67.5°	1075.3	789.6	493.7	433.5	423.0
70°	927.2	652.3	408.8	373.6	359.5
72.5°	786.2	525.1	341.9	313.8	306.7
75°	648.6	401.7	282.0	257.3	253.9
77.5°	511.3	285.4	222.2	207.9	200.9
80°	384.1	204.6	169.1	155.2	155.2
82.5°	267.8	137.6	116.3	109.2	109.2
85°	151.5	77.4	66.9	66.9	66.9
87.5°	56.5	28.1	28.1	24.7	24.7
90°	2.9	35.6	96.9	91.0	93.9
92.5°	61.3	83.0	86.0	89.0	89.0
95°	144.3	172.0	176.9	176.9	172.0
97.5°	240.3	265.9	276.8	276.8	276.8
100°	350.9	373.6	381.5	381.5	378.6
102.5°	467.6	484.4	495.3	498.2	495.3
105°	595.1	603.0	609.0	613.9	613.9
107.5°	721.6	733.5	733.5	735.5	721.6
110°	844.2	860.1	860.1	860.1	852.2

TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	976.7	993.4	990.5	982.6	976.7
115°	1107.2	1122.9	1118.0	1115.1	1107.2
117.5°	1236.7	1258.4	1244.5	1236.7	1228.8
120°	1367.2	1388.9	1367.2	1367.2	1358.3
122.5°	1485.8	1513.4	1499.6	1491.7	1485.8
125°	1610.3	1635.0	1627.1	1618.3	1615.2
127.5°	1731.9	1762.6	1751.7	1739.8	1731.9
130°	1845.6	1881.2	1876.2	1870.3	1859.4
132.5°	1973.1	2000.8	2002.8	1989.0	1981.0
135°	2082.8	2113.5	2119.4	2116.5	2108.6
137.5°	2205.5	2230.1	2235.1	2233.1	2221.3
140°	2313.2	2337.9	2351.7	2351.7	2340.9
142.5°	2423.9	2448.6	2456.5	2459.5	2448.6
145°	2528.7	2548.4	2564.3	2567.2	2556.4
147.5°	2622.6	2647.3	2659.2	2664.1	2653.3
150°	2719.5	2736.3	2747.1	2756.1	2747.1
152.5°	2805.5	2822.3	2836.1	2847.0	2836.1
155°	2891.5	2899.4	2908.3	2922.2	2913.2
157.5°	2965.6	2971.6	2976.5	2996.2	2982.4
160°	3031.9	3037.8	3040.7	3057.6	3045.7
162.5°	3093.1	3093.1	3096.2	3114.9	3101.1
165°	3145.5	3142.5	3142.5	3162.3	3148.5
167.5°	3193.0	3184.1	3184.1	3203.9	3190.0
170°	3228.6	3220.7	3217.7	3237.4	3220.7
172.5°	3253.3	3245.4	3242.4	3262.2	3245.4
175°	3273.1	3265.2	3259.2	3279.0	3262.2
177.5°	3283.9	3276.0	3270.1	3286.9	3270.1
180°	3279.0	3279.0	3279.0	3279.0	3279.0

TEST NUMBER: P904788

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.75	11.55	11.74	12.55	13.87	6.72	7.52	7.71	8.52	9.84
	3H	12.42	13.14	13.42	14.15	15.49	7.91	8.62	8.91	9.63	10.98
	4H	13.03	13.71	14.04	14.72	16.07	8.36	9.04	9.37	10.05	11.40
	6H	13.45	14.07	14.47	15.09	16.45	8.68	9.30	9.70	10.32	11.68
	8H	13.57	14.17	14.60	15.20	16.56	8.77	9.36	9.80	10.39	11.75
	12H	13.63	14.20	14.67	15.23	16.61	8.81	9.38	9.85	10.40	11.78
4H	2H	10.76	11.44	11.78	12.45	13.80	7.31	7.99	8.33	9.00	10.35
	3H	12.59	13.15	13.62	14.19	15.56	8.66	9.22	9.69	10.26	11.63
	4H	13.28	13.79	14.31	14.83	16.21	9.21	9.72	10.24	10.76	12.14
	6H	13.79	14.24	14.84	15.29	16.67	9.63	10.07	10.67	11.12	12.51
	8H	13.97	14.38	15.01	15.43	16.82	9.75	10.17	10.80	11.22	12.61
	12H	14.06	14.43	15.13	15.50	16.90	9.82	10.19	10.88	11.26	12.66
8H	4H	13.24	13.66	14.29	14.71	16.10	9.49	9.90	10.53	10.95	12.34
	6H	13.81	14.15	14.88	15.24	16.63	10.00	10.35	11.07	11.44	12.83
	8H	14.03	14.33	15.10	15.40	16.81	10.20	10.50	11.27	11.57	12.98
	12H	14.16	14.43	15.24	15.50	16.95	10.31	10.58	11.40	11.65	13.10
12H	4H	13.19	13.57	14.26	14.63	16.03	9.49	9.86	10.55	10.93	12.33
	6H	13.78	14.08	14.86	15.16	16.57	10.05	10.35	11.13	11.43	12.84
	8H	14.00	14.27	15.09	15.34	16.79	10.26	10.53	11.34	11.60	13.05