

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920803

Luminaire Tested: DFN2DIP-TR3F0-050D080US935-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P920803  
REPORT IS A COMBINATION OF REPORTS P901866 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-050D080US935-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 10478.4 lumens  
Efficiency: N/A  
Efficacy: 98.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 106.5  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9933  
Total Harmonic Distortion (THDi): 0.066  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P920803  
CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P920803  
 CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	75	75	75	58	58	58	42	42	42	35				35
1	95	91	87	84	86	82	79	76	66	64	62	51	50	49	38	37	36	30				30
2	87	80	74	69	78	72	67	63	58	55	52	46	43	41	34	32	31	26				26
3	79	70	63	58	71	64	58	53	52	47	44	41	38	35	30	28	27	22				22
4	72	62	55	49	65	57	50	45	46	41	38	36	33	30	27	25	23	19				19
5	67	56	48	42	60	51	44	39	41	36	33	33	29	27	25	22	21	17				17
6	61	50	42	37	55	45	39	34	37	32	29	30	26	23	22	20	18	15				15
7	57	45	37	32	51	41	34	30	34	29	25	27	23	21	21	18	16	14				14
8	53	41	33	28	48	37	31	26	31	26	22	25	21	19	19	17	15	12				12
9	49	37	30	25	44	34	28	23	28	23	20	23	19	17	18	15	13	11				11
10	46	34	27	23	41	31	25	21	26	21	18	21	18	15	16	14	12	10				10

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2217	2217	2217
5°	2220	2180	2195
10°	2196	2135	2122
15°	2165	2063	2010
20°	2124	1964	1873
25°	2081	1853	1741
30°	2025	1740	1575
35°	1970	1618	1428
40°	1914	1493	1261
45°	1848	1353	1108
50°	1781	1213	960
55°	1710	1063	818
60°	1628	907	672
65°	1534	749	603
70°	1419	601	544
75°	1276	526	491
80°	1068	435	421
85°	726	282	309

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1848 cd/sqm



TEST NUMBER: P920803

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	166.8	1.6
10°-20°	457.8	4.4
20°-30°	642.7	6.1
30°-40°	700.6	6.7
40°-50°	643.9	6.1
50°-60°	505.7	4.8
60°-70°	329.2	3.1
70°-80°	169.5	1.6
80°-90°	47.4	0.5
90°-100°	76.7	0.7
100°-110°	285.7	2.7
110°-120°	757.9	7.2
120°-130°	1256.9	12.0
130°-140°	1335.2	12.7
140°-150°	1240.9	11.8
150°-160°	997.6	9.5
160°-170°	642.8	6.1
170°-180°	221.3	2.1
0°-30°	1267.2	12.1
0°-40°	1967.8	18.8
0°-60°	3117.4	29.8
0°-90°	3663.3	35.0
90°-120°	1120.2	10.7
90°-150°	4953.3	47.3
90°-180°	6815.0	65.0
0°-180°	10478.4	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1779	1779	1779	1779	1779	
5°	1779	1771	1750	1765	1760	169
15°	1692	1675	1620	1589	1573	477
25°	1536	1484	1378	1312	1288	706
35°	1324	1242	1100	998	963	828
45°	1082	974	805	691	652	836
55°	823	697	523	427	396	735
65°	556	425	280	226	221	551
75°	296	184	129	118	116	313
85°	69	35	31	31	31	79
90°	2	20	34	42	45	10
95°	109	54	66	74	72	129
105°	511	562	103	121	128	546
115°	967	996	1038	259	138	952
125°	1367	1389	1421	1433	1438	1220
135°	1692	1719	1734	1751	1748	1307
145°	1963	1961	1990	2002	1993	1228
155°	2161	2146	2167	2177	2163	996
165°	2278	2268	2272	2284	2272	643
175°	2330	2318	2321	2333	2316	222
180°	2325	2325	2325	2325	2325	



TEST NUMBER: P920803

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	1779.3	1779.3	1779.3	1779.3	1779.3
2.5°	1787.3	1779.3	1761.5	1777.7	1774.4
5°	1779.3	1771.2	1750.2	1764.7	1760.0
7.5°	1764.7	1755.1	1732.6	1739.0	1730.9
10°	1745.4	1734.1	1702.0	1697.1	1687.5
12.5°	1721.3	1706.8	1663.3	1653.7	1635.9
15°	1692.3	1674.6	1619.9	1589.3	1573.2
17.5°	1658.5	1632.7	1565.0	1529.6	1503.8
20°	1619.9	1587.6	1507.1	1467.0	1431.4
22.5°	1578.0	1540.9	1447.5	1392.8	1368.7
25°	1536.1	1484.5	1378.3	1312.3	1288.1
27.5°	1486.3	1431.4	1313.9	1238.2	1201.2
30°	1433.1	1371.8	1243.0	1161.0	1117.4
32.5°	1381.6	1307.4	1175.5	1078.8	1038.5
35°	1323.6	1241.5	1099.8	998.3	962.9
37.5°	1267.2	1178.6	1029.0	917.7	877.6
40°	1207.6	1111.1	954.8	840.5	798.7
42.5°	1146.5	1043.4	880.8	761.6	721.4
45°	1082.1	974.1	805.1	690.7	652.0
47.5°	1020.9	906.6	732.7	618.3	582.9
50°	953.3	839.0	661.8	550.6	516.9
52.5°	887.2	766.4	594.2	487.9	457.4
55°	822.8	697.1	523.2	426.7	396.1
57.5°	756.8	628.0	460.5	370.4	344.6
60°	689.1	560.3	394.4	312.5	286.6
62.5°	623.2	494.4	338.1	260.9	248.1
65°	555.5	425.1	280.2	225.5	220.6
67.5°	491.1	360.7	225.5	198.0	193.2
70°	423.5	297.9	186.8	170.6	164.2
72.5°	359.1	239.9	156.2	143.4	140.1
75°	296.3	183.5	128.8	117.5	116.0
77.5°	233.5	130.4	101.5	95.0	91.7
80°	175.5	93.4	77.2	70.9	70.9
82.5°	122.3	62.9	53.1	49.9	49.9
85°	69.2	35.4	30.6	30.6	30.6
87.5°	25.8	12.8	12.8	11.3	11.3
90°	1.6	20.1	33.6	42.1	45.4
92.5°	42.1	35.4	40.4	43.7	45.4
95°	109.3	53.7	65.5	74.1	72.3
97.5°	196.7	58.9	85.7	90.9	92.5
100°	297.8	67.3	95.9	109.3	112.6
102.5°	408.7	405.4	99.3	117.6	122.9
105°	511.3	561.9	102.6	121.1	127.9
107.5°	630.8	672.7	106.1	124.4	131.2
110°	745.3	780.4	294.5	126.2	132.9



TEST NUMBER: P920803

CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	852.9	883.0	854.5	129.4	134.7
115°	967.2	995.7	1037.8	259.1	138.0
117.5°	1066.4	1100.0	1128.8	888.0	447.5
120°	1177.5	1202.6	1233.0	1253.2	1026.1
122.5°	1271.5	1298.6	1332.3	1342.3	1344.1
125°	1367.4	1389.4	1421.3	1433.1	1438.1
127.5°	1454.9	1478.5	1503.9	1520.6	1522.2
130°	1537.4	1564.3	1582.8	1601.4	1599.7
132.5°	1621.5	1643.5	1661.9	1677.1	1675.4
135°	1692.2	1719.2	1734.1	1751.2	1747.7
137.5°	1766.2	1786.3	1803.3	1820.1	1815.1
140°	1838.4	1852.0	1870.4	1885.6	1877.1
142.5°	1899.2	1910.9	1932.7	1946.1	1937.7
145°	1963.1	1961.3	1989.9	2001.6	1993.2
147.5°	2018.4	2013.4	2041.9	2050.4	2043.8
150°	2072.3	2060.5	2087.5	2097.5	2089.1
152.5°	2117.7	2104.3	2129.4	2139.7	2127.9
155°	2161.4	2146.5	2166.6	2176.6	2163.3
157.5°	2196.7	2183.4	2198.6	2210.4	2196.7
160°	2227.1	2217.0	2227.1	2237.1	2225.3
162.5°	2253.9	2243.9	2252.3	2264.1	2248.9
165°	2277.5	2267.5	2272.5	2284.2	2272.5
167.5°	2296.0	2285.9	2291.0	2302.8	2287.7
170°	2311.3	2301.0	2304.5	2316.3	2301.0
172.5°	2321.3	2311.3	2314.6	2326.4	2311.3
175°	2329.6	2317.8	2321.3	2333.0	2316.3
177.5°	2333.0	2321.3	2323.0	2334.8	2319.6
180°	2324.6	2324.6	2324.6	2324.6	2324.6



TEST NUMBER: P920803  
 CATALOG NUMBER: DFN2DIP-TR3F0-050D080US935-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.27	8.99	9.35	10.07	11.54	4.25	4.97	5.33	6.05	7.52
	3H	9.93	10.57	11.02	11.66	13.15	5.42	6.07	6.51	7.15	8.64
	4H	10.53	11.14	11.63	12.23	13.72	5.86	6.47	6.96	7.56	9.06
	6H	10.94	11.50	12.05	12.59	14.10	6.17	6.74	7.28	7.83	9.33
	8H	11.05	11.59	12.17	12.70	14.20	6.26	6.79	7.37	7.90	9.40
	12H	11.11	11.62	12.23	12.72	14.24	6.30	6.80	7.41	7.90	9.43
4H	2H	8.27	8.88	9.38	9.97	11.47	4.82	5.43	5.93	6.52	8.02
	3H	10.08	10.59	11.20	11.71	13.21	6.16	6.67	7.27	7.78	9.29
	4H	10.76	11.23	11.88	12.33	13.86	6.70	7.16	7.81	8.27	9.80
	6H	11.26	11.66	12.39	12.79	14.31	7.10	7.50	8.23	8.63	10.15
	8H	11.43	11.80	12.56	12.92	14.46	7.23	7.60	8.35	8.72	10.26
	12H	11.52	11.85	12.66	12.98	14.53	7.28	7.62	8.43	8.75	10.30
8H	4H	10.72	11.09	11.85	12.21	13.75	6.96	7.34	8.09	8.45	9.99
	6H	11.27	11.58	12.42	12.74	14.28	7.47	7.78	8.62	8.94	10.47
	8H	11.48	11.75	12.64	12.89	14.45	7.65	7.92	8.81	9.07	10.62
	12H	11.61	11.85	12.77	12.98	14.58	7.76	8.00	8.92	9.14	10.73
12H	4H	10.67	11.01	11.81	12.14	13.68	6.96	7.30	8.10	8.43	9.97
	6H	11.25	11.52	12.40	12.66	14.21	7.52	7.78	8.67	8.93	10.48
	8H	11.46	11.69	12.61	12.83	14.42	7.72	7.95	8.87	9.09	10.68