

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904856

Luminaire Tested: DFN2DIP-TR4F0-120D100US830-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904856
REPORT IS A COMBINATION OF REPORTS P900494 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-120D100US830-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17955.4 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 202
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9821
Total Harmonic Distortion (THDi): 0.08
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59
1	99	95	91	88	92	88	85	82	76	73	71	64	62	61	53	52	51
2	91	84	78	73	84	78	73	68	67	63	60	57	54	52	48	46	44
3	83	74	67	61	77	69	63	58	59	55	51	51	47	44	43	40	38
4	76	66	58	52	71	61	55	49	53	48	44	46	42	38	38	36	33
5	70	59	51	45	65	55	48	43	48	42	38	41	37	34	35	32	29
6	65	53	45	39	60	50	43	37	43	38	34	37	33	30	32	29	26
7	60	48	40	35	56	45	38	33	39	34	30	34	30	27	29	26	23
8	56	44	36	31	52	41	34	30	36	31	27	31	27	24	27	24	21
9	52	40	33	28	48	38	31	27	33	28	24	29	25	22	25	22	19
10	49	37	30	25	45	35	28	24	31	25	22	27	23	20	23	20	18

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3714	3714	3714
5°	3720	3655	3678
10°	3683	3583	3558
15°	3632	3465	3373
20°	3565	3301	3146
25°	3497	3118	2927
30°	3404	2931	2648
35°	3314	2729	2404
40°	3222	2520	2124
45°	3115	2288	1870
50°	3005	2055	1622
55°	2890	1805	1384
60°	2756	1544	1139
65°	2603	1278	1025
70°	2417	1030	927
75°	2183	908	843
80°	1845	761	731
85°	1286	508	549

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 3115 cd/sqm

TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	438.1	2.4
10°-20°	1202.7	6.7
20°-30°	1688.5	9.4
30°-40°	1840.6	10.3
40°-50°	1691.7	9.4
50°-60°	1328.6	7.4
60°-70°	864.8	4.8
70°-80°	445.2	2.5
80°-90°	122.1	0.7
90°-100°	184.5	1.0
100°-110°	586.1	3.3
110°-120°	1003.0	5.6
120°-130°	1319.1	7.3
130°-140°	1480.6	8.2
140°-150°	1451.9	8.1
150°-160°	1217.9	6.8
160°-170°	807.7	4.5
170°-180°	282.3	1.6
0°-30°	3329.4	18.5
0°-40°	5170.0	28.8
0°-60°	8190.3	45.6
0°-90°	9622.4	53.6
90°-120°	1773.5	9.9
90°-150°	6025.1	33.6
90°-180°	8333.0	46.4
0°-180°	17955.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4675	4675	4675	4675	4675	
5°	4675	4654	4598	4636	4624	443
15°	4446	4400	4256	4176	4133	1253
25°	4036	3900	3621	3448	3384	1856
35°	3478	3262	2890	2623	2530	2177
45°	2843	2559	2115	1815	1713	2195
55°	2162	1832	1375	1121	1041	1932
65°	1460	1117	736	592	580	1447
75°	778	482	338	309	305	823
85°	182	93	80	80	80	209
90°	3	32	88	83	85	18
95°	131	156	161	161	156	146
105°	541	548	554	558	558	571
115°	1006	1021	1016	1014	1006	996
125°	1464	1486	1479	1471	1468	1308
135°	1894	1921	1927	1924	1917	1464
145°	2299	2317	2331	2334	2324	1436
155°	2629	2636	2644	2656	2648	1210
165°	2860	2857	2857	2875	2862	807
175°	2976	2968	2963	2981	2966	283
180°	2981	2981	2981	2981	2981	

TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4674.6	4674.6	4674.6	4674.6	4674.6
2.5°	4695.7	4674.6	4628.0	4670.6	4662.0
5°	4674.6	4653.5	4598.3	4636.5	4623.9
7.5°	4636.5	4611.3	4552.1	4568.7	4547.6
10°	4585.8	4556.2	4471.7	4458.7	4433.6
12.5°	4522.4	4484.3	4369.8	4344.7	4298.1
15°	4446.2	4399.5	4255.9	4175.5	4133.3
17.5°	4357.3	4289.5	4111.7	4018.9	3951.1
20°	4255.9	4171.0	3959.6	3854.1	3760.7
22.5°	4145.9	4048.5	3803.0	3659.3	3596.1
25°	4036.0	3900.3	3621.2	3447.9	3384.2
27.5°	3904.9	3760.7	3452.0	3253.2	3155.7
30°	3765.3	3604.2	3265.7	3050.3	2935.8
32.5°	3629.7	3434.9	3088.4	2834.4	2728.5
35°	3477.6	3261.7	2889.6	2623.0	2529.6
37.5°	3329.4	3096.5	2703.3	2411.1	2305.6
40°	3172.8	2919.2	2508.6	2208.3	2098.3
42.5°	3012.1	2741.5	2314.2	2000.9	1895.5
45°	2842.9	2559.3	2115.3	1814.7	1713.2
47.5°	2682.2	2382.0	1925.0	1624.4	1531.4
50°	2504.5	2204.2	1738.8	1446.6	1358.2
52.5°	2330.8	2013.5	1561.0	1281.9	1201.6
55°	2161.6	1831.7	1374.8	1121.2	1040.8
57.5°	1988.3	1649.9	1210.0	973.1	905.3
60°	1810.6	1472.2	1036.3	821.0	753.2
62.5°	1637.4	1298.9	888.3	685.4	651.7
65°	1459.6	1116.7	736.1	592.5	579.5
67.5°	1290.4	947.4	592.5	520.2	507.7
70°	1112.7	782.8	490.6	448.4	431.3
72.5°	943.5	630.2	410.2	376.5	368.1
75°	778.3	482.0	338.5	308.8	304.7
77.5°	613.6	342.4	266.6	249.6	241.0
80°	461.0	245.5	202.8	186.2	186.2
82.5°	321.4	165.1	139.6	131.0	131.0
85°	181.8	92.9	80.3	80.3	80.3
87.5°	67.8	33.6	33.6	29.6	29.6
90°	2.7	32.3	88.0	82.7	85.4
92.5°	55.7	75.5	78.2	80.9	80.9
95°	131.2	156.4	160.9	160.9	156.4
97.5°	218.4	241.8	251.7	251.7	251.7
100°	319.1	339.7	346.9	346.9	344.2
102.5°	425.1	440.4	450.3	452.9	450.3
105°	541.0	548.2	553.6	558.1	558.1
107.5°	656.0	666.8	666.8	668.6	656.0
110°	767.5	781.8	781.8	781.8	774.7



TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	887.9	903.1	900.5	893.2	887.9
115°	1006.5	1020.9	1016.4	1013.7	1006.5
117.5°	1124.3	1144.1	1131.4	1124.3	1117.0
120°	1242.8	1262.6	1242.8	1242.8	1234.8
122.5°	1350.7	1375.8	1363.3	1356.1	1350.7
125°	1464.0	1486.4	1479.2	1471.1	1468.5
127.5°	1574.5	1602.3	1592.4	1581.7	1574.5
130°	1677.8	1710.1	1705.7	1700.3	1690.4
132.5°	1793.8	1818.9	1820.7	1808.2	1800.9
135°	1893.5	1921.4	1926.7	1924.1	1916.8
137.5°	2005.0	2027.4	2031.9	2030.1	2019.3
140°	2102.9	2125.3	2138.0	2138.0	2128.1
142.5°	2203.6	2226.0	2233.2	2235.9	2226.0
145°	2298.8	2316.8	2331.2	2333.8	2323.9
147.5°	2384.2	2406.7	2417.4	2422.0	2412.1
150°	2472.3	2487.6	2497.5	2505.5	2497.5
152.5°	2550.4	2565.7	2578.3	2588.2	2578.3
155°	2628.7	2635.8	2643.9	2656.5	2648.4
157.5°	2696.0	2701.4	2705.9	2723.9	2711.3
160°	2756.3	2761.6	2764.3	2779.6	2768.8
162.5°	2812.0	2812.0	2814.6	2831.7	2819.1
165°	2859.6	2856.8	2856.8	2874.8	2862.3
167.5°	2902.7	2894.6	2894.6	2912.6	2900.0
170°	2935.1	2927.9	2925.2	2943.2	2927.9
172.5°	2957.5	2950.3	2947.6	2965.6	2950.3
175°	2975.5	2968.3	2963.0	2980.9	2965.6
177.5°	2985.4	2978.2	2972.8	2988.0	2972.8
180°	2980.9	2980.9	2980.9	2980.9	2980.9

TEST NUMBER: P904856

CATALOG NUMBER: DFN2DIP-TR4F0-120D100US830-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.03	12.89	12.96	13.83	15.06	8.00	8.86	8.93	9.81	11.03
	3H	13.71	14.48	14.65	15.43	16.68	9.19	9.96	10.14	10.92	12.16
	4H	14.32	15.04	15.28	16.00	17.26	9.65	10.37	10.61	11.33	12.59
	6H	14.74	15.41	15.71	16.37	17.64	9.97	10.64	10.94	11.60	12.87
	8H	14.87	15.50	15.84	16.49	17.75	10.06	10.70	11.04	11.68	12.94
	12H	14.93	15.54	15.91	16.51	17.80	10.11	10.71	11.09	11.69	12.98
4H	2H	12.05	12.78	13.01	13.74	14.99	8.60	9.33	9.57	10.29	11.54
	3H	13.88	14.49	14.86	15.48	16.74	9.95	10.56	10.93	11.55	12.82
	4H	14.58	15.13	15.56	16.11	17.40	10.50	11.06	11.49	12.04	13.33
	6H	15.09	15.57	16.09	16.57	17.86	10.93	11.40	11.92	12.41	13.70
	8H	15.27	15.71	16.26	16.71	18.01	11.06	11.50	12.05	12.50	13.80
	12H	15.36	15.76	16.38	16.78	18.09	11.12	11.52	12.14	12.54	13.85
8H	4H	14.55	14.99	15.54	15.99	17.29	10.79	11.23	11.78	12.23	13.53
	6H	15.11	15.48	16.13	16.52	17.82	11.31	11.67	12.33	12.71	14.02
	8H	15.33	15.65	16.36	16.68	18.00	11.50	11.82	12.53	12.85	14.17
	12H	15.47	15.75	16.50	16.77	18.14	11.62	11.90	12.65	12.93	14.29
12H	4H	14.50	14.90	15.51	15.91	17.22	10.79	11.19	11.81	12.21	13.52
	6H	15.09	15.41	16.12	16.44	17.76	11.36	11.68	12.39	12.71	14.03
	8H	15.31	15.59	16.34	16.62	17.98	11.57	11.85	12.60	12.87	14.24