

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P920875

Luminaire Tested: DFN2DIP-TR3F0-080D070US935-FLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P920875
REPORT IS A COMBINATION OF REPORTS P901857 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D070US935-FLLONL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 12785.8 lumens
Efficiency: N/A
Efficacy: 95.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 134.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P920875
CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P920875

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20
RC	80				70				50				30				10				0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	108	108	108	108	100	100	100	100	85	85	85	72	72	72	59	59	59	59	59	59	53
1	99	94	90	87	91	87	84	81	75	72	70	63	61	60	52	51	50	50	50	50	45
2	90	82	76	71	83	76	71	66	65	61	58	55	52	50	46	44	42	42	42	42	38
3	82	72	65	59	76	67	61	56	58	53	49	49	45	42	41	38	36	36	36	36	32
4	75	64	56	50	69	60	53	47	51	46	42	44	40	36	37	33	31	31	31	31	27
5	69	57	49	43	63	53	46	41	46	40	36	39	35	31	33	30	27	27	27	27	24
6	63	51	43	37	59	48	41	35	41	36	31	35	31	28	30	26	24	24	24	24	21
7	59	46	38	33	54	43	36	31	38	32	28	32	28	24	27	24	21	21	21	21	19
8	54	42	34	29	50	39	32	27	34	29	25	30	25	22	25	22	19	19	19	19	17
9	51	38	31	26	47	36	29	25	31	26	22	27	23	20	23	20	17	17	17	17	15
10	47	35	28	23	44	33	26	22	29	24	20	25	21	18	21	18	16	16	16	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3340	3340	3340
5°	3343	3290	3313
10°	3314	3243	3266
15°	3264	3187	3194
20°	3196	3110	3120
25°	3129	3019	3035
30°	3045	2933	2927
35°	2965	2833	2813
40°	2867	2732	2705
45°	2769	2630	2594
50°	2662	2523	2465
55°	2550	2399	2347
60°	2423	2253	2211
65°	2285	2101	2051
70°	2108	1915	1878
75°	1864	1692	1715
80°	1569	1408	1409
85°	1109	928	910

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2769 cd/sqm



TEST NUMBER: P920875

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	252.3	2.0
10°-20°	709.8	5.6
20°-30°	1043.1	8.2
30°-40°	1211.4	9.5
40°-50°	1209.9	9.5
50°-60°	1055.0	8.3
60°-70°	779.9	6.1
70°-80°	441.2	3.5
80°-90°	120.1	0.9
90°-100°	67.1	0.5
100°-110°	250.0	2.0
110°-120°	663.1	5.2
120°-130°	1099.8	8.6
130°-140°	1168.3	9.1
140°-150°	1085.8	8.5
150°-160°	872.9	6.8
160°-170°	562.5	4.4
170°-180°	193.6	1.5
0°-30°	2005.1	15.7
0°-40°	3216.5	25.2
0°-60°	5481.5	42.9
0°-90°	6822.7	53.4
90°-120°	980.2	7.7
90°-150°	4334.1	33.9
90°-180°	5963.0	46.6
0°-180°	12785.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2680	2680	2680	2680	2680	
5°	2680	2670	2642	2662	2657	254
15°	2551	2536	2502	2513	2500	719
25°	2309	2289	2245	2250	2245	1063
35°	1992	1966	1925	1910	1897	1244
45°	1621	1603	1564	1536	1526	1251
55°	1227	1211	1180	1150	1137	1097
65°	827	812	786	763	750	818
75°	433	428	415	400	405	462
85°	106	103	101	93	90	118
90°	1	18	29	37	40	12
95°	96	47	57	65	63	113
105°	448	492	90	106	112	478
115°	846	871	908	227	121	833
125°	1196	1216	1244	1254	1258	1067
135°	1481	1504	1517	1532	1529	1144
145°	1718	1716	1741	1751	1744	1074
155°	1891	1878	1896	1904	1893	872
165°	1993	1984	1988	1999	1988	563
175°	2038	2028	2031	2041	2027	194
180°	2034	2034	2034	2034	2034	



TEST NUMBER: P920875

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2680.1	2680.1	2680.1	2680.1	2680.1
2.5°	2695.7	2682.9	2654.5	2680.1	2675.2
5°	2680.1	2670.0	2641.6	2662.1	2657.2
7.5°	2662.1	2646.8	2618.4	2639.1	2634.0
10°	2634.0	2615.9	2585.0	2605.5	2597.9
12.5°	2595.1	2579.8	2548.9	2561.7	2556.6
15°	2551.4	2536.1	2502.4	2512.8	2500.0
17.5°	2497.2	2481.9	2448.2	2461.2	2448.2
20°	2437.9	2422.6	2386.5	2394.2	2384.0
22.5°	2378.9	2355.6	2321.9	2321.9	2316.8
25°	2309.1	2288.6	2244.9	2249.8	2244.9
27.5°	2231.7	2213.7	2180.3	2172.6	2159.8
30°	2154.6	2133.8	2095.3	2087.7	2077.2
32.5°	2072.1	2056.8	2015.4	1999.8	1989.5
35°	1992.2	1966.5	1925.2	1909.6	1896.8
37.5°	1901.9	1878.7	1837.5	1819.4	1806.5
40°	1809.3	1788.5	1747.2	1724.2	1713.8
42.5°	1719.1	1698.2	1657.2	1631.2	1616.0
45°	1621.2	1603.1	1564.3	1536.1	1525.8
47.5°	1525.8	1507.7	1466.4	1438.0	1422.6
50°	1425.1	1412.3	1376.1	1340.1	1327.2
52.5°	1327.2	1309.1	1275.8	1247.4	1229.3
55°	1226.8	1211.3	1180.4	1149.5	1136.6
57.5°	1126.3	1113.4	1079.8	1048.9	1038.4
60°	1025.6	1015.5	979.4	951.0	943.3
62.5°	927.7	909.7	884.0	858.3	847.9
65°	827.4	811.8	786.1	762.8	750.0
67.5°	724.3	711.2	688.2	670.2	659.8
70°	628.9	618.5	595.3	577.2	567.1
72.5°	531.0	520.6	507.7	489.7	482.1
75°	432.8	427.9	414.8	399.5	404.7
77.5°	345.3	334.9	329.8	322.1	314.4
80°	257.9	255.1	249.9	242.3	237.0
82.5°	175.3	175.3	172.8	162.4	162.4
85°	105.6	103.1	100.7	92.7	90.2
87.5°	46.5	41.3	36.1	28.4	25.7
90°	1.4	17.7	29.4	36.9	39.7
92.5°	36.9	30.9	35.3	38.3	39.7
95°	95.6	47.0	57.3	64.8	63.3
97.5°	172.1	51.6	75.0	79.6	80.9
100°	260.6	58.9	83.9	95.6	98.6
102.5°	357.6	354.8	86.9	103.0	107.5
105°	447.5	491.6	89.8	105.9	111.8
107.5°	551.9	588.7	92.8	108.9	114.9
110°	652.1	682.9	257.6	110.5	116.2



TEST NUMBER: P920875

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	746.3	772.7	747.7	113.2	117.8
115°	846.3	871.2	908.1	226.7	120.8
117.5°	933.1	962.5	987.7	777.1	391.5
120°	1030.3	1052.3	1078.9	1096.6	897.8
122.5°	1112.6	1136.2	1165.8	1174.5	1176.0
125°	1196.5	1215.7	1243.7	1254.0	1258.3
127.5°	1273.1	1293.6	1315.9	1330.6	1332.0
130°	1345.2	1368.8	1384.9	1401.2	1399.8
132.5°	1418.8	1438.0	1454.1	1467.4	1466.0
135°	1480.7	1504.2	1517.4	1532.2	1529.3
137.5°	1545.3	1563.1	1577.9	1592.6	1588.2
140°	1608.6	1620.5	1636.6	1649.8	1642.5
142.5°	1661.7	1672.1	1691.1	1702.8	1695.5
145°	1717.7	1716.1	1741.1	1751.4	1744.1
147.5°	1766.1	1761.8	1786.7	1794.1	1788.3
150°	1813.3	1803.0	1826.6	1835.3	1828.0
152.5°	1853.0	1841.2	1863.3	1872.2	1861.9
155°	1891.3	1878.1	1895.7	1904.5	1892.8
157.5°	1922.2	1910.5	1923.7	1934.1	1922.2
160°	1948.8	1939.8	1948.8	1957.5	1947.1
162.5°	1972.2	1963.4	1970.7	1981.1	1967.8
165°	1992.8	1984.1	1988.4	1998.7	1988.4
167.5°	2009.1	2000.1	2004.7	2015.0	2001.7
170°	2022.3	2013.4	2016.4	2026.7	2013.4
172.5°	2031.1	2022.3	2025.3	2035.6	2022.3
175°	2038.4	2028.1	2031.1	2041.3	2026.7
177.5°	2041.3	2031.1	2032.6	2043.0	2029.6
180°	2034.0	2034.0	2034.0	2034.0	2034.0



TEST NUMBER: P920875
 CATALOG NUMBER: DFN2DIP-TR3F0-080D070US935-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.72	12.61	12.64	13.55	14.78	11.29	12.18	12.21	13.12	14.35
	3H	13.37	14.17	14.31	15.12	16.37	12.90	13.70	13.84	14.66	15.90
	4H	13.95	14.71	14.91	15.67	16.92	13.48	14.24	14.44	15.20	16.46
	6H	14.35	15.04	15.31	16.01	17.28	13.88	14.57	14.84	15.54	16.81
	8H	14.45	15.11	15.42	16.09	17.36	13.98	14.64	14.95	15.63	16.89
	12H	14.49	15.13	15.47	16.10	17.39	14.02	14.65	15.00	15.63	16.92
4H	2H	12.18	12.93	13.14	13.89	15.15	11.83	12.59	12.79	13.55	14.81
	3H	14.04	14.67	15.00	15.66	16.93	13.65	14.28	14.62	15.27	16.54
	4H	14.74	15.32	15.72	16.30	17.60	14.34	14.92	15.32	15.90	17.20
	6H	15.25	15.75	16.24	16.76	18.05	14.85	15.35	15.84	16.35	17.64
	8H	15.40	15.86	16.39	16.86	18.17	14.99	15.46	15.98	16.46	17.76
	12H	15.47	15.89	16.48	16.90	18.21	15.05	15.47	16.06	16.49	17.80
8H	4H	14.94	15.40	15.93	16.40	17.71	14.58	15.05	15.57	16.05	17.35
	6H	15.56	15.95	16.58	16.99	18.29	15.20	15.59	16.22	16.63	17.93
	8H	15.78	16.11	16.80	17.14	18.47	15.41	15.75	16.44	16.78	18.10
	12H	15.90	16.20	16.93	17.22	18.59	15.52	15.82	16.55	16.84	18.21
12H	4H	14.92	15.34	15.94	16.36	17.67	14.58	15.00	15.59	16.01	17.32
	6H	15.59	15.93	16.61	16.96	18.28	15.24	15.58	16.27	16.61	17.93
	8H	15.83	16.12	16.85	17.15	18.51	15.47	15.77	16.50	16.79	18.16