

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907312

Luminaire Tested: DFN2DIP-TR4F0-050D050US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907312
REPORT IS A COMBINATION OF REPORTS P900390 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D050US835-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 8675.0 lumens
Efficiency: N/A
Efficacy: 108.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 79.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1642	1642	1642
5°	1644	1616	1626
10°	1628	1584	1573
15°	1606	1532	1491
20°	1576	1459	1391
25°	1546	1378	1294
30°	1505	1296	1171
35°	1465	1206	1063
40°	1424	1114	939
45°	1377	1012	827
50°	1328	908	717
55°	1277	798	612
60°	1218	682	503
65°	1150	565	453
70°	1068	456	410
75°	965	401	373
80°	815	337	323
85°	569	225	243

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1377 cd/sqm

TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	193.7	2.2
10°-20°	531.7	6.1
20°-30°	746.5	8.6
30°-40°	813.7	9.4
40°-50°	747.9	8.6
50°-60°	587.3	6.8
60°-70°	382.3	4.4
70°-80°	196.8	2.3
80°-90°	54.7	0.6
90°-100°	97.8	1.1
100°-110°	310.9	3.6
110°-120°	532.1	6.1
120°-130°	699.7	8.1
130°-140°	785.4	9.1
140°-150°	770.2	8.9
150°-160°	646.1	7.4
160°-170°	428.5	4.9
170°-180°	149.8	1.7
0°-30°	1471.8	17.0
0°-40°	2285.5	26.3
0°-60°	3620.7	41.7
0°-90°	4254.5	49.0
90°-120°	940.8	10.8
90°-150°	3196.2	36.8
90°-180°	4421.0	51.0
0°-180°	8675.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2066	2066	2066	2066	2066	
5°	2066	2057	2033	2050	2044	196
15°	1966	1945	1881	1846	1827	554
25°	1784	1724	1601	1524	1496	821
35°	1537	1442	1277	1160	1118	962
45°	1257	1131	935	802	757	971
55°	956	810	608	496	460	854
65°	645	494	325	262	256	640
75°	344	213	150	136	135	364
85°	80	41	36	36	36	92
90°	1	17	47	44	45	9
95°	70	83	85	85	83	77
105°	287	291	294	296	296	303
115°	534	542	539	538	534	528
125°	777	788	785	780	779	694
135°	1004	1019	1022	1021	1017	776
145°	1220	1229	1237	1238	1233	762
155°	1394	1398	1402	1409	1405	642
165°	1517	1516	1516	1525	1518	428
175°	1578	1575	1572	1581	1573	150
180°	1581	1581	1581	1581	1581	

TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2066.5	2066.5	2066.5	2066.5	2066.5
2.5°	2075.8	2066.5	2045.9	2064.7	2060.9
5°	2066.5	2057.2	2032.8	2049.6	2044.1
7.5°	2049.6	2038.5	2012.3	2019.7	2010.3
10°	2027.2	2014.1	1976.8	1971.1	1959.9
12.5°	1999.2	1982.4	1931.8	1920.7	1900.0
15°	1965.5	1944.9	1881.4	1845.9	1827.2
17.5°	1926.2	1896.3	1817.7	1776.6	1746.6
20°	1881.4	1843.9	1750.4	1703.8	1662.5
22.5°	1832.8	1789.7	1681.2	1617.7	1589.7
25°	1784.1	1724.2	1600.8	1524.2	1496.0
27.5°	1726.2	1662.5	1526.0	1438.1	1395.1
30°	1664.5	1593.3	1443.7	1348.4	1297.8
32.5°	1604.6	1518.5	1365.3	1253.0	1206.2
35°	1537.3	1441.9	1277.4	1159.5	1118.3
37.5°	1471.8	1368.9	1195.1	1065.9	1019.3
40°	1402.6	1290.5	1108.9	976.2	927.6
42.5°	1331.6	1211.9	1023.0	884.5	837.9
45°	1256.8	1131.4	935.1	802.2	757.3
47.5°	1185.7	1053.0	851.0	718.1	677.0
50°	1107.2	974.4	768.7	639.5	600.4
52.5°	1030.4	890.1	690.1	566.7	531.2
55°	955.6	809.7	607.7	495.6	460.1
57.5°	879.0	729.4	534.9	430.2	400.2
60°	800.4	650.8	458.1	362.9	332.9
62.5°	723.8	574.2	392.7	303.0	288.1
65°	645.2	493.7	325.4	261.9	256.2
67.5°	570.4	418.9	261.9	230.0	224.4
70°	491.9	346.0	216.9	198.2	190.7
72.5°	417.1	278.6	181.4	166.5	162.7
75°	344.1	213.1	149.6	136.5	134.7
77.5°	271.2	151.4	117.9	110.3	106.5
80°	203.8	108.5	89.7	82.3	82.3
82.5°	142.1	73.0	61.7	57.9	57.9
85°	80.4	41.1	35.5	35.5	35.5
87.5°	30.0	14.9	14.9	13.1	13.1
90°	1.4	17.2	46.7	43.9	45.3
92.5°	29.6	40.0	41.5	42.9	42.9
95°	69.6	83.0	85.3	85.3	83.0
97.5°	115.8	128.2	133.5	133.5	133.5
100°	169.2	180.2	184.0	184.0	182.6
102.5°	225.5	233.6	238.8	240.3	238.8
105°	287.0	290.8	293.7	296.0	296.0
107.5°	348.0	353.7	353.7	354.7	348.0
110°	407.1	414.8	414.8	414.8	410.9

TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	471.0	479.1	477.7	473.9	471.0
115°	533.9	541.6	539.2	537.8	533.9
117.5°	596.4	606.9	600.2	596.4	592.6
120°	659.3	669.8	659.3	659.3	655.0
122.5°	716.5	729.9	723.2	719.4	716.5
125°	776.6	788.5	784.7	780.4	779.0
127.5°	835.2	850.0	844.8	839.0	835.2
130°	890.1	907.2	904.8	902.0	896.7
132.5°	951.6	964.9	965.9	959.2	955.4
135°	1004.5	1019.2	1022.1	1020.7	1016.9
137.5°	1063.6	1075.5	1077.9	1076.9	1071.2
140°	1115.5	1127.5	1134.1	1134.1	1128.9
142.5°	1168.9	1180.9	1184.7	1186.1	1180.9
145°	1219.5	1229.0	1236.6	1238.1	1232.8
147.5°	1264.8	1276.7	1282.4	1284.8	1279.5
150°	1311.5	1319.6	1324.8	1329.1	1324.8
152.5°	1353.0	1361.1	1367.7	1373.0	1367.7
155°	1394.4	1398.2	1402.5	1409.2	1404.9
157.5°	1430.2	1433.0	1435.4	1445.0	1438.3
160°	1462.1	1465.0	1466.4	1474.5	1468.8
162.5°	1491.7	1491.7	1493.1	1502.2	1495.5
165°	1517.0	1515.5	1515.5	1525.1	1518.4
167.5°	1539.8	1535.5	1535.5	1545.1	1538.4
170°	1557.0	1553.2	1551.8	1561.3	1553.2
172.5°	1568.9	1565.1	1563.7	1573.2	1565.1
175°	1578.5	1574.6	1571.8	1581.3	1573.2
177.5°	1583.7	1579.9	1577.0	1585.1	1577.0
180°	1581.3	1581.3	1581.3	1581.3	1581.3

TEST NUMBER: P907312

CATALOG NUMBER: DFN2DIP-TR4F0-050D050US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.77	9.60	9.74	10.58	11.86	4.75	5.57	5.72	6.55	7.84
	3H	10.45	11.18	11.43	12.18	13.48	5.94	6.67	6.92	7.66	8.97
	4H	11.06	11.75	12.05	12.75	14.06	6.39	7.08	7.38	8.08	9.39
	6H	11.48	12.12	12.49	13.12	14.45	6.71	7.35	7.71	8.35	9.68
	8H	11.60	12.21	12.62	13.23	14.55	6.80	7.41	7.81	8.42	9.75
	12H	11.67	12.24	12.68	13.25	14.60	6.84	7.42	7.86	8.43	9.78
4H	2H	8.79	9.49	9.79	10.48	11.80	5.34	6.04	6.34	7.03	8.35
	3H	10.62	11.20	11.63	12.22	13.55	6.69	7.27	7.70	8.29	9.62
	4H	11.31	11.84	12.33	12.85	14.21	7.24	7.77	8.26	8.78	10.14
	6H	11.82	12.28	12.85	13.32	14.67	7.66	8.11	8.69	9.15	10.50
	8H	12.00	12.42	13.03	13.45	14.82	7.79	8.21	8.82	9.24	10.61
	12H	12.09	12.48	13.14	13.52	14.89	7.85	8.24	8.90	9.28	10.65
8H	4H	11.28	11.70	12.31	12.73	14.10	7.52	7.94	8.55	8.97	10.34
	6H	11.84	12.19	12.90	13.27	14.63	8.04	8.39	9.09	9.46	10.82
	8H	12.06	12.37	13.12	13.43	14.81	8.23	8.54	9.29	9.60	10.98
	12H	12.20	12.47	13.26	13.52	14.95	8.35	8.62	9.41	9.67	11.10
12H	4H	11.23	11.61	12.28	12.66	14.03	7.52	7.91	8.57	8.95	10.32
	6H	11.82	12.13	12.88	13.19	14.57	8.09	8.39	9.15	9.45	10.84
	8H	12.04	12.31	13.10	13.36	14.79	8.30	8.57	9.36	9.62	11.05