

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907367

Luminaire Tested: DFN2DIP-TR4F0-060D100US835-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907367
REPORT IS A COMBINATION OF REPORTS P902001 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-060D100US835-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 15840.0 lumens
Efficiency: N/A
Efficacy: 122.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 129.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9781
Total Harmonic Distortion (THDi): 0.075
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907367
CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P907367

CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	104	104	104	104	94	94	94	94	76	76	76	60	60	60	45	45	45	38				38
1	95	91	87	83	86	82	79	76	67	65	63	53	51	50	39	39	38	32				32
2	86	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32	26				26
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27	22				22
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	27	25	23	19				19
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20	17				17
6	61	49	41	35	55	45	38	33	37	32	28	29	26	23	22	20	18	15				15
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	20	18	16	13				13
8	52	40	32	27	47	37	30	25	30	25	22	24	21	18	19	16	14	12				12
9	48	36	29	24	44	33	27	23	28	23	19	22	19	16	17	15	13	11				11
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	13	12	10				10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1855	1855	1855
5°	1858	1829	1841
10°	1843	1804	1816
15°	1816	1774	1777
20°	1779	1733	1737
25°	1743	1684	1691
30°	1697	1638	1632
35°	1654	1584	1570
40°	1600	1529	1511
45°	1547	1474	1451
50°	1489	1417	1381
55°	1429	1350	1316
60°	1360	1271	1243
65°	1285	1189	1156
70°	1190	1089	1062
75°	1057	970	976
80°	899	817	811
85°	650	554	537

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°
 Vertical Angle: 90°
 Luminance: 1791 cd/sqm



TEST NUMBER: P907367

CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	219.7	1.4
10°-20°	618.3	3.9
20°-30°	908.6	5.7
30°-40°	1055.3	6.7
40°-50°	1054.0	6.7
50°-60°	919.0	5.8
60°-70°	679.4	4.3
70°-80°	384.4	2.4
80°-90°	107.4	0.7
90°-100°	111.3	0.7
100°-110°	414.9	2.6
110°-120°	1100.3	6.9
120°-130°	1824.9	11.5
130°-140°	1938.4	12.2
140°-150°	1801.5	11.4
150°-160°	1448.4	9.1
160°-170°	933.3	5.9
170°-180°	321.2	2.0
0°-30°	1746.6	11.0
0°-40°	2801.8	17.7
0°-60°	4774.8	30.1
0°-90°	5945.9	37.5
90°-120°	1626.4	10.3
90°-150°	7191.2	45.4
90°-180°	9894.0	62.5
0°-180°	15840.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2335	2335	2335	2335	2335	
5°	2335	2326	2301	2319	2315	222
15°	2222	2209	2180	2189	2178	626
25°	2011	1994	1955	1960	1955	926
35°	1735	1713	1677	1663	1652	1084
45°	1412	1396	1363	1338	1329	1090
55°	1069	1055	1028	1001	990	955
65°	721	707	685	664	653	713
75°	377	373	361	348	352	402
85°	92	90	88	81	79	103
90°	2	29	49	61	66	15
95°	159	78	95	108	105	188
105°	742	816	149	176	186	793
115°	1404	1446	1507	376	200	1382
125°	1985	2017	2064	2081	2088	1771
135°	2457	2496	2518	2542	2537	1898
145°	2850	2847	2889	2906	2894	1782
155°	3138	3116	3146	3160	3141	1446
165°	3306	3292	3299	3316	3299	934
175°	3382	3365	3370	3387	3363	322
180°	3375	3375	3375	3375	3375	



TEST NUMBER: P907367

CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2334.6	2334.6	2334.6	2334.6	2334.6
2.5°	2348.2	2337.0	2312.2	2334.6	2330.3
5°	2334.6	2325.8	2301.0	2318.9	2314.6
7.5°	2318.9	2305.6	2280.8	2298.9	2294.4
10°	2294.4	2278.7	2251.7	2269.6	2262.9
12.5°	2260.6	2247.2	2220.3	2231.5	2227.0
15°	2222.4	2209.1	2179.8	2188.9	2177.7
17.5°	2175.3	2162.0	2132.7	2143.8	2132.7
20°	2123.6	2110.3	2078.8	2085.5	2076.7
22.5°	2072.2	2051.9	2022.6	2022.6	2018.1
25°	2011.4	1993.6	1955.4	1959.7	1955.4
27.5°	1944.0	1928.3	1899.2	1892.6	1881.4
30°	1876.9	1858.7	1825.2	1818.5	1809.4
32.5°	1804.9	1791.6	1755.6	1742.0	1733.0
35°	1735.4	1713.0	1677.0	1663.4	1652.2
37.5°	1656.8	1636.5	1600.6	1584.8	1573.6
40°	1576.0	1557.9	1522.0	1502.0	1492.9
42.5°	1497.4	1479.3	1443.6	1421.0	1407.6
45°	1412.2	1396.4	1362.6	1338.1	1329.0
47.5°	1329.0	1313.3	1277.4	1252.6	1239.2
50°	1241.4	1230.2	1198.8	1167.3	1156.1
52.5°	1156.1	1140.4	1111.3	1086.6	1070.9
55°	1068.7	1055.1	1028.2	1001.3	990.1
57.5°	981.1	969.9	940.6	913.7	904.6
60°	893.4	884.6	853.2	828.4	821.7
62.5°	808.1	792.4	770.0	747.6	738.6
65°	720.7	707.2	684.8	664.5	653.3
67.5°	630.9	619.5	599.5	583.8	574.7
70°	547.8	538.8	518.5	502.8	494.0
72.5°	462.5	453.5	442.3	426.6	419.9
75°	377.0	372.8	361.3	348.0	352.5
77.5°	300.8	291.8	287.2	280.6	273.9
80°	224.6	222.2	217.7	211.0	206.5
82.5°	152.7	152.7	150.5	141.5	141.5
85°	91.9	89.8	87.6	80.7	78.6
87.5°	40.5	36.0	31.4	24.8	22.4
90°	2.3	29.3	48.7	61.2	65.8
92.5°	61.2	51.3	58.6	63.5	65.8
95°	158.6	78.0	95.1	107.6	105.0
97.5°	285.6	85.5	124.4	131.9	134.3
100°	432.4	97.7	139.2	158.6	163.6
102.5°	593.3	588.7	144.1	170.8	178.3
105°	742.4	815.7	149.1	175.7	185.6
107.5°	915.8	976.7	154.0	180.7	190.5
110°	1081.9	1133.0	427.4	183.3	192.8



TEST NUMBER: P907367

CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1238.2	1282.0	1240.6	187.9	195.5
115°	1404.1	1445.6	1506.8	376.1	200.4
117.5°	1548.2	1597.0	1638.7	1289.3	649.6
120°	1709.5	1746.0	1790.1	1819.4	1489.7
122.5°	1846.1	1885.2	1934.2	1948.7	1951.3
125°	1985.3	2017.2	2063.6	2080.7	2087.9
127.5°	2112.3	2146.5	2183.3	2207.7	2210.0
130°	2232.0	2271.2	2297.9	2324.8	2322.5
132.5°	2354.1	2386.0	2412.7	2434.7	2432.4
135°	2456.8	2495.9	2517.7	2542.3	2537.4
137.5°	2564.1	2593.4	2618.0	2642.4	2635.1
140°	2669.0	2688.8	2715.4	2737.5	2725.3
142.5°	2757.2	2774.3	2805.9	2825.3	2813.2
145°	2850.0	2847.4	2888.9	2906.0	2893.8
147.5°	2930.3	2923.1	2964.5	2976.7	2967.2
150°	3008.6	2991.5	3030.7	3045.2	3033.0
152.5°	3074.4	3055.0	3091.6	3106.3	3089.2
155°	3138.0	3116.2	3145.5	3160.0	3140.6
157.5°	3189.3	3169.9	3191.9	3209.0	3189.3
160°	3233.4	3218.6	3233.4	3247.9	3230.8
162.5°	3272.2	3257.7	3269.9	3287.0	3265.0
165°	3306.4	3291.9	3299.2	3316.3	3299.2
167.5°	3333.4	3318.6	3326.2	3343.3	3321.2
170°	3355.4	3340.7	3345.6	3362.7	3340.7
172.5°	3369.9	3355.4	3360.4	3377.5	3355.4
175°	3382.1	3365.0	3369.9	3387.1	3362.7
177.5°	3387.1	3369.9	3372.6	3389.7	3367.6
180°	3374.9	3374.9	3374.9	3374.9	3374.9



TEST NUMBER: P907367
 CATALOG NUMBER: DFN2DIP-TR4F0-060D100US835-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.14	8.90	9.19	9.96	11.40	7.71	8.47	8.76	9.53	10.97
	3H	9.79	10.47	10.86	11.54	13.00	9.32	10.00	10.38	11.07	12.52
	4H	10.37	11.02	11.45	12.09	13.55	9.90	10.55	10.98	11.62	13.08
	6H	10.77	11.36	11.85	12.44	13.91	10.29	10.89	11.38	11.96	13.44
	8H	10.87	11.43	11.96	12.52	13.99	10.39	10.96	11.49	12.05	13.52
	12H	10.91	11.45	12.01	12.53	14.03	10.43	10.97	11.53	12.05	13.55
4H	2H	8.59	9.23	9.67	10.30	11.77	8.24	8.89	9.33	9.96	11.42
	3H	10.44	10.98	11.54	12.08	13.56	10.05	10.59	11.14	11.69	13.16
	4H	11.15	11.65	12.25	12.74	14.23	10.75	11.24	11.85	12.33	13.83
	6H	11.66	12.09	12.77	13.20	14.69	11.25	11.68	12.36	12.79	14.28
	8H	11.81	12.21	12.91	13.31	14.82	11.40	11.79	12.50	12.90	14.40
	12H	11.88	12.24	13.00	13.35	14.86	11.46	11.81	12.58	12.93	14.44
8H	4H	11.34	11.74	12.45	12.84	14.35	10.98	11.38	12.09	12.48	13.99
	6H	11.97	12.30	13.10	13.44	14.95	11.61	11.93	12.73	13.08	14.58
	8H	12.19	12.47	13.32	13.60	15.13	11.82	12.11	12.95	13.23	14.76
	12H	12.32	12.57	13.45	13.69	15.25	11.93	12.18	13.07	13.31	14.87
12H	4H	11.32	11.68	12.44	12.80	14.31	10.97	11.33	12.09	12.45	13.96
	6H	12.00	12.28	13.13	13.41	14.93	11.65	11.93	12.78	13.06	14.58
	8H	12.23	12.49	13.37	13.61	15.17	11.88	12.13	13.01	13.25	14.81