

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907392

Luminaire Tested: DFN2DIP-TR4F0-070D070US835-RLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907392  
REPORT IS A COMBINATION OF REPORTS P900430 AND P897293  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-070D070US835-RLLFLL  
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12145.0 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 117.7  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9977  
Total Harmonic Distortion (THDi): 0.049  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907392  
CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907392  
 CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	107	107	107	107	99	99	99	99	83	83	83	68	68	68	55	55	55	49				49
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42				42
2	90	83	77	72	82	76	71	67	65	61	58	54	51	49	44	42	41	36				36
3	82	73	66	60	75	68	61	57	58	53	49	48	45	42	40	37	35	31				31
4	75	65	57	51	69	60	54	48	51	46	42	43	40	36	36	33	31	27				27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	29	27	24				24
6	64	52	44	39	59	49	42	37	42	36	32	35	31	28	30	26	24	21				21
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19				19
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17				17
9	51	39	32	27	47	37	30	26	32	27	23	27	23	20	23	20	18	16				16
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2298	2298	2298
5°	2302	2262	2276
10°	2279	2217	2202
15°	2248	2144	2088
20°	2206	2043	1947
25°	2164	1930	1811
30°	2107	1814	1639
35°	2051	1689	1488
40°	1994	1560	1315
45°	1928	1416	1157
50°	1860	1272	1004
55°	1788	1117	857
60°	1706	955	705
65°	1611	791	634
70°	1496	638	574
75°	1351	562	522
80°	1142	472	453
85°	796	315	340

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 1928 cd/sqm



TEST NUMBER: P907392

CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	271.1	2.2
10°-20°	744.3	6.1
20°-30°	1045.0	8.6
30°-40°	1139.2	9.4
40°-50°	1047.0	8.6
50°-60°	822.3	6.8
60°-70°	535.2	4.4
70°-80°	275.5	2.3
80°-90°	76.6	0.6
90°-100°	137.0	1.1
100°-110°	435.3	3.6
110°-120°	744.9	6.1
120°-130°	979.6	8.1
130°-140°	1099.6	9.1
140°-150°	1078.3	8.9
150°-160°	904.5	7.4
160°-170°	599.9	4.9
170°-180°	209.7	1.7
0°-30°	2060.5	17.0
0°-40°	3199.7	26.3
0°-60°	5068.9	41.7
0°-90°	5956.3	49.0
90°-120°	1317.2	10.8
90°-150°	4474.7	36.8
90°-180°	6189.0	51.0
0°-180°	12145.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	2	24	65	61	63	12
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	



TEST NUMBER: P907392

CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P907392

CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8



TEST NUMBER: P907392  
 CATALOG NUMBER: DFN2DIP-TR4F0-070D070US835-RLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.94	10.76	10.91	11.75	13.03	5.91	6.74	6.89	7.72	9.01
	3H	11.62	12.35	12.60	13.34	14.65	7.10	7.84	8.09	8.83	10.14
	4H	12.23	12.92	13.22	13.92	15.23	7.55	8.25	8.55	9.24	10.56
	6H	12.65	13.29	13.65	14.29	15.62	7.88	8.52	8.88	9.51	10.84
	8H	12.77	13.38	13.79	14.40	15.72	7.97	8.58	8.98	9.59	10.92
	12H	12.83	13.41	13.85	14.42	15.77	8.01	8.59	9.03	9.60	10.95
4H	2H	9.96	10.65	10.96	11.65	12.97	6.51	7.20	7.51	8.20	9.52
	3H	11.79	12.37	12.80	13.39	14.72	7.86	8.44	8.87	9.46	10.79
	4H	12.48	13.01	13.50	14.02	15.38	8.41	8.94	9.43	9.95	11.31
	6H	12.99	13.45	14.02	14.49	15.84	8.83	9.28	9.86	10.32	11.67
	8H	13.17	13.59	14.20	14.62	15.99	8.96	9.38	9.99	10.41	11.78
	12H	13.26	13.64	14.31	14.69	16.06	9.02	9.40	10.07	10.45	11.82
8H	4H	12.45	12.87	13.48	13.90	15.27	8.69	9.11	9.72	10.14	11.51
	6H	13.01	13.36	14.07	14.44	15.80	9.21	9.56	10.26	10.63	11.99
	8H	13.23	13.54	14.29	14.59	15.98	9.40	9.71	10.46	10.76	12.15
	12H	13.37	13.64	14.43	14.69	16.12	9.52	9.79	10.58	10.84	12.27
12H	4H	12.40	12.78	13.45	13.83	15.20	8.69	9.07	9.74	10.12	11.49
	6H	12.99	13.29	14.05	14.35	15.74	9.26	9.56	10.32	10.62	12.01
	8H	13.21	13.48	14.27	14.53	15.96	9.47	9.74	10.53	10.79	12.22