

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907394

Luminaire Tested: DFN2DIP-TR4F0-070D080US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907394
REPORT IS A COMBINATION OF REPORTS P900447 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D080US835-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14010.0 lumens
Efficiency: N/A
Efficacy: 112.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56
1	98	93	89	86	90	86	83	80	73	70	68	61	59	57	49	48	47
2	89	82	75	70	82	75	70	66	64	60	56	53	50	48	43	41	40
3	81	72	64	58	74	66	60	55	56	51	47	47	43	40	38	36	34
4	74	63	56	49	68	59	52	46	50	45	40	42	38	35	34	31	29
5	68	57	48	42	63	52	45	40	45	39	35	38	33	30	31	28	25
6	63	51	43	37	58	47	40	35	40	35	30	34	30	26	28	25	22
7	58	46	38	32	53	43	35	30	37	31	27	31	27	23	26	22	20
8	54	42	34	28	50	39	32	27	33	28	24	28	24	21	24	20	18
9	50	38	30	25	46	35	29	24	31	25	21	26	22	19	22	18	16
10	47	35	28	23	43	33	26	22	28	23	19	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2164	2164	2164
5°	2167	2134	2148
10°	2150	2105	2119
15°	2118	2070	2073
20°	2075	2022	2027
25°	2033	1964	1973
30°	1980	1911	1904
35°	1929	1848	1832
40°	1867	1784	1763
45°	1805	1720	1693
50°	1738	1653	1611
55°	1667	1575	1536
60°	1587	1483	1450
65°	1499	1387	1348
70°	1388	1271	1239
75°	1234	1131	1138
80°	1048	954	946
85°	759	647	627

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1973 cd/sqm

TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	256.4	1.8
10°-20°	721.3	5.1
20°-30°	1060.0	7.6
30°-40°	1231.1	8.8
40°-50°	1229.6	8.8
50°-60°	1072.2	7.7
60°-70°	792.6	5.7
70°-80°	448.4	3.2
80°-90°	125.6	0.9
90°-100°	156.6	1.1
100°-110°	497.5	3.6
110°-120°	851.3	6.1
120°-130°	1119.6	8.0
130°-140°	1256.7	9.0
140°-150°	1232.3	8.8
150°-160°	1033.7	7.4
160°-170°	685.6	4.9
170°-180°	239.6	1.7
0°-30°	2037.7	14.5
0°-40°	3268.8	23.3
0°-60°	5570.6	39.8
0°-90°	6937.2	49.5
90°-120°	1505.3	10.7
90°-150°	5113.9	36.5
90°-180°	7073.0	50.5
0°-180°	14010.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2724	2724	2724	2724	2724	
5°	2724	2714	2685	2705	2700	259
15°	2593	2577	2543	2554	2541	730
25°	2347	2326	2281	2286	2281	1080
35°	2025	1998	1956	1941	1928	1264
45°	1648	1629	1590	1561	1550	1271
55°	1247	1231	1200	1168	1155	1115
65°	841	825	799	775	762	831
75°	440	435	422	406	411	470
85°	107	105	102	94	92	120
90°	2	28	75	70	72	14
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	

TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2723.7	2723.7	2723.7	2723.7	2723.7
2.5°	2739.6	2726.5	2697.6	2723.7	2718.7
5°	2723.7	2713.5	2684.6	2705.4	2700.4
7.5°	2705.4	2689.8	2660.9	2682.1	2676.8
10°	2676.8	2658.4	2627.0	2647.9	2640.1
12.5°	2637.3	2621.8	2590.4	2603.4	2598.1
15°	2592.9	2577.3	2543.1	2553.7	2540.6
17.5°	2537.8	2522.3	2488.1	2501.2	2488.1
20°	2477.5	2462.0	2425.3	2433.1	2422.8
22.5°	2417.5	2393.9	2359.7	2359.7	2354.4
25°	2346.7	2325.8	2281.4	2286.4	2281.4
27.5°	2268.0	2249.7	2215.8	2208.0	2194.9
30°	2189.7	2168.5	2129.4	2121.6	2111.0
32.5°	2105.7	2090.2	2048.2	2032.4	2021.8
35°	2024.6	1998.5	1956.5	1940.7	1927.6
37.5°	1932.9	1909.3	1867.3	1849.0	1835.9
40°	1838.7	1817.6	1775.6	1752.3	1741.7
42.5°	1747.0	1725.9	1684.2	1657.8	1642.2
45°	1647.5	1629.2	1589.7	1561.1	1550.5
47.5°	1550.5	1532.2	1490.2	1461.3	1445.8
50°	1448.3	1435.2	1398.5	1361.9	1348.8
52.5°	1348.8	1330.5	1296.6	1267.7	1249.3
55°	1246.8	1231.0	1199.6	1168.2	1155.1
57.5°	1144.6	1131.5	1097.3	1065.9	1055.4
60°	1042.3	1032.0	995.4	966.5	958.7
62.5°	942.8	924.5	898.4	872.3	861.7
65°	840.9	825.0	798.9	775.3	762.2
67.5°	736.1	722.8	699.4	681.1	670.5
70°	639.1	628.6	604.9	586.6	576.3
72.5°	539.6	529.1	516.0	497.7	489.9
75°	439.9	434.9	421.5	406.0	411.3
77.5°	351.0	340.4	335.1	327.3	319.6
80°	262.0	259.3	254.0	246.2	240.9
82.5°	178.1	178.1	175.6	165.1	165.1
85°	107.3	104.8	102.3	94.2	91.7
87.5°	47.2	42.0	36.7	28.9	26.1
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5

TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1

TEST NUMBER: P907394

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.90	10.76	10.86	11.74	13.01	9.47	10.33	10.43	11.30	12.58
	3H	11.56	12.33	12.53	13.32	14.62	11.09	11.86	12.06	12.84	14.14
	4H	12.15	12.88	13.13	13.87	15.17	11.68	12.40	12.66	13.39	14.70
	6H	12.55	13.22	13.55	14.21	15.53	12.07	12.74	13.07	13.74	15.06
	8H	12.65	13.29	13.66	14.30	15.62	12.18	12.82	13.18	13.83	15.15
	12H	12.70	13.31	13.71	14.31	15.66	12.22	12.83	13.23	13.83	15.18
4H	2H	10.36	11.09	11.36	12.08	13.39	10.02	10.75	11.01	11.74	13.04
	3H	12.23	12.84	13.23	13.85	15.18	11.84	12.44	12.84	13.46	14.78
	4H	12.94	13.50	13.95	14.51	15.86	12.54	13.09	13.55	14.10	15.45
	6H	13.46	13.94	14.48	14.97	16.31	13.05	13.53	14.07	14.56	15.90
	8H	13.61	14.05	14.63	15.08	16.44	13.20	13.64	14.22	14.67	16.03
	12H	13.68	14.08	14.72	15.13	16.49	13.26	13.66	14.30	14.70	16.07
8H	4H	13.14	13.59	14.16	14.61	15.97	12.78	13.23	13.80	14.25	15.61
	6H	13.77	14.14	14.82	15.21	16.56	13.41	13.78	14.45	14.85	16.20
	8H	13.99	14.32	15.04	15.37	16.74	13.62	13.95	14.68	15.00	16.38
	12H	14.12	14.41	15.18	15.46	16.87	13.74	14.02	14.80	15.07	16.49
12H	4H	13.12	13.53	14.16	14.57	15.93	12.77	13.18	13.81	14.22	15.58
	6H	13.80	14.13	14.85	15.18	16.55	13.45	13.77	14.50	14.83	16.20
	8H	14.04	14.33	15.10	15.38	16.79	13.68	13.97	14.74	15.02	16.44