

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923493

Luminaire Tested: DFN2DIP-TR3F0-040D050US940-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923493
REPORT IS A COMBINATION OF REPORTS P901822 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-040D050US940-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7445.8 lumens
Efficiency: N/A
Efficacy: 103.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 72.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	78	78	78	62	62	62	48	48	48
1	96	92	88	85	87	84	81	78	69	67	65	55	54	53	43	42	41
2	88	81	75	70	80	74	69	65	61	57	54	49	47	44	38	36	35
3	80	71	64	59	73	65	59	54	54	50	46	44	41	38	34	32	30
4	74	63	56	50	67	58	52	46	48	43	40	39	36	33	31	28	26
5	68	57	49	43	62	52	45	40	43	38	34	35	32	29	28	25	23
6	62	51	43	37	57	47	40	35	39	34	30	32	28	25	25	23	21
7	58	46	38	33	53	42	36	31	36	30	27	29	25	23	23	21	19
8	54	42	34	29	49	39	32	27	33	27	24	27	23	20	21	19	17
9	50	38	31	26	46	35	29	24	30	25	21	25	21	18	20	17	15
10	47	35	28	23	43	32	26	22	28	23	19	23	19	17	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1837	1837	1837
5°	1839	1806	1818
10°	1820	1769	1758
15°	1794	1709	1665
20°	1759	1627	1552
25°	1724	1535	1443
30°	1678	1442	1305
35°	1632	1341	1183
40°	1586	1237	1044
45°	1531	1121	919
50°	1475	1005	796
55°	1417	881	678
60°	1349	752	557
65°	1271	620	500
70°	1176	498	450
75°	1057	435	407
80°	884	360	349
85°	602	233	255

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1531 cd/sqm

TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.2	1.9
10°-20°	379.3	5.1
20°-30°	532.5	7.2
30°-40°	580.5	7.8
40°-50°	533.5	7.2
50°-60°	419.0	5.6
60°-70°	272.7	3.7
70°-80°	140.4	1.9
80°-90°	38.5	0.5
90°-100°	49.6	0.7
100°-110°	185.0	2.5
110°-120°	490.6	6.6
120°-130°	813.6	10.9
130°-140°	864.3	11.6
140°-150°	803.2	10.8
150°-160°	645.8	8.7
160°-170°	416.1	5.6
170°-180°	143.2	1.9
0°-30°	1049.9	14.1
0°-40°	1630.4	21.9
0°-60°	2582.9	34.7
0°-90°	3034.5	40.8
90°-120°	725.2	9.7
90°-150°	3206.2	43.1
90°-180°	4411.0	59.2
0°-180°	7445.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1474	1474	1474	1474	1474	
5°	1474	1468	1450	1462	1458	140
15°	1402	1387	1342	1317	1304	395
25°	1273	1230	1142	1087	1067	585
35°	1097	1029	911	827	798	686
45°	896	807	667	572	540	692
55°	682	578	434	354	328	609
65°	460	352	232	187	183	456
75°	245	152	107	97	96	260
85°	57	29	25	25	25	66
90°	1	13	22	27	29	7
95°	71	35	42	48	47	84
105°	331	364	66	78	83	354
115°	626	644	672	168	89	616
125°	885	899	920	928	931	789
135°	1095	1113	1122	1134	1131	846
145°	1271	1270	1288	1296	1290	795
155°	1399	1389	1402	1409	1400	645
165°	1474	1468	1471	1478	1471	416
175°	1508	1500	1502	1510	1499	144
180°	1505	1505	1505	1505	1505	

TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1474.2	1474.2	1474.2	1474.2	1474.2
2.5°	1480.9	1474.2	1459.5	1472.9	1470.2
5°	1474.2	1467.5	1450.1	1462.1	1458.2
7.5°	1462.1	1454.2	1435.6	1440.7	1434.1
10°	1446.2	1436.8	1410.2	1406.0	1398.2
12.5°	1426.2	1414.2	1378.0	1370.1	1355.4
15°	1402.1	1387.4	1342.1	1316.8	1303.5
17.5°	1374.1	1352.7	1296.6	1267.4	1246.0
20°	1342.1	1315.4	1248.7	1215.4	1186.0
22.5°	1307.4	1276.8	1199.3	1154.0	1134.1
25°	1272.7	1230.0	1141.9	1087.4	1067.2
27.5°	1231.5	1186.0	1088.6	1025.9	995.1
30°	1187.4	1136.6	1029.8	961.9	925.9
32.5°	1144.7	1083.2	973.9	893.9	860.4
35°	1096.7	1028.6	911.2	827.2	797.7
37.5°	1050.0	976.5	852.5	760.4	727.1
40°	1000.6	920.6	791.1	696.4	661.7
42.5°	949.8	864.5	729.8	631.0	597.7
45°	896.5	807.1	667.1	572.3	540.3
47.5°	845.9	751.2	607.1	512.3	483.0
50°	789.8	695.1	548.3	456.2	428.3
52.5°	735.0	635.0	492.3	404.2	378.9
55°	681.7	577.6	433.5	353.6	328.2
57.5°	627.1	520.3	381.6	306.8	285.5
60°	571.0	464.2	326.8	258.9	237.6
62.5°	516.4	409.7	280.1	216.2	205.5
65°	460.3	352.1	232.1	186.8	182.7
67.5°	407.0	298.8	186.8	164.1	160.1
70°	350.9	246.8	154.7	141.4	136.0
72.5°	297.6	198.8	129.4	118.8	116.1
75°	245.4	152.0	106.7	97.4	96.1
77.5°	193.5	108.0	84.1	78.7	76.0
80°	145.3	77.4	63.9	58.8	58.8
82.5°	101.4	52.1	44.1	41.3	41.3
85°	57.3	29.3	25.3	25.3	25.3
87.5°	21.4	10.6	10.6	9.4	9.4
90°	1.1	13.0	21.8	27.3	29.3
92.5°	27.3	22.9	26.1	28.4	29.3
95°	70.7	34.8	42.4	48.0	46.8
97.5°	127.3	38.2	55.5	58.9	59.8
100°	192.8	43.6	62.1	70.7	72.9
102.5°	264.6	262.4	64.3	76.2	79.5
105°	331.0	363.7	66.4	78.4	82.8
107.5°	408.3	435.4	68.7	80.5	85.0
110°	482.4	505.2	190.6	81.7	86.0

TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	552.1	571.6	553.1	83.8	87.1
115°	626.1	644.5	671.8	167.7	89.3
117.5°	690.3	712.0	730.7	574.8	289.6
120°	762.1	778.5	798.1	811.2	664.1
122.5°	823.0	840.5	862.4	868.9	870.0
125°	885.1	899.4	920.1	927.6	930.9
127.5°	941.7	957.0	973.5	984.3	985.3
130°	995.1	1012.6	1024.5	1036.5	1035.5
132.5°	1049.6	1063.8	1075.7	1085.6	1084.5
135°	1095.4	1112.9	1122.5	1133.5	1131.3
137.5°	1143.2	1156.3	1167.2	1178.1	1174.9
140°	1190.0	1198.8	1210.7	1220.5	1215.1
142.5°	1229.3	1237.0	1251.1	1259.7	1254.3
145°	1270.7	1269.5	1288.0	1295.7	1290.2
147.5°	1306.5	1303.2	1321.8	1327.2	1322.9
150°	1341.4	1333.8	1351.2	1357.7	1352.3
152.5°	1370.7	1362.1	1378.4	1385.0	1377.3
155°	1399.1	1389.4	1402.4	1408.9	1400.3
157.5°	1421.9	1413.3	1423.1	1430.7	1421.9
160°	1441.6	1435.0	1441.6	1448.0	1440.5
162.5°	1458.9	1452.5	1457.9	1465.5	1455.7
165°	1474.2	1467.8	1471.0	1478.5	1471.0
167.5°	1486.2	1479.6	1483.0	1490.6	1480.8
170°	1496.0	1489.4	1491.7	1499.2	1489.4
172.5°	1502.5	1496.0	1498.3	1505.8	1496.0
175°	1508.0	1500.3	1502.5	1510.1	1499.2
177.5°	1510.1	1502.5	1503.7	1511.3	1501.5
180°	1504.7	1504.7	1504.7	1504.7	1504.7

TEST NUMBER: P923493

CATALOG NUMBER: DFN2DIP-TR3F0-040D050US940-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	8.28	9.04	9.32	10.08	11.48	4.25	5.02	5.29	6.06	7.46
	3H	9.94	10.62	10.99	11.67	13.09	5.43	6.11	6.48	7.16	8.58
	4H	10.54	11.18	11.60	12.24	13.66	5.88	6.52	6.94	7.57	9.00
	6H	10.95	11.54	12.02	12.60	14.04	6.19	6.78	7.26	7.84	9.28
	8H	11.07	11.63	12.15	12.71	14.14	6.28	6.84	7.35	7.91	9.34
	12H	11.13	11.66	12.21	12.73	14.18	6.31	6.85	7.39	7.91	9.37
4H	2H	8.29	8.93	9.35	9.98	11.41	4.84	5.48	5.90	6.53	7.96
	3H	10.10	10.64	11.17	11.71	13.15	6.17	6.71	7.25	7.79	9.23
	4H	10.78	11.27	11.86	12.34	13.80	6.72	7.21	7.79	8.28	9.74
	6H	11.28	11.70	12.37	12.80	14.25	7.12	7.55	8.21	8.64	10.09
	8H	11.45	11.85	12.54	12.93	14.40	7.25	7.64	8.34	8.73	10.20
	12H	11.54	11.89	12.64	12.99	14.47	7.31	7.66	8.41	8.76	10.24
8H	4H	10.74	11.14	11.83	12.22	13.69	6.98	7.38	8.07	8.46	9.93
	6H	11.30	11.62	12.41	12.75	14.22	7.49	7.82	8.60	8.94	10.41
	8H	11.51	11.79	12.62	12.90	14.39	7.68	7.96	8.80	9.07	10.56
	12H	11.64	11.88	12.76	12.99	14.52	7.79	8.04	8.91	9.14	10.67
12H	4H	10.69	11.05	11.80	12.15	13.62	6.98	7.34	8.09	8.44	9.91
	6H	11.27	11.55	12.39	12.66	14.15	7.54	7.82	8.66	8.93	10.42
	8H	11.48	11.73	12.60	12.84	14.36	7.74	7.99	8.86	9.10	10.62

END OF REPORT