

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907396

Luminaire Tested: DFN2DIP-TR4F0-070D080US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907396
REPORT IS A COMBINATION OF REPORTS P900448 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-070D080US835-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13030.0 lumens
Efficiency: N/A
Efficacy: 104.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 124.7
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9977
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20					20					20					20
RC	80				70					50					30					10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	106	106	106	106	97	97	97	97	81	81	81	66	66	66	52	52	52	46	46	46
1	97	93	89	86	89	86	82	80	72	69	67	59	57	56	47	46	45	39	39	39
2	89	82	76	71	81	75	70	66	63	60	56	52	49	47	42	40	38	34	34	34
3	81	72	65	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29	29	29
4	75	64	57	51	68	59	53	48	50	45	41	42	38	35	34	31	29	25	25	25
5	69	57	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	22	22	22
6	63	52	44	38	58	48	41	36	41	35	31	34	30	27	28	25	23	20	20	20
7	59	47	39	34	54	43	37	32	37	32	28	31	27	24	26	23	20	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	18	16	16	16
9	51	39	32	27	47	36	30	25	31	26	22	26	22	20	22	19	17	15	15	15
10	47	36	29	24	44	33	27	23	29	24	20	24	20	18	20	17	15	13	13	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2298	2298	2298
5°	2302	2262	2276
10°	2279	2217	2202
15°	2248	2144	2088
20°	2206	2043	1947
25°	2164	1930	1811
30°	2107	1814	1639
35°	2051	1689	1488
40°	1994	1560	1315
45°	1928	1416	1157
50°	1860	1272	1004
55°	1788	1117	857
60°	1706	955	705
65°	1611	791	634
70°	1496	638	574
75°	1351	562	522
80°	1142	472	453
85°	796	315	340

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1973 cd/sqm

TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	271.1	2.1
10°-20°	744.3	5.7
20°-30°	1045.0	8.0
30°-40°	1139.2	8.7
40°-50°	1047.0	8.0
50°-60°	822.3	6.3
60°-70°	535.2	4.1
70°-80°	275.5	2.1
80°-90°	77.5	0.6
90°-100°	156.6	1.2
100°-110°	497.5	3.8
110°-120°	851.3	6.5
120°-130°	1119.6	8.6
130°-140°	1256.7	9.6
140°-150°	1232.3	9.5
150°-160°	1033.7	7.9
160°-170°	685.6	5.3
170°-180°	239.6	1.8
0°-30°	2060.5	15.8
0°-40°	3199.7	24.6
0°-60°	5068.9	38.9
0°-90°	5957.2	45.7
90°-120°	1505.3	11.6
90°-150°	5113.9	39.2
90°-180°	7073.0	54.3
0°-180°	13030.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2893	2893	2893	2893	2893	
5°	2893	2880	2846	2870	2862	274
15°	2752	2723	2634	2584	2558	775
25°	2498	2414	2241	2134	2094	1149
35°	2152	2019	1788	1623	1566	1347
45°	1760	1584	1309	1123	1060	1359
55°	1338	1134	851	694	644	1195
65°	903	691	456	367	359	896
75°	482	298	209	191	189	509
85°	112	58	50	50	50	129
90°	2	28	75	70	72	13
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	

TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2893.1	2893.1	2893.1	2893.1	2893.1
2.5°	2906.1	2893.1	2864.2	2890.6	2885.3
5°	2893.1	2880.0	2845.9	2869.5	2861.7
7.5°	2869.5	2853.9	2817.3	2827.5	2814.5
10°	2838.1	2819.8	2767.5	2759.5	2743.9
12.5°	2798.9	2775.3	2704.5	2688.9	2660.0
15°	2751.7	2722.8	2633.9	2584.2	2558.1
17.5°	2696.7	2654.8	2544.8	2487.2	2445.3
20°	2633.9	2581.4	2450.6	2385.3	2327.5
22.5°	2565.9	2505.6	2353.6	2264.7	2225.6
25°	2497.8	2413.9	2241.1	2133.9	2094.5
27.5°	2416.7	2327.5	2136.4	2013.4	1953.1
30°	2330.3	2230.6	2021.1	1887.8	1817.0
32.5°	2246.4	2125.9	1911.4	1754.2	1688.6
35°	2152.2	2018.6	1788.4	1623.4	1565.6
37.5°	2060.6	1916.4	1673.1	1492.2	1427.0
40°	1963.6	1806.7	1552.5	1366.7	1298.6
42.5°	1864.2	1696.7	1432.2	1238.3	1173.1
45°	1759.5	1583.9	1309.2	1123.1	1060.3
47.5°	1660.0	1474.2	1191.4	1005.3	947.8
50°	1550.0	1364.2	1076.1	895.3	840.6
52.5°	1442.5	1246.1	966.1	793.3	743.6
55°	1337.8	1133.6	850.8	693.9	644.2
57.5°	1230.6	1021.1	748.9	602.2	560.3
60°	1120.6	911.1	641.4	508.1	466.1
62.5°	1013.3	803.9	549.7	424.2	403.3
65°	903.3	691.1	455.6	366.7	358.6
67.5°	798.6	586.4	366.7	321.9	314.2
70°	688.6	484.4	303.6	277.5	266.9
72.5°	583.9	390.0	253.9	233.1	227.8
75°	481.7	298.3	209.4	191.1	188.6
77.5°	379.7	211.9	165.0	154.4	149.2
80°	285.3	151.9	125.6	115.3	115.3
82.5°	198.9	102.2	86.4	81.1	81.1
85°	112.5	57.5	49.7	49.7	49.7
87.5°	41.9	20.8	20.8	18.3	18.3
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5



TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1

TEST NUMBER: P907396

CATALOG NUMBER: DFN2DIP-TR4F0-070D080US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.62	10.41	10.62	11.42	12.75	5.59	6.39	6.59	7.39	8.73
	3H	11.29	12.00	12.30	13.02	14.37	6.78	7.49	7.79	8.51	9.86
	4H	11.90	12.57	12.92	13.59	14.95	7.23	7.90	8.25	8.92	10.28
	6H	12.32	12.94	13.35	13.96	15.34	7.55	8.17	8.58	9.19	10.56
	8H	12.44	13.03	13.48	14.07	15.44	7.64	8.23	8.68	9.27	10.64
	12H	12.50	13.06	13.55	14.10	15.49	7.68	8.24	8.72	9.27	10.67
4H	2H	9.63	10.31	10.66	11.32	12.69	6.18	6.86	7.21	7.87	9.24
	3H	11.46	12.02	12.50	13.06	14.44	7.53	8.09	8.57	9.14	10.51
	4H	12.15	12.66	13.19	13.70	15.10	8.08	8.59	9.12	9.63	11.03
	6H	12.66	13.10	13.72	14.16	15.56	8.50	8.94	9.55	10.00	11.39
	8H	12.84	13.25	13.89	14.30	15.71	8.62	9.04	9.68	10.09	11.50
	12H	12.93	13.30	14.00	14.37	15.78	8.69	9.06	9.76	10.13	11.54
8H	4H	12.11	12.52	13.17	13.58	14.99	8.36	8.77	9.41	9.82	11.23
	6H	12.68	13.02	13.76	14.11	15.52	8.87	9.21	9.95	10.31	11.71
	8H	12.89	13.19	13.98	14.27	15.70	9.07	9.36	10.15	10.44	11.87
	12H	13.03	13.29	14.12	14.37	15.84	9.18	9.45	10.27	10.52	11.99
12H	4H	12.06	12.44	13.14	13.50	14.92	8.36	8.73	9.43	9.80	11.21
	6H	12.65	12.95	13.74	14.03	15.46	8.92	9.22	10.01	10.30	11.73
	8H	12.87	13.13	13.96	14.21	15.68	9.13	9.39	10.22	10.47	11.94