

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923556

Luminaire Tested: DFN2DIP-TR3F0-060D080US940-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P923556
REPORT IS A COMBINATION OF REPORTS P900348 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-060D080US940-RLLFLL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 10861.0 lumens
Efficiency: N/A
Efficacy: 91.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 118.5
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9789
Total Harmonic Distortion (THDi): 0.074
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	49	49	49
1	96	92	89	85	88	84	81	78	70	67	65	56	55	53	44	43	42
2	88	81	75	70	80	74	69	65	61	58	55	50	47	45	39	37	36
3	81	72	65	59	73	66	60	55	55	50	47	44	41	39	35	33	31
4	74	64	56	50	67	58	52	47	49	44	40	40	36	33	31	29	27
5	68	57	49	43	62	52	45	40	44	39	35	36	32	29	28	26	24
6	63	51	43	38	57	47	40	35	40	34	30	33	29	26	26	23	21
7	58	46	38	33	53	43	36	31	36	31	27	30	26	23	24	21	19
8	54	42	34	29	49	39	32	28	33	28	24	27	23	21	22	19	17
9	50	38	31	26	46	36	29	25	30	25	22	25	21	19	20	18	16
10	47	35	28	24	43	33	26	22	28	23	19	23	19	17	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2756	2756	2756
5°	2758	2709	2727
10°	2730	2654	2637
15°	2690	2564	2498
20°	2639	2441	2328
25°	2587	2303	2164
30°	2517	2163	1957
35°	2448	2011	1775
40°	2378	1855	1567
45°	2297	1682	1378
50°	2213	1508	1194
55°	2125	1322	1016
60°	2024	1128	835
65°	1907	930	749
70°	1764	746	675
75°	1585	653	611
80°	1326	540	524
85°	903	350	383

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2297 cd/sqm

TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.2	1.9
10°-20°	568.9	5.2
20°-30°	798.7	7.4
30°-40°	870.7	8.0
40°-50°	800.3	7.4
50°-60°	628.5	5.8
60°-70°	409.1	3.8
70°-80°	210.6	1.9
80°-90°	60.2	0.6
90°-100°	139.6	1.3
100°-110°	443.6	4.1
110°-120°	759.1	7.0
120°-130°	998.3	9.2
130°-140°	1120.6	10.3
140°-150°	1098.9	10.1
150°-160°	921.8	8.5
160°-170°	611.3	5.6
170°-180°	213.7	2.0
0°-30°	1574.9	14.5
0°-40°	2445.6	22.5
0°-60°	3874.3	35.7
0°-90°	4554.1	41.9
90°-120°	1342.3	12.4
90°-150°	4560.1	42.0
90°-180°	6307.0	58.1
0°-180°	10861.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2211	2211	2211	2211	2211	
5°	2211	2201	2175	2193	2187	210
15°	2103	2081	2013	1975	1955	593
25°	1909	1845	1713	1631	1601	878
35°	1645	1543	1367	1241	1197	1030
45°	1345	1211	1001	858	810	1039
55°	1022	866	650	530	492	914
65°	690	528	348	280	274	685
75°	368	228	160	146	144	389
85°	86	44	38	38	38	99
90°	2	24	67	63	65	11
95°	99	118	122	122	118	111
105°	410	415	419	422	422	432
115°	762	773	769	767	762	753
125°	1108	1125	1120	1113	1111	990
135°	1433	1454	1458	1456	1451	1108
145°	1740	1754	1764	1766	1759	1087
155°	1990	1995	2001	2010	2004	916
165°	2164	2162	2162	2176	2166	611
175°	2252	2247	2242	2256	2244	214
180°	2256	2256	2256	2256	2256	

TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2211.3	2211.3	2211.3	2211.3	2211.3
2.5°	2221.3	2211.3	2189.1	2209.3	2205.3
5°	2211.3	2201.3	2175.1	2193.3	2187.3
7.5°	2193.3	2181.3	2153.3	2161.1	2151.2
10°	2169.2	2155.2	2115.3	2109.2	2097.2
12.5°	2139.3	2121.2	2067.1	2055.2	2033.1
15°	2103.2	2081.1	2013.1	1975.1	1955.2
17.5°	2061.2	2029.1	1945.0	1901.0	1869.0
20°	2013.1	1973.0	1873.0	1823.1	1779.0
22.5°	1961.1	1915.0	1798.9	1731.0	1701.0
25°	1909.2	1845.0	1713.0	1631.0	1600.9
27.5°	1847.2	1779.0	1632.9	1538.8	1492.8
30°	1781.1	1704.9	1544.8	1442.9	1388.7
32.5°	1717.0	1624.9	1461.0	1340.8	1290.7
35°	1645.0	1542.9	1366.9	1240.7	1196.6
37.5°	1574.9	1464.7	1278.8	1140.6	1090.7
40°	1500.8	1380.9	1186.6	1044.5	992.6
42.5°	1424.9	1296.8	1094.7	946.5	896.6
45°	1344.8	1210.6	1000.7	858.4	810.4
47.5°	1268.8	1126.8	910.6	768.4	724.4
50°	1184.7	1042.7	822.5	684.3	642.5
52.5°	1102.5	952.4	738.4	606.4	568.4
55°	1022.5	866.5	650.3	530.4	492.3
57.5°	940.6	780.4	572.4	460.3	428.2
60°	856.5	696.4	490.3	388.3	356.2
62.5°	774.5	614.5	420.2	324.2	308.3
65°	690.5	528.2	348.2	280.3	274.1
67.5°	610.4	448.2	280.3	246.1	240.1
70°	526.3	370.2	232.0	212.1	204.0
72.5°	446.3	298.1	194.0	178.2	174.1
75°	368.2	228.0	160.1	146.1	144.2
77.5°	290.3	162.0	126.1	118.1	114.0
80°	218.0	116.1	95.9	88.1	88.1
82.5°	152.0	78.1	66.0	62.0	62.0
85°	86.0	44.0	38.0	38.0	38.0
87.5°	32.1	16.0	16.0	14.0	14.0
90°	2.1	24.5	66.7	62.6	64.6
92.5°	42.2	57.2	59.2	61.2	61.2
95°	99.3	118.3	121.7	121.7	118.3
97.5°	165.3	183.0	190.5	190.5	190.5
100°	241.5	257.1	262.5	262.5	260.5
102.5°	321.7	333.3	340.7	342.8	340.7
105°	409.5	414.9	419.0	422.4	422.4
107.5°	496.5	504.7	504.7	506.0	496.5
110°	580.9	591.7	591.7	591.7	586.3

TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	672.0	683.6	681.5	676.1	672.0
115°	761.8	772.7	769.3	767.2	761.8
117.5°	850.9	865.9	856.3	850.9	845.4
120°	940.7	955.6	940.7	940.7	934.5
122.5°	1022.3	1041.3	1031.8	1026.4	1022.3
125°	1108.0	1125.0	1119.5	1113.4	1111.4
127.5°	1191.7	1212.7	1205.2	1197.1	1191.7
130°	1269.9	1294.3	1290.9	1286.9	1279.4
132.5°	1357.6	1376.6	1378.0	1368.5	1363.1
135°	1433.1	1454.2	1458.3	1456.3	1450.8
137.5°	1517.4	1534.5	1537.8	1536.5	1528.3
140°	1591.6	1608.6	1618.1	1618.1	1610.6
142.5°	1667.8	1684.8	1690.2	1692.3	1684.8
145°	1739.9	1753.5	1764.3	1766.4	1758.9
147.5°	1804.5	1821.5	1829.6	1833.1	1825.6
150°	1871.2	1882.7	1890.2	1896.3	1890.2
152.5°	1930.3	1941.9	1951.4	1958.9	1951.4
155°	1989.5	1994.9	2001.1	2010.5	2004.5
157.5°	2040.5	2044.6	2048.0	2061.5	2052.1
160°	2086.1	2090.2	2092.2	2103.7	2095.6
162.5°	2128.2	2128.2	2130.3	2143.2	2133.7
165°	2164.3	2162.2	2162.2	2175.9	2166.3
167.5°	2196.9	2190.8	2190.8	2204.4	2194.9
170°	2221.4	2216.0	2213.9	2227.6	2216.0
172.5°	2238.5	2233.0	2231.0	2244.5	2233.0
175°	2252.0	2246.6	2242.5	2256.1	2244.5
177.5°	2259.5	2254.1	2250.0	2261.6	2250.0
180°	2256.1	2256.1	2256.1	2256.1	2256.1

TEST NUMBER: P923556

CATALOG NUMBER: DFN2DIP-TR3F0-060D080US940-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.81	10.58	10.84	11.61	13.00	5.79	6.56	6.82	7.59	8.97
	3H	11.48	12.16	12.51	13.20	14.61	6.97	7.65	8.01	8.70	10.10
	4H	12.07	12.73	13.13	13.77	15.18	7.41	8.06	8.46	9.11	10.52
	6H	12.49	13.08	13.55	14.13	15.56	7.72	8.32	8.79	9.37	10.79
	8H	12.61	13.17	13.67	14.24	15.66	7.81	8.38	8.88	9.44	10.86
	12H	12.66	13.20	13.73	14.26	15.70	7.85	8.39	8.92	9.45	10.89
4H	2H	9.82	10.47	10.88	11.52	12.93	6.37	7.02	7.43	8.07	9.48
	3H	11.63	12.17	12.70	13.25	14.67	7.71	8.25	8.77	9.32	10.75
	4H	12.32	12.81	13.39	13.87	15.32	8.25	8.75	9.32	9.81	11.25
	6H	12.82	13.24	13.90	14.33	15.77	8.66	9.08	9.74	10.17	11.61
	8H	12.99	13.38	14.07	14.46	15.92	8.78	9.18	9.86	10.26	11.72
	12H	13.07	13.43	14.17	14.53	15.99	8.84	9.20	9.94	10.29	11.75
8H	4H	12.28	12.67	13.36	13.75	15.21	8.52	8.92	9.60	10.00	11.45
	6H	12.83	13.16	13.93	14.28	15.73	9.03	9.36	10.13	10.48	11.93
	8H	13.04	13.33	14.15	14.43	15.90	9.21	9.50	10.32	10.60	12.08
	12H	13.17	13.42	14.28	14.52	16.03	9.33	9.58	10.44	10.68	12.19
12H	4H	12.23	12.59	13.32	13.68	15.14	8.52	8.88	9.62	9.97	11.43
	6H	12.81	13.09	13.92	14.20	15.67	9.07	9.36	10.18	10.46	11.94
	8H	13.02	13.27	14.13	14.37	15.88	9.28	9.53	10.39	10.63	12.14

END OF REPORT