

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907466

Luminaire Tested: DFN2DIP-TR4F0-090D080US835-FLLFLL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P907466  
REPORT IS A COMBINATION OF REPORTS P900451 AND P897293  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR4F0-090D080US835-FLLFLL  
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 15990.0 lumens  
Efficiency: N/A  
Efficacy: 109.1 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29  
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 146.6  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.099  
Total Harmonic Distortion (THDi): 0.979  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P907466  
CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

### Luminous Intensity Polar Plot





TEST NUMBER: P907466

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				20	
RC	80				70				50				30				10				0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	73	73	73	61	61	61	56				56
1	99	95	91	87	92	88	85	82	76	73	71	65	63	61	54	53	52	47				47
2	90	83	77	71	84	77	72	67	67	62	59	57	54	51	48	46	44	39				39
3	82	73	65	59	76	68	61	56	59	54	50	50	46	43	42	40	37	33				33
4	75	64	56	50	70	60	53	48	52	47	42	45	41	37	38	35	32	29				29
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25				25
6	64	52	43	37	59	48	41	36	42	36	32	36	32	28	31	27	25	22				22
7	59	47	39	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19				19
8	55	42	35	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17				17
9	51	39	31	26	47	36	30	25	32	26	22	28	23	20	24	20	18	16				16
10	48	36	28	23	44	33	27	22	30	24	20	26	21	18	22	19	16	14				14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2782	2782	2782
5°	2786	2743	2762
10°	2764	2706	2724
15°	2723	2662	2666
20°	2668	2600	2606
25°	2614	2526	2537
30°	2545	2457	2449
35°	2481	2376	2355
40°	2401	2293	2267
45°	2321	2211	2176
50°	2234	2125	2071
55°	2143	2025	1975
60°	2040	1906	1864
65°	1928	1783	1734
70°	1785	1634	1593
75°	1586	1455	1464
80°	1348	1226	1216
85°	975	832	806

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2321 cd/sqm



TEST NUMBER: P907466

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	329.6	2.1
10°-20°	927.4	5.8
20°-30°	1362.9	8.5
30°-40°	1582.9	9.9
40°-50°	1580.9	9.9
50°-60°	1378.5	8.6
60°-70°	1019.0	6.4
70°-80°	576.6	3.6
80°-90°	159.4	1.0
90°-100°	156.6	1.0
100°-110°	497.5	3.1
110°-120°	851.3	5.3
120°-130°	1119.6	7.0
130°-140°	1256.7	7.9
140°-150°	1232.3	7.7
150°-160°	1033.7	6.5
160°-170°	685.6	4.3
170°-180°	239.6	1.5
0°-30°	2619.9	16.4
0°-40°	4202.8	26.3
0°-60°	7162.3	44.8
0°-90°	8917.2	55.8
90°-120°	1505.3	9.4
90°-150°	5113.9	32.0
90°-180°	7073.0	44.2
0°-180°	15990.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	3502	3502	3502	3502	3502	
5°	3502	3489	3452	3478	3472	332
15°	3334	3314	3270	3283	3266	939
25°	3017	2990	2933	2940	2933	1388
35°	2603	2570	2516	2495	2478	1626
45°	2118	2095	2044	2007	1994	1635
55°	1603	1583	1542	1502	1485	1433
65°	1081	1061	1027	997	980	1069
75°	566	559	542	522	529	604
85°	138	135	132	121	118	154
90°	2	28	75	70	72	15
95°	111	133	136	136	133	124
105°	459	465	470	474	474	485
115°	854	866	863	860	854	845
125°	1242	1262	1256	1249	1246	1110
135°	1607	1631	1635	1633	1627	1242
145°	1951	1966	1979	1981	1972	1219
155°	2231	2237	2244	2255	2248	1027
165°	2427	2425	2425	2440	2429	685
175°	2526	2519	2515	2530	2517	240
180°	2530	2530	2530	2530	2530	



TEST NUMBER: P907466

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	3501.9	3501.9	3501.9	3501.9	3501.9
2.5°	3522.3	3505.5	3468.4	3501.9	3495.5
5°	3501.9	3488.7	3451.6	3478.4	3471.9
7.5°	3478.4	3458.4	3421.2	3448.4	3441.6
10°	3441.6	3418.0	3377.6	3404.4	3394.4
12.5°	3390.8	3370.8	3330.5	3347.2	3340.5
15°	3333.7	3313.7	3269.7	3283.3	3266.5
17.5°	3262.9	3242.9	3199.0	3215.8	3199.0
20°	3185.4	3165.4	3118.2	3128.2	3115.0
22.5°	3108.2	3077.9	3033.9	3033.9	3027.1
25°	3017.1	2990.3	2933.2	2939.6	2933.2
27.5°	2916.0	2892.4	2848.9	2838.9	2822.1
30°	2815.3	2788.1	2737.7	2727.7	2714.2
32.5°	2707.4	2687.4	2633.4	2613.1	2599.5
35°	2603.1	2569.5	2515.5	2495.2	2478.4
37.5°	2485.2	2454.8	2400.8	2377.3	2360.5
40°	2364.0	2336.9	2282.9	2252.9	2239.4
42.5°	2246.1	2219.0	2165.4	2131.5	2111.5
45°	2118.2	2094.7	2043.9	2007.1	1993.6
47.5°	1993.6	1970.0	1916.0	1878.9	1858.9
50°	1862.1	1845.3	1798.1	1751.0	1734.2
52.5°	1734.2	1710.6	1667.0	1629.9	1606.3
55°	1603.1	1582.7	1542.3	1502.0	1485.2
57.5°	1471.6	1454.8	1410.9	1370.5	1356.9
60°	1340.1	1326.9	1279.7	1242.6	1232.6
62.5°	1212.2	1188.6	1155.0	1121.5	1107.9
65°	1081.1	1060.7	1027.1	996.8	980.0
67.5°	946.4	929.3	899.2	875.7	862.1
70°	821.7	808.1	777.8	754.2	741.0
72.5°	693.8	680.2	663.4	639.9	629.9
75°	565.6	559.1	542.0	522.0	528.8
77.5°	451.2	437.7	430.9	420.9	410.9
80°	336.9	333.3	326.5	316.5	309.8
82.5°	229.0	229.0	225.8	212.2	212.2
85°	137.9	134.7	131.5	121.1	117.9
87.5°	60.7	53.9	47.2	37.2	33.6
90°	2.3	27.5	74.8	70.2	72.5
92.5°	47.3	64.1	66.4	68.6	68.6
95°	111.4	132.7	136.5	136.5	132.7
97.5°	185.4	205.2	213.6	213.6	213.6
100°	270.8	288.3	294.4	294.4	292.1
102.5°	360.8	373.8	382.1	384.4	382.1
105°	459.2	465.3	469.9	473.7	473.7
107.5°	556.8	566.0	566.0	567.5	556.8
110°	651.4	663.6	663.6	663.6	657.5



TEST NUMBER: P907466

CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	753.6	766.6	764.3	758.2	753.6
115°	854.3	866.5	862.7	860.4	854.3
117.5°	954.2	971.0	960.3	954.2	948.1
120°	1054.9	1071.7	1054.9	1054.9	1048.0
122.5°	1146.4	1167.8	1157.1	1151.0	1146.4
125°	1242.5	1261.6	1255.5	1248.6	1246.4
127.5°	1336.4	1360.0	1351.6	1342.5	1336.4
130°	1424.1	1451.5	1447.7	1443.2	1434.8
132.5°	1522.5	1543.8	1545.4	1534.7	1528.6
135°	1607.1	1630.8	1635.4	1633.1	1627.0
137.5°	1701.7	1720.8	1724.6	1723.1	1713.9
140°	1784.9	1803.9	1814.6	1814.6	1806.2
142.5°	1870.3	1889.4	1895.5	1897.8	1889.4
145°	1951.2	1966.4	1978.6	1980.9	1972.5
147.5°	2023.6	2042.7	2051.8	2055.7	2047.3
150°	2098.4	2111.3	2119.7	2126.6	2119.7
152.5°	2164.7	2177.7	2188.4	2196.8	2188.4
155°	2231.1	2237.2	2244.1	2254.7	2247.9
157.5°	2288.3	2292.9	2296.7	2311.9	2301.3
160°	2339.4	2344.0	2346.3	2359.2	2350.1
162.5°	2386.7	2386.7	2389.0	2403.5	2392.8
165°	2427.1	2424.8	2424.8	2440.1	2429.4
167.5°	2463.7	2456.9	2456.9	2472.1	2461.4
170°	2491.2	2485.1	2482.8	2498.1	2485.1
172.5°	2510.3	2504.2	2501.9	2517.1	2504.2
175°	2525.5	2519.4	2514.8	2530.1	2517.1
177.5°	2533.9	2527.8	2523.2	2536.2	2523.2
180°	2530.1	2530.1	2530.1	2530.1	2530.1



TEST NUMBER: P907466  
 CATALOG NUMBER: DFN2DIP-TR4F0-090D080US835-FLLFLL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.34	12.25	12.24	13.18	14.36	10.91	11.82	11.81	12.75	13.93
	3H	13.00	13.82	13.92	14.76	15.97	12.53	13.35	13.45	14.28	15.50
	4H	13.59	14.37	14.52	15.31	16.53	13.12	13.90	14.05	14.84	16.06
	6H	13.99	14.71	14.94	15.66	16.89	13.52	14.24	14.46	15.18	16.41
	8H	14.10	14.78	15.05	15.74	16.98	13.63	14.31	14.58	15.27	16.50
	12H	14.15	14.80	15.11	15.76	17.01	13.67	14.32	14.63	15.28	16.53
4H	2H	11.81	12.58	12.74	13.52	14.74	11.46	12.24	12.40	13.18	14.40
	3H	13.68	14.32	14.62	15.29	16.53	13.28	13.93	14.23	14.90	16.14
	4H	14.39	14.98	15.35	15.95	17.21	13.99	14.58	14.95	15.54	16.80
	6H	14.91	15.42	15.88	16.41	17.67	14.50	15.01	15.47	16.00	17.26
	8H	15.06	15.54	16.03	16.52	17.79	14.65	15.13	15.62	16.11	17.38
	12H	15.14	15.57	16.13	16.57	17.84	14.72	15.15	15.71	16.14	17.42
8H	4H	14.59	15.07	15.57	16.05	17.33	14.23	14.71	15.21	15.69	16.97
	6H	15.23	15.62	16.23	16.65	17.92	14.86	15.26	15.86	16.28	17.55
	8H	15.45	15.80	16.46	16.81	18.10	15.08	15.43	16.09	16.44	17.73
	12H	15.58	15.89	16.59	16.89	18.23	15.20	15.51	16.21	16.51	17.85
12H	4H	14.58	15.01	15.57	16.01	17.29	14.23	14.66	15.22	15.66	16.94
	6H	15.26	15.61	16.26	16.62	17.91	14.91	15.26	15.91	16.27	17.56
	8H	15.50	15.81	16.51	16.81	18.15	15.14	15.45	16.16	16.46	17.79