

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907477

Luminaire Tested: DFN2DIP-TR4F0-090D100US835-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907477
REPORT IS A COMBINATION OF REPORTS P902008 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D100US835-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 17550.0 lumens
Efficiency: N/A
Efficacy: 107.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 163.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50
1	97	93	89	86	88	85	82	79	71	68	66	57	56	54	45	44	43
2	88	81	76	71	81	75	70	65	62	59	56	51	48	46	40	39	37
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32
4	74	64	56	50	68	59	52	47	49	44	41	41	37	34	32	30	28
5	68	57	49	43	62	53	46	41	44	39	35	37	33	30	29	27	25
6	63	51	43	38	58	47	41	36	40	35	31	33	29	26	27	24	22
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	25	22	20
8	54	42	35	30	50	39	32	28	33	28	24	28	24	21	23	20	18
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	20	17	15

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2955	2955	2955
5°	2960	2908	2927
10°	2931	2851	2831
15°	2890	2757	2684
20°	2837	2627	2503
25°	2782	2481	2329
30°	2709	2332	2107
35°	2637	2171	1913
40°	2564	2005	1690
45°	2479	1821	1488
50°	2391	1635	1291
55°	2299	1436	1101
60°	2193	1228	906
65°	2071	1017	816
70°	1923	820	738
75°	1737	723	671
80°	1468	606	582
85°	1023	404	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2479 cd/sqm

TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	2.0
10°-20°	957.0	5.5
20°-30°	1343.6	7.7
30°-40°	1464.6	8.3
40°-50°	1346.2	7.7
50°-60°	1057.2	6.0
60°-70°	688.1	3.9
70°-80°	354.2	2.0
80°-90°	96.4	0.5
90°-100°	111.3	0.6
100°-110°	414.9	2.4
110°-120°	1100.3	6.3
120°-130°	1824.9	10.4
130°-140°	1938.4	11.0
140°-150°	1801.5	10.3
150°-160°	1448.4	8.3
160°-170°	933.3	5.3
170°-180°	321.2	1.8
0°-30°	2649.2	15.1
0°-40°	4113.9	23.4
0°-60°	6517.2	37.1
0°-90°	7655.9	43.6
90°-120°	1626.4	9.3
90°-150°	7191.2	41.0
90°-180°	9894.0	56.4
0°-180°	17550.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	2	29	49	61	66	16
95°	159	78	95	108	105	188
105°	742	816	149	176	186	793
115°	1404	1446	1507	376	200	1382
125°	1985	2017	2064	2081	2088	1771
135°	2457	2496	2518	2542	2537	1898
145°	2850	2847	2889	2906	2894	1782
155°	3138	3116	3146	3160	3141	1446
165°	3306	3292	3299	3316	3299	934
175°	3382	3365	3370	3387	3363	322
180°	3375	3375	3375	3375	3375	

TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	2.3	29.3	48.7	61.2	65.8
92.5°	61.2	51.3	58.6	63.5	65.8
95°	158.6	78.0	95.1	107.6	105.0
97.5°	285.6	85.5	124.4	131.9	134.3
100°	432.4	97.7	139.2	158.6	163.6
102.5°	593.3	588.7	144.1	170.8	178.3
105°	742.4	815.7	149.1	175.7	185.6
107.5°	915.8	976.7	154.0	180.7	190.5
110°	1081.9	1133.0	427.4	183.3	192.8

TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1238.2	1282.0	1240.6	187.9	195.5
115°	1404.1	1445.6	1506.8	376.1	200.4
117.5°	1548.2	1597.0	1638.7	1289.3	649.6
120°	1709.5	1746.0	1790.1	1819.4	1489.7
122.5°	1846.1	1885.2	1934.2	1948.7	1951.3
125°	1985.3	2017.2	2063.6	2080.7	2087.9
127.5°	2112.3	2146.5	2183.3	2207.7	2210.0
130°	2232.0	2271.2	2297.9	2324.8	2322.5
132.5°	2354.1	2386.0	2412.7	2434.7	2432.4
135°	2456.8	2495.9	2517.7	2542.3	2537.4
137.5°	2564.1	2593.4	2618.0	2642.4	2635.1
140°	2669.0	2688.8	2715.4	2737.5	2725.3
142.5°	2757.2	2774.3	2805.9	2825.3	2813.2
145°	2850.0	2847.4	2888.9	2906.0	2893.8
147.5°	2930.3	2923.1	2964.5	2976.7	2967.2
150°	3008.6	2991.5	3030.7	3045.2	3033.0
152.5°	3074.4	3055.0	3091.6	3106.3	3089.2
155°	3138.0	3116.2	3145.5	3160.0	3140.6
157.5°	3189.3	3169.9	3191.9	3209.0	3189.3
160°	3233.4	3218.6	3233.4	3247.9	3230.8
162.5°	3272.2	3257.7	3269.9	3287.0	3265.0
165°	3306.4	3291.9	3299.2	3316.3	3299.2
167.5°	3333.4	3318.6	3326.2	3343.3	3321.2
170°	3355.4	3340.7	3345.6	3362.7	3340.7
172.5°	3369.9	3355.4	3360.4	3377.5	3355.4
175°	3382.1	3365.0	3369.9	3387.1	3362.7
177.5°	3387.1	3369.9	3372.6	3389.7	3367.6
180°	3374.9	3374.9	3374.9	3374.9	3374.9

TEST NUMBER: P907477

CATALOG NUMBER: DFN2DIP-TR4F0-090D100US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.28	11.06	11.30	12.08	13.44	6.25	7.03	7.27	8.06	9.42
	3H	11.95	12.65	12.98	13.68	15.06	7.44	8.14	8.47	9.17	10.55
	4H	12.56	13.22	13.60	14.25	15.64	7.89	8.55	8.93	9.58	10.97
	6H	12.98	13.59	14.03	14.62	16.03	8.21	8.82	9.26	9.85	11.25
	8H	13.10	13.68	14.16	14.73	16.13	8.30	8.88	9.35	9.93	11.33
	12H	13.16	13.71	14.22	14.76	16.18	8.34	8.89	9.40	9.94	11.36
4H	2H	10.29	10.95	11.34	11.99	13.38	6.84	7.50	7.89	8.54	9.93
	3H	12.12	12.67	13.17	13.73	15.13	8.19	8.74	9.24	9.80	11.20
	4H	12.81	13.31	13.87	14.36	15.79	8.74	9.24	9.80	10.29	11.72
	6H	13.32	13.75	14.39	14.83	16.25	9.15	9.59	10.22	10.66	12.08
	8H	13.49	13.90	14.56	14.96	16.40	9.28	9.69	10.35	10.75	12.19
	12H	13.59	13.95	14.67	15.03	16.47	9.35	9.71	10.43	10.79	12.23
8H	4H	12.77	13.17	13.84	14.24	15.68	9.01	9.42	10.08	10.48	11.92
	6H	13.34	13.67	14.43	14.78	16.21	9.53	9.86	10.62	10.97	12.40
	8H	13.55	13.84	14.65	14.94	16.39	9.72	10.01	10.82	11.11	12.56
	12H	13.69	13.94	14.79	15.03	16.52	9.84	10.10	10.94	11.18	12.68
12H	4H	12.72	13.09	13.81	14.17	15.61	9.02	9.38	10.10	10.46	11.90
	6H	13.31	13.60	14.41	14.70	16.15	9.58	9.87	10.68	10.96	12.42
	8H	13.53	13.79	14.63	14.87	16.37	9.79	10.05	10.89	11.13	12.62

END OF REPORT