

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907485

Luminaire Tested: DFN2DIP-TR4F0-090D120US835-RLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907485
REPORT IS A COMBINATION OF REPORTS P902044 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-090D120US835-RLLONL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 19530.0 lumens
Efficiency: N/A
Efficacy: 109.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 178.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.099
Total Harmonic Distortion (THDi): 0.979
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46
1	96	92	88	85	87	83	80	78	68	66	64	54	53	52	41	41	40
2	87	80	75	70	79	73	68	64	60	57	54	48	46	44	37	35	34
3	80	71	64	58	73	65	59	54	53	49	46	43	40	37	33	31	29
4	73	63	55	50	67	58	51	46	48	43	39	38	35	32	30	27	26
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	25	23
6	62	51	43	37	56	46	40	35	39	34	30	31	28	25	25	22	20
7	57	46	38	33	52	42	35	31	35	30	26	29	25	22	23	20	18
8	53	42	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2955	2955	2955
5°	2960	2908	2927
10°	2931	2851	2831
15°	2890	2757	2684
20°	2837	2627	2503
25°	2782	2481	2329
30°	2709	2332	2107
35°	2637	2171	1913
40°	2564	2005	1690
45°	2479	1821	1488
50°	2391	1635	1291
55°	2299	1436	1101
60°	2193	1228	906
65°	2071	1017	816
70°	1923	820	738
75°	1737	723	671
80°	1468	606	582
85°	1023	404	437

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 2479 cd/sqm

TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	348.6	1.8
10°-20°	957.0	4.9
20°-30°	1343.6	6.9
30°-40°	1464.6	7.5
40°-50°	1346.2	6.9
50°-60°	1057.2	5.4
60°-70°	688.1	3.5
70°-80°	354.2	1.8
80°-90°	97.6	0.5
90°-100°	133.5	0.7
100°-110°	497.8	2.5
110°-120°	1320.3	6.8
120°-130°	2189.8	11.2
130°-140°	2326.1	11.9
140°-150°	2161.8	11.1
150°-160°	1738.1	8.9
160°-170°	1119.9	5.7
170°-180°	385.5	2.0
0°-30°	2649.2	13.6
0°-40°	4113.9	21.1
0°-60°	6517.2	33.4
0°-90°	7657.1	39.2
90°-120°	1951.7	10.0
90°-150°	8629.4	44.2
90°-180°	11873.0	60.8
0°-180°	19530.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3720	3720	3720	3720	3720	
5°	3720	3703	3659	3689	3679	353
15°	3538	3501	3386	3322	3289	997
25°	3212	3104	2882	2744	2693	1477
35°	2767	2595	2299	2087	2013	1732
45°	2262	2036	1683	1444	1363	1747
55°	1720	1458	1094	892	828	1537
65°	1161	889	586	471	461	1151
75°	619	384	269	246	242	655
85°	145	74	64	64	64	166
90°	3	35	58	73	79	18
95°	190	94	114	129	126	225
105°	891	979	179	211	223	952
115°	1685	1735	1808	451	240	1659
125°	2382	2421	2476	2497	2506	2125
135°	2948	2995	3021	3051	3045	2277
145°	3420	3417	3467	3487	3472	2139
155°	3766	3739	3775	3792	3769	1735
165°	3968	3950	3959	3980	3959	1121
175°	4058	4038	4044	4064	4035	386
180°	4050	4050	4050	4050	4050	

TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3719.7	3719.7	3719.7	3719.7	3719.7
2.5°	3736.5	3719.7	3682.5	3716.5	3709.7
5°	3719.7	3702.9	3659.0	3689.3	3679.3
7.5°	3689.3	3669.3	3622.2	3635.4	3618.6
10°	3649.0	3625.4	3558.3	3547.9	3527.9
12.5°	3598.6	3568.3	3477.2	3457.2	3420.0
15°	3537.9	3500.8	3386.5	3322.5	3289.0
17.5°	3467.2	3413.3	3271.8	3197.9	3144.0
20°	3386.5	3319.0	3150.7	3066.8	2992.5
22.5°	3299.0	3221.5	3026.1	2911.8	2861.5
25°	3211.5	3103.6	2881.5	2743.6	2692.9
27.5°	3107.2	2992.5	2746.8	2588.6	2511.1
30°	2996.1	2867.9	2598.6	2427.2	2336.1
32.5°	2888.2	2733.2	2457.5	2255.4	2171.1
35°	2767.2	2595.4	2299.3	2087.2	2012.9
37.5°	2649.3	2464.0	2151.1	1918.6	1834.7
40°	2524.7	2322.9	1996.1	1757.2	1669.7
42.5°	2396.8	2181.5	1841.4	1592.2	1508.2
45°	2262.2	2036.5	1683.2	1443.9	1363.2
47.5°	2134.3	1895.4	1531.8	1292.5	1218.6
50°	1992.9	1753.9	1383.6	1151.1	1080.7
52.5°	1854.7	1602.2	1242.2	1020.0	956.1
55°	1720.0	1457.5	1093.9	892.2	828.2
57.5°	1582.2	1312.9	962.9	774.3	720.4
60°	1440.7	1171.4	824.7	653.2	599.3
62.5°	1302.9	1033.6	706.8	545.4	518.6
65°	1161.4	888.6	585.7	471.4	461.1
67.5°	1026.8	753.9	471.4	413.9	403.9
70°	885.4	622.9	390.4	356.8	343.2
72.5°	750.7	501.4	326.4	299.6	292.9
75°	619.3	383.6	269.3	245.7	242.5
77.5°	488.2	272.5	212.1	198.6	191.8
80°	366.8	195.4	161.4	148.2	148.2
82.5°	255.7	131.4	111.1	104.3	104.3
85°	144.6	73.9	63.9	63.9	63.9
87.5°	53.9	26.8	26.8	23.6	23.6
90°	2.8	35.1	58.5	73.4	79.0
92.5°	73.4	61.6	70.3	76.2	79.0
95°	190.3	93.6	114.1	129.1	126.0
97.5°	342.8	102.7	149.3	158.3	161.1
100°	518.8	117.3	167.0	190.3	196.3
102.5°	712.0	706.4	172.9	205.0	214.0
105°	890.8	978.9	178.9	210.9	222.7
107.5°	1098.9	1172.0	184.8	216.8	228.6
110°	1298.3	1359.6	512.9	219.9	231.4

TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1485.9	1538.4	1488.7	225.5	234.5
115°	1684.9	1734.7	1808.1	451.3	240.5
117.5°	1857.9	1916.4	1966.5	1547.1	779.5
120°	2051.4	2095.2	2148.1	2183.3	1787.6
122.5°	2215.3	2262.3	2321.1	2338.5	2341.6
125°	2382.3	2420.6	2476.3	2496.8	2505.5
127.5°	2534.7	2575.8	2620.0	2649.2	2652.0
130°	2678.4	2725.4	2757.4	2789.8	2787.0
132.5°	2824.9	2863.2	2895.2	2921.7	2918.9
135°	2948.1	2995.1	3021.2	3050.8	3044.9
137.5°	3076.9	3112.0	3141.6	3170.8	3162.1
140°	3202.9	3226.5	3258.5	3285.0	3270.4
142.5°	3308.6	3329.2	3367.1	3390.4	3375.8
145°	3420.0	3416.9	3466.6	3487.2	3472.5
147.5°	3516.4	3507.7	3557.5	3572.1	3560.6
150°	3610.3	3589.8	3636.8	3654.2	3639.6
152.5°	3689.3	3666.0	3709.9	3727.6	3707.1
155°	3765.5	3739.4	3774.6	3792.0	3768.7
157.5°	3827.1	3803.8	3830.3	3850.8	3827.1
160°	3880.0	3862.3	3880.0	3897.4	3876.9
162.5°	3926.7	3909.3	3923.9	3944.4	3918.0
165°	3967.7	3950.3	3959.0	3979.6	3959.0
167.5°	4000.1	3982.3	3991.4	4011.9	3985.5
170°	4026.5	4008.8	4014.7	4035.2	4008.8
172.5°	4043.9	4026.5	4032.5	4053.0	4026.5
175°	4058.5	4038.0	4043.9	4064.5	4035.2
177.5°	4064.5	4043.9	4047.1	4067.6	4041.2
180°	4049.9	4049.9	4049.9	4049.9	4049.9

TEST NUMBER: P907485

CATALOG NUMBER: DFN2DIP-TR4F0-090D120US835-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	9.81	10.56	10.86	11.61	13.03	5.78	6.53	6.83	7.58	9.00
	3H	11.48	12.15	12.54	13.21	14.65	6.96	7.63	8.02	8.69	10.13
	4H	12.08	12.72	13.16	13.78	15.23	7.41	8.05	8.48	9.11	10.55
	6H	12.50	13.08	13.58	14.15	15.61	7.73	8.31	8.81	9.38	10.84
	8H	12.62	13.18	13.71	14.26	15.71	7.82	8.37	8.90	9.45	10.91
	12H	12.68	13.21	13.77	14.29	15.76	7.86	8.39	8.95	9.46	10.94
4H	2H	9.82	10.45	10.89	11.51	12.96	6.37	7.00	7.45	8.06	9.51
	3H	11.64	12.17	12.72	13.26	14.71	7.71	8.24	8.80	9.33	10.79
	4H	12.33	12.81	13.42	13.89	15.37	8.26	8.74	9.35	9.82	11.30
	6H	12.84	13.25	13.94	14.35	15.83	8.67	9.09	9.77	10.19	11.66
	8H	13.01	13.40	14.11	14.49	15.98	8.80	9.19	9.90	10.28	11.77
	12H	13.10	13.45	14.22	14.56	16.05	8.86	9.21	9.98	10.32	11.81
8H	4H	12.29	12.68	13.39	13.77	15.26	8.53	8.92	9.63	10.01	11.50
	6H	12.85	13.17	13.97	14.31	15.79	9.05	9.37	10.17	10.50	11.99
	8H	13.07	13.35	14.19	14.47	15.97	9.24	9.52	10.36	10.64	12.14
	12H	13.20	13.45	14.33	14.56	16.11	9.35	9.60	10.48	10.71	12.26
12H	4H	12.24	12.59	13.35	13.70	15.19	8.53	8.88	9.65	9.99	11.48
	6H	12.83	13.11	13.95	14.23	15.73	9.10	9.38	10.22	10.49	12.00
	8H	13.04	13.29	14.17	14.40	15.95	9.30	9.55	10.43	10.66	12.21

END OF REPORT