

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923593

Luminaire Tested: DFN2DIP-TR3F0-080D040US940-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923593  
REPORT IS A COMBINATION OF REPORTS P901816 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-080D040US940-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 9594.8 lumens  
Efficiency: N/A  
Efficacy: 86.9 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: Semi-Direct  
  
Input Watts (W): 110.4  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923593  
CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P923593

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	91	91	91	79	79	79	68	68	68	68	68	68	63
1	101	97	93	90	95	91	88	85	80	78	76	71	69	67	61	60	59	61	60	59	54
2	93	86	80	75	87	81	75	71	71	67	64	63	60	57	55	52	51	55	52	51	47
3	85	76	69	63	80	72	65	60	63	58	54	56	52	49	49	46	44	49	46	44	40
4	78	68	60	54	73	64	57	52	57	51	47	50	46	43	44	41	38	44	41	38	35
5	72	61	53	47	67	57	50	45	51	45	41	46	41	37	40	37	34	40	37	34	31
6	67	55	47	41	62	52	45	39	46	41	36	41	37	33	37	33	30	37	33	30	27
7	62	50	42	36	58	47	40	35	42	36	32	38	33	30	34	30	27	34	30	27	25
8	58	45	38	32	54	43	36	31	39	33	29	35	30	27	31	27	24	31	27	24	22
9	54	42	34	29	51	40	33	28	36	30	26	32	27	24	29	25	22	29	25	22	20
10	50	38	31	26	47	37	30	25	33	28	24	30	25	22	27	23	20	27	23	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3674	3674	3674
5°	3678	3613	3636
10°	3639	3539	3516
15°	3587	3419	3330
20°	3519	3255	3104
25°	3449	3071	2886
30°	3356	2883	2609
35°	3264	2682	2366
40°	3171	2474	2089
45°	3063	2243	1837
50°	2951	2010	1591
55°	2834	1762	1355
60°	2698	1503	1113
65°	2542	1240	999
70°	2352	995	901
75°	2114	871	815
80°	1769	721	698
85°	1204	466	510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3063 cd/sqm



TEST NUMBER: P923593

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.3	2.9
10°-20°	758.6	7.9
20°-30°	1065.0	11.1
30°-40°	1160.9	12.1
40°-50°	1067.0	11.1
50°-60°	838.0	8.7
60°-70°	545.4	5.7
70°-80°	280.8	2.9
80°-90°	73.8	0.8
90°-100°	39.7	0.4
100°-110°	148.0	1.5
110°-120°	392.4	4.1
120°-130°	650.9	6.8
130°-140°	691.4	7.2
140°-150°	642.6	6.7
150°-160°	516.6	5.4
160°-170°	332.9	3.5
170°-180°	114.6	1.2
0°-30°	2099.9	21.9
0°-40°	3260.8	34.0
0°-60°	5165.8	53.8
0°-90°	6065.8	63.2
90°-120°	580.1	6.0
90°-150°	2565.0	26.7
90°-180°	3529.0	36.8
0°-180°	9594.8	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	1	10	17	22	24	9
95°	56	28	34	38	38	67
105°	265	291	53	63	66	283
115°	501	516	537	134	72	493
125°	708	720	736	742	745	632
135°	876	890	898	907	905	677
145°	1016	1016	1030	1036	1032	636
155°	1119	1112	1122	1127	1120	516
165°	1179	1174	1177	1183	1177	333
175°	1206	1200	1202	1208	1199	115
180°	1204	1204	1204	1204	1204	



TEST NUMBER: P923593

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	0.8	10.4	17.4	21.8	23.5
92.5°	21.8	18.3	20.9	22.6	23.5
95°	56.5	27.8	33.9	38.3	37.5
97.5°	101.9	30.5	44.4	47.1	47.9
100°	154.2	34.9	49.7	56.5	58.3
102.5°	211.6	210.0	51.4	60.9	63.6
105°	264.7	291.0	53.1	62.7	66.2
107.5°	326.6	348.4	54.9	64.5	67.9
110°	385.9	404.1	152.5	65.4	68.8



TEST NUMBER: P923593

CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	441.7	457.3	442.5	67.1	69.7
115°	500.8	515.6	537.4	134.1	71.5
117.5°	552.2	569.6	584.5	459.9	231.7
120°	609.8	622.8	638.5	649.0	531.4
122.5°	658.4	672.4	689.9	695.1	696.0
125°	708.1	719.5	736.0	742.2	744.8
127.5°	753.4	765.6	778.7	787.5	788.3
130°	796.1	810.1	819.6	829.2	828.4
132.5°	839.6	851.0	860.6	868.4	867.6
135°	876.3	890.3	898.0	906.8	905.1
137.5°	914.5	925.0	933.8	942.4	939.9
140°	952.0	959.0	968.6	976.4	972.1
142.5°	983.5	989.5	1000.9	1007.7	1003.4
145°	1016.5	1015.7	1030.4	1036.5	1032.2
147.5°	1045.2	1042.6	1057.4	1061.8	1058.4
150°	1073.1	1067.0	1081.0	1086.2	1081.8
152.5°	1096.6	1089.7	1102.7	1108.0	1101.9
155°	1119.3	1111.5	1121.9	1127.1	1120.2
157.5°	1137.6	1130.6	1138.5	1144.6	1137.6
160°	1153.2	1148.0	1153.2	1158.4	1152.4
162.5°	1167.2	1162.0	1166.4	1172.4	1164.6
165°	1179.4	1174.2	1176.8	1182.9	1176.8
167.5°	1189.0	1183.7	1186.4	1192.5	1184.6
170°	1196.9	1191.6	1193.3	1199.4	1191.6
172.5°	1202.0	1196.9	1198.6	1204.7	1196.9
175°	1206.3	1200.2	1202.0	1208.1	1199.4
177.5°	1208.1	1202.0	1202.9	1209.1	1201.2
180°	1203.8	1203.8	1203.8	1203.8	1203.8



TEST NUMBER: P923593  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D040US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.77	13.72	13.61	14.58	15.65	8.75	9.70	9.59	10.56	11.63
	3H	14.45	15.30	15.30	16.17	17.26	9.94	10.79	10.79	11.66	12.76
	4H	15.05	15.86	15.93	16.73	17.84	10.39	11.19	11.26	12.07	13.18
	6H	15.47	16.21	16.36	17.10	18.22	10.71	11.45	11.60	12.33	13.46
	8H	15.60	16.30	16.49	17.20	18.32	10.80	11.51	11.70	12.41	13.53
	12H	15.66	16.33	16.56	17.22	18.37	10.85	11.52	11.75	12.41	13.56
4H	2H	12.80	13.60	13.68	14.48	15.59	9.35	10.15	10.23	11.03	12.14
	3H	14.63	15.30	15.52	16.20	17.33	10.71	11.37	11.59	12.28	13.40
	4H	15.32	15.93	16.22	16.83	17.98	11.25	11.86	12.15	12.76	13.91
	6H	15.83	16.35	16.75	17.28	18.44	11.67	12.19	12.59	13.12	14.28
	8H	16.00	16.49	16.92	17.41	18.58	11.80	12.29	12.72	13.21	14.38
	12H	16.10	16.54	17.03	17.48	18.65	11.87	12.31	12.80	13.25	14.42
8H	4H	15.29	15.78	16.21	16.70	17.87	11.54	12.02	12.45	12.95	14.11
	6H	15.86	16.26	16.80	17.22	18.39	12.05	12.45	12.99	13.42	14.58
	8H	16.07	16.42	17.02	17.38	18.56	12.24	12.59	13.19	13.55	14.73
	12H	16.20	16.52	17.16	17.46	18.70	12.36	12.67	13.31	13.62	14.85
12H	4H	15.25	15.69	16.19	16.63	17.80	11.55	11.98	12.48	12.92	14.10
	6H	15.83	16.19	16.78	17.14	18.33	12.10	12.46	13.05	13.41	14.59
	8H	16.05	16.36	17.00	17.31	18.54	12.31	12.62	13.26	13.57	14.80