

Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P923605

Luminaire Tested: DFN2DIP-TR3F0-080D070US940-RLONL

Issue Date: 11/21/2024

**Test Information**


Test Method: LM-79-2019  
Report Number: P923605  
REPORT IS A COMBINATION OF REPORTS P901858 AND P898751  
Test Lab: INNOVATION CENTER  
Issue Date: 11/21/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: NEO-RAY  
Catalog Number: DFN2DIP-TR3F0-080D070US940-RLLONL  
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 12243.2 lumens  
Efficiency: N/A  
Efficacy: 91.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')  
CIE Type: General Diffuse  
  
Input Watts (W): 134.1  
Input Voltage (V):  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: 0.9968  
Total Harmonic Distortion (THDi): 0.064  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P923605  
CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLLONL

### Luminous Intensity Polar Plot





TEST NUMBER: P923605  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLONL

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	50	49	48	43
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	45	43	41	37
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	40	38	36	32
4	75	65	57	52	69	60	54	48	52	47	42	44	40	37	36	33	31	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	21	23	20	18	23	20	18	16
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	22	19	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3674	3674	3674
5°	3678	3613	3636
10°	3639	3539	3516
15°	3587	3419	3330
20°	3519	3255	3104
25°	3449	3071	2886
30°	3356	2883	2609
35°	3264	2682	2366
40°	3171	2474	2089
45°	3063	2243	1837
50°	2951	2010	1591
55°	2834	1762	1355
60°	2698	1503	1113
65°	2542	1240	999
70°	2352	995	901
75°	2114	871	815
80°	1769	721	698
85°	1204	466	510

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 3063 cd/sqm



TEST NUMBER: P923605

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLLONL

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	276.3	2.3
10°-20°	758.6	6.2
20°-30°	1065.0	8.7
30°-40°	1160.9	9.5
40°-50°	1067.0	8.7
50°-60°	838.0	6.8
60°-70°	545.4	4.5
70°-80°	280.8	2.3
80°-90°	75.4	0.6
90°-100°	69.5	0.6
100°-110°	259.0	2.1
110°-120°	686.8	5.6
120°-130°	1139.1	9.3
130°-140°	1209.9	9.9
140°-150°	1124.5	9.2
150°-160°	904.1	7.4
160°-170°	582.6	4.8
170°-180°	200.5	1.6
0°-30°	2099.9	17.2
0°-40°	3260.8	26.6
0°-60°	5165.8	42.2
0°-90°	6067.4	49.6
90°-120°	1015.2	8.3
90°-150°	4488.7	36.7
90°-180°	6176.0	50.4
0°-180°	12243.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	2948	2948	2948	2948	2948	
5°	2948	2935	2900	2924	2916	280
15°	2804	2775	2684	2634	2607	790
25°	2546	2460	2284	2175	2134	1171
35°	2193	2057	1822	1654	1595	1373
45°	1793	1614	1334	1144	1081	1385
55°	1363	1155	867	707	656	1218
65°	921	704	464	374	365	913
75°	491	304	214	195	192	519
85°	115	59	51	51	51	132
90°	1	18	30	38	41	11
95°	99	49	59	67	66	117
105°	463	509	93	110	116	495
115°	876	902	940	235	125	863
125°	1239	1259	1288	1299	1303	1105
135°	1534	1558	1572	1587	1584	1185
145°	1779	1777	1803	1814	1806	1113
155°	1959	1945	1963	1972	1960	903
165°	2064	2055	2059	2070	2059	583
175°	2111	2100	2104	2114	2099	201
180°	2107	2107	2107	2107	2107	



TEST NUMBER: P923605

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLLONL

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	2948.4	2948.4	2948.4	2948.4	2948.4
2.5°	2961.6	2948.4	2918.9	2945.8	2940.4
5°	2948.4	2935.1	2900.2	2924.3	2916.3
7.5°	2924.3	2908.4	2871.0	2881.6	2868.2
10°	2892.3	2873.6	2820.4	2812.2	2796.3
12.5°	2852.4	2828.3	2756.1	2740.2	2710.8
15°	2804.3	2774.8	2684.2	2633.6	2606.9
17.5°	2748.2	2705.4	2593.4	2534.8	2492.0
20°	2684.2	2630.7	2497.4	2430.9	2371.9
22.5°	2614.9	2553.4	2398.6	2308.0	2268.1
25°	2545.5	2460.1	2283.9	2174.7	2134.5
27.5°	2462.8	2371.9	2177.2	2051.8	1990.4
30°	2374.8	2273.1	2059.8	1923.9	1851.6
32.5°	2289.3	2166.5	1947.9	1787.7	1720.9
35°	2193.3	2057.2	1822.5	1654.4	1595.4
37.5°	2099.9	1953.0	1705.0	1520.7	1454.2
40°	2001.2	1841.2	1582.2	1392.8	1323.4
42.5°	1899.8	1729.1	1459.6	1262.0	1195.4
45°	1793.1	1614.2	1334.2	1144.5	1080.6
47.5°	1691.8	1502.4	1214.2	1024.5	965.9
50°	1579.6	1390.3	1096.7	912.4	856.6
52.5°	1470.1	1269.9	984.5	808.5	757.9
55°	1363.3	1155.3	867.1	707.1	656.5
57.5°	1254.1	1040.6	763.2	613.8	571.0
60°	1141.9	928.5	653.6	517.7	475.0
62.5°	1032.7	819.2	560.3	432.3	411.1
65°	920.6	704.3	464.2	373.7	365.4
67.5°	813.9	597.6	373.7	328.1	320.2
70°	701.8	493.7	309.4	282.8	272.1
72.5°	595.0	397.4	258.8	237.6	232.1
75°	490.9	304.1	213.5	194.7	192.3
77.5°	387.0	216.0	168.2	157.4	152.0
80°	290.7	154.9	128.0	117.4	117.4
82.5°	202.7	104.2	88.0	82.7	82.7
85°	114.7	58.6	50.6	50.6	50.6
87.5°	42.7	21.2	21.2	18.7	18.7
90°	1.4	18.3	30.4	38.2	41.1
92.5°	38.2	32.0	36.6	39.7	41.1
95°	99.0	48.7	59.4	67.1	65.5
97.5°	178.3	53.4	77.7	82.4	83.8
100°	269.9	61.0	86.9	99.0	102.1
102.5°	370.3	367.5	90.0	106.6	111.3
105°	463.4	509.2	93.0	109.7	115.8
107.5°	571.6	609.7	96.1	112.8	119.0
110°	675.4	707.2	266.8	114.4	120.4



TEST NUMBER: P923605

CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLLONL

**CANDELA DISTRIBUTION (continued):**

	0°	22.5°	45°	67.5°	90°
112.5°	772.9	800.2	774.4	117.3	122.0
115°	876.5	902.3	940.5	234.8	125.1
117.5°	966.4	996.8	1022.9	804.8	405.5
120°	1067.0	1089.8	1117.4	1135.7	929.9
122.5°	1152.3	1176.7	1207.4	1216.4	1218.0
125°	1239.2	1259.1	1288.1	1298.8	1303.2
127.5°	1318.5	1339.8	1362.8	1378.0	1379.5
130°	1393.2	1417.6	1434.3	1451.2	1449.7
132.5°	1469.4	1489.3	1506.0	1519.7	1518.3
135°	1533.5	1557.9	1571.6	1586.9	1583.9
137.5°	1600.4	1618.8	1634.1	1649.4	1644.8
140°	1666.0	1678.3	1695.0	1708.7	1701.1
142.5°	1721.0	1731.7	1751.4	1763.5	1756.0
145°	1779.0	1777.4	1803.2	1813.9	1806.3
147.5°	1829.1	1824.6	1850.5	1858.1	1852.1
150°	1877.9	1867.3	1891.8	1900.8	1893.2
152.5°	1919.0	1906.9	1929.8	1938.9	1928.3
155°	1958.7	1945.1	1963.4	1972.5	1960.3
157.5°	1990.7	1978.6	1992.3	2003.0	1990.7
160°	2018.3	2009.0	2018.3	2027.3	2016.6
162.5°	2042.6	2033.5	2041.0	2051.7	2038.0
165°	2063.9	2054.9	2059.3	2070.0	2059.3
167.5°	2080.7	2071.4	2076.2	2086.9	2073.1
170°	2094.4	2085.3	2088.3	2099.0	2085.3
172.5°	2103.5	2094.4	2097.6	2108.2	2094.4
175°	2111.1	2100.4	2103.5	2114.2	2099.0
177.5°	2114.2	2103.5	2105.1	2115.9	2102.0
180°	2106.6	2106.6	2106.6	2106.6	2106.6



TEST NUMBER: P923605  
 CATALOG NUMBER: DFN2DIP-TR3F0-080D070US940-RLONL

**CIE UGR TABLE:**

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.57	12.40	12.54	13.38	14.66	7.55	8.38	8.52	9.36	10.64
	3H	13.24	13.98	14.22	14.97	16.27	8.73	9.47	9.71	10.46	11.76
	4H	13.84	14.54	14.84	15.53	16.84	9.18	9.88	10.17	10.87	12.18
	6H	14.26	14.90	15.26	15.90	17.22	9.50	10.14	10.50	11.14	12.46
	8H	14.38	14.99	15.39	16.00	17.32	9.58	10.20	10.59	11.21	12.53
	12H	14.44	15.02	15.45	16.03	17.37	9.63	10.21	10.64	11.21	12.56
4H	2H	11.59	12.29	12.59	13.28	14.59	8.14	8.84	9.14	9.83	11.14
	3H	13.41	13.99	14.42	15.01	16.33	9.48	10.07	10.49	11.09	12.41
	4H	14.09	14.63	15.11	15.64	16.99	10.03	10.56	11.04	11.57	12.92
	6H	14.60	15.06	15.63	16.09	17.44	10.44	10.90	11.47	11.93	13.28
	8H	14.77	15.20	15.80	16.22	17.58	10.57	10.99	11.59	12.02	13.38
	12H	14.86	15.24	15.90	16.29	17.65	10.63	11.01	11.67	12.06	13.42
8H	4H	14.06	14.49	15.09	15.51	16.87	10.30	10.73	11.33	11.76	13.12
	6H	14.62	14.97	15.67	16.04	17.39	10.81	11.16	11.86	12.23	13.59
	8H	14.83	15.14	15.89	16.19	17.57	11.00	11.31	12.06	12.36	13.74
	12H	14.96	15.23	16.02	16.28	17.70	11.11	11.38	12.17	12.43	13.85
12H	4H	14.01	14.40	15.06	15.44	16.80	10.31	10.69	11.35	11.73	13.10
	6H	14.59	14.90	15.65	15.96	17.33	10.86	11.17	11.92	12.22	13.60
	8H	14.81	15.08	15.87	16.13	17.55	11.06	11.34	12.13	12.39	13.80