

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907498

Luminaire Tested: DFN2DIP-TR4F0-100D070US835-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907498
REPORT IS A COMBINATION OF REPORTS P900435 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D070US835-FLLFLL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 16095.0 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 153.2
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907498
CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P907498

CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	110	110	110	110	103	103	103	103	90	90	90	78	78	78	67	67	67	67	67	67	62
1	100	96	92	88	94	90	87	83	79	76	74	68	67	65	59	58	56	59	58	56	52
2	91	84	78	72	85	79	73	68	69	65	61	60	57	54	52	50	48	52	50	48	43
3	83	74	66	60	78	69	63	57	61	56	51	53	49	46	46	43	40	46	43	40	37
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	38	35	41	38	35	32
5	70	58	50	44	65	55	47	42	49	43	38	43	38	34	37	33	30	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	39	34	30	34	30	27	34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29	35	30	27	31	27	24	31	27	24	21
8	56	43	35	30	52	41	34	29	36	30	26	32	27	24	28	24	21	28	24	21	19
9	52	39	32	27	49	37	30	26	33	28	23	30	25	21	26	22	19	26	22	19	17
10	49	36	29	24	45	34	28	23	31	25	21	27	23	19	24	20	18	24	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3091	3091	3091
5°	3096	3048	3069
10°	3071	3007	3027
15°	3026	2957	2962
20°	2965	2889	2895
25°	2904	2806	2818
30°	2828	2730	2721
35°	2756	2639	2617
40°	2667	2548	2519
45°	2579	2457	2418
50°	2482	2361	2301
55°	2381	2250	2194
60°	2267	2118	2071
65°	2142	1982	1926
70°	1983	1815	1770
75°	1763	1616	1626
80°	1498	1362	1351
85°	1083	925	895

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2579 cd/sqm



TEST NUMBER: P907498

CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	366.2	2.3
10°-20°	1030.4	6.4
20°-30°	1514.3	9.4
30°-40°	1758.8	10.9
40°-50°	1756.6	10.9
50°-60°	1531.7	9.5
60°-70°	1132.3	7.0
70°-80°	640.6	4.0
80°-90°	175.4	1.1
90°-100°	137.0	0.9
100°-110°	435.3	2.7
110°-120°	744.9	4.6
120°-130°	979.6	6.1
130°-140°	1099.6	6.8
140°-150°	1078.3	6.7
150°-160°	904.5	5.6
160°-170°	599.9	3.7
170°-180°	209.7	1.3
0°-30°	2911.0	18.1
0°-40°	4669.7	29.0
0°-60°	7958.0	49.4
0°-90°	9906.3	61.5
90°-120°	1317.2	8.2
90°-150°	4474.7	27.8
90°-180°	6189.0	38.5
0°-180°	16095.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3891	3891	3891	3891	3891	
5°	3891	3876	3835	3865	3858	369
15°	3704	3682	3633	3648	3630	1043
25°	3352	3323	3259	3266	3259	1543
35°	2892	2855	2795	2772	2754	1806
45°	2354	2327	2271	2230	2215	1816
55°	1781	1759	1714	1669	1650	1592
65°	1201	1179	1141	1108	1089	1188
75°	628	621	602	580	588	671
85°	153	150	146	135	131	171
90°	2	24	65	61	63	15
95°	97	116	120	120	116	108
105°	402	407	411	414	414	424
115°	748	758	755	753	748	739
125°	1087	1104	1099	1093	1091	972
135°	1406	1427	1431	1429	1424	1087
145°	1707	1721	1731	1733	1726	1067
155°	1952	1958	1964	1973	1967	899
165°	2124	2122	2122	2135	2126	599
175°	2210	2204	2200	2214	2202	210
180°	2214	2214	2214	2214	2214	



TEST NUMBER: P907498

CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3891.1	3891.1	3891.1	3891.1	3891.1
2.5°	3913.7	3895.0	3853.7	3891.1	3883.9
5°	3891.1	3876.4	3835.1	3864.9	3857.7
7.5°	3864.9	3842.6	3801.3	3831.5	3824.0
10°	3824.0	3797.8	3752.9	3782.7	3771.6
12.5°	3767.6	3745.4	3700.5	3719.2	3711.6
15°	3704.1	3681.9	3633.0	3648.1	3629.5
17.5°	3625.5	3603.3	3554.4	3573.1	3554.4
20°	3539.3	3517.1	3464.7	3475.8	3461.1
22.5°	3453.6	3419.9	3371.0	3371.0	3363.5
25°	3352.4	3322.6	3259.1	3266.2	3259.1
27.5°	3240.0	3213.8	3165.4	3154.3	3135.6
30°	3128.1	3097.9	3041.9	3030.8	3015.7
32.5°	3008.2	2986.0	2926.0	2903.4	2888.3
35°	2892.3	2855.0	2795.0	2772.4	2753.7
37.5°	2761.3	2727.5	2667.6	2641.4	2622.7
40°	2626.7	2596.5	2536.6	2503.3	2488.2
42.5°	2495.7	2465.5	2406.0	2368.3	2346.1
45°	2353.6	2327.4	2271.0	2230.1	2215.1
47.5°	2215.1	2188.9	2128.9	2087.6	2065.4
50°	2069.0	2050.3	1997.9	1945.5	1926.9
52.5°	1926.9	1900.7	1852.2	1811.0	1784.8
55°	1781.2	1758.6	1713.7	1668.8	1650.2
57.5°	1635.1	1616.4	1567.6	1522.8	1507.7
60°	1489.0	1474.3	1421.9	1380.6	1369.5
62.5°	1346.9	1320.7	1283.4	1246.1	1231.0
65°	1201.2	1178.6	1141.3	1107.5	1088.9
67.5°	1051.6	1032.5	999.2	973.0	957.9
70°	913.0	897.9	864.2	838.0	823.3
72.5°	770.9	755.8	737.2	711.0	699.8
75°	628.4	621.3	602.2	580.0	587.5
77.5°	501.4	486.3	478.7	467.6	456.5
80°	374.3	370.4	362.8	351.7	344.2
82.5°	254.5	254.5	250.9	235.8	235.8
85°	153.2	149.7	146.1	134.6	131.0
87.5°	67.5	59.9	52.4	41.3	37.3
90°	2.0	24.0	65.4	61.4	63.4
92.5°	41.4	56.1	58.1	60.1	60.1
95°	97.4	116.1	119.5	119.5	116.1
97.5°	162.2	179.5	186.9	186.9	186.9
100°	236.9	252.3	257.6	257.6	255.6
102.5°	315.7	327.0	334.4	336.4	334.4
105°	401.8	407.1	411.1	414.5	414.5
107.5°	487.2	495.2	495.2	496.6	487.2
110°	570.0	580.7	580.7	580.7	575.3



TEST NUMBER: P907498

CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	659.4	670.8	668.8	663.4	659.4
115°	747.5	758.2	754.9	752.9	747.5
117.5°	834.9	849.6	840.3	834.9	829.6
120°	923.0	937.7	923.0	923.0	917.0
122.5°	1003.1	1021.8	1012.5	1007.1	1003.1
125°	1087.2	1103.9	1098.6	1092.6	1090.6
127.5°	1169.3	1190.0	1182.7	1174.7	1169.3
130°	1246.1	1270.1	1266.8	1262.8	1255.4
132.5°	1332.2	1350.9	1352.2	1342.9	1337.5
135°	1406.3	1426.9	1431.0	1428.9	1423.6
137.5°	1489.0	1505.7	1509.0	1507.7	1499.7
140°	1561.8	1578.5	1587.8	1587.8	1580.5
142.5°	1636.5	1653.2	1658.5	1660.5	1653.2
145°	1707.3	1720.6	1731.3	1733.3	1726.0
147.5°	1770.7	1787.4	1795.4	1798.7	1791.4
150°	1836.1	1847.4	1854.8	1860.8	1854.8
152.5°	1894.1	1905.5	1914.8	1922.2	1914.8
155°	1952.2	1957.5	1963.6	1972.9	1966.9
157.5°	2002.3	2006.3	2009.6	2023.0	2013.6
160°	2047.0	2051.0	2053.0	2064.3	2056.3
162.5°	2088.4	2088.4	2090.4	2103.0	2093.7
165°	2123.7	2121.7	2121.7	2135.1	2125.7
167.5°	2155.8	2149.8	2149.8	2163.1	2153.8
170°	2179.8	2174.5	2172.5	2185.8	2174.5
172.5°	2196.5	2191.1	2189.1	2202.5	2191.1
175°	2209.8	2204.5	2200.5	2213.8	2202.5
177.5°	2217.2	2211.8	2207.8	2219.2	2207.8
180°	2213.8	2213.8	2213.8	2213.8	2213.8



TEST NUMBER: P907498
 CATALOG NUMBER: DFN2DIP-TR4F0-100D070US835-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.19	13.16	13.04	14.04	15.13	11.76	12.73	12.61	13.61	14.70
	3H	13.86	14.73	14.72	15.62	16.74	13.39	14.26	14.25	15.14	16.27
	4H	14.45	15.28	15.33	16.17	17.30	13.98	14.81	14.86	15.69	16.83
	6H	14.86	15.62	15.75	16.52	17.66	14.38	15.14	15.27	16.04	17.19
	8H	14.96	15.69	15.86	16.60	17.75	14.49	15.22	15.39	16.13	17.28
	12H	15.02	15.71	15.92	16.62	17.79	14.54	15.23	15.44	16.14	17.31
4H	2H	12.66	13.49	13.55	14.38	15.51	12.32	13.15	13.20	14.04	15.17
	3H	14.54	15.23	15.44	16.15	17.30	14.15	14.84	15.04	15.76	16.91
	4H	15.26	15.89	16.17	16.81	17.98	14.85	15.48	15.76	16.40	17.57
	6H	15.78	16.33	16.70	17.27	18.44	15.37	15.92	16.29	16.86	18.03
	8H	15.93	16.44	16.86	17.38	18.57	15.52	16.03	16.45	16.96	18.15
	12H	16.01	16.47	16.96	17.42	18.62	15.59	16.05	16.53	17.00	18.20
8H	4H	15.47	15.97	16.39	16.91	18.10	15.11	15.61	16.03	16.55	17.74
	6H	16.10	16.52	17.05	17.50	18.69	15.74	16.16	16.69	17.14	18.32
	8H	16.32	16.70	17.28	17.66	18.87	15.95	16.33	16.91	17.29	18.50
	12H	16.46	16.79	17.42	17.75	19.00	16.08	16.40	17.04	17.36	18.62
12H	4H	15.46	15.92	16.40	16.87	18.06	15.10	15.56	16.05	16.52	17.71
	6H	16.13	16.51	17.09	17.47	18.68	15.78	16.15	16.74	17.12	18.33
	8H	16.38	16.71	17.34	17.67	18.92	16.02	16.35	16.99	17.31	18.57