

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P907516

Luminaire Tested: DFN2DIP-TR4F0-100D110US835-RLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P907516
REPORT IS A COMBINATION OF REPORTS P900508 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-100D110US835-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 18235.0 lumens
Efficiency: N/A
Efficacy: 98.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 185.8
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9972
Total Harmonic Distortion (THDi): 0.128
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P907516
CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

Luminous Intensity Polar Plot





TEST NUMBER: P907516
 CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47	47	47	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40	40	40	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34	34	34	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30	30	30	30
4	75	64	57	51	69	60	53	48	51	46	42	42	38	35	34	32	30	26	26	26	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23	23	23	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20	20	20	20
7	59	47	39	34	54	44	37	32	37	32	28	32	27	24	26	23	21	18	18	18	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16	16	16	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15	15	15	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14	14	14	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3283	3283	3283
5°	3289	3231	3252
10°	3256	3168	3146
15°	3211	3063	2982
20°	3152	2919	2781
25°	3091	2757	2588
30°	3010	2591	2342
35°	2930	2413	2126
40°	2849	2228	1878
45°	2754	2023	1653
50°	2657	1817	1434
55°	2555	1596	1224
60°	2437	1365	1007
65°	2301	1130	906
70°	2136	911	820
75°	1930	803	746
80°	1630	674	646
85°	1136	449	485

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2754 cd/sqm



TEST NUMBER: P907516

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	387.3	2.1
10°-20°	1063.3	5.8
20°-30°	1492.9	8.2
30°-40°	1627.4	8.9
40°-50°	1495.7	8.2
50°-60°	1174.7	6.4
60°-70°	764.6	4.2
70°-80°	393.6	2.2
80°-90°	110.4	0.6
90°-100°	215.3	1.2
100°-110°	684.0	3.8
110°-120°	1170.5	6.4
120°-130°	1539.4	8.4
130°-140°	1727.9	9.5
140°-150°	1694.4	9.3
150°-160°	1421.4	7.8
160°-170°	942.6	5.2
170°-180°	329.5	1.8
0°-30°	2943.6	16.1
0°-40°	4571.0	25.1
0°-60°	7241.3	39.7
0°-90°	8509.9	46.7
90°-120°	2069.8	11.4
90°-150°	7031.6	38.6
90°-180°	9725.0	53.3
0°-180°	18235.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4133	4133	4133	4133	4133	
5°	4133	4114	4066	4099	4088	392
15°	3931	3890	3763	3692	3654	1108
25°	3568	3448	3202	3048	2992	1641
35°	3075	2884	2555	2319	2236	1924
45°	2514	2263	1870	1604	1515	1941
55°	1911	1620	1216	991	920	1708
65°	1290	987	651	524	512	1279
75°	688	426	299	273	269	728
85°	161	82	71	71	71	184
90°	3	38	103	96	100	18
95°	153	182	188	188	182	170
105°	631	640	646	651	651	666
115°	1175	1191	1186	1183	1175	1162
125°	1708	1735	1726	1717	1714	1527
135°	2210	2242	2249	2246	2237	1708
145°	2683	2704	2721	2724	2712	1676
155°	3068	3076	3086	3100	3091	1412
165°	3337	3334	3334	3355	3340	941
175°	3473	3464	3458	3479	3461	330
180°	3479	3479	3479	3479	3479	



TEST NUMBER: P907516

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4133.0	4133.0	4133.0	4133.0	4133.0
2.5°	4151.6	4133.0	4091.7	4129.4	4121.9
5°	4133.0	4114.3	4065.5	4099.3	4088.1
7.5°	4099.3	4077.0	4024.6	4039.3	4020.7
10°	4054.4	4028.2	3953.6	3942.1	3919.9
12.5°	3998.5	3964.7	3863.5	3841.3	3800.0
15°	3931.0	3889.7	3762.7	3691.7	3654.4
17.5°	3852.4	3792.5	3635.4	3553.2	3493.3
20°	3762.7	3687.7	3500.8	3407.6	3325.0
22.5°	3665.5	3579.4	3362.3	3235.4	3179.4
25°	3568.3	3448.5	3201.6	3048.4	2992.1
27.5°	3452.4	3325.0	3052.0	2876.2	2790.1
30°	3329.0	3186.5	2887.3	2696.9	2595.7
32.5°	3209.2	3036.9	2730.6	2506.0	2412.3
35°	3074.6	2883.8	2554.8	2319.1	2236.5
37.5°	2943.7	2737.7	2390.1	2131.8	2038.5
40°	2805.2	2581.0	2217.9	1952.4	1855.2
42.5°	2663.1	2423.8	2046.1	1769.1	1675.8
45°	2513.5	2262.7	1870.3	1604.4	1514.7
47.5°	2371.5	2106.0	1702.0	1436.1	1354.0
50°	2214.3	1948.8	1537.3	1279.0	1200.8
52.5°	2060.7	1780.2	1380.2	1133.3	1062.3
55°	1911.1	1619.5	1215.5	991.3	920.2
57.5°	1758.0	1458.7	1069.9	860.3	800.4
60°	1600.8	1301.6	916.3	725.8	665.9
62.5°	1447.6	1148.4	785.3	606.0	576.2
65°	1290.5	987.3	650.8	523.8	512.3
67.5°	1140.9	837.7	523.8	459.9	448.8
70°	983.7	692.1	433.7	396.4	381.4
72.5°	834.1	557.1	362.7	332.9	325.4
75°	688.1	426.2	299.2	273.0	269.4
77.5°	542.5	302.8	235.7	220.6	213.1
80°	407.5	217.1	179.4	164.7	164.7
82.5°	284.1	146.0	123.4	115.9	115.9
85°	160.7	82.1	71.0	71.0	71.0
87.5°	59.9	29.8	29.8	26.2	26.2
90°	3.1	37.8	102.8	96.5	99.6
92.5°	65.0	88.1	91.2	94.4	94.4
95°	153.1	182.5	187.7	187.7	182.5
97.5°	254.9	282.1	293.7	293.7	293.7
100°	372.3	396.4	404.8	404.8	401.7
102.5°	496.1	513.9	525.5	528.6	525.5
105°	631.4	639.8	646.1	651.3	651.3
107.5°	765.6	778.2	778.2	780.3	765.6
110°	895.7	912.5	912.5	912.5	904.1



TEST NUMBER: P907516

CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1036.2	1054.0	1050.9	1042.5	1036.2
115°	1174.7	1191.4	1186.2	1183.1	1174.7
117.5°	1312.1	1335.1	1320.4	1312.1	1303.7
120°	1450.5	1473.6	1450.5	1450.5	1441.1
122.5°	1576.4	1605.7	1591.0	1582.6	1576.4
125°	1708.5	1734.7	1726.3	1716.9	1713.7
127.5°	1837.5	1870.0	1858.5	1845.9	1837.5
130°	1958.1	1995.9	1990.6	1984.3	1972.8
132.5°	2093.4	2122.8	2124.9	2110.2	2101.8
135°	2209.8	2242.3	2248.6	2245.5	2237.1
137.5°	2339.9	2366.1	2371.3	2369.2	2356.7
140°	2454.2	2480.4	2495.1	2495.1	2483.6
142.5°	2571.7	2597.9	2606.3	2609.4	2597.9
145°	2682.8	2703.8	2720.6	2723.7	2712.2
147.5°	2782.5	2808.7	2821.3	2826.5	2815.0
150°	2885.3	2903.1	2914.6	2924.1	2914.6
152.5°	2976.5	2994.3	3009.0	3020.6	3009.0
155°	3067.8	3076.1	3085.6	3100.3	3090.8
157.5°	3146.4	3152.7	3157.9	3178.9	3164.2
160°	3216.7	3223.0	3226.1	3244.0	3231.4
162.5°	3281.7	3281.7	3284.9	3304.8	3290.1
165°	3337.3	3334.1	3334.1	3355.1	3340.4
167.5°	3387.6	3378.2	3378.2	3399.2	3384.5
170°	3425.4	3417.0	3413.9	3434.8	3417.0
172.5°	3451.6	3443.2	3440.1	3461.1	3443.2
175°	3472.6	3464.2	3457.9	3478.9	3461.1
177.5°	3484.1	3475.7	3469.4	3487.3	3469.4
180°	3478.9	3478.9	3478.9	3478.9	3478.9



TEST NUMBER: P907516
 CATALOG NUMBER: DFN2DIP-TR4F0-100D110US835-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.95	11.75	11.94	12.75	14.07	6.92	7.73	7.92	8.73	10.05
	3H	12.63	13.34	13.63	14.35	15.69	8.11	8.83	9.11	9.84	11.18
	4H	13.23	13.91	14.25	14.92	16.27	8.56	9.24	9.58	10.25	11.60
	6H	13.65	14.28	14.68	15.29	16.66	8.88	9.51	9.91	10.52	11.89
	8H	13.78	14.37	14.81	15.41	16.76	8.97	9.57	10.00	10.60	11.96
	12H	13.84	14.40	14.88	15.43	16.81	9.02	9.58	10.05	10.61	11.99
4H	2H	10.97	11.65	11.99	12.66	14.01	7.52	8.20	8.54	9.21	10.56
	3H	12.79	13.36	13.82	14.40	15.76	8.86	9.43	9.89	10.47	11.83
	4H	13.48	14.00	14.52	15.03	16.42	9.41	9.93	10.45	10.96	12.35
	6H	14.00	14.44	15.04	15.50	16.88	9.83	10.28	10.88	11.33	12.71
	8H	14.17	14.59	15.22	15.63	17.03	9.96	10.37	11.01	11.42	12.82
	12H	14.27	14.64	15.33	15.70	17.10	10.02	10.40	11.09	11.46	12.86
8H	4H	13.45	13.86	14.50	14.91	16.31	9.69	10.10	10.74	11.15	12.55
	6H	14.01	14.36	15.09	15.45	16.84	10.21	10.55	11.28	11.64	13.04
	8H	14.23	14.53	15.31	15.61	17.02	10.40	10.70	11.48	11.78	13.19
	12H	14.37	14.63	15.45	15.70	17.16	10.52	10.78	11.60	11.85	13.31
12H	4H	13.40	13.77	14.47	14.84	16.24	9.69	10.07	10.76	11.13	12.53
	6H	13.99	14.29	15.07	15.36	16.78	10.26	10.56	11.34	11.63	13.05
	8H	14.21	14.47	15.29	15.54	17.00	10.47	10.73	11.55	11.80	13.26