

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926236

Luminaire Tested: DFN2DIP-TR3F0-050D030US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926236
REPORT IS A COMBINATION OF REPORTS P900275 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-050D030US950-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 7255.1 lumens
Efficiency: N/A
Efficacy: 106.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9933
Total Harmonic Distortion (THDi): 0.066
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	111	111	111	111	104	104	104	104	92	92	92	80	80	80	70	70	70
1	101	97	93	89	95	91	88	84	81	78	75	71	69	67	62	60	59
2	92	85	78	73	86	80	74	69	71	66	63	62	59	56	55	52	50
3	84	74	67	61	79	70	63	58	62	57	53	55	51	47	48	45	42
4	77	66	58	52	72	62	55	49	55	50	45	49	44	41	43	40	37
5	71	59	50	44	66	56	48	42	50	44	39	44	39	35	39	35	32
6	65	53	45	39	61	50	43	37	45	39	34	40	35	31	35	31	28
7	60	48	40	34	57	45	38	33	41	35	30	36	31	28	32	28	25
8	56	44	36	30	53	41	34	29	37	31	27	33	28	25	30	26	22
9	52	40	32	27	49	38	31	26	34	28	24	31	26	22	27	23	20
10	49	37	29	24	46	35	28	23	32	26	22	28	24	20	25	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2313	2313	2313
5°	2315	2279	2295
10°	2295	2246	2262
15°	2260	2207	2212
20°	2213	2154	2161
25°	2167	2090	2101
30°	2108	2031	2027
35°	2053	1962	1948
40°	1985	1892	1873
45°	1918	1821	1796
50°	1844	1747	1707
55°	1766	1661	1625
60°	1678	1560	1531
65°	1582	1455	1420
70°	1460	1326	1300
75°	1290	1172	1187
80°	1087	975	976
85°	767	641	630

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
Vertical Angle: 45°
Luminance: 1918 cd/sqm

TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	174.7	2.4
10°-20°	491.5	6.8
20°-30°	722.3	10.0
30°-40°	838.9	11.6
40°-50°	837.9	11.5
50°-60°	730.6	10.1
60°-70°	540.1	7.4
70°-80°	305.6	4.2
80°-90°	83.2	1.1
90°-100°	56.0	0.8
100°-110°	178.0	2.5
110°-120°	304.6	4.2
120°-130°	400.5	5.5
130°-140°	449.6	6.2
140°-150°	440.9	6.1
150°-160°	369.8	5.1
160°-170°	245.3	3.4
170°-180°	85.7	1.2
0°-30°	1388.5	19.1
0°-40°	2227.5	30.7
0°-60°	3796.0	52.3
0°-90°	4724.9	65.1
90°-120°	538.5	7.4
90°-150°	1829.5	25.2
90°-180°	2530.0	34.9
0°-180°	7255.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1856	1856	1856	1856	1856	
5°	1856	1849	1829	1844	1840	176
15°	1767	1756	1733	1740	1731	498
25°	1599	1585	1554	1558	1554	736
35°	1380	1362	1333	1322	1314	862
45°	1123	1110	1083	1064	1057	866
55°	850	839	817	796	787	760
65°	573	562	544	528	519	567
75°	300	296	287	277	280	320
85°	73	71	70	64	62	82
90°	1	10	27	25	26	7
95°	40	48	49	49	48	44
105°	164	166	168	169	169	173
115°	306	310	309	308	306	302
125°	445	451	449	447	446	397
135°	575	583	585	584	582	444
145°	698	704	708	709	706	436
155°	798	800	803	807	804	367
165°	868	868	868	873	869	245
175°	904	901	900	905	900	86
180°	905	905	905	905	905	

TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1856.0	1856.0	1856.0	1856.0	1856.0
2.5°	1866.8	1857.9	1838.3	1856.0	1852.7
5°	1856.0	1849.0	1829.3	1843.5	1840.2
7.5°	1843.5	1832.9	1813.3	1827.7	1824.0
10°	1824.0	1811.6	1790.2	1804.3	1799.1
12.5°	1797.1	1786.6	1765.2	1774.1	1770.4
15°	1766.8	1756.2	1732.9	1740.2	1731.2
17.5°	1729.3	1718.7	1695.4	1704.3	1695.4
20°	1688.3	1677.7	1652.7	1658.0	1651.0
22.5°	1647.4	1631.2	1608.0	1608.0	1604.3
25°	1599.1	1584.9	1554.5	1558.0	1554.5
27.5°	1545.5	1533.0	1509.9	1504.6	1495.7
30°	1492.1	1477.7	1451.0	1445.7	1438.5
32.5°	1434.9	1424.3	1395.7	1384.9	1377.8
35°	1379.6	1361.8	1333.2	1322.4	1313.6
37.5°	1317.1	1301.1	1272.4	1259.9	1251.1
40°	1253.0	1238.6	1210.0	1194.0	1186.9
42.5°	1190.5	1176.1	1147.7	1129.6	1119.0
45°	1122.7	1110.2	1083.3	1063.8	1056.6
47.5°	1056.6	1044.1	1015.5	995.8	985.2
50°	986.9	978.0	953.0	928.1	919.1
52.5°	919.1	906.6	883.5	863.8	851.3
55°	849.6	838.9	817.4	796.0	787.1
57.5°	779.9	771.0	747.7	726.4	719.1
60°	710.3	703.3	678.3	658.5	653.3
62.5°	642.5	630.0	612.2	594.3	587.2
65°	573.0	562.2	544.4	528.3	519.4
67.5°	501.6	492.6	476.6	464.1	456.9
70°	435.5	428.3	412.2	399.7	392.8
72.5°	367.8	360.5	351.6	339.1	333.8
75°	299.7	296.3	287.2	276.7	280.3
77.5°	239.2	231.9	228.4	223.0	217.8
80°	178.6	176.7	173.1	167.8	164.2
82.5°	121.3	121.3	119.6	112.5	112.5
85°	73.1	71.4	69.6	64.2	62.5
87.5°	32.1	28.6	25.0	19.7	17.8
90°	0.9	9.8	26.7	25.1	25.9
92.5°	16.9	22.9	23.8	24.5	24.5
95°	39.9	47.5	48.8	48.8	47.5
97.5°	66.3	73.4	76.4	76.4	76.4
100°	96.8	103.1	105.3	105.3	104.6
102.5°	129.1	133.8	136.7	137.6	136.7
105°	164.3	166.5	168.1	169.4	169.4
107.5°	199.2	202.4	202.4	203.0	199.2
110°	233.1	237.5	237.5	237.5	235.3

TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	269.6	274.3	273.4	271.2	269.6
115°	305.7	310.0	308.6	307.9	305.7
117.5°	341.3	347.4	343.5	341.3	339.1
120°	377.4	383.4	377.4	377.4	374.9
122.5°	410.1	417.8	413.9	411.7	410.1
125°	444.6	451.3	449.1	446.7	445.9
127.5°	478.0	486.5	483.6	480.2	478.0
130°	509.4	519.3	517.9	516.3	513.3
132.5°	544.6	552.3	552.8	549.0	546.8
135°	575.0	583.4	585.1	584.2	582.0
137.5°	608.7	615.6	617.0	616.5	613.1
140°	638.5	645.4	649.2	649.2	646.1
142.5°	669.1	675.9	678.1	679.0	675.9
145°	698.0	703.5	707.9	708.6	705.7
147.5°	724.0	730.8	734.0	735.4	732.4
150°	750.7	755.4	758.3	760.8	758.3
152.5°	774.5	779.0	782.9	785.9	782.9
155°	798.2	800.3	802.8	806.6	804.2
157.5°	818.6	820.2	821.7	827.1	823.3
160°	836.9	838.6	839.4	844.0	840.8
162.5°	853.8	853.8	854.7	859.8	856.0
165°	868.3	867.5	867.5	872.9	869.1
167.5°	881.4	878.9	878.9	884.4	880.5
170°	891.2	889.0	888.3	893.7	889.0
172.5°	898.0	895.9	895.0	900.5	895.9
175°	903.5	901.3	899.7	905.2	900.5
177.5°	906.5	904.3	902.7	907.3	902.7
180°	905.2	905.2	905.2	905.2	905.2

TEST NUMBER: P926236

CATALOG NUMBER: DFN2DIP-TR3F0-050D030US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	11.42	12.44	12.24	13.28	14.31	10.99	12.01	11.81	12.85	13.89
	3H	13.08	14.00	13.91	14.84	15.91	12.62	13.53	13.44	14.38	15.44
	4H	13.67	14.53	14.52	15.39	16.47	13.21	14.07	14.05	14.92	16.00
	6H	14.07	14.87	14.93	15.73	16.82	13.60	14.40	14.46	15.26	16.35
	8H	14.18	14.94	15.05	15.82	16.91	13.71	14.47	14.58	15.35	16.44
	12H	14.23	14.95	15.10	15.83	16.94	13.76	14.48	14.63	15.35	16.47
4H	2H	11.90	12.76	12.75	13.62	14.69	11.56	12.42	12.41	13.27	14.35
	3H	13.77	14.49	14.63	15.38	16.47	13.38	14.10	14.24	14.99	16.08
	4H	14.48	15.14	15.35	16.02	17.14	14.08	14.74	14.95	15.62	16.74
	6H	15.00	15.56	15.89	16.47	17.59	14.59	15.16	15.48	16.07	17.19
	8H	15.14	15.67	16.04	16.58	17.71	14.74	15.27	15.63	16.17	17.31
	12H	15.22	15.70	16.13	16.62	17.76	14.81	15.28	15.72	16.21	17.35
8H	4H	14.69	15.22	15.58	16.12	17.25	14.33	14.86	15.22	15.76	16.90
	6H	15.31	15.75	16.23	16.70	17.83	14.95	15.39	15.87	16.34	17.47
	8H	15.53	15.92	16.46	16.85	18.01	15.17	15.55	16.09	16.49	17.64
	12H	15.66	16.00	16.59	16.93	18.14	15.28	15.63	16.22	16.56	17.76
12H	4H	14.68	15.16	15.59	16.08	17.22	14.33	14.81	15.24	15.73	16.87
	6H	15.34	15.73	16.27	16.67	17.82	14.99	15.38	15.92	16.32	17.47
	8H	15.58	15.93	16.52	16.86	18.06	15.23	15.57	16.16	16.50	17.71