

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926312

Luminaire Tested: DFN2DIP-TR3F0-070D090US950-FLLFLL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926312
REPORT IS A COMBINATION OF REPORTS P900363 AND P897195
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-070D090US950-FLLFLL
Description: 3 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 14209.9 lumens
Efficiency: N/A
Efficacy: 100.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 141.1
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9971
Total Harmonic Distortion (THDi): 0.049
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50
RCR																	
0	106	106	106	106	98	98	98	98	81	81	81		67	67	67		53
1	97	93	89	85	89	85	82	79	71	69	67		59	57	55		47
2	88	81	75	70	81	75	69	65	63	59	55		51	49	46		41
3	81	71	64	58	74	66	59	54	55	50	47		45	42	39		37
4	74	63	55	49	67	58	51	46	49	44	40		41	37	34		33
5	68	56	48	42	62	52	45	39	44	38	34		36	32	29		29
6	62	50	42	36	57	47	39	34	39	34	30		33	29	25		27
7	58	45	37	32	53	42	35	30	36	30	26		30	26	23		24
8	53	41	33	28	49	38	31	27	33	27	23		27	23	20		22
9	50	38	30	25	46	35	28	24	30	25	21		25	21	18		21
10	46	34	27	22	43	32	26	21	28	22	19		23	19	16		19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3238	3238	3238
5°	3241	3190	3212
10°	3213	3144	3167
15°	3164	3090	3096
20°	3098	3015	3025
25°	3033	2927	2942
30°	2952	2844	2838
35°	2874	2747	2728
40°	2780	2648	2622
45°	2685	2550	2515
50°	2581	2446	2390
55°	2472	2326	2275
60°	2349	2184	2144
65°	2215	2037	1988
70°	2044	1857	1820
75°	1807	1641	1662
80°	1520	1365	1366
85°	1075	899	882

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°

Vertical Angle: 45°

Luminance: 2685 cd/sqm

TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	244.6	1.7
10°-20°	688.1	4.8
20°-30°	1011.3	7.1
30°-40°	1174.5	8.3
40°-50°	1173.1	8.3
50°-60°	1022.9	7.2
60°-70°	756.1	5.3
70°-80°	427.8	3.0
80°-90°	120.6	0.8
90°-100°	168.0	1.2
100°-110°	533.9	3.8
110°-120°	913.7	6.4
120°-130°	1201.6	8.5
130°-140°	1348.7	9.5
140°-150°	1322.6	9.3
150°-160°	1109.5	7.8
160°-170°	735.8	5.2
170°-180°	257.2	1.8
0°-30°	1943.9	13.7
0°-40°	3118.5	21.9
0°-60°	5314.4	37.4
0°-90°	6619.0	46.6
90°-120°	1615.6	11.4
90°-150°	5488.5	38.6
90°-180°	7591.0	53.4
0°-180°	14209.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2598	2598	2598	2598	2598	
5°	2598	2589	2561	2581	2576	247
15°	2474	2459	2426	2436	2424	697
25°	2239	2219	2176	2181	2176	1030
35°	1932	1907	1866	1851	1839	1206
45°	1572	1554	1517	1489	1479	1213
55°	1189	1174	1144	1114	1102	1063
65°	802	787	762	740	727	793
75°	420	415	402	387	392	448
85°	102	100	98	90	88	114
90°	2	30	80	75	78	14
95°	120	142	146	146	142	133
105°	493	499	504	508	508	520
115°	917	930	926	924	917	907
125°	1334	1354	1348	1340	1338	1192
135°	1725	1750	1755	1753	1746	1333
145°	2094	2110	2124	2126	2117	1308
155°	2394	2401	2408	2420	2413	1102
165°	2605	2602	2602	2619	2607	735
175°	2710	2704	2699	2716	2702	258
180°	2716	2716	2716	2716	2716	

TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2598.4	2598.4	2598.4	2598.4	2598.4
2.5°	2613.6	2601.1	2573.5	2598.4	2593.6
5°	2598.4	2588.7	2561.1	2581.0	2576.2
7.5°	2581.0	2566.1	2538.5	2558.7	2553.7
10°	2553.7	2536.1	2506.2	2526.1	2518.7
12.5°	2516.0	2501.2	2471.2	2483.6	2478.6
15°	2473.6	2458.7	2426.1	2436.2	2423.7
17.5°	2421.1	2406.3	2373.6	2386.1	2373.6
20°	2363.5	2348.7	2313.7	2321.2	2311.4
22.5°	2306.3	2283.8	2251.2	2251.2	2246.1
25°	2238.8	2218.8	2176.5	2181.2	2176.5
27.5°	2163.7	2146.2	2113.9	2106.4	2093.9
30°	2089.0	2068.7	2031.4	2024.0	2013.9
32.5°	2008.8	1994.1	1954.0	1938.9	1928.8
35°	1931.5	1906.6	1866.5	1851.4	1838.9
37.5°	1844.0	1821.5	1781.4	1763.9	1751.4
40°	1754.1	1734.0	1693.9	1671.7	1661.6
42.5°	1666.6	1646.5	1606.7	1581.5	1566.7
45°	1571.7	1554.3	1516.6	1489.3	1479.2
47.5°	1479.2	1461.7	1421.7	1394.1	1379.3
50°	1381.7	1369.2	1334.2	1299.3	1286.8
52.5°	1286.8	1269.3	1237.0	1209.4	1191.8
55°	1189.4	1174.4	1144.4	1114.5	1102.0
57.5°	1091.9	1079.5	1046.8	1016.9	1006.9
60°	994.4	984.5	949.6	922.0	914.6
62.5°	899.4	882.0	857.1	832.2	822.1
65°	802.2	787.0	762.2	739.6	727.1
67.5°	702.2	689.6	667.2	649.8	639.7
70°	609.7	599.7	577.1	559.6	549.8
72.5°	514.8	504.8	492.3	474.8	467.4
75°	419.7	414.9	402.1	387.3	392.4
77.5°	334.9	324.7	319.7	312.2	304.9
80°	249.9	247.4	242.3	234.9	229.8
82.5°	169.9	169.9	167.5	157.5	157.5
85°	102.4	100.0	97.6	89.9	87.5
87.5°	45.0	40.1	35.0	27.6	24.9
90°	2.5	29.5	80.2	75.3	77.8
92.5°	50.8	68.8	71.3	73.6	73.6
95°	119.5	142.4	146.5	146.5	142.4
97.5°	198.9	220.2	229.2	229.2	229.2
100°	290.6	309.5	316.0	316.0	313.6
102.5°	387.2	401.2	410.1	412.6	410.1
105°	492.8	499.3	504.3	508.4	508.4
107.5°	597.6	607.4	607.4	609.0	597.6
110°	699.1	712.3	712.3	712.3	705.7

TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	808.8	822.7	820.2	813.8	808.8
115°	916.9	930.0	925.9	923.5	916.9
117.5°	1024.1	1042.1	1030.7	1024.1	1017.5
120°	1132.2	1150.1	1132.2	1132.2	1124.8
122.5°	1230.4	1253.4	1241.9	1235.3	1230.4
125°	1333.6	1354.0	1347.5	1340.1	1337.7
127.5°	1434.2	1459.6	1450.7	1440.8	1434.2
130°	1528.4	1557.9	1553.8	1548.8	1539.9
132.5°	1634.0	1656.9	1658.5	1647.1	1640.6
135°	1724.8	1750.2	1755.2	1752.7	1746.2
137.5°	1826.3	1846.8	1851.0	1849.3	1839.5
140°	1915.6	1936.0	1947.5	1947.5	1938.5
142.5°	2007.3	2027.7	2034.3	2036.8	2027.7
145°	2094.1	2110.4	2123.5	2126.0	2117.0
147.5°	2171.9	2192.3	2202.1	2206.2	2197.3
150°	2252.1	2266.0	2275.0	2282.3	2275.0
152.5°	2323.3	2337.2	2348.7	2357.7	2348.7
155°	2394.5	2401.0	2408.5	2419.9	2412.6
157.5°	2455.9	2460.8	2464.9	2481.3	2469.8
160°	2510.7	2515.7	2518.2	2532.0	2522.2
162.5°	2561.5	2561.5	2564.0	2579.5	2568.1
165°	2604.9	2602.4	2602.4	2618.8	2607.4
167.5°	2644.2	2636.9	2636.9	2653.2	2641.7
170°	2673.7	2667.1	2664.7	2681.0	2667.1
172.5°	2694.1	2687.6	2685.1	2701.5	2687.6
175°	2710.5	2703.9	2699.1	2715.5	2701.5
177.5°	2719.5	2713.0	2708.0	2722.0	2708.0
180°	2715.5	2715.5	2715.5	2715.5	2715.5

TEST NUMBER: P926312

CATALOG NUMBER: DFN2DIP-TR3F0-070D090US950-FLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	10.98	11.81	11.96	12.81	14.12	10.55	11.38	11.53	12.38	13.70
	3H	12.62	13.37	13.62	14.38	15.72	12.16	12.90	13.15	13.91	15.25
	4H	13.20	13.91	14.21	14.92	16.27	12.74	13.44	13.75	14.45	15.80
	6H	13.60	14.25	14.62	15.26	16.62	13.13	13.78	14.15	14.79	16.15
	8H	13.70	14.32	14.72	15.35	16.70	13.23	13.85	14.25	14.88	16.24
	12H	13.74	14.33	14.77	15.35	16.74	13.27	13.85	14.30	14.88	16.26
4H	2H	11.43	12.14	12.45	13.15	14.50	11.09	11.79	12.10	12.80	14.15
	3H	13.28	13.87	14.31	14.91	16.27	12.89	13.48	13.92	14.52	15.88
	4H	13.99	14.53	15.02	15.56	16.94	13.59	14.13	14.62	15.16	16.54
	6H	14.49	14.96	15.54	16.01	17.39	14.09	14.55	15.13	15.61	16.99
	8H	14.64	15.07	15.68	16.12	17.51	14.23	14.66	15.27	15.71	17.11
	12H	14.70	15.10	15.77	16.16	17.56	14.29	14.68	15.35	15.74	17.14
8H	4H	14.18	14.61	15.22	15.66	17.06	13.82	14.26	14.87	15.30	16.70
	6H	14.80	15.16	15.86	16.25	17.64	14.44	14.80	15.51	15.89	17.28
	8H	15.01	15.33	16.09	16.40	17.81	14.65	14.96	15.72	16.04	17.45
	12H	15.14	15.41	16.21	16.48	17.94	14.76	15.03	15.84	16.10	17.56
12H	4H	14.16	14.55	15.22	15.62	17.02	13.81	14.21	14.87	15.27	16.67
	6H	14.83	15.14	15.90	16.21	17.63	14.48	14.79	15.55	15.87	17.28
	8H	15.06	15.34	16.14	16.41	17.86	14.71	14.98	15.78	16.05	17.51