

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926317

Luminaire Tested: DFN2DIP-TR3F0-080D030US950-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926317
REPORT IS A COMBINATION OF REPORTS P901802 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-080D030US950-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 9320.6 lumens
Efficiency: N/A
Efficacy: 90.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: Semi-Direct

Input Watts (W): 103.6
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9968
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926317
CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P926317
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20									20
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	74	74	74	74	74	74	74	74	74	74	74	20																
	1	103	99	95	92	97	93	90	87	84	81	79	75	73	71	67	65	64	64	64	64	64	64	64	64	64	64	64	64	60																
	2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	59	57	55	55	55	55	55	55	55	55	55	55	55	55	51																
	3	86	77	70	64	82	73	67	62	66	61	57	59	55	52	53	50	48	48	48	48	48	48	48	48	48	48	48	48	44																
	4	79	69	61	55	75	65	58	53	59	54	49	53	49	45	48	45	42	42	42	42	42	42	42	42	42	42	42	42	39																
	5	73	62	54	48	69	59	52	46	53	47	43	48	44	40	44	40	37	37	37	37	37	37	37	37	37	37	37	37	34																
	6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	33	33	33	33	33	33	33	33	33	33	33	30																
	7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	32	29	29	29	29	29	29	29	29	29	29	29	29	27																
	8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	27	27	27	27	27	27	27	27	27	27	27	24																
	9	55	43	35	30	52	41	34	29	37	32	27	34	29	26	31	27	24	24	24	24	24	24	24	24	24	24	24	24	22																
	10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	22	22	22	22	22	22	22	22	22	22	22	20																

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	3931	3931	3931
5°	3935	3865	3890
10°	3894	3786	3761
15°	3838	3657	3563
20°	3765	3482	3321
25°	3690	3286	3087
30°	3590	3085	2791
35°	3492	2869	2532
40°	3393	2646	2234
45°	3277	2400	1965
50°	3157	2151	1702
55°	3032	1886	1450
60°	2886	1608	1191
65°	2719	1327	1069
70°	2517	1065	964
75°	2261	932	871
80°	1892	771	747
85°	1288	499	547

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3277 cd/sqm



TEST NUMBER: P926317

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	295.6	3.2
10°-20°	811.5	8.7
20°-30°	1139.4	12.2
30°-40°	1242.0	13.3
40°-50°	1141.5	12.2
50°-60°	896.5	9.6
60°-70°	583.5	6.3
70°-80°	300.4	3.2
80°-90°	78.4	0.8
90°-100°	31.9	0.3
100°-110°	118.7	1.3
110°-120°	314.9	3.4
120°-130°	522.3	5.6
130°-140°	554.8	6.0
140°-150°	515.6	5.5
150°-160°	414.5	4.4
160°-170°	267.1	2.9
170°-180°	91.9	1.0
0°-30°	2246.6	24.1
0°-40°	3488.6	37.4
0°-60°	5526.6	59.3
0°-90°	6488.9	69.6
90°-120°	465.5	5.0
90°-150°	2058.1	22.1
90°-180°	2832.0	30.4
0°-180°	9320.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3154	3154	3154	3154	3154	
5°	3154	3140	3103	3128	3120	299
15°	3000	2969	2872	2818	2789	845
25°	2723	2632	2444	2327	2284	1252
35°	2347	2201	1950	1770	1707	1469
45°	1918	1727	1427	1224	1156	1481
55°	1459	1236	928	756	702	1303
65°	985	754	497	400	391	976
75°	525	325	228	208	206	555
85°	123	63	54	54	54	141
90°	1	8	14	18	19	9
95°	45	22	27	31	30	54
105°	212	233	43	50	53	227
115°	402	414	431	108	57	396
125°	568	577	591	596	598	507
135°	703	714	721	728	726	543
145°	816	815	827	832	828	510
155°	898	892	900	904	899	414
165°	946	942	944	949	944	267
175°	968	963	964	969	962	92
180°	966	966	966	966	966	



TEST NUMBER: P926317

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3154.3	3154.3	3154.3	3154.3	3154.3
2.5°	3168.5	3154.3	3122.8	3151.5	3145.8
5°	3154.3	3140.1	3102.8	3128.5	3120.1
7.5°	3128.5	3111.6	3071.6	3082.9	3068.5
10°	3094.3	3074.4	3017.4	3008.6	2991.6
12.5°	3051.7	3025.9	2948.6	2931.6	2900.2
15°	3000.1	2968.7	2871.7	2817.5	2789.0
17.5°	2940.1	2894.4	2774.5	2711.8	2666.0
20°	2871.7	2814.5	2671.9	2600.7	2537.6
22.5°	2797.5	2731.8	2566.2	2469.2	2426.5
25°	2723.3	2631.9	2443.5	2326.6	2283.6
27.5°	2634.9	2537.6	2329.3	2195.2	2129.4
30°	2540.7	2431.9	2203.6	2058.3	1981.0
32.5°	2449.2	2317.8	2084.0	1912.6	1841.1
35°	2346.6	2200.9	1949.8	1770.0	1706.9
37.5°	2246.6	2089.5	1824.1	1627.0	1555.8
40°	2141.0	1969.8	1692.7	1490.1	1415.8
42.5°	2032.5	1849.9	1561.5	1350.2	1278.9
45°	1918.3	1726.9	1427.4	1224.5	1156.1
47.5°	1809.9	1607.3	1299.0	1096.1	1033.4
50°	1689.9	1487.4	1173.3	976.1	916.4
52.5°	1572.8	1358.6	1053.3	865.0	810.8
55°	1458.6	1236.0	927.7	756.5	702.3
57.5°	1341.7	1113.3	816.5	656.6	610.8
60°	1221.7	993.4	699.3	553.9	508.2
62.5°	1104.8	876.4	599.4	462.5	439.8
65°	984.9	753.5	496.7	399.8	390.9
67.5°	870.7	639.4	399.8	351.0	342.6
70°	750.8	528.2	331.0	302.5	291.1
72.5°	636.6	425.2	276.9	254.1	248.3
75°	525.2	325.3	228.4	208.4	205.7
77.5°	414.0	231.1	179.9	168.4	162.7
80°	311.0	165.7	136.9	125.6	125.6
82.5°	216.8	111.4	94.2	88.4	88.4
85°	122.7	62.7	54.2	54.2	54.2
87.5°	45.7	22.7	22.7	20.0	20.0
90°	0.7	8.4	13.9	17.6	18.8
92.5°	17.6	14.7	16.8	18.2	18.8
95°	45.4	22.3	27.2	30.8	30.1
97.5°	81.8	24.5	35.6	37.8	38.4
100°	123.7	28.0	39.9	45.4	46.8
102.5°	169.8	168.5	41.2	48.8	51.0
105°	212.5	233.4	42.6	50.3	53.1
107.5°	262.1	279.5	44.1	51.7	54.6
110°	309.7	324.3	122.3	52.5	55.2



TEST NUMBER: P926317

CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	354.4	366.9	355.1	53.8	55.9
115°	401.8	413.7	431.2	107.6	57.3
117.5°	443.1	457.1	469.0	369.0	185.9
120°	489.2	499.7	512.3	520.7	426.3
122.5°	528.3	539.6	553.6	557.7	558.5
125°	568.2	577.3	590.6	595.5	597.6
127.5°	604.5	614.3	624.9	631.8	632.5
130°	638.8	650.1	657.7	665.3	664.7
132.5°	673.7	682.9	690.5	696.8	696.1
135°	703.1	714.4	720.6	727.6	726.2
137.5°	733.8	742.2	749.3	756.2	754.1
140°	763.9	769.5	777.1	783.4	780.0
142.5°	789.1	794.0	803.1	808.6	805.2
145°	815.7	814.9	826.8	831.7	828.2
147.5°	838.7	836.6	848.5	851.9	849.2
150°	861.1	856.2	867.4	871.5	868.0
152.5°	879.9	874.3	884.8	889.0	884.2
155°	898.1	891.9	900.2	904.4	898.9
157.5°	912.8	907.3	913.6	918.4	912.8
160°	925.4	921.2	925.4	929.6	924.6
162.5°	936.5	932.3	935.9	940.7	934.4
165°	946.3	942.2	944.3	949.1	944.3
167.5°	954.0	949.8	951.9	956.9	950.6
170°	960.3	956.1	957.5	962.4	956.1
172.5°	964.5	960.3	961.7	966.6	960.3
175°	967.9	963.1	964.5	969.4	962.4
177.5°	969.4	964.5	965.3	970.1	963.8
180°	965.9	965.9	965.9	965.9	965.9



TEST NUMBER: P926317
 CATALOG NUMBER: DFN2DIP-TR3F0-080D030US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	13.51	14.53	14.29	15.33	16.29	9.49	10.51	10.27	11.30	12.27
	3H	15.20	16.11	15.99	16.91	17.91	10.69	11.60	11.48	12.40	13.40
	4H	15.81	16.67	16.61	17.48	18.48	11.14	12.00	11.95	12.82	13.82
	6H	16.23	17.02	17.05	17.84	18.86	11.47	12.26	12.29	13.08	14.10
	8H	16.36	17.11	17.19	17.95	18.97	11.56	12.32	12.39	13.15	14.17
	12H	16.42	17.14	17.26	17.97	19.02	11.61	12.33	12.44	13.16	14.20
4H	2H	13.55	14.41	14.36	15.23	16.23	10.10	10.96	10.91	11.78	12.78
	3H	15.39	16.10	16.21	16.95	17.97	11.46	12.18	12.29	13.02	14.05
	4H	16.08	16.73	16.92	17.57	18.62	12.02	12.66	12.85	13.51	14.56
	6H	16.60	17.16	17.45	18.03	19.08	12.44	13.00	13.29	13.87	14.92
	8H	16.77	17.30	17.63	18.16	19.22	12.57	13.09	13.42	13.95	15.02
	12H	16.87	17.34	17.75	18.22	19.29	12.64	13.11	13.51	13.99	15.06
8H	4H	16.06	16.59	16.92	17.45	18.51	12.30	12.83	13.16	13.69	14.76
	6H	16.63	17.06	17.51	17.96	19.03	12.82	13.25	13.70	14.16	15.22
	8H	16.84	17.22	17.73	18.12	19.20	13.01	13.39	13.90	14.29	15.37
	12H	16.98	17.31	17.87	18.20	19.34	13.13	13.47	14.03	14.36	15.50
12H	4H	16.02	16.49	16.90	17.38	18.45	12.32	12.79	13.19	13.67	14.74
	6H	16.60	16.98	17.49	17.88	18.97	12.87	13.25	13.76	14.15	15.23
	8H	16.82	17.16	17.72	18.05	19.19	13.08	13.42	13.98	14.31	15.45