

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P910068

Luminaire Tested: DFN2DIP-TR4F0-050D120US840-RLFL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P910068
REPORT IS A COMBINATION OF REPORTS P900516 AND P897293
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-050D120US840-RLLFLL
Description: 4 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Frosted Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 15016.7 lumens
Efficiency: N/A
Efficacy: 112.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 133.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.996
Total Harmonic Distortion (THDi): 0.064
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

Luminous Intensity Polar Plot



TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	37	37	37
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20
5	65	54	47	41	58	49	42	38	39	34	31	30	27	24	21	19	18
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1658	1658	1658
5°	1661	1632	1642
10°	1644	1600	1588
15°	1622	1547	1506
20°	1592	1474	1404
25°	1561	1392	1307
30°	1520	1308	1182
35°	1479	1218	1073
40°	1438	1125	948
45°	1391	1022	835
50°	1341	917	724
55°	1290	806	618
60°	1230	689	508
65°	1162	571	458
70°	1079	460	414
75°	975	406	376
80°	823	340	326
85°	574	227	245

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 2988 cd/sqm

TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	195.6	1.3
10°-20°	536.9	3.6
20°-30°	753.8	5.0
30°-40°	821.7	5.5
40°-50°	755.2	5.0
50°-60°	593.1	3.9
60°-70°	386.1	2.6
70°-80°	198.7	1.3
80°-90°	61.6	0.4
90°-100°	237.2	1.6
100°-110°	753.5	5.0
110°-120°	1289.5	8.6
120°-130°	1696.0	11.3
130°-140°	1903.6	12.7
140°-150°	1866.7	12.4
150°-160°	1565.9	10.4
160°-170°	1038.5	6.9
170°-180°	363.0	2.4
0°-30°	1486.3	9.9
0°-40°	2308.0	15.4
0°-60°	3656.4	24.3
0°-90°	4302.8	28.7
90°-120°	2280.2	15.2
90°-150°	7746.5	51.6
90°-180°	10714.0	71.3
0°-180°	15016.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2087	2087	2087	2087	2087	
5°	2087	2078	2053	2070	2064	198
15°	1985	1964	1900	1864	1845	559
25°	1802	1741	1617	1539	1511	829
35°	1552	1456	1290	1171	1129	972
45°	1269	1143	944	810	765	980
55°	965	818	614	500	465	862
65°	652	499	329	264	259	646
75°	348	215	151	138	136	368
85°	81	42	36	36	36	93
90°	3	42	113	106	110	15
95°	169	201	207	207	201	188
105°	696	705	712	718	718	734
115°	1294	1313	1307	1303	1294	1280
125°	1882	1911	1902	1892	1888	1682
135°	2434	2470	2477	2474	2465	1882
145°	2956	2979	2997	3001	2988	1847
155°	3380	3389	3399	3416	3405	1556
165°	3677	3673	3673	3696	3680	1037
175°	3826	3816	3810	3832	3813	363
180°	3832	3832	3832	3832	3832	

TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2086.9	2086.9	2086.9	2086.9	2086.9
2.5°	2096.3	2086.9	2066.1	2085.1	2081.2
5°	2086.9	2077.5	2052.9	2069.8	2064.3
7.5°	2069.8	2058.6	2032.2	2039.6	2030.1
10°	2047.2	2034.0	1996.3	1990.5	1979.2
12.5°	2018.9	2002.0	1950.9	1939.6	1918.7
15°	1984.9	1964.1	1900.0	1864.1	1845.2
17.5°	1945.2	1915.0	1835.6	1794.1	1763.8
20°	1900.0	1862.1	1767.7	1720.6	1678.9
22.5°	1850.9	1807.4	1697.8	1633.7	1605.4
25°	1801.7	1741.2	1616.6	1539.2	1510.8
27.5°	1743.2	1678.9	1541.1	1452.3	1408.9
30°	1680.9	1609.0	1457.9	1361.7	1310.6
32.5°	1620.4	1533.5	1378.8	1265.4	1218.1
35°	1552.5	1456.1	1290.0	1170.9	1129.3
37.5°	1486.3	1382.4	1206.9	1076.4	1029.4
40°	1416.4	1303.2	1119.8	985.8	936.8
42.5°	1344.7	1223.9	1033.1	893.2	846.2
45°	1269.2	1142.6	944.3	810.1	764.8
47.5°	1197.4	1063.4	859.4	725.2	683.7
50°	1118.1	984.0	776.3	645.8	606.3
52.5°	1040.6	898.9	696.9	572.3	536.4
55°	965.0	817.7	613.7	500.5	464.6
57.5°	887.7	736.6	540.2	434.4	404.1
60°	808.3	657.2	462.6	366.5	336.2
62.5°	730.9	579.9	396.6	306.0	290.9
65°	651.6	498.6	328.6	264.5	258.7
67.5°	576.0	423.0	264.5	232.3	226.6
70°	496.8	349.4	219.0	200.2	192.6
72.5°	421.2	281.3	183.2	168.1	164.3
75°	347.5	215.2	151.1	137.8	136.0
77.5°	273.9	152.9	119.1	111.4	107.6
80°	205.8	109.6	90.6	83.1	83.1
82.5°	143.5	73.7	62.3	58.5	58.5
85°	81.2	41.5	35.9	35.9	35.9
87.5°	30.3	15.0	15.0	13.2	13.2
90°	3.4	41.6	113.2	106.3	109.8
92.5°	71.6	97.0	100.5	104.0	104.0
95°	168.6	201.1	206.8	206.8	201.1
97.5°	280.7	310.8	323.6	323.6	323.6
100°	410.2	436.8	446.0	446.0	442.5
102.5°	546.5	566.1	578.9	582.4	578.9
105°	695.6	704.8	711.8	717.5	717.5
107.5°	843.4	857.4	857.4	859.6	843.4
110°	986.7	1005.2	1005.2	1005.2	996.0

TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1141.6	1161.2	1157.7	1148.5	1141.6
115°	1294.0	1312.6	1306.8	1303.3	1294.0
117.5°	1445.4	1470.9	1454.7	1445.4	1436.2
120°	1598.0	1623.4	1598.0	1598.0	1587.6
122.5°	1736.7	1769.0	1752.8	1743.5	1736.7
125°	1882.2	1911.1	1901.9	1891.5	1887.9
127.5°	2024.4	2060.1	2047.4	2033.6	2024.4
130°	2157.2	2198.8	2193.0	2186.1	2173.3
132.5°	2306.2	2338.6	2340.9	2324.7	2315.5
135°	2434.5	2470.3	2477.3	2473.8	2464.6
137.5°	2577.8	2606.7	2612.4	2610.1	2596.3
140°	2703.7	2732.6	2748.8	2748.8	2736.0
142.5°	2833.2	2862.1	2871.2	2874.7	2862.1
145°	2955.6	2978.7	2997.2	3000.7	2988.0
147.5°	3065.3	3094.2	3108.2	3113.9	3101.2
150°	3178.7	3198.2	3211.0	3221.4	3211.0
152.5°	3279.1	3298.7	3315.0	3327.7	3315.0
155°	3379.6	3388.9	3399.3	3415.5	3405.1
157.5°	3466.4	3473.2	3479.0	3502.1	3486.0
160°	3543.7	3550.7	3554.1	3573.8	3559.9
162.5°	3615.3	3615.3	3618.9	3640.8	3624.6
165°	3676.6	3673.2	3673.2	3696.2	3680.1
167.5°	3732.1	3721.7	3721.7	3744.8	3728.6
170°	3773.7	3764.4	3760.9	3784.1	3764.4
172.5°	3802.5	3793.3	3789.8	3812.9	3793.3
175°	3825.7	3816.4	3809.5	3832.5	3812.9
177.5°	3838.4	3829.1	3822.1	3841.8	3822.1
180°	3832.5	3832.5	3832.5	3832.5	3832.5

TEST NUMBER: P910068

CATALOG NUMBER: DFN2DIP-TR4F0-050D120US840-RLLFLL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	6.47	7.16	7.60	8.27	9.82	2.45	3.13	3.57	4.24	5.79
	3H	8.14	8.75	9.27	9.87	11.44	3.63	4.24	4.76	5.36	6.92
	4H	8.74	9.32	9.88	10.44	12.01	4.07	4.65	5.21	5.77	7.34
	6H	9.16	9.69	10.31	10.81	12.40	4.38	4.92	5.54	6.04	7.62
	8H	9.28	9.78	10.43	10.93	12.50	4.47	4.98	5.62	6.12	7.69
	12H	9.33	9.81	10.49	10.95	12.55	4.51	4.99	5.67	6.13	7.72
4H	2H	6.47	7.05	7.63	8.18	9.75	3.02	3.60	4.18	4.73	6.30
	3H	8.29	8.77	9.45	9.92	11.50	4.36	4.84	5.52	5.99	7.58
	4H	8.98	9.42	10.13	10.56	12.16	4.90	5.35	6.06	6.49	8.09
	6H	9.48	9.86	10.65	11.02	12.61	5.32	5.70	6.48	6.86	8.45
	8H	9.65	10.01	10.82	11.16	12.77	5.44	5.80	6.61	6.95	8.56
	12H	9.74	10.06	10.92	11.23	12.84	5.50	5.82	6.68	6.99	8.60
8H	4H	8.93	9.29	10.10	10.44	12.05	5.17	5.53	6.34	6.68	8.29
	6H	9.49	9.78	10.68	10.98	12.59	5.69	5.98	6.87	7.17	8.78
	8H	9.71	9.96	10.90	11.14	12.76	5.88	6.13	7.07	7.31	8.93
	12H	9.84	10.06	11.03	11.24	12.89	5.99	6.22	7.18	7.39	9.04
12H	4H	8.88	9.20	10.06	10.36	11.98	5.17	5.49	6.35	6.66	8.27
	6H	9.47	9.72	10.66	10.90	12.52	5.74	5.99	6.92	7.16	8.79
	8H	9.68	9.91	10.87	11.08	12.73	5.94	6.16	7.13	7.34	8.99

END OF REPORT