

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P926363

Luminaire Tested: DFN2DIP-TR3F0-090D080US950-RLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P926363
REPORT IS A COMBINATION OF REPORTS P901874 AND P898751
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR3F0-090D080US950-RLLONL
Description: 3 foot, Triangle Define Geo, with Direct 1in Regressed Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 14853.8 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular w/ Sides (W: 2.74' x L: 3.16' x H: 0.1')
CIE Type: General Diffuse

Input Watts (W): 156
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9951
Total Harmonic Distortion (THDi): 0.07
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P926363
CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLLONL

Luminous Intensity Polar Plot





TEST NUMBER: P926363
 CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	55	55	55	49																																				
1	98	94	90	87	90	87	84	81	73	71	69	61	59	58	50	49	48	42																																				
2	90	83	77	72	82	76	71	67	65	61	58	54	52	49	44	42	41	36																																				
3	82	73	66	60	75	68	62	57	58	53	49	48	45	42	40	37	35	31																																				
4	75	65	57	51	69	60	54	48	51	46	42	43	40	37	36	33	31	27																																				
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	32	30	27	24																																				
6	64	52	44	39	59	49	42	37	42	36	32	36	31	28	30	27	24	21																																				
7	59	47	40	34	55	44	37	32	38	33	29	32	28	25	27	24	22	19																																				
8	55	43	36	30	51	40	33	29	35	29	26	30	26	23	25	22	20	17																																				
9	51	39	32	27	47	37	30	26	32	27	23	28	23	20	23	20	18	16																																				
10	48	36	29	24	44	34	28	23	30	24	21	25	21	19	22	18	16	14																																				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	4422	4422	4422
5°	4427	4348	4377
10°	4380	4259	4231
15°	4318	4115	4009
20°	4235	3917	3736
25°	4151	3697	3473
30°	4039	3470	3140
35°	3929	3228	2848
40°	3817	2977	2514
45°	3686	2700	2211
50°	3552	2420	1915
55°	3411	2121	1631
60°	3247	1810	1340
65°	3059	1493	1203
70°	2831	1198	1084
75°	2544	1048	980
80°	2129	868	840
85°	1448	562	615

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3686 cd/sqm



TEST NUMBER: P926363

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	332.6	2.2
10°-20°	913.0	6.1
20°-30°	1281.8	8.6
30°-40°	1397.3	9.4
40°-50°	1284.2	8.6
50°-60°	1008.6	6.8
60°-70°	656.5	4.4
70°-80°	337.9	2.3
80°-90°	90.8	0.6
90°-100°	84.9	0.6
100°-110°	316.6	2.1
110°-120°	839.7	5.7
120°-130°	1392.7	9.4
130°-140°	1479.4	10.0
140°-150°	1374.9	9.3
150°-160°	1105.4	7.4
160°-170°	712.3	4.8
170°-180°	245.2	1.7
0°-30°	2527.4	17.0
0°-40°	3924.6	26.4
0°-60°	6217.4	41.9
0°-90°	7302.7	49.2
90°-120°	1241.3	8.4
90°-150°	5488.3	36.9
90°-180°	7551.0	50.8
0°-180°	14853.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	3549	3549	3549	3549	3549	
5°	3549	3533	3491	3520	3510	336
15°	3375	3340	3231	3170	3138	951
25°	3064	2961	2749	2617	2569	1409
35°	2640	2476	2194	1991	1920	1652
45°	2158	1943	1606	1378	1300	1667
55°	1641	1390	1044	851	790	1466
65°	1108	848	559	450	440	1099
75°	591	366	257	234	231	625
85°	138	70	61	61	61	158
90°	2	22	37	47	50	14
95°	121	60	73	82	80	143
105°	567	623	114	134	142	605
115°	1072	1103	1150	287	153	1055
125°	1515	1540	1575	1588	1594	1351
135°	1875	1905	1922	1940	1936	1448
145°	2175	2173	2205	2218	2208	1360
155°	2395	2378	2401	2412	2397	1104
165°	2524	2512	2518	2531	2518	713
175°	2581	2568	2572	2585	2566	246
180°	2576	2576	2576	2576	2576	



TEST NUMBER: P926363

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	3548.6	3548.6	3548.6	3548.6	3548.6
2.5°	3564.6	3548.6	3513.1	3545.5	3539.1
5°	3548.6	3532.6	3490.7	3519.6	3510.1
7.5°	3519.6	3500.5	3455.6	3468.2	3452.1
10°	3481.1	3458.6	3394.6	3384.7	3365.6
12.5°	3433.1	3404.2	3317.2	3298.2	3262.7
15°	3375.2	3339.8	3230.7	3169.7	3137.7
17.5°	3307.7	3256.3	3121.3	3050.8	2999.4
20°	3230.7	3166.3	3005.8	2925.7	2854.8
22.5°	3147.2	3073.3	2886.9	2777.9	2729.9
25°	3063.8	2960.8	2749.0	2617.4	2569.0
27.5°	2964.3	2854.8	2620.4	2469.5	2395.6
30°	2858.3	2736.0	2479.1	2315.5	2228.6
32.5°	2755.3	2607.5	2344.5	2151.7	2071.2
35°	2639.9	2476.0	2193.5	1991.2	1920.3
37.5°	2527.4	2350.7	2052.1	1830.3	1750.3
40°	2408.6	2216.0	1904.3	1676.4	1592.9
42.5°	2286.5	2081.2	1756.7	1519.0	1438.8
45°	2158.1	1942.8	1605.8	1377.5	1300.5
47.5°	2036.1	1808.2	1461.3	1233.0	1162.5
50°	1901.2	1673.2	1320.0	1098.1	1031.0
52.5°	1769.4	1528.5	1185.1	973.1	912.1
55°	1640.9	1390.5	1043.6	851.2	790.1
57.5°	1509.4	1252.5	918.6	738.7	687.3
60°	1374.4	1117.5	786.8	623.2	571.7
62.5°	1243.0	986.1	674.3	520.3	494.7
65°	1108.0	847.7	558.8	449.7	439.9
67.5°	979.6	719.2	449.7	394.9	385.3
70°	844.7	594.2	372.4	340.4	327.4
72.5°	716.2	478.3	311.4	285.8	279.4
75°	590.8	366.0	256.9	234.4	231.3
77.5°	465.7	260.0	202.3	189.5	183.0
80°	349.9	186.4	154.0	141.4	141.4
82.5°	243.9	125.4	106.0	99.5	99.5
85°	137.9	70.5	61.0	61.0	61.0
87.5°	51.4	25.6	25.6	22.5	22.5
90°	1.8	22.3	37.2	46.7	50.3
92.5°	46.7	39.2	44.7	48.5	50.3
95°	121.1	59.5	72.6	82.1	80.1
97.5°	218.0	65.3	94.9	100.7	102.5
100°	330.0	74.6	106.3	121.1	124.8
102.5°	452.9	449.2	110.0	130.3	136.1
105°	566.6	622.6	113.7	134.1	141.7
107.5°	698.9	745.4	117.5	137.9	145.4
110°	825.8	864.7	326.3	139.9	147.2



TEST NUMBER: P926363

CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	945.0	978.4	946.8	143.4	149.2
115°	1071.6	1103.3	1150.0	287.1	152.9
117.5°	1181.6	1218.8	1250.7	984.0	495.8
120°	1304.7	1332.5	1366.2	1388.5	1136.9
122.5°	1408.9	1438.8	1476.2	1487.3	1489.3
125°	1515.1	1539.5	1574.9	1587.9	1593.5
127.5°	1612.1	1638.2	1666.4	1684.9	1686.7
130°	1703.5	1733.3	1753.7	1774.3	1772.5
132.5°	1796.7	1821.0	1841.4	1858.2	1856.4
135°	1875.0	1904.9	1921.5	1940.3	1936.5
137.5°	1956.9	1979.3	1998.1	2016.7	2011.1
140°	2037.0	2052.1	2072.5	2089.3	2079.9
142.5°	2104.3	2117.3	2141.4	2156.3	2147.0
145°	2175.1	2173.1	2204.8	2217.9	2208.5
147.5°	2236.5	2230.9	2262.5	2271.9	2264.5
150°	2296.2	2283.1	2313.0	2324.0	2314.8
152.5°	2346.5	2331.6	2359.4	2370.8	2357.7
155°	2394.9	2378.3	2400.6	2411.7	2396.9
157.5°	2434.0	2419.2	2436.0	2449.1	2434.0
160°	2467.7	2456.5	2467.7	2478.8	2465.7
162.5°	2497.4	2486.3	2495.6	2508.6	2491.8
165°	2523.5	2512.5	2518.0	2531.0	2518.0
167.5°	2544.0	2532.8	2538.5	2551.6	2534.8
170°	2560.9	2549.6	2553.4	2566.5	2549.6
172.5°	2572.0	2560.9	2564.6	2577.7	2560.9
175°	2581.2	2568.2	2572.0	2585.0	2566.5
177.5°	2585.0	2572.0	2573.9	2587.0	2570.2
180°	2575.7	2575.7	2575.7	2575.7	2575.7



TEST NUMBER: P926363
 CATALOG NUMBER: DFN2DIP-TR3F0-090D080US950-RLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	12.18	13.00	13.15	13.99	15.27	8.16	8.98	9.13	9.96	11.25
	3H	13.85	14.59	14.83	15.57	16.88	9.34	10.08	10.32	11.07	12.37
	4H	14.45	15.15	15.45	16.14	17.46	9.79	10.48	10.78	11.48	12.79
	6H	14.86	15.51	15.87	16.50	17.83	10.10	10.74	11.11	11.74	13.07
	8H	14.99	15.60	16.00	16.61	17.94	10.19	10.80	11.20	11.81	13.14
	12H	15.04	15.62	16.06	16.63	17.98	10.23	10.81	11.25	11.82	13.17
4H	2H	12.20	12.89	13.20	13.89	15.20	8.75	9.44	9.75	10.44	11.75
	3H	14.02	14.59	15.03	15.62	16.95	10.09	10.67	11.10	11.69	13.02
	4H	14.70	15.23	15.72	16.24	17.60	10.63	11.16	11.65	12.18	13.53
	6H	15.21	15.66	16.23	16.70	18.05	11.05	11.50	12.08	12.54	13.89
	8H	15.38	15.80	16.41	16.83	18.20	11.17	11.60	12.20	12.63	13.99
	12H	15.46	15.85	16.51	16.89	18.26	11.23	11.62	12.28	12.66	14.03
8H	4H	14.67	15.09	15.70	16.12	17.49	10.91	11.33	11.94	12.36	13.73
	6H	15.22	15.57	16.28	16.64	18.01	11.42	11.77	12.47	12.84	14.20
	8H	15.43	15.74	16.49	16.80	18.18	11.60	11.91	12.67	12.97	14.35
	12H	15.56	15.83	16.63	16.89	18.31	11.72	11.99	12.78	13.04	14.47
12H	4H	14.62	15.00	15.66	16.05	17.42	10.91	11.29	11.96	12.34	13.71
	6H	15.20	15.50	16.26	16.56	17.94	11.46	11.77	12.53	12.83	14.21
	8H	15.41	15.68	16.47	16.73	18.16	11.67	11.94	12.73	12.99	14.42