

Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: NEO-RAY

Report Number: P904567

Luminaire Tested: DFN2DIP-TR4F0-040D100US830-FLLONL

Issue Date: 11/21/2024

Test Information

Test Method: LM-79-2019
Report Number: P904567
REPORT IS A COMBINATION OF REPORTS P901997 AND P898849
Test Lab: INNOVATION CENTER
Issue Date: 11/21/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: NEO-RAY
Catalog Number: DFN2DIP-TR4F0-040D100US830-FLLONL
Description: 4 foot, Triangle Define Geo, with Direct Frosted Lens, Indirect Open No Lens
Light Source: -
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 13063.6 lumens
Efficiency: N/A
Efficacy: 120.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.29
Luminous Opening: Rectangular w/ Sides (W: 3.43' x L: 3.96' x H: 0.1')
CIE Type: Semi-Indirect

Input Watts (W): 108.3
Input Voltage (V):
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: 0.9952
Total Harmonic Distortion (THDi): 0.069
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLLONL

Luminous Intensity Polar Plot



TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLONL

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	62	60	58	47	45	44	32	31	31
2	85	77	72	67	76	70	65	60	55	51	48	41	39	37	28	27	26
3	77	68	61	55	69	61	55	50	48	44	41	36	33	31	25	23	22
4	71	60	53	47	63	54	48	43	43	38	34	32	29	27	22	21	19
5	65	53	46	40	58	48	41	36	38	33	30	29	26	23	20	18	16
6	59	48	40	34	53	43	36	31	34	29	26	26	23	20	18	16	14
7	55	43	35	30	49	39	32	27	31	26	23	24	20	18	17	14	13
8	51	39	31	26	45	35	29	24	28	23	20	22	18	16	15	13	11
9	47	35	28	23	42	32	26	21	26	21	18	20	16	14	14	12	10
10	44	32	25	21	39	29	23	19	24	19	16	18	15	13	13	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1165	1165	1165
5°	1167	1149	1157
10°	1158	1134	1141
15°	1141	1115	1117
20°	1118	1089	1092
25°	1095	1058	1063
30°	1066	1029	1026
35°	1039	995	987
40°	1006	961	950
45°	972	926	912
50°	936	890	868
55°	898	848	827
60°	855	799	781
65°	808	747	726
70°	748	684	667
75°	665	609	613
80°	565	514	509
85°	409	348	338

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 90°

Vertical Angle: 90°

Luminance: 1687 cd/sqm

TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLLONL

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.1	1.1
10°-20°	388.5	3.0
20°-30°	570.9	4.4
30°-40°	663.1	5.1
40°-50°	662.3	5.1
50°-60°	577.5	4.4
60°-70°	426.9	3.3
70°-80°	241.5	1.8
80°-90°	69.3	0.5
90°-100°	104.9	0.8
100°-110°	391.0	3.0
110°-120°	1037.0	7.9
120°-130°	1720.0	13.2
130°-140°	1827.0	14.0
140°-150°	1698.0	13.0
150°-160°	1365.2	10.5
160°-170°	879.7	6.7
170°-180°	302.8	2.3
0°-30°	1097.5	8.4
0°-40°	1760.6	13.5
0°-60°	3000.3	23.0
0°-90°	3738.1	28.6
90°-120°	1532.9	11.7
90°-150°	6778.0	51.9
90°-180°	9326.0	71.4
0°-180°	13063.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1467	1467	1467	1467	1467	
5°	1467	1461	1446	1457	1454	139
15°	1396	1388	1370	1375	1368	393
25°	1264	1253	1229	1231	1229	582
35°	1090	1076	1054	1045	1038	681
45°	887	878	856	841	835	685
55°	672	663	646	629	622	600
65°	453	444	430	418	411	448
75°	237	234	227	219	222	253
85°	58	56	55	51	49	64
90°	2	28	46	58	62	12
95°	150	74	90	101	99	177
105°	700	769	140	166	175	748
115°	1323	1362	1420	354	189	1303
125°	1871	1901	1945	1961	1968	1669
135°	2316	2352	2373	2396	2392	1789
145°	2686	2684	2723	2739	2728	1680
155°	2958	2937	2965	2978	2960	1363
165°	3116	3103	3110	3126	3110	880
175°	3188	3172	3176	3192	3170	303
180°	3181	3181	3181	3181	3181	

TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLLONL

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1467.0	1467.0	1467.0	1467.0	1467.0
2.5°	1475.5	1468.5	1452.9	1467.0	1464.3
5°	1467.0	1461.4	1445.9	1457.1	1454.4
7.5°	1457.1	1448.7	1433.1	1444.5	1441.7
10°	1441.7	1431.8	1414.9	1426.2	1421.9
12.5°	1420.4	1412.0	1395.2	1402.2	1399.3
15°	1396.5	1388.1	1369.7	1375.4	1368.4
17.5°	1366.9	1358.5	1340.1	1347.1	1340.1
20°	1334.4	1326.0	1306.3	1310.4	1304.9
22.5°	1302.0	1289.3	1270.9	1270.9	1268.1
25°	1263.9	1252.6	1228.7	1231.4	1228.7
27.5°	1221.5	1211.6	1193.4	1189.2	1182.2
30°	1179.3	1168.0	1146.9	1142.6	1137.0
32.5°	1134.2	1125.8	1103.2	1094.7	1088.9
35°	1090.4	1076.4	1053.8	1045.3	1038.2
37.5°	1041.0	1028.3	1005.7	995.9	988.8
40°	990.3	978.9	956.3	943.8	938.1
42.5°	940.9	929.5	907.1	892.9	884.5
45°	887.3	877.5	856.2	840.8	835.1
47.5°	835.1	825.2	802.7	787.1	778.7
50°	780.0	773.0	753.3	733.5	726.4
52.5°	726.4	716.6	698.3	682.8	672.9
55°	671.6	663.0	646.1	629.1	622.2
57.5°	616.4	609.4	591.0	574.1	568.4
60°	561.4	555.8	536.1	520.6	516.3
62.5°	507.8	497.9	483.9	469.8	464.1
65°	452.9	444.3	430.3	417.5	410.6
67.5°	396.4	389.3	376.7	366.8	361.2
70°	344.2	338.6	325.8	315.9	310.4
72.5°	290.7	284.9	278.0	268.1	263.8
75°	237.0	234.2	227.1	218.7	221.5
77.5°	189.0	183.3	180.5	176.3	172.1
80°	141.1	139.6	136.8	132.6	129.8
82.5°	96.0	96.0	94.6	88.9	88.9
85°	57.8	56.5	55.0	50.7	49.4
87.5°	25.4	22.6	19.8	15.6	14.0
90°	2.2	27.6	45.9	57.7	62.0
92.5°	57.7	48.4	55.2	59.9	62.0
95°	149.5	73.5	89.6	101.4	99.0
97.5°	269.2	80.6	117.3	124.3	126.6
100°	407.6	92.1	131.2	149.5	154.2
102.5°	559.2	554.9	135.8	161.0	168.1
105°	699.7	768.8	140.5	165.6	174.9
107.5°	863.2	920.6	145.2	170.3	179.6
110°	1019.7	1067.9	402.8	172.8	181.7

TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLLONL

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
112.5°	1167.1	1208.3	1169.3	177.1	184.3
115°	1323.4	1362.5	1420.2	354.5	188.9
117.5°	1459.2	1505.2	1544.5	1215.2	612.3
120°	1611.3	1645.7	1687.2	1714.9	1404.1
122.5°	1740.0	1776.9	1823.1	1836.7	1839.2
125°	1871.2	1901.3	1945.0	1961.1	1967.9
127.5°	1990.9	2023.2	2057.9	2080.9	2083.0
130°	2103.8	2140.7	2165.9	2191.2	2189.1
132.5°	2218.8	2248.9	2274.1	2294.8	2292.6
135°	2315.6	2352.5	2373.0	2396.2	2391.6
137.5°	2416.8	2444.4	2467.6	2490.6	2483.7
140°	2515.6	2534.3	2559.4	2580.2	2568.7
142.5°	2598.8	2614.9	2644.7	2663.0	2651.6
145°	2686.2	2683.8	2722.9	2739.0	2727.5
147.5°	2761.9	2755.1	2794.2	2805.7	2796.7
150°	2835.7	2819.6	2856.6	2870.2	2858.7
152.5°	2897.8	2879.5	2914.0	2927.8	2911.7
155°	2957.7	2937.2	2964.8	2978.4	2960.1
157.5°	3006.1	2987.8	3008.5	3024.6	3006.1
160°	3047.6	3033.7	3047.6	3061.3	3045.2
162.5°	3084.2	3070.5	3082.0	3098.1	3077.4
165°	3116.4	3102.8	3109.6	3125.8	3109.6
167.5°	3141.9	3127.9	3135.1	3151.2	3130.4
170°	3162.6	3148.8	3153.4	3169.5	3148.8
172.5°	3176.3	3162.6	3167.3	3183.4	3162.6
175°	3187.8	3171.7	3176.3	3192.5	3169.5
177.5°	3192.5	3176.3	3178.8	3194.9	3174.1
180°	3181.0	3181.0	3181.0	3181.0	3181.0

TEST NUMBER: P904567

CATALOG NUMBER: DFN2DIP-TR4F0-040D100US830-FLLONL

CIE UGR TABLE:

Reflectances:											
Ceiling		0.7	0.7	0.5	0.5	0.3	0.7	0.7	0.5	0.5	0.3
Wall		0.5	0.3	0.5	0.3	0.3	0.5	0.3	0.5	0.3	0.3
Reference plane		0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
Room dimensions		Viewed crosswise					Viewed endwise				
X=2H	Y=2H	5.39	6.09	6.51	7.20	8.75	4.96	5.66	6.08	6.77	8.32
	3H	7.04	7.66	8.17	8.79	10.35	6.57	7.19	7.70	8.31	9.88
	4H	7.62	8.21	8.76	9.34	10.90	7.15	7.74	8.29	8.86	10.43
	6H	8.01	8.56	9.16	9.68	11.26	7.54	8.08	8.68	9.21	10.79
	8H	8.11	8.63	9.26	9.77	11.34	7.64	8.15	8.79	9.30	10.87
	12H	8.15	8.65	9.31	9.78	11.38	7.67	8.17	8.83	9.30	10.90
4H	2H	5.83	6.43	6.98	7.55	9.12	5.49	6.08	6.64	7.21	8.77
	3H	7.68	8.18	8.84	9.33	10.91	7.29	7.79	8.44	8.94	10.52
	4H	8.39	8.85	9.55	9.99	11.59	7.99	8.44	9.14	9.58	11.18
	6H	8.90	9.29	10.06	10.45	12.04	8.49	8.88	9.65	10.04	11.63
	8H	9.04	9.41	10.20	10.56	12.17	8.63	9.00	9.79	10.15	11.76
	12H	9.11	9.44	10.28	10.60	12.21	8.69	9.02	9.86	10.18	11.79
8H	4H	8.57	8.94	9.73	10.09	11.70	8.21	8.58	9.37	9.73	11.34
	6H	9.20	9.50	10.38	10.69	12.30	8.84	9.14	10.02	10.33	11.94
	8H	9.42	9.68	10.60	10.85	12.48	9.05	9.31	10.23	10.48	12.11
	12H	9.54	9.77	10.73	10.94	12.60	9.16	9.39	10.35	10.56	12.22
12H	4H	8.55	8.88	9.73	10.05	11.66	8.20	8.53	9.38	9.69	11.31
	6H	9.23	9.49	10.41	10.66	12.29	8.88	9.14	10.06	10.31	11.94
	8H	9.46	9.69	10.65	10.86	12.52	9.10	9.34	10.29	10.51	12.16

END OF REPORT